



Description:

Water jerrycans PROFI 22 L, natural-coloured made of fracture-proof polyethylene (HD-PE), stackable

- intake integrated in jerrycan for safe, space-saving deposit of spigot and screw plug
- can be stacked to save space and fits in can holder art. no. 435500
- large opening (48 mm diameter) allows easy filling, emptying and cleaning
- Canister (production date until October 2021!) with screw connection ET-232802 and (from October 2021!) with screw connection ET-232101 including removable drain tap Art.-No. 550105
- with gripping surface on the base for secure handling
- resistant to greases, resins, alkalis, oils and acids
- opening sealed with screw plug for screwing in spigots and corner valves (wide thread 22 mm)
- on request: Custom-made product without screw plug opening, branding, print, labelling, individual scales and colours possible
- food-safe, resistant to temperature: -20°C to +70°C and free from bisphenol A (BPA)
- w = inside diameter of filling opening = 48 mm / a = outside thread diameter = 65 mm
- d=depth=165 mm w=width=350 mm h=height=495 mm

Information:

Article

Articlenumber	816700	Colour	natural
GTIN	4007228816709	Volume in l	22
Customs tariff	39233090	Weight (kg)	1,35
Packaging Unit (PU)	3	T x B x H (mm)	165 x 350 x 495

Outer packaging

Content in pieces	3	Gross weight unit (kg)	4,65
L x B x H (mm)	530 x 395 x 545		

Pallet

Number of boxes	16	Carton per layer	4
Number of layers	4	Weight (kg)	94,4
L x B x H (m)	1,2 x 0,8 x 2,33		