

Electronic torque tester DremoTest E

With calibration certificate

GEDORE
WERKZEUGE FÜR'S LEBEN

Application:


For checking and adjusting all clockwise torque wrenches used in workshops, in industry and for quality assurance processes.

Execution:

- With auto-reset function
- 1st peak value recognition (first peak/crunch point recognition)
- Fixed hexagonal box nut mount
- Convertible between Nm and lbf.ft, integrated measuring transducer
- Serial RS232 interface

Advantage:

- Simple to use and with a robust design



Art. no.	52292 600
Brand	GEDORE
Manufacturer Part Number	1856111
Min. torque	9 Nm
Max. torque	320 Nm
Drive	3/8 inch, 1/2 inch
Min./max. torque	9-320 Nm
Error limit (%)	1 %
Calibration certificate	Yes
Gross Weight	3.850 kg
Product Group	556

EAN

4002805928349