




TEKNISK SPECIFIKATION TECHNICAL SPECIFICATION TECHNISCHE SPECIFIKATION			
Kvalitet/ Quality/ Qualität: 203	Dato/ Date/ Datum: 23.03.2012		
			Standard/ Method/ Standard
Vægt/ Weight/ Gewicht	g/m ²	340	EN 12127
Komposition/ Composition/ Gewebemischung	%	70/30 PES/Tencel®	
Konstruktion/ Construction/ Webkonstruktion	3/1+1/1 twill Cavalry Twill		
STYRKE /PHYSICAL PROPERTIES/ FESTIGKEIT			
Slidstyrke/ Abrasion resistance/ Strapazierfåhigkeit (Mindestwert) 12 KPA	t	>60.000	BS 5690
Brudstyrke kæde/ Tensile Warp/ Bruchfestigkeit Kette (Mindestwert)	N.	2000	ISO 5081
Brudstyrke skud/ Tensile Weft Bruchfestigkeit Schuss (Mindestwert)	N.	1500	ISO 5081
Rivstyrke kæde/ Tearing strength warp/ Reiðfestigkeit Kette (Mindestwert)	N.	55	ISO 4674/A1
Rivstyrke skud/ Tearing strength Weft/ Reiðfestigkeit Schuss (Mindestwert)	N.	60	ISO 4674/A1
FARVEÆGTHEDER/ COLOUR FASTNESS/ FARBECHTHEIT			
Vask/ Washing/ Waschtechtheit	Note	4-5	ISO 105-C06
Sved/ Perspiration/ Schweißtechtheit	Note	4-5	ISO 105-E04
Lys/ light/ Lichtechtheit	Note	-	ISO 105-B04
Gnid, våd/ Rubbing, wet/ Reibechtheit nass (Kette/Schuss)	Note	3-5	ISO 105-X12
Gnid, tør/ Rubbing dry/ Reibechtheit trocken (Kette/Schuss)	Note	3	ISO 105-X12
Dimensionsstabilitet/ Dimensional stability/ Dimensionsstabilität	%	+/- 1,5%	ISO 6330
Vandsøjle/ Water resistance/ Wassersåule	mm H ₂ O	-	ISO 20811
Åndbarhed/ Water vapour permeability/ Atmungsaktivitåt	g/m ² /24 hrs	-	CUP METHOD
Finish/ Finish/ Ausführung			
Certifikater/ Certificates/ Zertifikate			
Vaskesymboler/Landry symbols/ Pflegesymbole			
Bemærkninger/ Remarks/ Bemerkungen:			