

Product information

92 91 03

Precision Cross Jaw Tweezers




- Hold automatically: Their spring force makes these holding tweezers perfect for soldering small and very small components, among other uses
- For applications that require a high-precision self-closing function, for example in microscopy or for precision assembly or soldering tasks
- For soldering work on transistors, gold wire diodes, etc.
- Suitable for a wide variety of applications in the electronics industry thanks to perfectly symmetrical tips and excellent balance
- The high-quality premium stainless steel versions offer high temperature resistance and excellent corrosion resistance to most chemicals, salts and acids
- Handcrafted, with an excellent matt, scratch-free and non-reflective surface
- Precision cross-over tweezers for particularly challenging applications when corrosion resistance and toughness are the main requirements
- Premium stainless steel

General

Article No.	92 91 03
Reference number	7X.SA.1
EAN	4003773086826
Material	premium stainless steel
Gripping surfaces	smooth gripping surfaces
Weight	13 g
Dimensions	115 x 10 x 11 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Surface	matt finish
Tips width (A)	0.22 mm
Tips width (B)	0.25 mm
Tweezers tip version	needle-point
Corrosion-resistant	yes
ESD-tested	no
VDE tested	no
Sectors	Industry electronics
Magnetic	non-magnetisable (80%)



technical change and errors excepted