



# SAFETY DATA SHEET

This safety data sheet was created pursuant to the requirements of: Regulation (EC) No. 1907/2006 and Regulation (EC) No. 1272/2008

**BLU TACK HANDY WHITE**  
Supersedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**Product Name** BLU TACK HANDY WHITE  
**Pure substance/mixture** Mixture

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Recommended use** Adhesive  
**Uses advised against** None known

### 1.3. Details of the supplier of the safety data sheet

#### Company Name

Bostik Limited  
Common Rd  
ST16 3EH  
Stafford UK  
Tel: +44 (1785) 27 26 25  
Fax: +44 (1785) 25 72 36

**E-mail address** SDS.box-EU@bostik.com

### 1.4. Emergency telephone number

**United Kingdom** +44 (1785) 272650  
**Ireland** **NPIC - National Poison Information Centre**  
Members of the Public: +353 (01) 8092166 (8.00 am to 10.00 pm - 7 days a week)  
Healthcare Professionals: +353 (01) 8092566 (24 hour service)  
**Europe** 112

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

Regulation (EC) No 1272/2008

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

### 2.2. Label elements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

**Signal word**  
None

#### Hazard statements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

### 2.3. Other hazards

# SAFETY DATA SHEET

BLU TACK HANDY WHITE  
Supercedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

No information available.

## PBT & vPvB

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT). This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

## SECTION 3: Composition/information on ingredients

### 3.1 Substances

Not applicable

### 3.2 Mixtures

Chemical name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH registration number
White mineral oil, petroleum	232-455-8	8042-47-5	1 - <5	Asp. Tox. 1 (H304)	-	01-2119487078-27-xxxx
Distillates, petroleum, hydrotreated light paraffinic (IP346 <3% DMSO)	265-158-7	64742-55-8	1 - <5	Asp. Tox. 1 (H304)	-	01-2119487077-29-XXXX

**Full text of H- and EUH-phrases: see section 16**

This product does not contain candidate substances of very high concern at a concentration  $\geq 0.1\%$  (Regulation (EC) No. 1907/2006 (REACH), Article 59)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>General advice</b>	Show this safety data sheet to the doctor in attendance. If medical advice is needed, have product container or label at hand.
<b>Inhalation</b>	IF exposed or concerned: Get medical advice/attention. Remove to fresh air.
<b>Eye contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a doctor.
<b>Skin contact</b>	In the case of skin irritation or allergic reactions see a doctor. Wash skin with soap and water.
<b>Ingestion</b>	Clean mouth with water. Do NOT induce vomiting. Drink 1 or 2 glasses of water. Never give anything by mouth to an unconscious person.

### 4.2. Most important symptoms and effects, both acute and delayed

**Symptoms** No information available.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Note to doctors** Treat symptomatically.

# SAFETY DATA SHEET

BLU TACK HANDY WHITE  
Supercedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

**Suitable Extinguishing Media** Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** No information available.

### 5.2. Special hazards arising from the substance or mixture

**Specific hazards arising from the chemical** Thermal decomposition can lead to release of toxic and corrosive gases/vapours.

**Hazardous combustion products** Carbon oxides. Carbon dioxide (CO<sub>2</sub>).

### 5.3. Advice for firefighters

**Special protective equipment and precautions for fire-fighters** Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions** Ensure adequate ventilation.

**For emergency responders** Use personal protection recommended in Section 8.

### 6.2. Environmental precautions

**Environmental precautions** Do not flush into surface water or sanitary sewer system. See Section 12 for additional Ecological Information.

### 6.3. Methods and material for containment and cleaning up

**Methods for containment** Prevent further leakage or spillage if safe to do so. Use a non-combustible material like vermiculite, sand or earth to soak up the product and place into a container for later disposal.

**Methods for cleaning up** Take up mechanically, placing in appropriate containers for disposal.

**Prevention of secondary hazards** Clean contaminated objects and areas thoroughly observing environmental regulations.

### 6.4. Reference to other sections

**Reference to other sections** See section 8 for more information. See section 13 for more information.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

**Advice on safe handling** Ensure adequate ventilation. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing.

**General hygiene considerations** Handle in accordance with good industrial hygiene and safety practice. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Take off all contaminated clothing and wash it before reuse.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage Conditions** Keep container tightly closed in a dry and well-ventilated place.

# SAFETY DATA SHEET

BLU TACK HANDY WHITE  
Supersedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

## 7.3. Specific end use(s)

**Specific use(s)**  
Adhesive.

**Risk Management Methods (RMM)** The information required is contained in this Safety Data Sheet.

**Other information** Observe technical data sheet.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

**Exposure Limits** This product contains titanium dioxide in a non-respirable form. Inhalation of titanium dioxide is unlikely to occur from exposure to this product

Chemical name	European Union	United Kingdom
Limestone 1317-65-3	-	TWA: 10 mg/m <sup>3</sup> TWA: 4 mg/m <sup>3</sup> STEL: 30 mg/m <sup>3</sup> STEL: 12 mg/m <sup>3</sup>

**Derived No Effect Level (DNEL)** No information available

Derived No Effect Level (DNEL)			
White mineral oil, petroleum (8042-47-5)			
Type	Exposure route	Derived No Effect Level (DNEL)	Safety factor
worker Long term Systemic health effects	Inhalation	164.56 mg/m <sup>3</sup>	
worker Long term Systemic health effects	Dermal	217.05 mg/kg bw/d	

Derived No Effect Level (DNEL)			
White mineral oil, petroleum (8042-47-5)			
Type	Exposure route	Derived No Effect Level (DNEL)	Safety factor
Consumer Long term Systemic health effects	Inhalation	34.78 mg/m <sup>3</sup>	
Consumer Long term Systemic health effects	Dermal	93.02 mg/kg bw/d	
Consumer Long term Systemic health effects	Oral	25 mg/kg bw/d	

**Predicted No Effect Concentration (PNEC)** No information available.

### 8.2. Exposure controls

**Engineering controls** Ensure adequate ventilation, especially in confined areas.

**Personal protective equipment**  
**Eye/face protection** No special technical protective measures are necessary.

# SAFETY DATA SHEET

BLU TACK HANDY WHITE  
Supersedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

**Skin and body protection** None under normal use conditions.

**Environmental exposure controls** No information available.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	Solid
Appearance	Flakes
Colour	White
Odour	No information available.
Odour threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
Melting point / freezing point	No data available	None known
Initial boiling point and boiling range	No data available	None known
Flammability	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Flash point	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature		None known
pH	.	
pH (as aqueous solution)	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	
Water solubility	No data available	None known
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Vapour pressure	No data available	None known
Relative density	1.8	
Bulk Density	No data available	
Density	No data available	
Relative vapour density	No data available	None known
Particle characteristics		
Particle Size	No information available	
Particle Size Distribution	No information available	

### 9.2. Other information

#### VOC Content (%)

9.2.1. Information with regards to physical hazard classes  
Not applicable

9.2.2. Other safety characteristics  
No information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity** No information available.

### 10.2. Chemical stability

**Stability** Stable under normal conditions.

# SAFETY DATA SHEET

BLU TACK HANDY WHITE  
Supercedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

## Explosion data

Sensitivity to mechanical impact None.  
Sensitivity to static discharge None.

## 10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

## 10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

## 10.5. Incompatible materials

Incompatible materials None known based on information supplied.

## 10.6. Hazardous decomposition products

Hazardous decomposition products None under normal use conditions. Stable under recommended storage conditions.

## SECTION 11: Toxicological information

### 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

#### Information on likely routes of exposure

##### Product Information

Inhalation Based on available data, the classification criteria are not met.  
Eye contact Based on available data, the classification criteria are not met.  
Skin contact Based on available data, the classification criteria are not met.  
Ingestion Based on available data, the classification criteria are not met.

#### Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

#### Acute toxicity

#### Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

#### Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
White mineral oil, petroleum	>5000 mg/kg (Rattus)	LD50 > 2000 mg/kg (rabbit)	CL50 (4h) >5mg/l (Rattus)
Distillates, petroleum, hydrotreated light paraffinic (IP346 <3% DMSO)	LD50 > 5000 mg/kg (Rattus)	LD50 > 5000 mg/kg (Oryctolagus cuniculus) OECD 402	=3900 mg/m <sup>3</sup> (Rattus) 4 h

#### Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation Based on available data, the classification criteria are not met.

# SAFETY DATA SHEET

BLU TACK HANDY WHITE  
Supercedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

White mineral oil, petroleum (8042-47-5)

Method	Species	Exposure route	Effective dose	Exposure time	Results
OECD Test No. 404: Acute Dermal Irritation/Corrosion	Rabbit	Dermal			Non-irritant

**Serious eye damage/eye irritation** Based on available data, the classification criteria are not met.

White mineral oil, petroleum (8042-47-5)

Method	Species	Exposure route	Effective dose	Exposure time	Results
OECD Test No. 405: Acute Eye Irritation/Corrosion	Rabbit	eye			Non-irritant

**Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.

White mineral oil, petroleum (8042-47-5)

Method	Species	Exposure route	Results
OECD Test No. 406: Skin Sensitisation	Guinea pig	Dermal	No sensitisation responses were observed

**Germ cell mutagenicity** Based on available data, the classification criteria are not met.

Component Information

White mineral oil, petroleum (8042-47-5)

Method	Species	Results
OECD Test No. 471: Bacterial Reverse Mutation Test	Salmonella typhimurium, in vitro	Not mutagenic

**Carcinogenicity** Based on available data, the classification criteria are not met.

**Reproductive toxicity** Based on available data, the classification criteria are not met.

**STOT - single exposure** Based on available data, the classification criteria are not met.

**STOT - repeated exposure** Based on available data, the classification criteria are not met.

**Aspiration hazard** Based on available data, the classification criteria are not met.

## 11.2. Information on other hazards

### 11.2.1. Endocrine disrupting properties

**Endocrine disrupting properties** No information available.

### 11.2.2. Other information

**Other adverse effects** No information available.

## SECTION 12: Ecological information

# SAFETY DATA SHEET

BLU TACK HANDY WHITE  
Supersedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

## 12.1. Toxicity

### Ecotoxicity

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea	M-Factor	M-Factor (long-term)
White mineral oil, petroleum 8042-47-5	-	LC50: >10000mg/L (96h, Lepomis macrochirus)	-	LC50 (48h) >100 mg/l Daphnia magna		
Distillates, petroleum, hydrotreated light paraffinic (IP346 <3% DMSO) 64742-55-8	-	LC50: >5000mg/L (96h, Oncorhynchus mykiss)	-	EC50: >1000mg/L (48h, Daphnia magna)		

## 12.2. Persistence and degradability

**Persistence and degradability** No information available.

White mineral oil, petroleum (8042-47-5)

Method	Exposure time	Value	Results
OECD Test No. 301F: Ready Biodegradability: Manometric Respirometry Test (TG 301 F)	28 days	31% biodegradation	Inherently biodegradable

## 12.3. Bioaccumulative potential

### Bioaccumulation

#### Component Information

Chemical name	Partition coefficient
White mineral oil, petroleum	6

## 12.4. Mobility in soil

**Mobility in soil** No information available.

## 12.5. Results of PBT and vPvB assessment

**PBT and vPvB assessment** The product does not contain any substance(s) classified as PBT or vPvB.

Chemical name	PBT and vPvB assessment
White mineral oil, petroleum	The substance is not PBT / vPvB PBT assessment does not apply
Distillates, petroleum, hydrotreated light paraffinic (IP346 <3% DMSO)	The substance is not PBT / vPvB

## 12.6. Endocrine disrupting properties

**Endocrine disrupting properties** No information available.

## 12.7. Other adverse effects

No information available.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods



# SAFETY DATA SHEET

BLU TACK HANDY WHITE  
Supercedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

<b>Waste from residues/unused products</b>	Dispose of waste in accordance with environmental legislation. Dispose of in accordance with local regulations.
<b>Contaminated packaging</b>	Do not reuse empty containers.
<b>Other information</b>	Waste codes should be assigned by the user based on the application for which the product was used.

## SECTION 14: Transport information

### Land transport (ADR/RID)

14.1 UN number or ID number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special Provisions	None

### IMDG

14.1 UN number or ID number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Marine pollutant	NP
14.6 Special Provisions	None
14.7 Maritime transport in bulk according to IMO instruments	Not applicable

### Air transport (ICAO-TI / IATA-DGR)

14.1 UN number or ID number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special Provisions	None

## Section 15: REGULATORY INFORMATION

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### European Union

#### Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

##### **SVHC: Substances of Very High Concern for Authorisation:**

This product does not contain candidate substances of very high concern at a concentration  $\geq 0.1\%$  (Regulation (EC) No. 1907/2006 (REACH), Article 59)

##### **EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction**

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

##### **Substance subject to authorisation per REACH Annex XIV**

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

# SAFETY DATA SHEET

**BLU TACK HANDY WHITE**  
Supersedes Date: 24-May-2022

Revision date 24-May-2022  
Revision Number 4

## Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

## Persistent Organic Pollutants

Not applicable

## National regulations

### 15.2. Chemical safety assessment

Chemical Safety Assessments have been carried out by the Reach registrants for substances registered at >10 tpa. No Chemical Safety Assessment has been carried out for this mixture

## **SECTION 16: Other information**

### Key or legend to abbreviations and acronyms used in the safety data sheet

#### Full text of H-Statements referred to under section 3

H304 - May be fatal if swallowed and enters airways

#### **Legend**

TWA	TWA (time-weighted average)
STEL	STEL (Short Term Exposure Limit)
Ceiling	Ceiling Limit Value
*	Skin designation
SVHC	Substance(s) of Very High Concern
PBT	Persistent, Bioaccumulative, and Toxic (PBT) Chemicals
vPvB	Very Persistent and very Bioaccumulative (vPvB) Chemicals
STOT RE	Specific target organ toxicity - Repeated exposure
STOT SE	Specific target organ toxicity - Single exposure
EWC	European Waste Catalogue
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
IMDG	International Maritime Dangerous Goods (IMDG)
IATA	International Air Transport Association (IATA)
RID	Regulations concerning the International Transport of Dangerous Goods by Rail

#### **Key literature references and sources for data**

No information available

**Prepared By** Product Safety & Regulatory Affairs

**Revision date** 24-May-2022

#### Indication of changes

**Revision note** SDS sections updated, 4.

**Training Advice** No information available

**Further information** No information available

**This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006**

#### **Disclaimer**

# SAFETY DATA SHEET

**BLU TACK HANDY WHITE**

**Supersedes Date:** 24-May-2022

**Revision date** 24-May-2022

**Revision Number** 4

---

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**