



Motor-protective circuit-breaker, 440 V: 1.5 kW, Ir= 1.6 - 2.5 A, IP20



Part no. PKZM01-2,5
278481
EL Number 4365016
(Norway)

General specifications	
Product name	Eaton Moeller® series PKZM01 Motor-protective circuit-breaker
Part no.	PKZM01-2,5
EAN	4015082784812
Product Length/Depth	93 millimetre
Product height	90 millimetre
Product width	45 millimetre
Product weight	0.293 kilogram
Certifications	VDE 0660 CSA CE IEC/EN 60947-4-1 UL Category Control No.: NLRV UL UL 60947-4-1 CSA File No.: 165628 CSA Class No.: 3211-05 CSA-C22.2 No. 60947-4-1-14 UL File No.: E36332 IEC/EN 60947
Product Tradename	PKZM01
Product Type	Motor-protective circuit-breaker
Product Sub Type	None
Catalog Notes	IE3-ready devices are identified by the logo on their packaging.
Features & Functions	
Actuator type	Push button
Features	Phase-failure sensitivity (according to IEC/EN 60947-4-1, VDE 0660 Part 102)
Functions	Motor protection Phase failure sensitive
Number of poles	Three-pole
General information	
Connection	Screw terminals
Degree of protection	Terminals: IP00 IP20
Lifespan, electrical	50,000 operations (at 400V, AC-3)
Lifespan, mechanical	50,000 Operations (Main conducting paths)
Mounting position	Can be snapped on to IEC/EN 60715 top-hat rail with 7.5 or 15 mm height.
Operating frequency	25 Operations/h
Overvoltage category	III
Pollution degree	3
Product category	Motor protective circuit breaker
Protection	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
Rated impulse withstand voltage (Uimp)	6000 V AC
Shock resistance	25 g, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
Suitable for	Also motors with efficiency class IE3 Branch circuit: Manual type E if used with terminal, or suitable for group installations, (UL/CSA)
Temperature compensation	-25 - 55 °C, Operating range ≤ 0.25 %/K, residual error for T > 40° -5 - 40 °C to IEC/EN 60947, VDE 0660
Climatic environmental conditions	
Altitude	Max. 2000 m
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	55 °C

Ambient operating temperature (enclosed) - min	25 °C
Ambient operating temperature (enclosed) - max	40 °C
Ambient storage temperature - min	40 °C
Ambient storage temperature - max	80 °C
Climatic proofing	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Terminal capacities	
Terminal capacity (flexible with ferrule)	1 x (1 - 6) mm ² , ferrule to DIN 46228 2 x (1 - 6) mm ² , ferrule to DIN 46228
Terminal capacity (solid)	1 x (1 - 6) mm ² 2 x (1 - 6) mm ²
Terminal capacity (solid/stranded AWG)	18 - 10
Stripping length (main cable)	10 mm
Electrical rating	
Rated frequency - min	50 Hz
Rated frequency - max	60 Hz
Rated operational current (Ie)	2.5 A
Rated operational power at AC-3, 220/230 V, 50 Hz	0.37 kW
Rated operational power at AC-3, 380/400 V, 50 Hz	0.75 kW
Rated operational power at AC-3, 440 V, 50 Hz	1.1 kW
Rated operational voltage (Ue) - min	440 V
Rated operational voltage (Ue) - max	440 V
Rated uninterrupted current (Iu)	2.5 A
Short-circuit rating	
Rated short-circuit breaking capacity Icu at 400 V AC	50 kA
Short-circuit current	60 kA DC, up to 250 V DC, Main conducting paths
Short-circuit current rating (group protection)	50 kA, 600 V High Fault, Fuse, SCCR (UL/CSA) with 600 A, 600 V High Fault, Fuse, SCCR (UL/CSA) 50 kA, 600 V High Fault, CB, SCCR (UL/CSA) with 600 A, 600 V High Fault, CB, SCCR (UL/CSA)
Short-circuit release	38.8 A, I _{rm} , Setting range max. Basic device fixed 15.5 x I _u , Trip Blocks ± 20% tolerance, Trip blocks
Switching capacity	
Switching capacity	2.5 A (3 contacts in series), DC-5 up to 250V 2.5 A, AC-3 up to 440 V
Motor rating	
Assigned motor power at 200/208 V, 60 Hz, 3-phase	0.5 HP
Assigned motor power at 230/240 V, 60 Hz, 1-phase	0.17 HP
Assigned motor power at 230/240 V, 60 Hz, 3-phase	0.5 HP
Assigned motor power at 460/480 V, 60 Hz, 3-phase	1 HP
Assigned motor power at 575/600 V, 60 Hz, 3-phase	1.5 HP
Trip blocks	
Overload release current setting - min	1.6 A
Overload release current setting - max	2.5 A
Design verification	
Equipment heat dissipation, current-dependent P _{vid}	5.16 W
Heat dissipation capacity P _{diss}	0 W
Heat dissipation per pole, current-dependent P _{vid}	1.72 W
Rated operational current for specified heat dissipation (I _n)	2.5 A
Static heat dissipation, non-current-dependent P _{vs}	0 W
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Motor protection circuit-breaker (EC000074)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Motor protection circuit-breaker (ecl@ss13-27-37-04-01 [AGZ529021])		
Overload release current setting	A	1.6 - 2.5
Adjustment range undelayed short-circuit release	A	39 - 39
With thermal overload protection		No
Phase failure sensitive		Yes
Switch off technique		Thermomagnetic
Rated operating voltage	V	440 - 440
Rated permanent current I _u	A	2.5
Rated operation power at AC-3, 230 V	kW	0.37
Rated operation power at AC-3, 400 V	kW	0.75
Power loss	W	5.16
Type of electrical connection of main circuit		Screw connection
Type of control element		Push button
Device construction		Built-in device fixed built-in technique
With integrated auxiliary switch		No
With integrated under voltage release		No
Number of poles		3
Rated short-circuit breaking capacity I _{cu} at 400 V, AC	kA	50
Degree of protection (IP)		IP20
Height	mm	90
Width	mm	45
Depth	mm	93