

Knurling tool (series RD1 model 131)

for knurl pressing on lathes and turning machines



Application:

For pressing knurl profiles in accordance with DIN 82 RAA, RBL, RBR, RGE, RGV, (RKE, RKV on request) in the material groups of steel, stainless steel and non-ferrous metals.

Execution:

- hardened steel tool holder, integrated tip height, cemented carbide runner pins, set screw in the shaft for clearance angle collection

Advantage:

- click-pin design for user-friendly handling
- Easy conversion to a marking tool
- Knurling without plunging also possible
- inexpensive knurl production



Art. no.	19003 025
Brand	ZEUS
Manufacturer Part Number	31000715
Suitable for knurling size	20 x 8 x 6 mm, 25 x 8 x 6 mm
Shank width	25 mm
Shaft height	25 mm
For min./max. workpiece diameter	8-200 mm
Gross Weight	0.452 kg
Product Group	1FP