



Optocoupler, Phototransistor Output, with Base Connection




21842



FEATURES

- Isolation test voltage 5000 V_{RMS}
- Long term stability
- Industry standard dual-in-line package
- Compliant to RoHS directive 2002/95/EC and in accordance to WEEE 2002/96/EC



AGENCY APPROVALS

- Underwriters lab file no. E52744
- DIN EN 60747-5-5 (VDE 0884)
- BSI IEC 60950 IEC 60065
- FIMKO

DESCRIPTION

The CNY17 is an optically coupled pair consisting of a gallium arsenide infrared emitting diode optically coupled to a silicon NPN phototransistor.

Signal information, including a DC level, can be transmitted by the device while maintaining a high degree of electrical isolation between input and output.

The CNY17 can be used to replace relays and transformers in many digital interface applications, as well as analog applications such as CRT modulation.

ORDER INFORMATION

PART	REMARKS
CNY17-1.	CTR 40 % to 80 %, DIP-6
CNY17-2.	CTR 63 % to 125 %, DIP-6
CNY17-3.	CTR 100 % to 200 %, DIP-6
CNY17-4.	CTR 160 % to 320 %, DIP-6

ABSOLUTE MAXIMUM RATINGS ⁽¹⁾

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
INPUT				
Reverse voltage		V _R	5	V
Forward current		I _F	60	mA
Surge current	t ≤ 10 µs	I _{FSM}	3	A
Power dissipation		P _{diss}	100	mW
OUTPUT				
Collector emitter breakdown voltage		BV _{CEO}	70	V
Emitter base breakdown voltage		BV _{EBO}	7	V
Collector current		I _C	50	mA
	t < 1 ms	I _C	100	mA
Power dissipation		P _{diss}	150	mW



CNY17.

Optocoupler, Phototransistor Output, Vishay Semiconductors
with Base Connection

ABSOLUTE MAXIMUM RATINGS ⁽¹⁾				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
COUPLER				
Isolation test voltage between emitter and detector referred to climate DIN 50014, part 2, Nov. 74	t = 1 s	V _{ISO}	5000	V _{RMS}
Creepage distance			≥ 7	mm
Clearance distance			≥ 7	mm
Isolation thickness between emitter and detector			≥ 0.4	mm
Comparative tracking index per DIN IEC 112/VDE 0303, part 1			175	
Isolation resistance	V _{IO} = 500 V, T _{amb} = 25 °C	R _{IO}	≥ 10 ¹²	Ω
	V _{IO} = 500 V, T _{amb} = 100 °C	R _{IO}	≥ 10 ¹¹	Ω
Storage temperature		T _{stg}	- 55 to + 125	°C
Operating temperature		T _{amb}	- 55 to + 100	°C
Soldering temperature ⁽²⁾	max. 10 s, dip soldering: distance to seating plane ≥ 1.5 mm	T _{sld}	260	°C

Notes(1) T_{amb} = 25 °C, unless otherwise specified.

Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of time can adversely affect reliability.

(2) Refer to wave profile for soldering conditions for through hole devices.

ELECTRICAL CHARACTERISTICS ⁽¹⁾							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT							
Forward voltage	I _F = 60 mA		V _F		1.25	1.65	V
Breakdown voltage	I _R = 10 mA		V _{BR}	6			V
Reverse current	V _R = 6 V		I _R		0.01	10	μA
Capacitance	V _R = 0 V, f = 1 MHz		C _O		25		pF
Thermal resistance			R _{th}		750		K/W
OUTPUT							
Collector emitter capacitance	V _{CE} = 5 V, f = 1 MHz		C _{CE}		5.2		pF
Collector base capacitance	V _{CB} = 5 V, f = 1 MHz		C _{CB}		6.5		pF
Emitter base capacitance	V _{EB} = 5 V, f = 1 MHz		C _{EB}		7.5		pF
Thermal resistance			R _{th}		500		K/W
COUPLER							
Collector emitter, saturation voltage	V _F = 10 mA, I _C = 2.5 mA		V _{CEsat}		0.25	0.4	V
Coupling capacitance			C _C		0.6		pF
Collector emitter, leakage current	V _{CE} = 10 V	CNY17-1	I _{CEO}		2	50	nA
		CNY17-2	I _{CEO}		2	50	nA
		CNY17-3	I _{CEO}		5	100	nA
		CNY17-4	I _{CEO}		5	100	nA

Note(1) T_{amb} = 25 °C, unless otherwise specified.


Minimum and maximum values were tested requirements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.

CURRENT TRANSFER RATIO (1)

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
I _C /I _F	V _{CE} = 5 V, I _F = 10 mA	CNY17-1	CTR	40		80	%
		CNY17-2	CTR	63		125	%
		CNY17-3	CTR	100		200	%
		CNY17-4	CTR	160		320	%
	V _{CE} = 5 V, I _F = 1 mA	CNY17-1	CTR	13	30		%
		CNY17-2	CTR	22	45		%
		CNY17-3	CTR	34	70		%
		CNY17-4	CTR	56	90		%


Note(1) Current transfer ratio and collector-emitter leakage current by dash number (T_{amb} °C).**SWITCHING CHARACTERISTICS**

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
LINEAR OPERATION (WITHOUT SATURATION)							
Turn-on time	I _F = 10 mA, V _{CC} = 5 V, R _L = 75 Ω		t _{on}		3		μs
Rise time	I _F = 10 mA, V _{CC} = 5 V, R _L = 75 Ω		t _r		2		μs
Turn-off time	I _F = 10 mA, V _{CC} = 5 V, R _L = 75 Ω		t _{off}		2.3		μs
Fall time	I _F = 10 mA, V _{CC} = 5 V, R _L = 75 Ω		t _f		2		μs
Cut-off frequency	I _F = 10 mA, V _{CC} = 5 V, R _L = 75 Ω		f _{CO}		250		kHz
SWITCHING OPERATION (WITH SATURATION)							
Turn-on time	I _F = 20 mA	CNY17-1	t _{on}		3		μs
	I _F = 10 mA	CNY17-2	t _{on}		4.2		μs
		CNY17-3	t _{on}		4.2		μs
	I _F = 5 mA	CNY17-4	t _{on}		6		μs
Rise time	I _F = 20 mA	CNY17-1	t _r		2		μs
	I _F = 10 mA	CNY17-2	t _r		3		μs
		CNY17-3	t _r		3		μs
	I _F = 5 mA	CNY17-4	t _r		4.6		μs
Turn-off time	I _F = 20 mA	CNY17-1	t _{off}		18		μs
	I _F = 10 mA	CNY17-2	t _{off}		23		μs
		CNY17-3	t _{off}		23		μs
	I _F = 5 mA	CNY17-4	t _{off}		25		μs
Fall time	I _F = 20 mA	CNY17-1	t _f		11		μs
	I _F = 10 mA	CNY17-2	t _f		14		μs
		CNY17-3	t _f		14		μs
	I _F = 5 mA	CNY17-4	t _f		15		μs

TYPICAL CHARACTERISTICS
 $T_{amb} = 25 \text{ }^{\circ}\text{C}$, unless otherwise specified



icny17_01

Fig. 1 - Linear Operation (without Saturation)




icny17_02

Fig. 2 - Switching Operation (with Saturation)




icny17_04

Fig. 4 - Current Transfer Ratio vs. Diode Current




icny17_05

Fig. 5 - Current Transfer Ratio vs. Diode Current



icny17_03

Fig. 3 - Current Transfer Ratio vs. Diode Current



icny17_06

Fig. 6 - Current Transfer Ratio vs. Diode Current




Fig. 7 - Current Transfer Ratio vs. Diode Current




Fig. 10 - Output Characteristics




Fig. 8 - Current Transfer Ratio (CTR) vs. Temperature




Fig. 11 - Forward Voltage




Fig. 9 - Transistor Characteristics




Fig. 12 - Collector Emitter Off-state Current

Optocoupler, Phototransistor Output, Vishay Semiconductors with Base Connection




Fig. 13 - Saturation Voltage vs.
Collector Current and Modulation Depth CNY17-1




Fig. 16 - Saturation Voltage vs.
Collector Current and Modulation Depth CNY17-4




Fig. 14 - Saturation Voltage vs.
Collector Current and Modulation Depth CNY17-2




Fig. 17 - Permissible Power Dissipation for Transistor and Diode




Fig. 15 - Saturation Voltage vs.
Collector Current and Modulation Depth CNY17-3


CNY17.




Vishay Semiconductors Optocoupler, Phototransistor Output,
with Base Connection

PACKAGE DIMENSIONS in millimeters

DIP-6



DIP-6, 400 mil



PACKAGE MARKING





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.