

## Category 6 Keystone Panel Mount Coupler (Shielded)



### **Category 6 Keystone Panel Mount Coupler Shielded (SACK3S, SACK3S-24)**

#### **Features**

- Designed to fit US industry standard keystone mount outlets wall plates and patch panels
- RJ45 complies with FCC68
- High performance data throughput, meets Category 6 data transfer rates
- Operating temperature: ~40°C ~ +60°C
- Jack insertion life > 750 mating cycles
- Available as part of our innovative Panel Mount and D UNIVERSAL ranges

#### **Packaging:**

- Standard product is supplied in individual polythene bags. To save time for panel assemblers, SACK3S-24 is available as a “bulk pack” of 24 pieces without individual bags.

#### **Specifications**

- Dimensions  
**SACK3S:** 29.7 x 17 x 19.25 mm approx.      **SACK3S-24:** 280 x 70 x 35mm approx.  
Materials:  
Housing: Nickel plated zinc alloy  
Contacts: 50µ"/ 1.27µm gold plating over nickel plated phosphor bronze  
Earthing lug material: Stainless steel SUS304
- Weight:  
**SACK3S:** 18g approx.      **SACK3S-24:** 460g approx.




**EAN: SACK3s** – 5055386503961 **SACK3S-24** - 5055386504999

**Commodity Code:** 85444920

**Country of Origin:** China

ROHS Compliant

**Code: SACK3S**



**ELECTRICAL:**

Current Rating : 1.5A  
Dielectric Withstanding Voltage : 1000V/AC 60Hz  
Insulation Resistance : 500 MΩ MIN.  
Contact Resistance : 20 mΩ MAX.

**MECHANICAL:**

Durability: RJ45 With 750 Mating Cycles  
and RJ11 With 200 Mating Cycles  
Supporting Cable Diameter: 6~9mm  
Operating Temperature: -10°C to +60°C  
Storage Temperature: -40°C to +70°C

**MATERIAL:**

Dust cap: PP  
Ground Lug: SUS304  
Front cover: Zn alloy + Nickel Plated  
LATCH: PC 94VO  
Bottom cover: Zn alloy + Nickel Plated