



TEGERA® 114

Leather glove, unlined, 0,6-0,7 mm full grain goatskin of top quality, nylon, Cat. II, grey, white, elasticated 180°, for fine assembly work

PROPERTIES

High level of protection, extremely good fingertip sensitivity, durable, perfect fit

SPECIFICATION

TYPE OF GLOVE Work gloves - General handling

CATEGORY Cat. II

SIZE RANGE (EU) 5, 6, 7, 8, 9, 10, 11

PALM MATERIAL Full grain goatskin of top quality

PALM THICKNESS 0,6-0,7 mm

BACK MATERIAL Nylon

LINING Unlined

DEXTERITY 5

FASTENING Elasticated 180°

LENGTH RANGE 210-260 mm

COLOUR Grey, white

PAIRS PER PACKAGE/CARTON 12/120

DISPLAY Thread

MATERIAL SPECIFICATION Leather 50%, nylon 49%, natural latex 1%

SIZE	ART. NO.	EAN NO.
5	114-5	7392626013940
6	114-6	7392626011465
7	114-7	7392626011472
8	114-8	7392626011489
9	114-9	7392626011496
10	114-10	7392626011403
11	114-11	7392626011410

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.



TEGERA® 114

PRIMARY PROTECTION

Prevents risk of: abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt

PRIMARY ENVIRONMENTS OF USE

Dry environments, dirty environments

PRIMARY AREAS OF USE

Fine assembly, assembly, inspection work, machine operating, building and construction, carpentry, installation work, HVAC installation, tiling, construction, soil preparation, engineering, transport work, machine driving, warehouse work, airport work, wood industry work, gardening, repair work, shop work


PRIMARY INDUSTRIES OF USE

Mining, pulp and paper, automotive, transportation, building and construction, HoReCa, service, retail

TYPE OF WORK

Light weight

CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2017-05-30

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

TEGERA® 114

EC TYPE EXAMINATION

Notified Body: 0493 Centexbel, Technologiepark 7, BE-9052 Zwijnaarde (Gent) Belgium

COMPLIANCE DESCRIPTION

EN 420:2003 Protective gloves - general requirements and test methods

EN 388:2003 Protective gloves against mechanical risks

Property	Level Achieved	(Maximum Performance)
A) Resistance to abrasion (No. of revolutions)	2	(4)
B) Resistance to cutting (Index)	0	(5)
C) Tear resistance (Newton)	0	(4)
D) Puncturing resistance (Newton)	1	(4)

EN 388 - Testing (specifies the requirements that apply for each safety level).

Level of protection/Performance level	1	2	3	4	5
A) Resistance to abrasion (No. of revolutions)	100	500	2 000	8 000	
B) Resistance to cutting (Index)	1,2	2,5	5,0	10,0	20,0
C) Tear resistance (Newton)	10	25	50	75	
D) Puncturing resistance (Newton)	20	60	100	150	



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2017-05-30

3(3)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com