



VIEWED FROM FRONT OF FOOTSWITCH

NOTE:
FOR EARTHING METHODS
REFER TO 5031-136

(07) (08)

SCALE :- NTS				
FIRST USED ON :- 6289-SB				
TOOL No. :- ----				
REV.	CHANGE NOTE	CHANGE BY	DATE	CHECKED BY
06	CN7282	DB	26/06/00	
07	CN12421	MJC	13/06/07	
08	CN14053	MJC	07/12/10	MH

THIS DOCUMENT IS THE PROPERTY OF HERGA ELECTRIC LTD AND SUPPLIED IN CONFIDENCE. IT MUST NOT BE REPRODUCED OR DISCLOSED TO A THIRD PARTY WITHOUT THE WRITTEN CONSENT OF HERGA ELECTRIC LTD

herga electric Ltd
NORTHERN WAY, BURY ST EDMUNDS, SUFFOLK, ENGLAND, IP32 6NN www.herga.com TEL :- 01284 701422 FAX :- 01284 753112

UNLESS OTHERWISE STATED ALL DIMENSIONS IN mm GENERAL TOLERANCES :-
± 30 MINUTES ON ANGULAR DIMS
± 0.5 ON DIM. WITH NO DECIMAL PLACE
± 0.3 ON DIM. WITH ONE DECIMAL PLACE
± 0.1 ON DIM. WITH TWO DECIMAL PLACES

STRAIGHTNESS	PARALLELISM	CONCENTRICITY	LINE PROFILE
FLATNESS	SQUARENESS	M.M.C	SURFACE PROFILE
ROUNDNESS	ANGULARITY	RUN OUT	SYMMETRY
CYLINDRICITY	POSITION	SURFACE FINISH	

MATERIAL :- ----
FINISH :- ----
SHRINKAGE :- ----

TITLE :-
WIRING DIAGRAM
5020-044