

SDUC offset steel boring bar, positive, right

for longitudinal and copy turning using DC indexable insert

ATORN[®]

Application


For longitudinal and copy turning with DC 55° indexable insert.

Version

- precision-manufactured **steel** boring bar, with inner cooling, D type, 93.5° pitch angle, 55° tip angle, 7° clearance angle

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



Art. No.	17847 032
ISO name	A 16 Q SDUC R/L 07
Min. bore diameter	22 mm
Shaft diameter	16 mm
Cutting edge height	7.5 mm
Clearance length	25 mm
Length	180 mm
Clamping surface height	15 mm
Programming size	11 mm
Suitable for indexable inserts	DC.. 0702..
Tool design	Right
DIN	8024

EAN-Code

4050293110807