


CHARACTERISTICS

Ambient temperature	-10 ÷ +90 °C
Fluid	50 µm filtered air, with or without lubrication
Commutation system	poppet
Max pressure	10 bar
Connections	M5, tube Ø4
Nominal bore (mm)	2,5
Nominal flow rate (NI/min)	70
Valve body	zamak
Seals	NBR
Spool	nickel-plated brass



Ball push - spring

■ Tube Ø4




AI-9000

AI-9010

AI-9020

AI-9030

■ M5



AI-9000M


AI-9010M

AI-9020M

AI-9030M

Roller lever - spring

■ Tube Ø4




AI-9100

AI-9110

AI-9120

AI-9130

■ M5



AI-9100M


AI-9110M

AI-9120M

AI-9130M

One-way roller lever - spring

■ Tube Ø4




AI-9200

AI-9210

AI-9220

AI-9230

■ M5



AI-9200M


AI-9210M

AI-9220M

AI-9230M

Bulkhead mechanical push button - spring

■ Tube Ø4




AI-9300

AI-9310

AI-9320

AI-9330

■ M5



AI-9300M


AI-9310M

AI-9320M

AI-9330M

Button lever - spring

■ Tube Ø4




AI-9350

AI-9360

AI-9370

AI-9380

■ M5



AI-9350M


AI-9360M

AI-9370M

AI-9380M

Mechanical push button for panel operation - spring

■ Tube Ø4




AI-9400

AI-9410

AI-9420

AI-9430

■ M5



AI-9400M

AI-9410M

AI-9420M

AI-9430M

AI-3511Q ■	AI-3514Q ■	AI-3515Q ■	AI-3520Q ■	AI-3524Q ■	AI-3522Q ■	AI-3525Q ■	AI-3526Q ■
AI-3512Q ■	AI-3516Q ■	AI-3517Q ■	AI-3521Q ■		AI-3523Q ■		
AI-3513Q ■	AI-3514QD ■	AI-3519Q ■					
	AI-3516QD ■						

AI JET

Pneumatic switches JET series

- Light with compact design
- Low operating force and high response time
- M5 threaded connections or push-in fitting tube Ø4
- Wide range of actuators and manual overrides for mounting panel (Original Univer)



TECHNICAL CHARACTERISTICS


Ambient temperature	-10 ÷ +90 °C
Fluid temperature	max +50 °C
Fluid	not dehumidified filtered air 50 µm, lubricated or not
Commutation system	poppet system
Ways/Positions	2/2 NC, 3/2 NC, 2/2 NO, 3/2 NO
Pressure	max 10 bar
Control	manual, mechanical
Return	mechanical spring
Connections	M5, tube Ø4
Nominal Ø	2,5 mm
Nominal flow rate (NI/min)	70 NI/min

CONSTRUCTIVE CHARACTERISTICS

Valve body	zamak
Seals	nitrile rubber
Spool	nickel-plated brass

OTHER VERSIONS AVAILABLE

Flow rate characteristics




P = Working pressure
PA = Supply pressure
Qn = Flow rate



Ball-push - spring tube Ø4



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		tube Ø4	14	0,060	AI-9000
3/2 NO		tube Ø4	14	0,060	AI-9010
2/2 NC		tube Ø4	14	0,060	AI-9020
2/2 NO (b)		tube Ø4	14	0,060	AI-9030




A Pre-stroke 1 = Supply port
B Maximum opening 2 = Use
C Total stroke 3 = Exhaust

Ball-push - spring M5






	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		M5	14	0,060	AI-9000M
3/2 NO		M5	14	0,060	AI-9010M
2/2 NC		M5	14	0,060	AI-9020M
2/2 NO (b)		M5	14	0,060	AI-9030M




A Pre-stroke 1 = Supply port
B Maximum opening 2 = Use
C Total stroke 3 = Exhaust

Roller lever - tube Ø4



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		tube Ø4	7	0,085	AI-9100
3/2 NO		tube Ø4	7	0,085	AI-9110
2/2 NC		tube Ø4	7	0,085	AI-9120
2/2 NO (b)		tube Ø4	7	0,085	AI-9130



B Maximum opening
C Total stroke


1 = Supply port
2 = Use
3 = Exhaust

(a) = at 6 bar (b) = upon request 2/2 NO version

Roller lever - spring M5



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		M5	7	0,085	AI-9100M
3/2 NO		M5	7	0,085	AI-9110M
2/2 NC		M5	7	0,085	AI-9120M
2/2 NO (b)		M5	7	0,085	AI-9130M




B Maximum opening
C Total stroke

1 = Supply port
2 = Use
3 = Exhaust

Uni-directional roller lever - spring tube Ø4



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		tube Ø4	4	0,085	AI-9200
3/2 NO		tube Ø4	4	0,085	AI-9210
2/2 NC		tube Ø4	4	0,085	AI-9220
2/2 NO (b)		tube Ø4	4	0,085	AI-9230




B Maximum opening
C Total stroke

1 = Supply port
2 = Use
3 = Exhaust

Uni-directional roller lever - spring M5



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		M5	4	0,085	AI-9200M
3/2 NO		M5	4	0,085	AI-9210M
2/2 NC		M5	4	0,085	AI-9220M
2/2 NO (b)		M5	4	0,085	AI-9230M







B Maximum opening
C Total stroke


1 = Supply port
2 = Use
3 = Exhaust

(a) = at 6 bar (b) = upon request 2/2 NO version

Mechanical push button with screw mounting - spring tube Ø4



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		tube Ø4	14	0,082	AI-9300
3/2 NO		tube Ø4	14	0,082	AI-9310
2/2 NC		tube Ø4	14	0,082	AI-9320
2/2 NO (b)		tube Ø4	14	0,082	AI-9330








- A Pre-stroke
 B Maximum opening
 C Total stroke
 D Wrench 14

- 1 = Supply port
 2 = Use
 3 = Exhaust

Mechanical push button with screw mounting - spring M5



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		M5	14	0,082	AI-9300M
3/2 NO		M5	14	0,082	AI-9310M
2/2 NC		M5	14	0,082	AI-9320M
2/2 NO (b)		M5	14	0,082	AI-9330M





- A Pre-stroke
 B Maximum opening
 C Total stroke
 D Wrench 14

- 1 = Supply port
 2 = Use
 3 = Exhaust



(a) = at 6 bar (b) = upon request 2/2 NO version

Button - spring tube Ø4



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		tube Ø4	7	0,065	AI-9350
3/2 NO		tube Ø4	7	0,065	AI-9360
2/2 NC		tube Ø4	7	0,065	AI-9370
2/2 NO (b)		tube Ø4	7	0,065	AI-9380

Button yellow colour





☐ B Maximum opening

☐ C Total stroke



1 = Supply port
2 = Use
3 = Exhaust

Button - spring M5



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		M5	7	0,065	AI-9350M
3/2 NO		M5	7	0,065	AI-9360M
2/2 NC		M5	7	0,065	AI-9370M
2/2 NO (b)		M5	7	0,065	AI-9380M

Button yellow colour



☐ B Maximum opening



☐ C Total stroke

1 = Supply port
2 = Use
3 = Exhaust

Mechanical push button for panel mounting - spring tube Ø4



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		tube Ø4	14	0,075	AI-9400
3/2 NO		tube Ø4	14	0,075	AI-9410
2/2 NC		tube Ø4	14	0,075	AI-9420
2/2 NO (b)		tube Ø4	14	0,075	AI-9430





1 = Supply port
2 = Use
3 = Exhaust

Mechanical push button for panel mounting - spring M5



	Symbol	Connection	Force (a) N	Weight Kg	Part no.
3/2 NC		M5	14	0,075	AI-9400M
3/2 NO		M5	14	0,075	AI-9410M
2/2 NC		M5	14	0,075	AI-9420M
2/2 NO (b)		M5	14	0,075	AI-9430M



1 = Supply port
2 = Use
3 = Exhaust

MANUAL ACTUATORS

	Recessed button	■ BLACK ■ RED ■ GREEN AI-3511Q AI-3512Q AI-3513Q		Rotating lever selector	■ BLACK ■ BLACK AI-3522Q AI-3523Q
	Head button	■ RED ■ BLACK AI-3514Q AI-3516Q		Lever operator	■ BLACK AI-3524Q
	Button	■ GREEN ■ RED ■ BLACK AI-3515Q AI-3517Q AI-3519Q		Omni-directional operator	■ BLACK AI-3525Q
	Rotating selector	■ BLACK ■ BLACK AI-3520Q AI-3521Q		Push-pull operator	■ BLACK AI-3526Q

(a) = at 6 bar (b) = upon request 2/2 NO version
For actuator dimensions refer to section "Accessories>Actuators"