

Conical washers DIN 6319 type G



Application:

For transferring clamping forces in cases where clamping elements need to adapt to uneven clamping surfaces.

Execution:

- Stamped, pressed and tempered

Advantage:

- Thanks to the large diameter, these are particularly ideal for clamping via the slot in the case of clamps.



Art. no.	26208 720
Brand	AMF
Manufacturer Part Number	82024
Suitable cheese-head screw DIN 912	M16
Internal diameter	19 mm
Outer diameter	44 mm
Height	7 mm
Diameter	26 mm
DIN	6319
Gross Weight	0.066 kg
Product Group	260

EAN

4020772082024