

IEC 309 PIN & SLEEVE DEVICES • LIGHT & STAGE DEVICES



Well hidden from View!

It is necessary that electrical installations on stages function without interruption and not be a distraction to the viewers.

The Walther Electric Solution:

Black devices which prevent bothersome light reflections and thus make the electrical installation on stages almost "invisible"!

Standard Style

New Light & Stage Style















Now You See It

Now You Don't

Male Plugs IP 44 for Light & Stage Applications

IEC/EN 60 309

		  			Amperage	Poles	<div style="background-color: yellow; padding: 2px;">110 V</div> 50 a. 60 Hz <small>3pole 4pole 5pole 4h 4h 4h</small>	<div style="background-color: blue; color: white; padding: 2px;">230 V</div> 50 a. 60 Hz <small>3pole 4pole 5pole 6h 9h 9h</small>	<div style="background-color: red; color: white; padding: 2px;">400 V</div> 50 a. 60 Hz <small>3pole 4pole 5pole 9h 6h 6h</small>	<div style="background-color: black; color: white; padding: 2px;">500 V</div> 50 a. 60 Hz <small>3pole 4pole 5pole 7h 7h 7h</small>		
		2 P+E	3 P+E	3 P+N+E	Part numbers							
	16	3						211 306 SW			10	112
	16	4							211 406 SW		10	154
	16	5							211 SW		10	170
	32	3						231 306 SW			10	211
	32	4							231 406 SW		10	217
	32	5							231 SW		10	240
	63	3						261 306 SW			5	475
	63	4							261 406 SW		5	566
	63	5							261 SW		5	613
	125	3						279 306 SW ¹⁾			2	1185
125	4							279 406 SW ¹⁾		2	1329	
125	5							279 SW ¹⁾		2	1473	
231SW	Plugs with gland entry, in 16 - 63 A = IP 44  , in 125 A = IP 67  ¹⁾											
	16	3	215 304 SW	215 306 SW							10	101
	Plugs IP 44  with inverted cable entry											
	16	5							210 SW		10/60	176
	32	5							230 SW		10/60	250
230SW	Plugs IP 44  , with cable gland											

Consult customer service for other amperage and voltage ratings and configurations.



Female Connectors & Socket-Outlets IP 44 for Light & Stage Applications IEC/EN 60 309

  			Amperage	Poles	110 V	230 V	400 V	500 V										
2 P+E	3 P+E	3 P+N+E			50 a. 60 Hz	50 a. 60 Hz	50 a. 60 Hz	50 a. 60 Hz										
					3pole 4h	4pole 4h	5pole 4h	3pole 6h	4pole 9h	5pole 9h	3pole 9h	4pole 6h	5pole 6h	3pole 7h	4pole 7h	5pole 7h		
Part numbers																		
	16	3												10			147	
	16	4												10			197	
	16	5												10			214	
	32	3												10			265	
	32	4												10			278	
	32	5												10			300	
	63	3												5			656	
	63	4												5			771	
	63	5												5			787	
125	3												2			1362		
125	4												2			1536		
125	5												2			1710		
331306SW	Couplers with gland entry, 16 - 63 A = IP 44 , 125 A = IP 67  2)																	
	16	3			315 304 SW									10			140	
	315306SW	Couplers IP 44 , with inverted cable entry																
	16	5												10/60			219	
	32	5												10/60			311	
310SW	Couplers IP 44 , with cable gland																	
	16	3			410 304 SW									10			128	
	16	4												10			106	
	16	5												10			165	
	32	3												10			208	
	32	4												10			215	
	32	5												10			226	
	63	3												5			586	
	63	4												5			645	
	63	5												5			776	
125	3												2			990		
125	4												2			1155		
125	5												2			1319		
430SW	Panel sockets, straight, 16 - 63 A = IP 44 , 125 A = IP 67  3), fingerproof acc. to BGV A2																	

Consult customer service for other amperage and voltage ratings and configurations.