


Data Sheet



Type Number 6238
Designation IEC ---
System Li-Manganese dioxide / Organic Electrolyte

UL Recognition:..... MH 13654 (N)
Nominal Voltage 3 V
Typical Capacity C 1350 mAh
 Load 1.0 kOhm, at 20°C down to 2 V

Weight (approx.) 17 g
Volume 7 ccm
Coding..... Date of Manufacturing Quarter/Year

Temperature Ranges

	min	max.
Storage	-55°C	75 °C
Discharge	-30°C	75°C

Dimensions

	min	max.
Diameter (A)	16,5	17
Height (B)	33,1	33,5
Shoulder Diameter[L].....	7	
Shoulder Height [M].....	0,4	

Segment Electronic

Main Applications Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d,7d/w Current [µA]:	1000 Ω	Time: Capacity [mAh]: Energy [MWh]:	500 h 1350 3600

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration