

Product specification sheet

Revision dated March 2021

1.	Product code	340FCD/0*																																																		
2.	Product description	Fully coated double dipped-nitrile on cut resistant liner																																																		
3.	Material	Nylon. HPPE. Steel. Glass. Spandex																																																		
4.	Coating	Double-Dipped Nitrile. Flat and Sandy																																																		
5.	Glove dimensions, codes and length	<table border="1"> <thead> <tr> <th rowspan="2">Dimensions</th> <th colspan="7">Size</th> </tr> <tr> <th>XS 6</th> <th>S 7</th> <th>M 8</th> <th>L 9</th> <th>XL 10</th> <th>XXL 11</th> <th>XXXL 12</th> </tr> </thead> <tbody> <tr> <td>Product code</td> <td>340FCD/06</td> <td>340FCD/06</td> <td>340FCD/06</td> <td>340FCD/06</td> <td>340FCD/10</td> <td>340FCD/11</td> <td>-</td> </tr> <tr> <td>Length (mm)</td> <td>220</td> <td>230</td> <td>240</td> <td>250</td> <td>260</td> <td>270</td> <td>-</td> </tr> </tbody> </table>									Dimensions	Size							XS 6	S 7	M 8	L 9	XL 10	XXL 11	XXXL 12	Product code	340FCD/06	340FCD/06	340FCD/06	340FCD/06	340FCD/10	340FCD/11	-	Length (mm)	220	230	240	250	260	270	-											
Dimensions	Size																																																			
	XS 6	S 7	M 8	L 9	XL 10	XXL 11	XXXL 12																																													
Product code	340FCD/06	340FCD/06	340FCD/06	340FCD/06	340FCD/10	340FCD/11	-																																													
Length (mm)	220	230	240	250	260	270	-																																													
6.	Glove standards	<table border="1"> <thead> <tr> <th>EN388</th> <th>Level</th> <th>EN407</th> <th>Level</th> </tr> </thead> <tbody> <tr> <td>Abrasion</td> <td>4</td> <td>Limited flame spread (burning behaviour)</td> <td>-</td> </tr> <tr> <td>Coup cut</td> <td>X</td> <td>Contact heat</td> <td>-</td> </tr> <tr> <td>Tear</td> <td>4</td> <td>Convective heat</td> <td>-</td> </tr> <tr> <td>Puncture</td> <td>2</td> <td>Radiant Heat</td> <td>-</td> </tr> <tr> <td>ISO cut</td> <td>F</td> <td>Small splashes of molten metal</td> <td>-</td> </tr> <tr> <td>Impact</td> <td>-</td> <td>Large splashes of molten metal</td> <td>-</td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th>EN511</th> <th>Level</th> <th>EN60903</th> </tr> </thead> <tbody> <tr> <td>Convective cold</td> <td>-</td> <td>Arc flash</td> </tr> <tr> <td>Contact cold</td> <td>-</td> <td>Type</td> </tr> <tr> <td>Water resistance</td> <td>-</td> <td>Mechanical</td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th>EN374 type</th> </tr> </thead> <tbody> <tr> <td></td> </tr> </tbody> </table>									EN388	Level	EN407	Level	Abrasion	4	Limited flame spread (burning behaviour)	-	Coup cut	X	Contact heat	-	Tear	4	Convective heat	-	Puncture	2	Radiant Heat	-	ISO cut	F	Small splashes of molten metal	-	Impact	-	Large splashes of molten metal	-	EN511	Level	EN60903	Convective cold	-	Arc flash	Contact cold	-	Type	Water resistance	-	Mechanical	EN374 type	
EN388	Level	EN407	Level																																																	
Abrasion	4	Limited flame spread (burning behaviour)	-																																																	
Coup cut	X	Contact heat	-																																																	
Tear	4	Convective heat	-																																																	
Puncture	2	Radiant Heat	-																																																	
ISO cut	F	Small splashes of molten metal	-																																																	
Impact	-	Large splashes of molten metal	-																																																	
EN511	Level	EN60903																																																		
Convective cold	-	Arc flash																																																		
Contact cold	-	Type																																																		
Water resistance	-	Mechanical																																																		
EN374 type																																																				
7.	Thickness (mm)	n/a																																																		
8.	Gauge	13																																																		
9.	Cuff type	Knitted																																																		
10.	Design	Hand specific																																																		
11.	Surface	-																																																		
12.	Colour	Black / Blue / Black																																																		
13.	Quality assurance	Manufactured under ISO 9001																																																		
14.	Shelf life	5 years																																																		
15.	Standards compliant with	EN388	EN407	EN511	EN 60903	EN420	EN374-1	EN374-2	EN374-4	EN374-5	Food approved																																									
		✓				✓					✓																																									
16.	Technologies	NitreGrip ✓			NitreGuard ✓			Sanitised		✗																																										

The above data represents the product norm, which may be changed without notice and is intended as a guide only.