

DMS 3
DMS 3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Type	DMS 3
Order No.	9007440000
Version	Mains-operated torque screwdriver, 1/4" DIN 3126 Form E6.3, 3
GTIN (EAN)	4008190404987
Qty.	1 pc(s).

**DMS 3
DMS 3**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	239 mm	Width (inches)	9.409 inch
Height	127 mm	Height (inches)	5 inch
Weight	400 g	Net weight	411.23 g
Diameter	35 mm		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Charging time	45 min
---------------	--------

Electric screwdriver

Battery voltage	2.4 V	Bit holder	1/4" DIN 3126 Form E6.3
Charger input	230 V AC; 50 Hz; 50 mA	Charger output	2.9 V AC; 1.4 A; 4.1 VA
Charging time	45 min	Idling speed	200 u. 400 min ⁻¹
Rated voltage	2.4 V	Rechargeable batteries	Ni-Mh cells
Torque setting, max.	3 Nm	Torque setting, min.	0.3 Nm
Weight	400 g	Weight of charger	700 g
Weight of rechargeable battery	122 g		

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC001395
UNSPSC	27-11-27-20	eClass 5.1	21-05-08-01
eClass 6.2	21-05-08-90	eClass 7.1	21-05-08-04
eClass 8.1	21-05-08-04	eClass 9.0	21-05-21-90
eClass 9.1	21-04-04-17		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	WSCAD

Data sheet

DMS 3
DMS 3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

