

## Knurling tool (series RD2 model 851)

for knurl pressing on lathes and turning machines



### Application:

For knurl forming for knurl profiles in accordance with DIN 82 RAA, RBL30°/45°, RBR30°/45°, RGE 30° and RGE 45° in the steel, stainless steel and non-ferrous metals material groups.

### Version:

- hardened steel tool holder, integrated tip height, HSS runner pin

### Advantage:

- Available adapter system guarantees high compatibility
- modular design enables right-handed and left-handed knurl press holder
- Inexpensive knurl production
- flexible centring



<b>Art. no.</b>	<b>19006 012</b>
<b>Suitable for knurling size</b>	15 x 4 x 4 mm
<b>Shank width</b>	12 mm
<b>Shaft height</b>	12 mm
<b>For min./max. workpiece diameter</b>	6-60 mm