

PRODUCT-DETAILS

## CP-D 24/4.2

CP-D 24/4.2 Power supply In: 100-240VAC Out: 24VDC/4.2A



### General Information

Extended Product Type	CP-D 24/4.2
Product ID	1SVR427045R0400
EAN	4016779661195
Catalog Description	CP-D 24/4.2 Power supply In: 100-240VAC Out: 24VDC/4.2A
Long Description	The CP-D 24/4.2 is a power supply from the CP-D range. The primary switch mode power supply offers a wide range input of 90-264 V AC and 120-375 V DC, rated input voltage is 100-240 V AC. The rated output power is 100 W, rated output current is 4.2 A at an output voltage of 24 V DC. The output voltage is adjustable within a range of 24 to 28 V DC. The power supply provides a U/I output characteristic.

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044090

### Popular Downloads

Data Sheet, Technical Information	2CDC114057D0201
Instructions and Manuals	1SVC427043M0000

### Dimensions

Product Net Width	89.9 mm
Product Net Height	91 mm
Product Net Depth / Length	57.5 mm
Product Net Weight	0.386 kg

## Container Information

Package Level 1 Width	91 mm
Package Level 1 Depth / Length	134 mm
Package Level 1 Height	105 mm
Package Level 1 Gross Weight	0.449 kg
Package Level 1 EAN	4016779661195
Package Level 1 Units	box 1 piece

## Technical

Function	Switch mode power supply
Number of Phases	1
Rated Input Voltage ( $U_{IN}$ )	100 ... 240 V AC
Input Voltage ( $U_{in}$ )	90 ... 264 V AC 120 ... 375 V DC
Rated Frequency (f)	50 Hz 60 Hz
Rated Frequency Limits	47 ... 63 Hz
Characteristic of Output	U/I characteristic curve
Rated Output Power	100 W
Output Power	100 W
Rated Output Voltage	24 V DC
Output Voltage ( $U_{out}$ )	24 V DC
Rated Output Current	4.2 A
Output Current	4.2 A
Output Current Maximum ( $I_{out}$ )	4.2 A
Rated Impulse Withstand Voltage ( $U_{imp}$ )	Input Circuit / Output Circuit 3 kV
Rated Insulation Voltage ( $U_i$ )	Input Circuit / Output Circuit 300 V Input Circuit / PE 300 V Output Circuit / PE 50 V
Degree of Protection	Housing IP20 Terminals IP20
Pollution Degree	2
Connecting Capacity Input Circuit	Flexible with Ferrule 0.2 ... 2.5 mm <sup>2</sup> Rigid 0.2 ... 2.5 mm <sup>2</sup>
Connecting Capacity Output Circuit	Flexible with Ferrule 0.2 ... 2.5 mm <sup>2</sup> Rigid 0.2 ... 2.5 mm <sup>2</sup>
Tightening Torque	Input Circuit 0.7 N·m Output Circuit 0.7 N·m
Wire Stripping Length	Input Circuit 7 mm Output Circuit 7 mm
Minimum Mounting Distance	Electrical Conductive Board, Horizontal 25 mm Electrical Conductive Board, Vertical 25 mm Other Device Same Type, Horizontal 25 mm Other Device Same Type, Vertical 25 mm
Mounting Position	1
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715

## Standards

CAN/CSA C22.2 No.107.1  
 CAN/CSA C22.2 No.60950  
 IEC/EN 63000  
 IEC 60950-1  
 IEC/EN 61000-6-2  
 IEC/EN 61000-6-3  
 UL 508  
 UL 60950

---

**Environmental**

Ambient Air Temperature	Operation -40 ... +70 °C Storage -40 ... +85 °C
Maximum Operating Altitude Permissible	4850 m
RoHS Status	Following EU Directive 2011/65/EU

---

**Technical UL/CSA**

Connecting Capacity Input Circuit UL/CSA	Rigid 24-12 AWG
Connecting Capacity Output Circuit UL/CSA	Rigid 24-12 AWG
Tightening Torque UL/CSA	Input Circuit 6 in-lb Output Circuit 6 in-lb

---

**Electromagnetic Compatibility**

Electrostatic Discharge (ESD Immunity) acc. to IEC 61000-4-2	Level 4 Air Discharge 15 kV Level 4 Contact Discharge 4 kV
Radiated Electromagnetic Field Immunity acc. to IEC 61000-4-3	Level 3 10 V/m
Electrical Fast Transient (Burst Immunity) acc. to IEC 61000-4-4	Level 4 Power Supply Port Signal 4 kV
Surge Immunity acc. to IEC 61000-4-5	Level 3 Line-to-Line 2 kV
Conducted Disturbances Immunity acc. to IEC 61000-4-6	Level 3 10 V
Electromagnetic Compatibility (EMC)	Emission - Class B Immunity - Class B

---

**Certificates and Declarations (Document Number)**

cUL Certificate	cUL508_E174460
cUR Certificate	cUR60950_E196145
Declaration of Conformity - CE	1SVD982033-00
Declaration of Conformity - UKCA	1SVD982033-10
EAC Certificate	EAC_RU_C-DE.ME77.B.00768_20
Instructions and Manuals	1SVC427043M0000
RoHS Information	1SVD982033
UL Certificate	UL508_E174460
UR Certificate	UR60950_E196145

---

## Classifications

---

Object Classification Code		T
ETIM 4	EC002540 - DC-power supply	
ETIM 5	EC002540 - DC-power supply	
ETIM 6	EC002540 - DC-power supply	
ETIM 7	EC002540 - DC-power supply	
ETIM 8	EC002540 - DC-power supply	
eClass	V11.0 : 27040701	
UNSPSC	39121004	
E-Number (Finland)	2712081	
E-Number (Sweden)	5218730	

---

---

## Categories

---

Low Voltage Products and Systems → Control Products → Power Supplies → CP-D

