


## Adjustable Clamping Levers 120 Version N with Internal Thread, Disengaged by Pulling

**Material:** Handle: Zinc die-cast. Threaded bush and locking screw: Steel, black oxide finish. Handle: plastic coated, colour black RAL 9005.

**Version N** = Handle slanted, with metric-threaded bush.

As they are adjustable, they are very versatile in use.

The threaded insert is connected to the lever via the serration and can be released by pulling.



Ordering Details: e.g.: Product No. 665 705 00, Adjustable Clamping Lever, Thread M5

| Product No.<br>Version N | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | d <sub>5</sub><br>mm | h <sub>1</sub><br>mm | h <sub>2</sub><br>mm | Stroke<br>h <sub>4</sub><br>mm | h <sub>3</sub><br>mm | l <sub>2</sub><br>mm | t<br>mm | Weight<br>g |
|--------------------------|----------------------|----------------------|----------------------|----------------------|----------------------|--------------------------------|----------------------|----------------------|---------|-------------|
| 665 705 00               | 14                   | M5                   | 10                   | 25                   | 4,5                  | 3,5                            | 35                   | 45                   | 9       | 33          |
| 665 706 00               | 14                   | M6                   | 10                   | 25                   | 4,5                  | 3,5                            | 35                   | 45                   | 9       | 33          |
| 665 707 00               | 18                   | M6                   | 13,5                 | 31                   | 6,5                  | 4                              | 45                   | 62                   | 12      | 70          |
| 665 708 00               | 18                   | M8                   | 13,5                 | 31                   | 6,5                  | 4                              | 45                   | 62                   | 12      | 70          |
| 665 709 00               | 22                   | M8                   | 16                   | 36                   | 8                    | 4                              | 52                   | 74                   | 15      | 116         |
| 665 710 00               | 22                   | M10                  | 16                   | 36                   | 8                    | 4                              | 52                   | 74                   | 15      | 116         |
| 665 711 00               | 25                   | M10                  | 19                   | 43                   | 11                   | 4                              | 63                   | 89                   | 18      | 173         |
| 665 712 00               | 25                   | M12                  | 19                   | 43                   | 11                   | 4                              | 63                   | 89                   | 18      | 173         |
| 665 713 00               | 30                   | M12                  | 23                   | 50,5                 | 12                   | 5                              | 76                   | 108                  | 24      | 285         |
| 665 716 00               | 30                   | M16                  | 23                   | 50,5                 | 12                   | 5                              | 76                   | 108                  | 24      | 285         |


## Adjustable Clamping Levers 120 Version G with External Thread, Disengaged by Pulling

**Material:** Handle: zinc die-cast. Threaded stud and locking screw: Steel, black oxide finish. Handle: Plastic coated, colour black RAL 9005.

**Version G** = Handle slanted, with metric-threaded stud.

As they are adjustable, they are very versatile in use.

The threaded insert is connected to the lever via the serration and can be released by pulling.



Ordering Details: e.g.: Product No. 665 755 12, Adjustable Clamping Lever, Thread M5x12

| Product No.<br>Version G | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | l <sub>1</sub><br>mm | d <sub>4</sub><br>mm | h <sub>1</sub><br>mm | h <sub>2</sub><br>mm | h <sub>3</sub><br>mm | Stroke<br>h <sub>4</sub><br>mm | l <sub>2</sub><br>mm | Weight<br>g |
|--------------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|--------------------------------|----------------------|-------------|
| 665 755 12               | 14                   | M5                   | 12                   | 10                   | 25                   | 4,5                  | 35                   | 3,5                            | 45                   | 37          |
| 665 755 16               | 14                   | M5                   | 16                   | 10                   | 25                   | 4,5                  | 35                   | 3,5                            | 45                   | 38          |
| 665 755 20               | 14                   | M5                   | 20                   | 10                   | 25                   | 4,5                  | 35                   | 3,5                            | 45                   | 39          |
| 665 755 25               | 14                   | M5                   | 25                   | 10                   | 25                   | 4,5                  | 35                   | 3,5                            | 45                   | 39          |
| 665 755 32               | 14                   | M5                   | 32                   | 10                   | 25                   | 4,5                  | 35                   | 3,5                            | 45                   | 40          |
| 665 756 16               | 18                   | M6                   | 16                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 76          |
| 665 756 20               | 18                   | M6                   | 20                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 77          |
| 665 756 25               | 18                   | M6                   | 25                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 80          |
| 665 756 32               | 18                   | M6                   | 32                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 81          |
| 665 756 40               | 18                   | M6                   | 40                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 82          |
| 665 758 16               | 18                   | M8                   | 16                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 78          |
| 665 758 20               | 18                   | M8                   | 20                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 80          |
| 665 758 25               | 18                   | M8                   | 25                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 81          |
| 665 758 32               | 18                   | M8                   | 32                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 87          |
| 665 758 40               | 18                   | M8                   | 40                   | 13,5                 | 31                   | 6,5                  | 45                   | 4                              | 62                   | 89          |
| 665 760 20               | 22                   | M10                  | 20                   | 16                   | 36                   | 8                    | 52                   | 4                              | 74                   | 132         |
| 665 760 25               | 22                   | M10                  | 25                   | 16                   | 36                   | 8                    | 52                   | 4                              | 74                   | 136         |
| 665 760 32               | 22                   | M10                  | 32                   | 16                   | 36                   | 8                    | 52                   | 4                              | 74                   | 137         |
| 665 760 40               | 22                   | M10                  | 40                   | 16                   | 36                   | 8                    | 52                   | 4                              | 74                   | 143         |
| 665 760 50               | 22                   | M10                  | 50                   | 16                   | 36                   | 8                    | 52                   | 4                              | 74                   | 148         |
| 665 762 25               | 25                   | M12                  | 25                   | 19                   | 43                   | 11                   | 63                   | 4                              | 89                   | 203         |
| 665 762 32               | 25                   | M12                  | 32                   | 19                   | 43                   | 11                   | 63                   | 4                              | 89                   | 206         |
| 665 762 40               | 25                   | M12                  | 40                   | 19                   | 43                   | 11                   | 63                   | 4                              | 89                   | 214         |
| 665 762 50               | 25                   | M12                  | 50                   | 19                   | 43                   | 11                   | 63                   | 4                              | 89                   | 219         |
| 665 766 32               | 30                   | M16                  | 32                   | 23                   | 50,5                 | 12                   | 76                   | 5                              | 108                  | 362         |
| 665 766 40               | 30                   | M16                  | 40                   | 23                   | 50,5                 | 12                   | 76                   | 5                              | 108                  | 373         |
| 665 766 50               | 30                   | M16                  | 50                   | 23                   | 50,5                 | 12                   | 76                   | 5                              | 108                  | 386         |

### Note

This clamping lever has proven ideal wherever the swivel range is limited or where a specific lever position is most convenient for the operator. The lever also features a modern design. By pulling the lever, the serrations are disengaged. Now the handle

can be turned into any direction and the threaded insert can be screwed in or out by turning the locking screw. When the lever is released, the serration re-engages automatically because of the spring tension.