

CNC precision short drill chuck

For clockwise and anti-clockwise rotation

ATORN[®]

Application

For use on machining centres and CNC milling machines with tool change. For drilling, reaming, countersinking and also light milling and smoothing tasks.

Version

- Shank in accordance with DIN 69893, HST type A
- Integrated spur gear ensures high retaining torque
- glass bead blasted

Advantage

- Wear parts hardened and polished for long service life
- Remains securely clamped even with sudden spindle stop

Delivery

Including hexagon key



Art. No.	21329 542
Tool holding device	HSK 63
Min./max. clamping width	0.5-16 mm
Outer diameter	57 mm
Projecting length	109 mm
Length 2	113 mm
Running direction	Clockwise/anti-clockwise rotation
Coolant supply	Internal axial
Balancing quality	G 6,3 at 25000 rpm

EAN-Code

4050293321333