

AGWP 10 Select cordless tapping machine

lithium-ion 18 volt



Application:

for fast drilling and cleaning of threads.

Execution:

- cordless screw taps with reversing transmission for automatic reversal of rotation direction when withdrawing drill spindle from screw hole
- high concentricity through zero-play connection between drilling shaft and thread chuck (B12 taper seat)
- metal gear head

Delivery:

additional handle, plastic tool case, does not include tapping chuck



Art. no.	71028 380
Applications	Heavy screw/drill application
Model	AGWP 10 Select
Motor design	Brushless motor
Number of rechargeable batteries/batteries	0
Battery voltage	18 V/AC
Max. thread-cutting performance	M10
Idle speed left	760 rpm
Min./max. rotation speed from cutting at nominal load	0-440 rpm
Min./max. rotation speed at nominal load left-handed rotation	0-670 rpm
Clamping neck diameter	43 mm
Battery included	No
Width across corners	23 mm
With working lights	No
With rubber-coated handle	No
Product Group	Prod. Gr. 704

EAN

4014586885537