


# Panasonic ideas for life

## Compact DIP8-pin type of 60V to 600V load voltage

#### PhotoMOS® GU 2 Form A (AQW210)

#### 9.78 3.85 3.9 1.154 9.78 9.78 9.78 1.42 CAD Data

mm inch



#### **FEATURES**

#### 1. Compact 8-pin DIP size

The device comes in a compact (W)  $6.4 \times$  (L)  $9.78 \times$ (H) 3.9 mm (W)  $.252 \times$ (L)  $.385 \times$ (H) .154 inch, 8-pin DIP size (through hole terminal type).

- 2. Applicable for 2 Form A use as well as two independent 1 Form A use
- **3. Controls low-level analog signals** PhotoMOS relays feature extremely low closed-circuit offset voltage to enable control of low-level analog signals without distortion.

## 4. High sensitivity and high speed response

Can control max. 0.6 A load current with 5 mA input current. Fast operation speed of typ. 0.65 ms (AQW212).

- 5. Low-level off state leakage current of max. 1  $\mu$ A
- 6. Wide variation of load voltage 60V to 600V

#### TYPICAL APPLICATIONS

- High-speed inspection machines
- Telephone equipment
- Computer

#### **TYPES**

	Output rating*				Par	Packing quantity			
			Package	Through hole terminal	S				
	Load	Load current	rackage			Tape and ree	l packing style		
	Load voltage			Tube pac	king style	Picked from the 1/2/3/4-pin side	Picked from the 5/6/7/8-pin side	Tube	Tape and reel
AC/DC dual use	60V	500 mA	· DIP8-pin	AQW212	AQW212A	AQW212AX	AQW212AZ	1 tube contains: 50 pcs.	1,000 pcs.
	100 V	300 mA		AQW215	AQW215A	AQW215AX	AQW215AZ		
	200 V	160 mA		AQW217	AQW217A	AQW217AX	AQW217AZ		
	350 V	120 mA		AQW210	AQW210A	AQW210AX	AQW210AZ	1 batch contains:	
	400 V	100 mA		AQW214	AQW214A	AQW214AX	AQW214AZ	500 pcs.	
	600 V	40 mA		AQW216	AQW216A	AQW216AX	AQW216AZ		

<sup>\*</sup>Indicate the peak AC and DC values.

Note: The surface mount terminal shape indicator "A" and the packing style indicator "X" or "Z" are not marked on the relay.

#### **RATING**

1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)


Item		Symbol	AQW212(A)	AQW215(A)	AQW217(A)	AQW210(A)	AQW214(A)	AQW216(A)	Remarks
	LED forward current	lF							
Input	LED reverse voltage	VR							
	Peak forward current			f = 100 Hz, Duty factor = 0.1%					
	Power dissipation	Pin							
Output	Load voltage (peak AC)	VL	60 V	100 V	200 V	350 V	400 V	600 V	
	Continuous load current	l <sub>L</sub>	0.50 A (0.60A)	0.30 A (0.35 A)	0.16 A (0.2 A)	0.12 A (0.14 A)	0.10 A (0.13 A)	0.04 A (0.05 A)	Peak AC, DC ( ): in case of using only 1 channel
	Peak load current	Ipeak	1.0 A	0.9 A	0.48 A	0.36 A	0.3 A	0.12 A	A connection: 100 ms (1 shot), V <sub>L</sub> = DC
	Power dissipation	Pout		•					
Total power dissipation		P⊤							
I/O isolation voltage		Viso			Between input and output/between contact sets				
Tempera	ature Operating	Торг		-4	Non-condensing at low temperatures				
limits	Storage	T <sub>stg</sub>		-4					

#### GU 2 Form A (AQW21O)

2. Electrical characteristics (Ambient temperature: 25°C 77°F)

Item			Symbol	AQW212(A)	AQW215(A)	AQW217(A)	AQW210(A)	AQW214(A)	AQW216(A)	Condition
Input	LED operate current	Typical	IFon	0.9 mA						- I∟ = Max.
		Maximum	IFon							
	LED turn off current	Minimum	] <sub> </sub>			I∟= Max.				
		Typical	Foff		IL = IVIAX.					
	LED dropout voltage	Typical	VF		- I <sub>F</sub> = 50 mA					
		Maximum	VF	1.5 V						
Output	On resistance	Typical	Ron	0.83 Ω	2.3 Ω	11 Ω	23 Ω	30 Ω	70 Ω	I <sub>F</sub> = 5 mA
		Maximum		2.5 Ω	4.0 Ω	15 Ω	35 Ω	50 Ω	120 Ω	I∟ = Max. Within 1 son time
	Off state leakage current	Maximum	ILeak		I <sub>F</sub> = 0 mA V <sub>L</sub> = Max.					
Transfer characteristics	Turn on time*	Typical	<b>T</b> on	0.65 ms	0.60 ms	0.25 ms	0.25 ms	0.31 ms	0.28 ms	I <sub>F</sub> = 5 mA I <sub>L</sub> = Max.
		Maximum		2 ms	2 ms	1.0 ms	0.5 ms	0.5 ms	0.5 ms	
	Turn off time*	Typical	Toff	0.08 ms	0.06 ms	0.05 ms	0.05 ms	0.05 ms	0.04 ms	I <sub>F</sub> = 5 mA
		Maximum	I off		I∟ = Max.					
	I/O capacitance	Typical	Ciso		f = 1 MHz V <sub>B</sub> = 0 V					
		Maximum	Ciso	1.5 pF						
	Initial I/C isolation resistance	Minimum	Riso	1,000 ΜΩ						500 V DC

<sup>\*</sup>Turn on/Turn off time



#### RECOMMENDED OPERATING CONDITIONS

Please obey the following conditions to ensure proper relay operation and resetting.

Item	Symbol	Recommended value	Unit		
Input LED current	lF	5	mA		

- Dimensions
- Schematic and Wiring Diagrams
- Cautions for Use
- These products are not designed for automotive use.


If you are considering to use these products for automotive applications, please contact your local Panasonic technical representative.

Please refer to our information on PhotoMOS Relays for Automotive Applications.

#### **REFERENCE DATA**


1. Load current vs. ambient temperature characteristics

Allowable ambient temperature: -40°C to +85°C




2-(1) On resistance vs. ambient temperature characteristics

Measured portion: between terminals 5 and 6, 7 and 8; LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)



2.-(2) On resistance vs. ambient temperature characteristics


Measured portion: between terminals 5 and 6, 7 and 8; LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)



#### GU 2 Form A (AQW21O)


3. Turn on time vs. ambient temperature characteristics

LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)




 Turn off time vs. ambient temperature characteristics

LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)




## LED operate current vs. ambient temperature characteristics

Sample: All types; Load voltage: Max. (DC); Continuous load current: Max. (DC)




#### 6. LED turn off current vs. ambient temperature characteristics

Sample: All types; Load voltage: Max. (DC); Continuous load current: Max. (DC)




## 7. LED dropout voltage vs. ambient temperature characteristics

Sample: All types; LED current: 5 to 50 mA




#### 8.-(1) Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F




## 8.-(2) Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C  $77^{\circ}F$ 




## 9.-(1) Off state leakage current vs. load voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C  $77^{\circ}F$ 




## 9.-(2) Off state leakage current vs. load voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F




## 10. Turn on time vs. LED forward current characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature:  $25^{\circ}C$   $77^{\circ}F$ 



## 11. Turn off time vs. LED forward current characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 77°F



## 12. Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Frequency: 1 MHz;

Ambient temperature: 25°C 77°F

