



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 9

SDS No. : 43182  
V001.11

Pritt Stick

Revision: 13.02.2019  
printing date: 21.01.2020

Replaces version from: 12.10.2017

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Pritt Stick

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:  
Glue stick

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd  
Wood Lane End  
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000  
Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.2. Label elements

##### Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

**SECTION 3: Composition/information on ingredients****3.2. Mixtures****General chemical description:**

Glue stick

**Base substances of preparation:**

Polyglycoside ether

Polysaccharides

Soap

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

**SECTION 4: First aid measures****4.1. Description of first aid measures****General information:**

In case of adverse health effects seek medical advice.

**Inhalation:**

Move to fresh air, consult doctor if complaint persists.

**Skin contact:**

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

**Eye contact:**

Rinse immediately with plenty of running water, seek medical advice if necessary.

**Ingestion:**

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

No data available.

**4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media:**

carbon dioxide, foam, powder, water spray jet, fine water spray

**Extinguishing media which must not be used for safety reasons:**

High pressure waterjet

**5.2. Special hazards arising from the substance or mixture**In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO<sub>2</sub>) can be released.**5.3. Advice for firefighters**

Wear protective equipment.

Wear self-contained breathing apparatus.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures**

Wear protective equipment.

**6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

No particular measures required.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

**7.2. Conditions for safe storage, including any incompatibilities**

Store in sealed original container.

Store in a cool, dry place.

Avoid strictly temperatures below + 5 °C and above + 50 °C.

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

**7.3. Specific end use(s)**

Glue stick

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Sucrose 57-50-1 [SUCROSE]		10	Time Weighted Average (TWA):		EH40 WEL
Sucrose 57-50-1 [SUCROSE]		20	Short Term Exposure Limit (STEL):		EH40 WEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, PARTICULATES]		10	Time Weighted Average (TWA):		EH40 WEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, TOTAL VAPOUR AND PARTICULATES]	150	474	Time Weighted Average (TWA):		EH40 WEL

#### Occupational Exposure Limits

Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Sucrose 57-50-1 [SUCROSE]		10	Time Weighted Average (TWA):		IR_OEL
Sucrose 57-50-1 [SUCROSE]		20	Short Term Exposure Limit (STEL):	15 minutes	IR_OEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, PARTICULATES]		10	Time Weighted Average (TWA):		IR_OEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, TOTAL (VAPOUR AND PARTICULATES)]	150	470	Time Weighted Average (TWA):		IR_OEL

#### Biological Exposure Indices:

None

#### 8.2. Exposure controls:

Respiratory protection:  
Not needed.

Hand protection:  
Not needed.

Eye protection:  
Not needed.

Skin protection:  
Not needed.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Appearance	sticks solid white
Odor	typical, slightly
Odour threshold	No data available / Not applicable
pH (20 °C (68 °F))	10,15 - 10,25
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	100 °C (212 °F)
Flash point	Not applicable
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density (20 °C (68 °F))	1,15 - 1,19 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (23 °C (73.4 °F); Solvent: Water)	Partially soluble
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity (Brookfield; 80 °C (176 °F))	4.000 - 7.500 mPa.s
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

### 9.2. Other information

Softening point/range	63 - 65 °C (145.4 - 149 °F)
-----------------------	-----------------------------

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

None if used for intended purpose.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

None if used for intended purpose.

### 10.5. Incompatible materials

None if used properly.

### 10.6. Hazardous decomposition products

None known.

---

**SECTION 11: Toxicological information**

---

**General toxicological information:**

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

**11.1. Information on toxicological effects****Acute oral toxicity:**

No data available.

**Acute dermal toxicity:**

No data available.

**Acute inhalative toxicity:**

No data available.

**Skin corrosion/irritation:**

No data available.

**Serious eye damage/irritation:**

No data available.

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

No data available.

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

No data available.

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

No data available.

**Aspiration hazard:**

No data available.

**SECTION 12: Ecological information****General ecological information:**

Do not empty into drains, soil or bodies of water.

**12.1. Toxicity****Toxicity (Fish):**

No data available.

**Toxicity (Daphnia):**

No data available.

**Chronic toxicity to aquatic invertebrates**

No data available.

**Toxicity (Algae):**

No data available.

**Toxicity to microorganisms**

No data available.

**12.2. Persistence and degradability**

No data available.

**12.3. Bioaccumulative potential**

No data available.

**12.4. Mobility in soil**

No data available.

**12.5. Results of PBT and vPvB assessment**

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

**12.6. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

Product disposal:  
Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:  
Use packages for recycling only when totally empty.

Waste code  
080410

## SECTION 14: Transport information

- 14.1. UN number**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**  
not applicable

## SECTION 15: Regulatory information

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content 0,00 %  
(VOCV 814.018 VOC regulation  
CH)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.



---

**SECTION 16: Other information**

---

**Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**