

# HS6070 SERIES PLANET



HS6071E

HS6073K

HS6076E

HS6075K

HS6074E

HS6072K


**THE PHOENIX PLANET HS6070 SERIES** is designed to provide extreme security protection for domestic and business use.

- **SECURITY PROTECTION** – Tested to the prestigious European EN1143-1 Security standard. ECB.S Certified Grade IV, has a recommended Insurance rating of £60,000 cash or £600,000 valuables\*.
- **APPROVALS** – UK Police approved (Secured by Design scheme) and the Association of Insurance Surveyors (AiS).
- **FIRE PROTECTION** – Tested to the European LFS 30P fire protection standard (EN15659) giving 30 minutes fire protection for paper documents.
- **KEY LOCKING** – Fitted with 2 high security double bitted VdS Class II key locks.
- **ELECTRONIC LOCKING** – Fitted with a high security VdS Class II electronic lock with dual control, master code & time delay and a high security double bitted VdS Class II key lock.
- **FIXING** – Ready prepared for wall fixing, with fixing bolts for brick walls supplied.
- **SPECIAL FEATURE** – Pre-prepared for alarm or power cable.
- **CONSTRUCTION** – 3 way angular locking bolts, double wall construction with specially formulated concrete infill, anti-drill plates and re-locker protection, provide a safe of great strength.
- **COLOUR** – Finished in a high quality scratch resistant grey paint RAL7024.
- **GDPR** – Maintain GDPR Compliance at home or in the office by keeping your company's vital and important records secure and protected.

✚ Suitable for storage of controlled drugs whose active ingredients exceed 500 grams.

MODEL NUMBER	EXTERNAL DIMENSIONS H x W x D	INTERNAL DIMENSIONS H x W x D	DOOR SWING / HANDLE DEPTH	WEIGHT	CAPACITY	SHELVES			
						LEVER ARCH FOLDER (H320xW75x290mm) Total no. of file per unit	FOOLSCAP LEVER ARCH FOLDER (H350xW80xD285mm) Total no. of file per unit	FOOLSCAP BOX FILE (H370xW75xD245mm) Total no. of file per unit	
HS6071K/E	580 x 580 x 545mm	470 x 465 x 360mm	545mm/50mm	328kg	80 Litres	1	6	5	6
HS6072K/E	680 x 580 x 545mm	570 x 465 x 360mm	545mm/50mm	372kg	100 Litres	1	6	5	6
HS6073K/E	850 x 580 x 545mm	740 x 465 x 360mm	545mm/50mm	445kg	129 Litres	1	12	10	6
HS6074K/E	1210 x 580 x 545mm	1100 x 465 x 360mm	545mm/50mm	595kg	190 Litres	2	18	15	12
HS6075K/E	1310 x 670 x 545mm	1175 x 530 x 330mm	625mm/50mm	695kg	205 Litres	3	21	18	21
HS6076K/E	1210 x 860 x 655mm	1095 x 745 x 470mm	815mm/50mm	855kg	395 Litres	2	27	27	18

*This information is provided as a guide only. Actual capacities may vary depending on the storage method or shelving used.*



HS6070K

HS6070E

\* Ratings are approximate only and may vary due to area conditions and location. Please check with your underwriter.