



SIMATIC S7-1500, CPU 1511-1 PN, central processing unit with work memory 300 KB for program and 1.5 MB for data, 1st interface: PROFINET IRT with 2-port switch, 25 ns bit performance, SIMATIC Memory Card required \*\*\*\* approvals and certificate according to entry 109815653 at support.industry.siemens.com to be observed! \*\*\*\*

General information	
Product type designation	CPU 1511-1 PN
HW functional status	FS01
Firmware version	V3.0
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> <li>Isochronous mode</li> </ul>	Yes; Distributed and central; with minimum OB 6x cycle of 500 µs (distributed) and 1 ms (central)
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul>	V18 (FW V3.0); with older TIA Portal versions configurable as 6ES7511-1AK02-0AB0
Configuration control	
via dataset	Yes
Display	
Screen diagonal [cm]	3.45 cm
Control elements	
Number of keys	8
Mode buttons	2
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Mains buffering	
<ul style="list-style-type: none"> <li>Mains/voltage failure stored energy time</li> </ul>	5 ms
<ul style="list-style-type: none"> <li>Repeat rate, min.</li> </ul>	1/s
Input current	
Current consumption (rated value)	0.73 A
Current consumption, max.	0.9 A
Inrush current, max.	1.15 A; Rated value
$I^2t$	0.5 A <sup>2</sup> ·s
Power	
Infeed power to the backplane bus	10 W
Power consumption from the backplane bus (balanced)	5.5 W
Power loss	
Power loss, typ.	7.5 W
Memory	
Number of slots for SIMATIC memory card	1
SIMATIC memory card required	Yes
Work memory	

<ul style="list-style-type: none"> <li>integrated (for program)</li> </ul>	300 kbyte
<ul style="list-style-type: none"> <li>integrated (for data)</li> </ul>	1.5 Mbyte
<b>Load memory</b>	
<ul style="list-style-type: none"> <li>Plug-in (SIMATIC Memory Card), max.</li> </ul>	32 Gbyte
<b>Backup</b>	
<ul style="list-style-type: none"> <li>maintenance-free</li> </ul>	Yes
<b>CPU processing times</b>	
for bit operations, typ.	25 ns
for word operations, typ.	32 ns
for fixed point arithmetic, typ.	42 ns
for floating point arithmetic, typ.	170 ns
<b>CPU-blocks</b>	
Number of elements (total)	4 000; Blocks (OB, FB, FC, DB) and UDTs
<b>DB</b>	
<ul style="list-style-type: none"> <li>Number range</li> </ul>	1 ... 60 999; subdivided into: number range that can be used by the user: 1 ... 59 999, and number range of DBs created via SFC 86: 60 000 ... 60 999
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	1.5 Mbyte; For DBs with absolute addressing, the max. size is 64 KB
<b>FB</b>	
<ul style="list-style-type: none"> <li>Number range</li> </ul>	0 ... 65 535
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	300 kbyte
<b>FC</b>	
<ul style="list-style-type: none"> <li>Number range</li> </ul>	0 ... 65 535
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	300 kbyte
<b>OB</b>	
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	300 kbyte
<ul style="list-style-type: none"> <li>Number of free cycle OBs</li> </ul>	100
<ul style="list-style-type: none"> <li>Number of time alarm OBs</li> </ul>	20
<ul style="list-style-type: none"> <li>Number of delay alarm OBs</li> </ul>	20
<ul style="list-style-type: none"> <li>Number of cyclic interrupt OBs</li> </ul>	20; With minimum OB 3x cycle of 250 µs
<ul style="list-style-type: none"> <li>Number of process alarm OBs</li> </ul>	50
<ul style="list-style-type: none"> <li>Number of DPV1 alarm OBs</li> </ul>	3
<ul style="list-style-type: none"> <li>Number of isochronous mode OBs</li> </ul>	2
<ul style="list-style-type: none"> <li>Number of technology synchronous alarm OBs</li> </ul>	2
<ul style="list-style-type: none"> <li>Number of startup OBs</li> </ul>	100
<ul style="list-style-type: none"> <li>Number of asynchronous error OBs</li> </ul>	4
<ul style="list-style-type: none"> <li>Number of synchronous error OBs</li> </ul>	2
<ul style="list-style-type: none"> <li>Number of diagnostic alarm OBs</li> </ul>	1
<b>Nesting depth</b>	
<ul style="list-style-type: none"> <li>per priority class</li> </ul>	24
<b>Counters, timers and their retentivity</b>	
<b>S7 counter</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	2 048
Retentivity	
— adjustable	Yes
<b>IEC counter</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
<b>S7 times</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	2 048
Retentivity	
— adjustable	Yes
<b>IEC timer</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
<b>Data areas and their retentivity</b>	
Retentive data area (incl. timers, counters, flags), max.	256 kbyte; in total; available retentive memory for bit memories, timers, counters, DBs, and technology data (axes): 216 KB
Extended retentive data area (incl. timers, counters, flags), max.	1.5 Mbyte; When using PS 6 0W 24/48/60 V DC HF
<b>Flag</b>	
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	16 kbyte

<ul style="list-style-type: none"> <li>Number of clock memories</li> </ul>	8; 8 clock memory bit, grouped into one clock memory byte
<b>Data blocks</b>	
<ul style="list-style-type: none"> <li>Retentivity adjustable</li> <li>Retentivity preset</li> </ul>	Yes No
<b>Local data</b>	
<ul style="list-style-type: none"> <li>per priority class, max.</li> </ul>	64 kbyte; max. 16 KB per block
<b>Address area</b>	
Number of IO modules	2 048; max. number of modules / submodules
<b>I/O address area</b>	
<ul style="list-style-type: none"> <li>Inputs</li> <li>Outputs</li> </ul>	32 kbyte; All inputs are in the process image 32 kbyte; All outputs are in the process image
<b>per integrated IO subsystem</b>	
<ul style="list-style-type: none"> <li>Inputs (volume)</li> <li>Outputs (volume)</li> </ul>	8 kbyte 8 kbyte
<b>per CM/CP</b>	
<ul style="list-style-type: none"> <li>Inputs (volume)</li> <li>Outputs (volume)</li> </ul>	8 kbyte 8 kbyte
<b>Subprocess images</b>	
<ul style="list-style-type: none"> <li>Number of subprocess images, max.</li> </ul>	32
<b>Hardware configuration</b>	
Number of distributed IO systems	32; A distributed I/O system is characterized not only by the integration of distributed I/O via PROFINET or PROFIBUS communication modules, but also by the connection of I/O via AS-i master modules or links (e.g. IE/PB-Link)
<b>Number of DP masters</b>	
<ul style="list-style-type: none"> <li>Via CM</li> </ul>	4; A maximum of 4 CMs/CPs (PROFIBUS, PROFINET, Ethernet) can be inserted in total
<b>Number of IO Controllers</b>	
<ul style="list-style-type: none"> <li>integrated</li> <li>Via CM</li> </ul>	1 4; A maximum of 4 CMs/CPs (PROFIBUS, PROFINET, Ethernet) can be inserted in total
<b>Rack</b>	
<ul style="list-style-type: none"> <li>Modules per rack, max.</li> <li>Number of lines, max.</li> </ul>	32; CPU + 31 modules 1
<b>PtP CM</b>	
<ul style="list-style-type: none"> <li>Number of PtP CMs</li> </ul>	the number of connectable PtP CMs is only limited by the number of available slots
<b>Time of day</b>	
<b>Clock</b>	
<ul style="list-style-type: none"> <li>Type</li> <li>Backup time</li> <li>Deviation per day, max.</li> </ul>	Hardware clock 6 wk; At 40 °C ambient temperature, typically 10 s; Typ.: 2 s
<b>Operating hours counter</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	16
<b>Clock synchronization</b>	
<ul style="list-style-type: none"> <li>supported</li> <li>in AS, master</li> <li>in AS, slave</li> <li>on Ethernet via NTP</li> </ul>	Yes Yes Yes Yes
<b>Interfaces</b>	
Number of PROFINET interfaces	1
<b>1. Interface</b>	
<b>Interface types</b>	
<ul style="list-style-type: none"> <li>RJ 45 (Ethernet)</li> <li>Number of ports</li> <li>integrated switch</li> </ul>	Yes; X1 2 Yes
<b>Protocols</b>	
<ul style="list-style-type: none"> <li>IP protocol</li> <li>PROFINET IO Controller</li> <li>PROFINET IO Device</li> <li>SIMATIC communication</li> <li>Open IE communication</li> <li>Web server</li> <li>Media redundancy</li> </ul>	Yes; IPv4 Yes Yes Yes Yes; Optionally also encrypted Yes Yes

PROFINET IO Controller	
<b>Services</b>	
— PG/OP communication	Yes
— Isochronous mode	Yes
— Direct data exchange	Yes; Requirement: IRT and isochronous mode (MRPD optional)
— IRT	Yes
— PROFIenergy	Yes; per user program
— Prioritized startup	Yes; Max. 32 PROFINET devices
— Number of connectable IO Devices, max.	128; In total, up to 512 distributed I/O devices can be connected via AS-i, PROFIBUS or PROFINET
— Of which IO devices with IRT, max.	64
— Number of connectable IO Devices for RT, max.	128
— of which in line, max.	128
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8; in total across all interfaces
— Number of IO Devices per tool, max.	8
— Updating times	The minimum value of the update time also depends on communication share set for PROFINET IO, on the number of IO devices, and on the quantity of configured user data
<b>Update time for IRT</b>	
— for send cycle of 250 $\mu$ s	250 $\mu$ s to 4 ms; Note: In the case of IRT with isochronous mode, the minimum update time of 500 $\mu$ s of the isochronous OB is decisive
— for send cycle of 500 $\mu$ s	500 $\mu$ s to 8 ms; Note: In the case of IRT with isochronous mode, the minimum update time of 625 $\mu$ s of the isochronous OB is decisive
— for send cycle of 1 ms	1 ms to 16 ms
— for send cycle of 2 ms	2 ms to 32 ms
— for send cycle of 4 ms	4 ms to 64 ms
— With IRT and parameterization of "odd" send cycles	Update time = set "odd" send clock (any multiple of 125 $\mu$ s: 375 $\mu$ s, 625 $\mu$ s ... 3 875 $\mu$ s)
<b>Update time for RT</b>	
— for send cycle of 250 $\mu$ s	250 $\mu$ s to 128 ms
— for send cycle of 500 $\mu$ s	500 $\mu$ s to 256 ms
— for send cycle of 1 ms	1 ms to 512 ms
— for send cycle of 2 ms	2 ms to 512 ms
— for send cycle of 4 ms	4 ms to 512 ms
<b>PROFINET IO Device</b>	
<b>Services</b>	
— PG/OP communication	Yes
— Isochronous mode	No
— IRT	Yes
— PROFIenergy	Yes; per user program
— Shared device	Yes
— Number of IO Controllers with shared device, max.	4
— activation/deactivation of I-devices	Yes; per user program
— Asset management record	Yes; per user program
<b>Interface types</b>	
<b>RJ 45 (Ethernet)</b>	
• 100 Mbps	Yes
• Autonegotiation	Yes
• Autocrossing	Yes
• Industrial Ethernet status LED	Yes
<b>Protocols</b>	
PROFIsafe	No
<b>Number of connections</b>	
• Number of connections, max.	128; via integrated interfaces of the CPU and connected CPs / CMs
• Number of connections reserved for ES/HMI/web	10
• Number of connections via integrated interfaces	88
• Number of S7 routing paths	16
<b>Redundancy mode</b>	
• H-Sync forwarding	Yes
<b>Media redundancy</b>	
— Media redundancy	only via 1st interface (X1)
— MRP	Yes; MRP Automanager according to IEC 62439-2 Edition 2.0, MRP

<ul style="list-style-type: none"> <li>— MRP interconnection, supported</li> <li>— MRPD</li> <li>— Switchover time on line break, typ.</li> <li>— Number of stations in the ring, max.</li> </ul>	Manager; MRP Client Yes; as MRP ring node according to IEC 62439-2 Edition 3.0 Yes; Requirement: IRT 200 ms; For MRP, bumpless for MRPD 50
<b>SIMATIC communication</b>	
<ul style="list-style-type: none"> <li>• PG/OP communication</li> <li>• S7 routing</li> <li>• Data record routing</li> <li>• S7 communication, as server</li> <li>• S7 communication, as client</li> <li>• User data per job, max.</li> </ul>	Yes; encryption with TLS V1.3 pre-selected Yes Yes Yes Yes See online help (S7 communication, user data size)
<b>Open IE communication</b>	
<ul style="list-style-type: none"> <li>• TCP/IP <ul style="list-style-type: none"> <li>— Data length, max.</li> <li>— several passive connections per port, supported</li> </ul> </li> <li>• ISO-on-TCP (RFC1006) <ul style="list-style-type: none"> <li>— Data length, max.</li> </ul> </li> <li>• UDP <ul style="list-style-type: none"> <li>— Data length, max.</li> <li>— UDP multicast</li> </ul> </li> <li>• DHCP</li> <li>• DNS</li> <li>• SNMP</li> <li>• DCP</li> <li>• LLDP</li> <li>• Encryption</li> </ul>	Yes 64 kbyte Yes Yes 64 kbyte Yes 2 kbyte; 1 472 bytes for UDP broadcast Yes; max. 78 multicast circuits Yes Yes Yes Yes Yes Yes Yes; Optional
<b>Web server</b>	
<ul style="list-style-type: none"> <li>• HTTP</li> <li>• HTTPS</li> </ul>	Yes; Standard and user pages Yes; Standard and user pages
<b>OPC UA</b>	
<ul style="list-style-type: none"> <li>• Runtime license required</li> <li>• OPC UA Client <ul style="list-style-type: none"> <li>— Application authentication</li> <li>— Security policies</li> <li>— User authentication</li> <li>— Number of connections, max.</li> <li>— number of nodes of the client interfaces, recommended max.</li> <li>— Number of elements for one call of OPC-UA_NodeGetHandleList/OPC-UA_ReadList/C max.</li> <li>— Number of elements for one call of OPC-UA_NameSpaceGetIndexList, max.</li> <li>— Number of elements for one call of OPC-UA_MethodGetHandleList, max.</li> <li>— number of simultaneous calls of the client instructions for session management, per connection, max.</li> <li>— number of simultaneous calls of the client instructions for data access, per connection, max.</li> <li>— Number of registerable nodes, max.</li> <li>— Number of registerable method calls of OPC-UA_MethodCall, max.</li> <li>— Number of inputs/outputs when calling OPC-UA_MethodCall, max.</li> </ul> </li> <li>• OPC UA Server <ul style="list-style-type: none"> <li>— Application authentication</li> <li>— Security policies</li> <li>— User authentication</li> <li>— GDS support (certificate management)</li> <li>— Number of sessions, max.</li> <li>— Number of accessible variables, max.</li> </ul> </li> </ul>	Yes; "Small" license required Yes; Data Access (registered Read/Write), Method Call Yes Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256 "anonymous" or by user name & password 4 1 000 300 20 100 1 5 5 000 100 20 Yes; Data Access (Read, Write, Subscribe), Method Call, Alarms & Condition (A&C), Custom Address Space Yes available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256, Aes128Sha256RsaOaep, Aes256Sha256RsaPss "anonymous" or by user name & password Yes 32 50 000

— Number of registerable nodes, max.	10 000
— Number of subscriptions per session, max.	50
— Sampling interval, min.	100 ms
— Publishing interval, min.	200 ms
— Number of server methods, max.	20
— Number of inputs/outputs per server method, max.	20
— number of monitored items, recommended max.	4 000; for 1 s sampling interval and 1 s send interval
— Number of server interfaces, max.	10 of each "Server interfaces" / "Companion specification" type and 20 of the type "Reference namespace"
— Number of nodes for user-defined server interfaces, max.	15 000
• Alarms and Conditions	Yes
— Number of program alarms	100
— Number of alarms for system diagnostics	50
<b>Further protocols</b>	
• MODBUS	Yes; MODBUS TCP
<b>S7 message functions</b>	
Number of login stations for message functions, max.	32
Program alarms	Yes
Number of configurable program messages, max.	5 000; Program messages are generated by the "Program_Alarm" block, ProDiag or GRAPH
Number of loadable program messages in RUN, max.	2 500
Number of simultaneously active program alarms	
• Number of program alarms	600
• Number of alarms for system diagnostics	100
• Number of alarms for motion technology objects	160
<b>Test commissioning functions</b>	
Joint commission (Team Engineering)	Yes; Parallel online access possible for up to 5 engineering systems
Status block	Yes; Up to 8 simultaneously (in total across all ES clients)
Single step	No
Number of breakpoints	8
<b>Status/control</b>	
• Status/control variable	Yes
• Variables	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters
• Number of variables, max.	
— of which status variables, max.	200; per job
— of which control variables, max.	200; per job
<b>Forcing</b>	
• Forcing	Yes
• Forcing, variables	Peripheral inputs/outputs
• Number of variables, max.	200
<b>Diagnostic buffer</b>	
• present	Yes
• Number of entries, max.	1 000
— of which powerfail-proof	500
<b>Traces</b>	
• Number of configurable Traces	4; Up to 512 KB of data per trace are possible
<b>Interrupts/diagnostics/status information</b>	
<b>Diagnostics indication LED</b>	
• RUN/STOP LED	Yes
• ERROR LED	Yes
• MAINT LED	Yes
• STOP ACTIVE LED	Yes
• Connection display LINK TX/RX	Yes
<b>Supported technology objects</b>	
Motion Control	Yes; Note: The number of technology objects affects the cycle time of the PLC program; selection guide via the TIA Selection Tool
• Number of available Motion Control resources for technology objects	1 120
• Required Motion Control resources	
— per speed-controlled axis	40
— per positioning axis	80

— per synchronous axis	160
— per external encoder	80
— per output cam	20
— per cam track	160
— per probe	40
• Positioning axis	
— Number of positioning axes at motion control cycle of 4 ms (typical value)	11
— Number of positioning axes at motion control cycle of 8 ms (typical value)	14
Controller	
• PID_Compact	Yes; Universal PID controller with integrated optimization
• PID_3Step	Yes; PID controller with integrated optimization for valves
• PID-Temp	Yes; PID controller with integrated optimization for temperature
Counting and measuring	
• High-speed counter	Yes
<b>Ambient conditions</b>	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C; No condensation
• horizontal installation, max.	60 °C; Display: 50 °C, at an operating temperature of typically 50 °C, the display is switched off
• vertical installation, min.	-30 °C; No condensation
• vertical installation, max.	40 °C; Display: 40 °C, at an operating temperature of typically 40 °C, the display is switched off
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
<b>configuration / header</b>	
configuration / programming / header	
Programming language	
— LAD	Yes
— FBD	Yes
— STL	Yes
— SCL	Yes
— GRAPH	Yes
Know-how protection	
• User program protection/password protection	Yes
• Copy protection	Yes
• Block protection	Yes
Access protection	
• protection of confidential configuration data	Yes
• Password for display	Yes
• Protection level: Write protection	Yes
• Protection level: Read/write protection	Yes
• Protection level: Complete protection	Yes
programming / cycle time monitoring / header	
• lower limit	adjustable minimum cycle time
• upper limit	adjustable maximum cycle time
<b>Dimensions</b>	
Width	35 mm
Height	147 mm
Depth	129 mm
<b>Weights</b>	
Weight, approx.	336 g
<b>last modified:</b>	12/13/2022 