

35625 ✓ ACTIVE

SOLISTRAND


TE Internal #: 35625

Ring Terminals & Spade Terminals, Ring Tongue, 4AWG Wire Size,
16.8 – 26.7mm² Wire Size, 33100 – 52600CMA Wire Size, M6 / 1/4

[View on TE.com >](#)



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **33100 – 52600 CMA**

Ring & Spade Stud Size: **1/4, M6**

Features

Product Type Features

Shape Description	RING-080
Ring & Spade Stud Size	1/4, M6
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	90°

Body Features

Inspection Slot	No
Weight per Piece	9.21 g
Ring & Spade Plating Material	Tin

Contact Features

Terminal & Splice Type	Ring Tongue
------------------------	-------------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	33100 – 52600 CMA
Stud Diameter	6.73 mm[.265 in]
Tongue Thickness	1.78 mm[.07 in]
Barrel Inside Diameter	7.52 mm[.296 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	100
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1490413-3
HYP10 SOLIS 4AWG NEST



TE Part # 1490414-2
HYP10 SOLIS HD 6-4AWG INDENTER



TE Part # 1-1490413-6
NEST, 90 DEG SOLISTRAND, 4



TE Part # 1901000-2
NEST #4

Customers Also Bought



TE Part #2102352-1
CeeLok FAS-T, Receptacle Kit, Ni



TE Part #2-33457-2
TERMINAL,SOLIS R 12-10 10



TE Part #1766811-1
CONTACT,PIN,#0



TE Part #2-34161-3
TERMINAL,PG R 16-14 10



TE Part #225554-6
TNC RT ANG PLUG DUAL W/P



TE Part #2-1437624-3
PKB70B1/4=KNOB PLASTIC W/SKIRT



TE Part #3-1617004-0
B07D692BB2-0069 = M5757/23-006



TE Part #200838-2
BLOCK,34 POSN,M SERIES



Documents

Product Drawings

TERMINAL,SOLIS R 90DEG 4 1/4

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_35625_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_35625_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_35625_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

UL Report

English

UL Report

English