

SAFETY DATA SHEET

Product Name: Alkaline dry Zinc-manganese dioxide battery

Review Date: 18 July 2019

Section 1- Chemical Product and Company Identification

PRODUCT NAME: Alkaline dry Zinc-manganese dioxide battery LR03,1.5V

APPLICATIONS:

For Stock No. 41864	DIGITAL CLAMP METER DCM400
Stock No. 41911	DIGITAL CLAMP METER DCM401
Stock No. 41967	DIGITAL CLAMP METER DCM402
Stock No. 41821	DIGITAL MULTIMETER DMM300
Stock No. 15102	LASER DISTANCE METER LDM-40M

SUPPLIER: Draper Tools Ltd
Hursley Road
Chandlers Ford
Eastleigh
Hampshire
SO53 1YF

Draper Helpline +44 (0) 2380 494344
Opening hours 8:30-17:00 Monday – Friday.

SECTION 2 HAZARDS IDENTIFICATION

Hazards Identification:

The battery is not restricted to IATA DGR(60th Edition) according to special provision A23.
The battery is not subject to IMO IMDG Code(2016 Edition).

Emergency Overview:

Avoid contact and inhalation the internal materials. Emit toxic fumes under fire conditions.

SECTION 3 INFORMATION ON INGREDIENTS

Product name: Alkaline Dry Zinc-Manganese Dioxide Battery AAA LR03 1.5V

Ingredient	Concentration	CAS No.	EC No.
Zinc	28%	7440-66-6	231-175-3
Manganese Dioxide	22%	1313-13-9	215-202-6
Iron	20%	7439-89-6	231-096-4
Distilled water	15%	7732-18-5	231-791-2
Carbon	8%	1333-86-4	215-609-9
Potassium Hydroxide	4%	1310-58-3	215-181-3

SECTION 4 FIRST-AID MEASURES

Skin Exposure:

If the internal battery materials of an opened battery cell come into contact with the skin, immediately flush with plenty of water.

Inhalation Exposure:

In case of inhale the internal battery materials, remove immediately to fresh air and seek medical attention.

Eye Exposure:

In case of the internal battery materials in contact with eyes, flush with copious amounts of water for at least 15 minutes. Assure adequate flushing by separating the eyelids with fingers. Call a physician.

Oral Exposure:

If swallowed the internal battery materials, do not induce vomiting. Seek immediate medical attention.

SECTION5 FIRE FIGHTING MEASURES

Extinguishing Media:

Suitable: Dry chemical, Carbon dioxide and appropriate foam.

Firefighting:

Protective Equipment: Wear self-contained breathing apparatus and protective clothing to prevent contact with skin and eyes.

Specific hazards: Emit toxic fumes under fire conditions.

Specific Hazards:

The leaking electrolyte may corrosive. Under the conditions of short-circuited, overcharged, overdischarged, punctured, crushed, and exposed on the temperature higher than that specified by manufacture, the battery may burn or explode.

SECTION6 ACCIDENTAL RELEASE MEASURES

Procedure of Personal Precaution:

Exercise appropriate precautions to minimize direct contact with skin and eyes.

Methods for Cleaning up:

In case of internal materials leak, mix with inert material (e.g. dry sand, vermiculite) and transfer to a dry, clean, lidded container for disposal. Avoid raising dust. Ventilate area and wash spill site after material pickup is complete. Avoid directly release the cleaning waste water into the environment.

SECTION7 HANDLING AND STORAGE

Handling:

Wear appropriate protective clothing and safety gloves. Avoid contact and inhalation the internal materials. Keep away from ignition sources, heat and flame. No smoking at working site. Incompatibilities: strong oxidizing agents, corrosives and foods. If it is not intend to do, do not short-circuit, overcharge, overdischarge, puncture and crush the battery. Do not expose the battery on the temperature higher than that specified by manufacture.

Storage:

Store in a cool, dry, and well-ventilated area. Keep away from ignition sources, heat and flame. Store in a tightly closed container. Incompatibilities: strong oxidizing agents, corrosives and foods. Such batteries must be packed in inner packaging in such a manner as to effectively prevent short circuits and to prevent movement which could lead to short circuits.

SECTION 8 EXPOSURE CONTROL/PPE

Engineering Controls:

Use ventilation equipment if available. Safety shower and eye bath.

Personal Protective Equipment:

Respiratory: Government approved respirator if needed.

Eye: Chemical safety goggles if needed.

Clothing: Wear appropriate protective clothing.

Hand: Protective gloves.

Other Protect:

No smoking, drinking and eating at working site. Wash thoroughly after handling.

SECTION 9 PHYSICAL/CHEMICAL PROPERTIES

Appearance: Golden and green cylinder plastics film shell

Odor: Odorless

Melting Point/°C: >300°C

Solubility: Partial soluble in water

SECTION 10 STABILITY AND REACTIVITY

Stability:

Stable under normal temperatures and pressures.

Conditions to Avoid:

Avoid exposure to heat and open flame. Do not puncture, crush or incinerate. Prevent short circuits.

Prevent movement which could lead to short circuits. Do not attempt to recharge this battery.

Materials to Avoid:

Strong oxidizing agents, corrosives.

Hazardous Polymerization:

Will not occur.

Hazardous Decomposition Products:

When exposed to extreme heat/fire batteries may rupture leaking corrosive material and/or emit toxic fumes. Burning batteries may emit toxic fumes of zinc oxide and manganese oxide.

SECTION 11 TOXICOLOGICAL INFORMATION

Toxicity Data:

No data available.

Irritation Data:

The internal battery materials may cause irritation to eyes and skin.

SECTION 12 ECOLOGICAL INFORMATION

No data available.

SECTION 13 DISPOSAL CONSIDERATION

Appropriate Method of Disposal of Substance:

Dispose of in accordance with all applicable federal, state and local regulations.

SECTION 14 TRANSPORT INFORMATION

IATA DGR (60th Edition): Not restricted to IATA DGR according to special provision A123.

IMO IMDG Code (2016 Edition): Not subject to IMO IMDG Code.

SECTION 15 REGULATORY INFORMATION

Manganese Dioxide Battery is unregulated for purpose of transportation by U.S. Department of Transportation (DOT), International Civil Aviation Administration (ICAA), International Air Transport Association (IATA) and the International Maritime Dangerous Goods regulations (IMDG). The requirements for shipping these batteries, in all modes of transportation, are that they be separated from each other to prevent short-circuits and to prevent movement that could lead to short-circuits. Products must also be packed in strong packaging that can withstand the rigors normal to transportation.

SECTION 16 OTHER INFORMATION

Date:
2019-07-18

Revision:
0

Other Information:

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. We make no warranty of merchantability or any other warranty, express or implied, with respect to such information, and we assume no liability resulting from its use. Users should make their own investigation to determine the suitability of the information for their particular purposes. In no way shall we be liable for any claims, losses, or damages of any third party or for lost profits or any special, indirect, incidental, consequential or exemplary damages, howsoever arising from using the above information.