





Part no. PKZM0-16-PI  
 Catalog No. 199159  
 Alternate Catalog No. XTPRPI016BC1NL  
 EL-Nummer (Norway) 4312284

### Delivery program

|   |          |    |  |  |
|---|----------|----|--|--|
| Product range   |          |    |  | PKZM0 motor protective circuit-breakers up to 32 A                                 |
| Basic function  |          |    |  | Motor protection   |
|   |          |    |  |  |
| Notes   |          |    |  | Also suitable for motors with efficiency class IE3.                                |
| Connection technique  |          |    |  | Push in terminals  |
| <b>Max. motor rating</b>  |          |    |  |  |
| AC-3  |          |    |  |  |
| 220 V 230 V 240 V   | P        | kW |  | 4  |
| 380 V 400 V 415 V   | P        | kW |  | 7.5  |
| 440 V   | P        | kW |  | 9  |
| 500 V   | P        | kW |  | 9  |
| 660 V 690 V   | P        | kW |  | 12.5   |
| Rated uninterrupted current   | $I_u$    | A  |  | 16   |
| <b>Setting range</b>  |          |    |  |  |
| Overload releases   | $I_r$    | A  |  | 10 - 16  |
|  |          |    |  |  |
| short-circuit release   |          |    |  |  |
|  |          |    |  |  |
| max.  | $I_{rm}$ | A  |  | 248  |
| Phase-failure sensitivity   |          |    |  | IEC/EN 60947-4-1, VDE 0660 Part 102  |

### Technical data

|   |  |    |  |  |
|---|--|----|--|--|
| <b>General</b>  |  |    |  |  |
| Standards   |  |    |  | IEC/EN 60947, VDE 0660, UL, CSA  |
| Climatic proofing   |  |    |  | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30       |
| Ambient temperature   |  |    |  |  |
| Storage   |  | °C |  | - 40 - 80  |
| Open  |  | °C |  | -25 - +55  |
| Enclosed  |  | °C |  | - 25 - 40  |
| Mounting position   |  |    |  |  |
| Direction of incoming supply  |  |    |  | as required  |
| Degree of protection  |  |    |  |  |
| Device  |  |    |  | IP20   |
| Terminations  |  |    |  | IP20   |
| Protection against direct contact when actuated from front (EN 50274)     |  |    |  | Finger and back-of-hand proof  |
| Mechanical shock resistance half-sinusoidal shock 10 ms to IEC 60068-2-27 |  | g  |  | 25   |
| Altitude  |  | m  |  | Max. 2000  |

|  |  |                 |                             |
|--|--|-----------------|-----------------------------|
| Terminal capacity main cable               |  |                 |                             |
| Push-in terminals                          |  |                 |                             |
| Solid                                      |  | mm <sup>2</sup> | 1 x (1 - 6)<br>2 x (1 - 6)  |
| flexible                                   |  | mm <sup>2</sup> | 1 x (1 - 6)<br>2 x (1 - 6)  |
| flexible with ferrules                     |  | mm <sup>2</sup> | 1 x (1 - 6)<br>2 x (1 - 4)  |
| flexible with ultrasonic welded busbar end |  | mm <sup>2</sup> | 1 x (1 - 10)<br>2 x (1 - 6) |
| flexible with uninsulated wire end ferrule |  | mm <sup>2</sup> | 1 x (1 - 10)<br>2 x (1 - 6) |
| Solid or stranded                          |  | AWG             | 18 - 8                      |
| Stripping length                           |  | mm              | 12                          |
| Standard screwdriver                       |  |                 | 3.0 x 0.5                   |

### Main conducting paths

|   |                                 |                   |       |
|---|---------------------------------|-------------------|-------|
| Rated impulse withstand voltage                         | U <sub>imp</sub>                | V AC              | 6000  |
| Overvoltage category/pollution degree                   |                                 |                   | III/3 |
| Rated operational voltage                               | U <sub>e</sub>                  | V AC              | 690   |
| Rated uninterrupted current = rated operational current | I <sub>u</sub> = I <sub>e</sub> | A                 | 16    |
| Rated frequency   | f                               | Hz                | 50/60 |
| Current heat loss (3 pole at operating temperature)     |                                 | W                 | 6.43  |
| Impedance per pole                                      |                                 | mΩ                | 8     |
| Lifespan, mechanical                                    | Operations                      | x 10 <sup>6</sup> | 0.1   |
| Lifespan, electrical (AC-3 at 400 V)                    |                                 |                   |       |
| Lifespan, electrical                                    | Operations                      | x 10 <sup>6</sup> | 0.1   |
| Max. operating frequency                                |                                 | Ops/h             | 40    |
| Motor switching capacity                                |                                 |                   |       |
| AC-3 (up to 690V)                                       |                                 | A                 | 16    |

### Trip blocks

|   |  |                  |  |
|---|--|------------------|--|
| Temperature compensation                              |  |                  |  |
| to IEC/EN 60947, VDE 0660                             |  | °C               | - 5 ... 40                                 |
| Operating range                                       |  | °C               | - 25 ... 55                                |
| Temperature compensation residual error for T > 40 °C |  |                  | ± 0.25 %/K                                 |
| Setting range of overload releases                    |  | x I <sub>u</sub> | 0.6 - 1                                    |
| short-circuit release                                 |  |                  | Basic device, fixed: 15.5 x I <sub>u</sub> |
| Short-circuit release tolerance                       |  |                  | ± 20%                                      |
| Phase-failure sensitivity                             |  |                  | IEC/EN 60947-4-1, VDE 0660 Part 102        |

### Rating data for approved types

|  |  |      |               |
|--|--|------|---------------|
| Switching capacity                             |  |      |               |
| Maximum motor rating                           |  |      |               |
| Three-phase                                    |  |      |               |
| 200 V<br>208 V                                 |  | HP   | 3             |
| 230 V<br>240 V                                 |  | HP   | 5             |
| 460 V<br>480 V                                 |  | HP   | 10            |
| 575 V<br>600 V                                 |  | HP   | 10            |
| Single-phase                                   |  |      |               |
| 230 V<br>240 V                                 |  | HP   | 2             |
| Short Circuit Current Rating, type E           |  | SCCR |               |
| 240 V  |  | kA   | 42            |
| 480 Y / 277 V                                  |  | kA   | 42            |
| Accessories required                           |  |      | LSA-PKZ0-E-PI |
| Short Circuit Current Rating, group protection |  | SCCR |               |
| 600 V High Fault                               |  |      |               |

|                     |    |     |
|---------------------|----|-----|
| SCCR (fuse)         | kA | 10  |
| max. Fuse           | A  | 150 |
| SCCR (CB)           | kA | 10  |
| max. CB             | A  | 125 |
| SCCR with CL (fuse) | A  | 50  |
| max. Fuse (with CL) | A  | 600 |
| SCCR with CL (CB)   | kA | 50  |
| max. CB (with CL)   | A  | 600 |

## Design verification as per IEC/EN 61439

|  |    |     |
|--|----|-----|
| Technical data for design verification |    |     |
| Operating ambient temperature min.     | °C | -25 |
| Operating ambient temperature max.     | °C | 55  |

## Technical data ETIM 8.0


|   |    |  |
|---|----|--|
| Low-voltage industrial components (EG000017) / Motor protection circuit-breaker (EC000074)  |    |  |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Motor protection circuit-breaker (ecl@ss10.0.1-27-37-04-01 [AGZ529016]) |    |  |
| Overload release current setting  | A  | 16 - 16                                  |
| Adjustment range undelayed short-circuit release  | A  | 248 - 248                                |
| With thermal protection   |    | No                                       |
| Phase failure sensitive   |    | Yes                                      |
| Switch off technique  |    | Thermomagnetic                           |
| Rated operating voltage   | V  | 690 - 690                                |
| Rated permanent current Iu  | A  | 16                                       |
| Rated operation power at AC-3, 230 V  | kW | 4  |
| Rated operation power at AC-3, 400 V  | kW | 7.5                                      |
| Type of electrical connection of main circuit   |    | Spring clamp connection                  |
| Type of control element   |    | Turn button                              |
| Device construction   |    | Built-in device fixed built-in technique |
| With integrated auxiliary switch  |    | No                                       |
| With integrated under voltage release   |    | No                                       |
| Number of poles   |    | 3  |
| Rated short-circuit breaking capacity Icu at 400 V, AC  | kA | 50                                       |
| Degree of protection (IP)   |    | IP20                                     |
| Height  | mm | 109                                      |
| Width   | mm | 45                                       |
| Depth   | mm | 75                                       |

## Approvals


|                                      |  |   |
|--------------------------------------|--|---|
| Product Standards                    |  | IEC/EN 60947-4-1; UL 60947-4-1; CSA - C22.2 No. 60947-4-1-14; CE marking                          |
| UL File No.                          |  | E36332  |
| UL Category Control No.              |  | NLRV  |
| CSA File No.                         |  | 165628  |
| CSA Class No.                        |  | 3211-05   |
| North America Certification          |  | UL listed, CSA certified  |
| Specially designed for North America |  | No  |
| Suitable for                         |  | Branch circuit: Manual type E if used with Line Side Adapter, or suitable for group installations |

## Dimensions

|   |
|---|
| Motor-protective circuit-breaker with standard auxiliary contact<br>PKZM0-...(+NHI-E-...-PKZ0)<br>PKZM0-...-T(+NHI-E-...-PKZ0)<br>PKM0-...(+NHI-E-...-PKZ0) |
|---|



Motor-protective circuit-breakers with lockable rotary handles  
PKZM0-...+AK-PKZ0



Motor-protective circuit-breakers with early-make auxiliary contacts  
PKZM0-...+VHI-...-PKZ0

### Additional product information (links)

|  |   |
|--|---|
| Schaltvermögen   | <a href="https://de.ecat.eaton.com/flip-cat/?edition=MOTCONT1_DE#page_3/44">https://de.ecat.eaton.com/flip-cat/?edition=MOTCONT1_DE#page_3/44</a>   |
| Motor starters and "Special Purpose Ratings" for the North American market | <a href="http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf">http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf</a> |
| Busbar Component Adapters for modern Industrial control panels             | <a href="http://www.moeller.net/binary/ver_techpapers/ver960en.pdf">http://www.moeller.net/binary/ver_techpapers/ver960en.pdf</a>   |