

90° angular milling cutter with weld-on shank

For indexable milling inserts LN.X 1006..

ATORN[®]

Application


Four cutting edges per milling insert and special chip breaker geometry result in profitability and high chip removal rates during facing, angular cutting, trimming, and groove cutting.

Version

- with weld-on shank
- wear-proof, nickel-plated design
- with inner cooling

Advantage

- 4 cutting edges on double-sided indexable insert
- special chip breaker geometry enables low power consumption
- large insert thickness



Art. No.	16016 320
Cutting edge diameter	20 mm
Clearance length	30 mm
Length	100 mm
Shaft diameter	20 mm
max. ap	9 mm
Number of cutting edges	3 PCS
Suitable indexable insert no.	1

EAN-Code

4050293344424