

## Electronically temperature-controlled soldering station ANALOG 60 anti-static

150-450°C adjustable



### Application:

For professional soldering tasks.

### Execution:

- Voltage 230 V, 50/60 Hz
- Noise-suppressed
- Antistatic
- 24-V secondary voltage
- Temperature measured with thermosensor
- Potential equalisation socket (connected to the soldering tip with high resistance)
- Multi-functional support rest
- With 2-m connection cable



|   |                       |
|---|-----------------------|
| <b>Art. no.</b>                         | <b>54372 020</b>      |
| <b>Brand</b>                            | ERSA                  |
| <b>Manufacturer Part Number</b>         | 0ANA60A               |
| <b>Type</b>                             | ANALOG 60 anti-static |
| <b>Type description</b>                 | 0832 CDLF             |
| <b>Power rating</b>                     | 60 W                  |
| <b>Min./max. temperature conditions</b> | 150 to 450 °C         |
| <b>Heat-up time</b>                     | 60 s                  |
| <b>Tip diameter</b>                     | 2.2 mm                |
| <b>Shape of tip</b>                     | Chisel-shaped         |
| <b>Gross Weight</b>                     | 2.535 kg              |
| <b>Product Group</b>                    | 5JN                   |

### EAN

4003008054927