



AMP-LATCH

TE Internal #: 1658528-2
Ribbon Cable Connectors, Wire-to-Board, 10 Position, 2.54mm [.1in] Centerline, Insulation Displacement Crimp (IDC), Row-to-Row Spacing 2.54 mm [.1 in]

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**
Number of Positions: **10**
Centerline (Pitch): **2.54 mm [.1 in]**
Termination Method to Wire & Cable: **Insulation Displacement Crimp (IDC)**
Row-to-Row Spacing: **2.54 mm [.1 in]**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Ribbon Cable
Number of Positions	10
Number of Rows	2

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Wire Contact Termination Area Plating Material Thickness	.127 µm[5 µin]
Wire Contact Termination Area Plating Material	Gold Flash
	15 µin
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)
------------------------------------	-------------------------------------

Mechanical Attachment



Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Color	Black
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>









EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS	 TE Part # CAT-AM71-UN385 Universal Headers: Ejector Latch	 TE Part # 1-111446-4 10 UNIV I/O, NO EARS, LEAD FREE	 TE Part # 1-111504-4 10 UNIV I/O, NO EARS, LEAD FREE
 TE Part # 104128-1 010 LOPRO HDR SP 30DP LATCH	 TE Part # 2-1761605-3 IDC LOW PRO HDR 10P RA BLUE	 TE Part # 1761681-3 IDC LOW PRO HDR 10P VERT HT BLACK	 TE Part # 2-1761603-3 IDC LOW PRO HDR 10P VERT BLUE
 TE Part # 1761607-3 IDC LOW PRO HDR 10P RA LG LAT	 TE Part # 1-111506-6 010 UNIV I/O 30DP SLOT LTCH	 TE Part # 1761606-3 IDC LOW PRO HDR 10P VERT LG LAT BLK	 TE Part # 2-1761711-3 IDC LOW PRO HDR 10P VERT LG LA
 TE Part # 5103309-1 A/L LOW PRO HDR 10P VERT BLACK	 TE Part # 5103308-1 A/L LOW PRO HDR 10P VERT BLACK	 TE Part # 5104340-1 A/L LOW PRO HDR 10P RA HT	 TE Part # 2-1761606-3 IDC LOW PRO HDR 10P VERT LG LAT BLUE
 TE Part # 2-1761607-3 IDC LOW PRO HDR 10P RA LG LAT	 TE Part # 1761682-3 IDC LOW PRO HDR 10P RA HT BLACK	 TE Part # 1761683-3 IDC LOW PRO HDR 10P VERT HT BLACK	 TE Part # 1761686-3 IDC LOW PRO HDR 10P VERT LG LAT

Customers Also Bought



TE Part #1658642-1
D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1

TE Part #1-206062-4
CPC CABLE CLAMPS

TE Part #1-1658528-1
636-1030LF=FEM SKT BLADE POL 1

TE Part #1-1614447-0
RN 0805 1K2 0.1% 10PPM 1K RL

TE Part #1-2040586-1
DYNAMIC 4000 REC AND TAB CONT

TE Part #1478763-9
METAL BACKSHELL 9 WAY 45 DE

TE Part #1-1649327-3
RT214012

TE Part #1-1649328-9
RTD34005

TE Part #1-2232784-2
GIC 7.92MM CONN HDR ASS'Y 2POS RED

TE Part #C17298-000
WP WHITE POLYESTER LABELS

Documents

Product Drawings

636-1041LF FEM SOCKET, LEAD FREE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1658528-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1658528-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1658528-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[Ribbon Cable Interconnect Solutions](#)

English

[Product Environmental Compliance](#)

[TE Material Declaration](#)

English

[Instruction Sheets](#)

[Instruction Sheet \(U.S.\)](#)

English