

## Pneumatic straight grinder GK 282 H

**MANNESMANN  
DEMAG**

### Application:

For light deburring work

### Delivery:

Includes hose unit and collet chuck keys



<b>Art. no.</b>	<b>75061 075</b>
<b>Brand</b>	MANNESMANN DEMAG
<b>Manufacturer Part Number</b>	29938025
<b>Model</b>	GK 282 H
<b>Valve design</b>	Lever valve
<b>Max. idle speed</b>	30000 rpm
<b>Min./max. idle speed</b>	0-30000 rpm
<b>Power output</b>	240 W
<b>Air consumption</b>	6.6 l/s
<b>Connection thread</b>	G 1/4 inch
<b>Sound-pressure level</b>	67 dB
<b>Length</b>	141 mm
<b>Diameter of housing</b>	30 mm
<b>Collet chuck diameter</b>	6 mm
<b>Suitable for max. sanding block diameter</b>	16 mm
<b>Max. HM rotating milling cutter diameter</b>	10 mm
<b>Weight</b>	0.33 kg
<b>Gross Weight</b>	1.247 kg
<b>Product Group</b>	7AA

### EAN

4251757300356