

T50R0UVC2



Article Number: 112-05060

Standard Cable Tie, 8" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg



Download spec sheet

Base Data

Local Order Number	T50R0UVC2
Type	T50R
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"> • UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures. • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Standard Cable Tie, 8" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	225.0 N
Length L (Imperial)	8.0 "
Length L (Metric)	202.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18 "
Width W (Metric)	4.6 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.97 "
Bundle Diameter Max. (Metric)	50.0 mm
Thickness T (Imperial)	0.05 "
Thickness T (Metric)	1.2 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100 Pieces

Carton Quantity 5000 Pieces

Weight (Metric) 1.3 kg

Material and Specifications

Material Polyamide 6.6 UV-stabilized (PA66UV)

Material Shortcut PA66UV

US MILSPEC MS3367-1-0

Flammability UL94 V2

Halogenfree Yes

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

Certification/Specification UL-ZODZ2.E64139
MS3367
SAE - AS33671
Cage Code 53421
BACS38K

UL Listed (US and Canada) No

UL Recognized (US and Canada) No