

## Pneumatic straight grinder G 357 H

**MANNESMANN  
DEMAG**

### Application:

For light deburring work

### Advantage:

- Floating bearing ensures scratch-free workpiece processing
- Reduced cutter wear and tool life extension - tooth breakage is avoided

### Delivery:

Includes hose unit and collet chuck keys



|   |                  |
|---|------------------|
| <b>Art. no.</b>                                 | <b>75061 090</b> |
| <b>Brand</b>                                    | MANNESMANN DEMAG |
| <b>Manufacturer Part Number</b>                 | 60022755         |
| <b>Model</b>                                    | G 357 H          |
| <b>Valve design</b>                             | Lever valve      |
| <b>Max. idle speed</b>                          | 38000 rpm        |
| <b>Min./max. idle speed</b>                     | 0-38000 rpm      |
| <b>Power output</b>                             | 320 W            |
| <b>Air consumption</b>                          | 7.5 l/s          |
| <b>Connection thread</b>                        | G 1/4 inch       |
| <b>Sound-pressure level</b>                     | 73 dB            |
| <b>Length</b>                                   | 170 mm           |
| <b>Diameter of housing</b>                      | 39 mm            |
| <b>Collet chuck diameter</b>                    | 6 mm             |
| <b>Suitable for max. sanding block diameter</b> | 16 mm            |
| <b>Max. HM rotating milling cutter diameter</b> | 10 mm            |
| <b>Weight</b>                                   | 0.5 kg           |
| <b>Gross Weight</b>                             | 1.565 kg         |
| <b>Product Group</b>                            | 7AA              |

### EAN

4251757301063