

TECHNICAL DATASHEET

Update : 26/02/2019

FINE PITCH METRIC TAP - RIGHT HAND THREAD - HSSE 3% VANADIUM - MULTI-



Description

Fine pitch metric thread . Through hole tap



Characteristics

Ref.	EAN	Threading	Threading diameter mm	Thread mm	Capacity length mm	Tail diameter mm	Total length mm	Body material	Din standard	Square drive adapter mm	Tolerance
861841		Metric fine	M6	0,75	14	4,5	80	HSSE 3% Vanadium	374	3,4	6H
861842		Metric fine	M8	1	22	6	90	HSSE 3% Vanadium	374	4,9	6H
861843		Metric fine	M10	1	20	7	90	HSSE 3% Vanadium	374	5,5	6H
861844		Metric fine	M12	1	22	9	100	HSSE 3% Vanadium	374	7	6H
861845		Metric fine	M12	1,5	22	9	100	HSSE 3% Vanadium	374	7	6H
861846		Metric fine	M16	1,5	22	12	100	HSSE 3% Vanadium	374	9	6H
861847		Metric fine	M20	1,5	25	16	125	HSSE 3% Vanadium	374	12	6H