

FELLER GMBH

A-2525 GUENSELSDORF, AUSTRIA - TEL.: .. 43(2256) 62 32 50 - FAX: .. 43 (2256) 62 32 57
e-mail: sales@feller-at.com <http://www.feller-at.com>

Description: C14G-HARSJT3X14 (1,5)AWG-C13M/1,00M SW9005

Rating of cord set: ENEC 10A/250Vac UL/CSA 15A/250Vac

1. PLUG: Type C14G

Interconnection coupler according to : EN/IEC 60320-2-2/E, UL 817, C22.2No.21
Rated current and voltage : 10 A, 250 V AC
15 A, 250 V AC (USA, CANADA)
Plugbase : PPO GFR
Pins : solid brass, nickel-plated, crimped
Pins dimension : 4,00mm x 2,00mm
Outer mold : PVC compound, hardness Shore A75-77
Approvals : CE, ENEC, UL, CSA
SCIP database : f11f2d33-0014-4c1e-afbc-cfccfbf97c1c

2. CORD: Type HARSJT3x14 (1,5)AWG BLACK

Flexible cord according to : UL62, CSA 22.2No49, 227 IEC53, ÖVE K41a, HD21.S2, JISC 3306-1987, AS3191, GB/T 5023.5-2008/IEC 60227-5:2003, K60227-5
Marked : *JF*<ÖVE><HAR>H05VVF3G1, 5mm2*N1095*CE*UL*E41542
*SJT*3X14AWG*(2.08mm2)*75C*300V*FT2*CSA
*CCC*A014300*60227 IEC53 (RVV) 300/500V 3x1,5mm2
KTL SW01001-2001A<PS>E*JET*HVCTF3X2,0mm2*75C
Number of cores : 3
Conductor construction : 41x0,25 mm O.D. 1,84mm
Conductor insulation : Extruded PVC O.D. 3,40mm
Jacket : Extruded PVC O.D. 9,20mm +/- 0,30mm
Resistance of conductors : max. 8,88 Ω /km
Temperature resistance : UL -20°C to +75°C / HAR -20°C to +70°C
Dielectric strength : 2kVac, 1min.
Insulation resistance : >0,010 M Ω /km
Colour of conductors : yellow/green, brown, blue
Approvals : HARMONIZED, ÖVE, UL, CSA

3. CONNECTOR: Type C13M

Molded connector according to : EN/IEC 60320/C13, UL817, C22.2 No. 21
Rated current and voltage : 10 A, 250 V AC
15 A, 250 V AC (USA, Canada)
Construction : double insulation, contacts crimped
Contacts of the connection : self-adjusting phosphor bronze CuSn6
Inner insulation : PPO GFR
Outer mold : PVC compound, hardness Shore A 75-77
Approvals : CE, ENEC, UL, CSA

Environmental conformity


: EU-Directive 2012/19/EU (WEEE)
EU-Directive 2011/65/EU
EU-Directive 1907/2006 EG (REACH -compliant)

TESTING

Electrical testing : 100%
Visual inspection : 100%
High pot test wire to wire : 3kVac for 2 sec.
Continuity test : 25Aac to grounding / 20Aac to line and neutral
Polarity test : yes
Skin high pot test : 6kVac line to skin

design subject to change without prior notice, except written agreements with customer

DATE of ISSUE:	January, 2024	
REV:	ORIG:	DG



Feller Type: C14G-HARSJT3X14(1,5)AWG-C13M/1,00M SW9005

PN: 88F360

All dimensions in mm

31.01.2024

DG

RoHS compliant

FELLER 

A-2525 Günselsdorf, Austria

Telefon 0043-2256-62325-0

Fax: 0043-2256-62325-7

email: sales@feller-at.com

<http://www.feller-at.com>