

SIPLUS S7-400 MC RAM 16 MB -25 ... +70 DEGREES C WITH CONFORMAL COATING BASED ON 6ES7952-1AS00-0AA0 . RAM MEMORY CARD FOR S7-400, LONG VERSION 16 MBYTES



Figure similar

Memory	
Type of memory	RAM
Memory size	16 Mbyte
Ambient conditions	
Ambient temperature in operation	
• Min.	-25 °C; = Tmin
• max.	70 °C; = Tmax
Extended ambient conditions	
• Relative to ambient temperature-atmospheric pressure-installation altitude	Tmin ... Tmax at 1080 hPa ... 795 hPa (-1000 m ... +2000 m) // Tmin ... (Tmax - 10K) at 795 hPa ... 658 hPa (+2000 m ... +3500 m) // Tmin ... (Tmax - 20K) at 658 hPa ... 540 hPa (+3500 m ... +5000 m)
Relative humidity	
— With condensation, max.	100 %; Relative humidity, incl. condensation / frost permitted (no commissioning under condensation conditions)
Resistance	
— against biologically active substances / conformity with EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna). The supplied connector covers must remain on the unused interfaces during operation!
— against chemically active substances / conformity with EN 60721-3-3	Yes; Class 3C4 incl. salt spray according to EN 60068-2-52 (degree of severity 3). The supplied connector covers must remain on the unused interfaces during operation!
— against mechanically active substances / conformity with EN 60721-3-3	Yes; Class 3S4 incl. sand, dust. The supplied connector covers must remain on the unused interfaces during operation!
Accessories	
belongs to product	S7-400

Weights

Weight, approx.

54 g

last modified:

12.03.2015