

PE platform trolley

Application:

For transporting products which must be protected against damage from electric discharges.

Execution:

- Modular system, entirely screwed
- Steel tube/profile steel welded

Advantage:

- Reliable dissipation of electric charges thanks to continuously conductive structure
- Robust design for extremely high load capacity
- High-quality rollers ensure outstanding mobility and very light running even under heavy loads
- Robust design and high load capacity ensure a long service life even when used for industrial loads



Art. no.	50268 635
Brand	FETRA
Manufacturer Part Number	9500
Material of loading surface	Wood, electroconductive
Load-carrying capacity	500 kg
Length	970 mm
Width	509 mm
Height	950 mm
Loading surface length	850 mm
Loading surface size	850 x 500 mm
ESD-capable	Yes
Loading-surface height	235 mm
Loading-surface width	500 mm
Length x width x height	970 x 509 x 950 mm
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
With wheel lock	Yes
Total stop optional	Yes
Wheel diameter	160 mm
Material of wheel	TPE-ESD
Colour	Slate grey RAL 7015
Surface	Powder-coated
Gross Weight	24.000 kg
Product Group	5AB

EAN

4017976195001