

Drill/counter sink milling cutter, 90°, with Weldon shank

For AP... indexable milling inserts T003..

ATORN[®]

Application


For drilling/countersinking in all materials.

Version

- With Weldon shank
- Wear-resistant, nickel-plated version
- Robust supports
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm

Advantage

- High cutting performance
- Safe chip removal thanks to positive cutting geometry



Art. No.	16017 053
Cutting edge diameter	25 mm
Clearance length	50 mm
Length	150 mm
Shaft diameter	25 mm
max. ap	19 mm
Number of cutting edges	2 PCS
Number of cutting inserts	3 PCS
Suitable indexable insert no.	21

EAN-Code

4050293113389