

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: SURVEY LINE - ALL COLOURS

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC9a: Coatings and paints, thinners, paint removers.

1.3. Details of the supplier of the safety data sheet

Company name: EVERBUILD BUILDING PRODUCTS LTD
SITE 41, KNOWSTHORPE WAY
CROSS GREEN INDUSTRIAL ESTATE
LEEDS
WEST YORKSHIRE
LS9OSW
ENGLAND

Tel: 0044 113 240 3456

Fax: 0044 113 240 0024

Email: sds@everbuild.co.uk

1.4. Emergency telephone number

Emergency tel: 0044 113 240 3456 (office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: F+: R12; Xi: R36; -: R52/53; -: R66; -: R67

Classification under CLP: STOT SE 3: H336; Aquatic Chronic 3: H412; Eye Irrit. 2: H319; Flam. Aerosol 1: H222; -: H229

Most important adverse effects: Extremely flammable. Irritating to eyes. Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness.

2.2. Label elements

Label elements under CLP:

Hazard statements: H222: Extremely flammable aerosol.
H229: Pressurised container: May burst if heated
H319: Causes serious eye irritation.
H336: May cause drowsiness or dizziness.
H412: Harmful to aquatic life with long lasting effects.

Signal words: Danger

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 2

Hazard pictograms: GHS02: Flame
GHS07: Exclamation mark



Precautionary statements: P211: Do not spray on an open flame or other ignition source.
P251: Pressurized container: Do not pierce or burn, even after use.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P304+340: IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312: Call a POISON CENTER or doctor if you feel unwell.
P210: Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P261: Avoid breathing vapours/spray.
P264: Wash contaminated skin thoroughly after handling.
P271: Use only outdoors or in a well-ventilated area.
P273: Avoid release to the environment.
P337+313: If eye irritation persists: Get medical attention.
P403+233: Store in a well-ventilated place. Keep container tightly closed.
P405: Store locked up.
P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.
P501: Dispose of contents/container to hazardous waste point.

Label elements under CHIP:

Hazard symbols: Extremely flammable.
Irritant.



Risk phrases: R12: Extremely flammable.
R36: Irritating to eyes.
R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66: Repeated exposure may cause skin dryness or cracking.
R67: Vapours may cause drowsiness and dizziness.

Safety phrases: S2: Keep out of the reach of children.
S29: Do not empty into drains.
S51: Use only in well-ventilated areas.

Precautionary phrases: Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

[cont...]

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 3

Do not spray on a naked flame or any incandescent material. Keep away from sources of ignition - No smoking. Keep out of the reach of children.

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

ACETONE

EINECS	CAS	CHIP Classification	CLP Classification	Percent
200-662-2	67-64-1	F: R11; Xi: R36; -: R66; -: R67	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	10-30%

BUTANE

203-448-7	106-97-8	F+: R12 Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	10-30%
-----------	----------	---	-------------------------------------	--------

ETHYL METHYL KETONE

201-159-0	78-93-3	F: R11; Xi: R36; -: R66; -: R67	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	10-30%
-----------	---------	---------------------------------	--	--------

PROPANE

200-827-9	74-98-6	F+: R12 Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	10-30%
-----------	---------	---	-------------------------------------	--------

ETHYL ACETATE - REACH registered number(s): 01-2119475103-46-XXXX

205-500-4	141-78-6	F: R11; Xi: R36; -: R66; -: R67	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	1-10%
-----------	----------	---------------------------------	--	-------

LOW BOILING POINT NAPHTHA - UNSPECIFIED - SOLVENT NAPHTHA (PETROLEUM), LIGHT AROM.

265-199-0	64742-95-6	Xn: R65; -: R10; Xi: R37; N: R51/53	Asp. Tox. 1: H304; Flam. Liq. 3: H226; STOT SE 3: H335; Aquatic Chronic 2: H411	1-10%
-----------	------------	-------------------------------------	---	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water. For persistent irritation seek medical advice.

Eye contact: Bathe the eye with running water for 15 minutes. Make sure contact lenses are removed before rinsing. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

[cont...]

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 4

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing. Drowsiness or mental confusion may occur.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder. Use water spray to cool containers. Do not use water jet.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Highly flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture. Vapour may travel considerable distance to source of ignition and flash back. Bursting aerosols can be forcibly projected from a fire.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks. Refer to section 13 of SDS for suitable method of disposal.

[cont...]

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 5

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.
Do not handle in a confined space. Avoid the formation or spread of mists in the air.
Smoking is forbidden. Use non-sparking tools.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area.
Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ACETONE

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1210 mg/m ³	3620 mg/m ³	-	-

BUTANE

UK	1450 mg/m ³	1810 mg/m ³	-	-
----	------------------------	------------------------	---	---

ETHYL METHYL KETONE

UK	600 mg/m ³	899 mg/m ³	-	-
----	-----------------------	-----------------------	---	---

PROPANE

UK	1800 mg/m ³	7200 mg/m ³	-	-
----	------------------------	------------------------	---	---

ETHYL ACETATE

UK	200 ppm	400 ppm	-	-
----	---------	---------	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

[cont...]

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 6

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Aerosol

Colour: Various

Odour: Characteristic odour

Solubility in water: Insoluble

Also soluble in: Most organic solvents.

Boiling point/range°C: <=35

Flammability limits %: lower: 1.8

upper: 9.5

Flash point°C: -40

Autoflammability°C: 410-580

Relative density: 1.2-1.3

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids. Strong bases.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

[cont...]

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 7

Hazardous ingredients:

ACETONE

IVN	RAT	LD50	5500	mg/kg
ORL	MUS	LD50	3000	mg/kg
ORL	RAT	LD50	5800	mg/kg

ETHYL ACETATE

DERMAL	RBT	LD50	>20000	mg/kg
ORAL	RAT	LD50	6100	mg/kg
ORAL	RBT	LD50	4934	mg/kg
VAPOURS	RAT	4H LC50	29.3	ppmV

LOW BOILING POINT NAPHTHA - UNSPECIFIED - SOLVENT NAPHTHA (PETROLEUM), LIGHT AROM.

ORL	RAT	LD50	8400	mg/kg
-----	-----	------	------	-------

Relevant effects for mixture:

Effect	Route	Basis
Irritation	OPT	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing. Drowsiness or mental confusion may occur.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

ACETONE

BLUEGILL (<i>Lepomis macrochirus</i>)	LC50	8300	mg/l
---	------	------	------

ETHYL ACETATE

Daphnia magna	48H EC50	3090	mg/l
Pimephales promelas (Fat-head Minnow)	96H LC50	230	mg/l

12.2. Persistence and degradability

Persistence and degradability: No data available.

[cont...]

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 8

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: Volatile.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Harmful to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company. Dispose of according to local or national legislation

Waste code number: 16 05 04

Disposal of packaging: Make sure containers are empty before discarding (explosion risk). Do not puncture or incinerate even when empty. Dispose of waste and residues in accordance with local authority requirements

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS

14.3. Transport hazard class(es)

Transport class: 2

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Tunnel code: D

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

[cont...]

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 9

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.

H220: Extremely flammable gas.

H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H226: Flammable liquid and vapour.

H229: Pressurised container: May burst if heated

H304: May be fatal if swallowed and enters airways.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

R10: Flammable.

R11: Highly flammable.

R12: Extremely flammable.

R36: Irritating to eyes.

R37: Irritating to respiratory system.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65: Harmful: may cause lung damage if swallowed.

R66: Repeated exposure may cause skin dryness or cracking.

R67: Vapours may cause drowsiness and dizziness.

Legend to abbreviations: PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

IC50 = median inhibitory concentration

[cont...]

SAFETY DATA SHEET
SURVEY LINE - ALL COLOURS

Page: 10

dw = dry weight
bw = body weight
cc = closed cup
oc = open cup
MUS = mouse
GPG = guinea pig
RBT = rabbit
HAM = hamster
HMN = human
MAM = mammal
PGN = pigeon
IVN = intravenous
SCU = subcutaneous
SKN = skin
DRM = dermal
OCC = ocular/corneal
PCP = physico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.