

PLUG-IN RELAY COMPACT UNIT 115V AC, 2 CO LED
MODULE RED SOCKET W. LOGIC ISOLATION PLUG-
IN TERMINAL (PUSH-IN)

General technical data:

Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
Type of voltage		AC
Control supply voltage		
• with AC		
— at 50 Hz Rated value		
— minimum	V	115
— maximum	V	115
— at 60 Hz Rated value		
— minimum	V	115
— maximum	V	115
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		2
Operating current of the auxiliary contacts		
• at AC-15		
— at 230 V	A	2.5
Design of the switching function positively driven		No
Switching behavior		monostable

Mechanical data:

Type of electrical connection		spring-loaded terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		Yes
Width	mm	15.5
Height	mm	71
Depth	mm	98

Certificates/ approvals:

[Declaration of Conformity](#)

Further information

Industry Mall (Online ordering system)<http://www.siemens.com/industrymall>**Cax online generator**<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=LZS:RT4D4S15>**Information- and Downloadcenter (Catalogs, Brochures,...)**<http://www.siemens.com/industrial-controls/catalogs>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/LZS:RT4D4S15>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=LZS:RT4D4S15&lang=en

last modified:

15.01.2015