



ATEX compliant products



SMC - provide products compliant to ATEX Directive

■ Outline of ATEX directive

Since 1st July 2003, equipment used in potentially explosive atmospheres within the EU is required to comply with the ATEX directive.

● ATEX, New Approach directives and CE marking

Directive 94/9/EC, known as ATEX directive, is one of the directives based on the New Approach towards technical harmonization and standardization.

The New Approach is a new regulatory technique and strategy laid down by the European Council Resolution of 1985, in order to allow free movement of goods within the EU market and to prevent barriers to trade.

Products in compliance with all provisions of applicable directives (such as Directive 94/9/EC for ATEX) must bear the CE marking. This is an indication that the products comply with the requirements of applicable directives and have been subjected to the conformity assessment procedure provided for in these directives.

● ATEX definitions

Potentially explosive atmospheres are atmospheres likely to become explosive due to local and operational conditions.

The ATEX directive regards explosive atmospheres which are defined as *mixtures with air, under atmospheric conditions, of flammable substances in the form of gases, vapors, mists or dusts in which, after ignition has occurred, combustion spreads to the entire unburned mixture.* (Quotation from Directive 94/9/EC, Article 1.)


Certified equipment is designed to prevent the generation of ignition sources such as: Electric sparks, arcs and flashes, electrostatic discharges, electromagnetic waves, ionizing radiation, hot surfaces, flames and hot gases, mechanically generated sparks, optical radiation, chemical flame initiation, compression.

● Zone Classification

Potentially explosive environments are classified into zones in accordance with Directive 1999/92/EC.

These are:

- 0, 1, 2 for gas explosive atmospheres
- 20, 21, 22 for dust explosive atmospheres



■ New elements at a glance



Previous legislation covered the most obvious sources of ignition generated by electrical devices.

The ATEX directive and the corresponding harmonized standards have extended the applicability of legislation to non-electrical products as well.

Pneumatic equipment used in potentially explosive atmospheres must, therefore, be assessed in line with the new directive.

The ATEX directive defines categories of equipment and protective systems, which can be used in the corresponding zones as per the following table.

Zone		Equipment category	Presence of the explosive atmosphere
Gas	Dust		
0	20	1	Continuously or for long periods >1000 hours/year
1	21	2	Occasionally 10-1000 hours/year
2	22	3	Rarely or for short periods <10 hours/year



●ATEX label example and explanation

SMC CORPORATION
4-14-1 Soto-Kanda
Chiyoda-ku
Tokyo 101-0021, Japan

Do not un-plug when energized

II 3 G / D


Ex nA II T6 X

VQCxxx
HO
Tamb =-10°C to +50°C
IP65
T 80°C

Part-number
Year
Operating temperature
IP (only for Dust)
T temperature(only for Dust)

II 2 GDc

70°C(T6)Ta-10 to 40°C
90°C(T5)Ta 40 to 60°C
Tech. File No.C95-TD0002H SMC UK
Vincent Avenue, Crownhill,
Milton Keynes



"Do not un-plug when energized"

ATEX compliance

Group	II			
Category	1	2	3	
Atmosphere*	G	D	G	D
*G=Gas D=Dust				

Max. Surface temperature

T1	450°C
T2	300°C
T3	200°C
T4	135°C
T5	100°C
T6	85°C

	Category	Standards for Electrical product	Standards for Non-electrical product
General requirements	all	EN60079-0	EN13463-1
Dust protection	all	EN61241-0	EN13463-1
Types of Protection			
Constructional safety "c"	2		EN13463-5
Types of Protection "n"	3	EN60079-15	
Increased Safety "e"	2	EN60079-7	
Encapsulation "m"	2	EN60079-18	
Flameproof Enclosure "d"	2	EN60079-1	EN13463-3
Oil Immersion "o"	2	EN60079-6	
Pressurized "p"	2	EN60079-2	EN13463-7
Powder Filling "q"	2	EN60079-5	
Intrinsically Safety "ia"	1	EN60079-11	
Intrinsically Safety "ib"	2	EN60079-11	

X = means that special conditions for use are in the installation manual e.g. protect products against impact

INDEX

Actuator

55-C76 Air Cylinder	P. 01
55-C85 Air Cylinder	P. 03
55-C95 Air Cylinder	P. 05
55-CP95 Air Cylinder	P. 07
55-CG1 Air Cylinder	P. 09
55-CS1 Air Cylinder	P. 11
55-(E)CQ2 Compact Cylinder	P. 13
55-C55 Compact Cylinder	P. 15
55-CXS Dual Rod Cylinder	P. 17
55-MY1B Mechanically Rodless Cylinder	P. 19
55-MY1M Mechanically Rodless Cylinder	P. 20
55-MY1H Mechanically Rodless Cylinder	P. 21

Rotary Actuator

55-CRB1 Rotary Actuator	P. 23
55-CRB2 Rotary Actuator	P. 25
55-CRBU2 Rotary Actuator	P. 27
55-C(D)RQ2 Rotary Actuator	P. 29
56-C(D)RB1 Rotary Actuator	P. 31
56-C(D)RB2 Rotary Actuator	P. 33
56-C(D)RBU2 Rotary Actuator	P. 35
Auto Switches	P. 37
Instruments	
56-IP200 Pneumatic Cylinder Positioner	P. 54
55/56-IP5000/5100 Pneumatic Positioner	P. 55
IP6000/6100-X14 Elec. Pneumatic Positioner	P. 56
IP8000/8100-X14 Elec. Pneumatic Positioner	P. 59
52-IP8001/8101 Smart Positioner	P. 63

Others

56-PA3000/5000 Process Pump	P. 67
55-PA3000/5000 Process Pump	P. 68
56-VBA Booster Regulator	P. 69
56-IS1000 Pressure switch	P. 71

Directional Valves

52-SY 5 Port Solenoid Valves	P. 74
56-VQC 5 Port Solenoid Valves	P. 96
56-EX250 Serial Transmission	P.111
56-EX500 Serial Transmission	P.112
VCC 2/3 Port Air operated Valves	P.114
56-VND 2 Port Steam Valves	P.120
55-LVA Chemical valves	P.121

Safety Precautions

Safety Instructions	P.129
---------------------	-------

Out of scope

SMC products "out of scope"	P.131
-----------------------------	-------

ATEX Compliant

Air cylinder/ Double acting Series 55-C76

∅32, ∅40

How to order

55 - CD76 **W** **E** 32 - 50 **C** - XC6

ATEX category 2

Built-in magnet

-	None
D	Built-in magnet

Type

-	Standard
W*	Double rod
K**	Non-rotating rod

* Only with "E" option.
** Only with rubber bumper and "E" option.

Mounting

E	Double end type
F*	Front nose type
Y*	Front nose in line type

* Except for air cushion type.

Bore size

32	32mm
40	40mm

Special

-	Standard
XC6A	Stainless steel piston rod and rod-end nut
XC6B	Stainless steel piston rod, rod-end nut and mounting nut
XC22	Fluoro rubber seals (Only with rubber cushion type) (Not available with "K", non rotating rod option)

Cushion

-	Rubber cushion
C	Air cushion (only "E" execution) ^{Note 1)}

Note 1) Not available with "K" non rotating rod option

Standard Stroke

Bore size	Standard stroke (mm)
32mm	10, 25, 40, 50, 80, 100
40mm	125, 160, 200, 250, 300

Mounting Bracket Part No.

Mounting bracket		Bore size (mm)	
		32	40
Mounting bracket	Flange, Foot (1pc.)	C76F32A	C76F40A
	Flange, Foot (2 pcs. with mounting nut 1 pc.)	C76F32B	C76F40B
	Trunnion	C76T32	C76T40
	Clevis	C76C32	C76C40
Accessories	Single knuckle joint	KJ10DA	KJ12DA
	Double knuckle joint	GKM10-20A	GKM12-24A
	Floating joint	JA25-10-150	JA40-12-175

For 55-CD76

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-A73(H), A80(H), F7P(V), C73, C80, and H7A2, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.		Electrical entry	Indicator	Wiring (Output)	Load voltage			Lead wire* (m)			Applicable load	
	Rail mounting	Band mounting				DC	AC	0.5 (-)	3 (L)	5 (Z)			
Reed auto switch	D-A73□-588	-	Grommet (Perpendicular entry)	Yes	2-wiring	24V	12V	-	●	●	●	Relay PLC	
	D-A80□-588			No		24V or less	48V	48V or less	●	●	-		IC circuit
	D-A73H□-588	D-C73□-588	Yes	24V		12V	-	●	●	●	-		IC circuit
	D-A80H□-588	D-C80□-588	No	24V or less		48V	48V or less	●	●	-	IC circuit		
Solid state auto switch	D-F7PV□-588	-	Grommet (Perpendicular entry)	Yes	3-wiring (PNP)	24V	5V, 12V	-	●	●	○	IC circuit	
	D-F7P□-588								D-H7A2□-588	●	●		○

- Lead wire length 0.5m --- Nil (e.g.) D-A73-588
- 3 m --- L (e.g.) D-A73L-588
- 5 m --- Z (e.g.) D-A73Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

Note 2) When mounting an auto switch on a 55-series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

When ordering a band mounting type auto switch, also order a mounting bracket from the following list at the same time.

Auto switch mounting bracket/ Part no. (Band mounting type)

Auto switch Model	Tube I.D. (mm)	
	32	40
D-C73□-588		
D-C80□-588	BM2-032	BM2-040
D-H7A2□-588		

ATEX Compliant Air Cylinder Standard *Series 55-C76*




Specifications

Bore size	ø32	ø40
ATEX category ¹⁾	CE Ex II 2GDc 90°C (T5) Ta -10°C to 40°C 110°C (T4) Ta 40°C to 60°C	
Action	Double acting	
Fluid	Air	
Proof pressure	1.5MPa	
Max. operating pressure	1.0MPa	
Min. operating pressure	0.05MPa	
Ambient and fluid temperature	-10 to 60°C (No freezing)	
Lubrication	Not required (Non-lube)	
Operating piston speed	50 to 1000 mm/s	
Allowable stroke tolerance	0/+1.4	
Cushion	Rubber cushion, Air cushion	
Port size	G1/8	G1/4
Mounting	Double end, Front nose, Front nose in line	


Symbol

Standard: Double Action


Rubber Cushion
Single Rod




Rubber Cushion
Double Rod




Air Cushion
Single Rod



Air Cushion
Double Rod



Non-rotating rod: Double Acting/Single Rod



Note 1) This cylinder can be used in zones 1 and 21 and in zones 2 and 22.
If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zones 2 and 22 and not in zones 1 and 21.

Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.


Simple Specials -XA (Change of rod end shape) as detailed for the equivalent standard Non-Atex range of C76 series

ATEX Compliant

ISO Cylinder/Double Acting Series 55-C85

ø8, ø10, ø12, ø16, ø20, ø25

How to Order



* Not available with air cushion.
** Other strokes available on request.

Mounting Bracket Part No.

Bore (mm)	8	10	12	16	20	25
Bracket						
Foot (1 pc.)	C85L10A	C85L16A	C85L25A			
Foot (2 pcs. with mounting nut 1 pc.)	C85L10B	C85L16B	C85L25B			
Flange	C85F10	C85F16	C85F25			
Trunnion	C85T10	C85T16	C85T25			
Clevis	C85C10	C85C16	C85C25			
Single knuckle joint	KJ4D	KJ6D	KJ8D	KJ10D		
Double knuckle joint	GKM4-8	GKM6-10	GKM8-16	GKM10-20		
Floating joint	JA10-4-070	JA15-6-100	JA20-8-125	JA30-10-125		

Note) Please order mounting brackets separately.

ATEX Compliant ISO Cylinder/Standard **Series 55-C85**

For 55-CD85

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-A73(H), A80(H), F7P(V), C73, C80, and H7A2, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.		Electrical entry	Indicator	Wiring (Output)	Load voltage			Lead wire* (m)			Applicable load
	Rail mounting	Band mounting				DC	AC	0.5 (—)	3 (L)	5 (Z)		
Reed auto switch	D-A73□-588	—	Grommet (Perpendicular entry)	Yes	2-wiring	24V	12V	—	●	●	●	—
	D-A80□-588			No		24V or less	48V	48V or less	●	●	—	IC circuit
	D-A73H□-588	D-C73□-588	Grommet (In-line entry)	Yes		24V	12V	—	●	●	●	—
	D-A80H□-588	D-C80□-588		No		24V or less	48V	48V or less	●	●	—	IC circuit
Solid state auto switch	D-F7PV□-588	—	Grommet (Perpendicular entry)	Yes	3-wiring (PNP)	24V	5V, 12V	—	●	●	○	IC circuit
	D-F7P□-588								D-H7A2□-588	Grommet (In-line entry)	●	

- Lead wire length 0.5m --- Nil (e.g.) D-A73-588
- 3 m --- L (e.g.) D-A73L-588
- 5 m --- Z (e.g.) D-A73Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

Note 2) When mounting an auto switch on a 55- series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

When ordering a band mounting type auto switch, also order a mounting bracket from the following list at the same time.

Auto switch mounting bracket/ Part no. (Band mounting type)

Auto switch Model	Tube I.D. (mm)					
	8	10	12	16	20	25
D-C73□-588						
D-C80□-588	BJ2-008	BJ2-010	BJ2-012	BJ2-016	BM2-020	BM2-025
D-H7A2□-588						



Rubber Bumper/Single Rod



Air Cushion/Single Rod


Specifications

Bore size (mm)	8	10	12	16	20	25	
ATEX category ¹⁾	90°C (T5) Ta -10°C to 40°C 110°C (T4) Ta 40°C to 60°C						
Piston rod dia. (mm)	4	4	6	6	8	10	
Piston rod thread	M4 X 0.7	M4 X 0.7	M6 X 1	M6 X 1	M8 X 1.25	M10 X 1.25	
Ports	M5	M5	M5	M5	G1/8	G1/8	
Action	Double acting						
Fluid	Air						
Proof pressure	1.5MPa						
Max. operating pressure	1.0MPa						
Min. operating pressure	0.1MPa	0.08MPa			0.05MPa		
Ambient and fluid temperature	-10 to 60°C (no freezing)						
Cushion	Rubber bumper, Air cushion (Except for ø8)						
Lubrication	Not required (Non lube)						
Piston speed	50 to 750mm/s Rubber bumper, 50 to 1000mm/s Air cushion						
Allowable kinetic energy	Rubber bumper	0.02J	0.03J	0.04J	0.09J	0.27J	0.4J
	Air cushion	—	0.17J	0.19J	0.4J	0.66J	0.97J
Non-rotating accuracy	±1° 30'	±1° 30'	±1°	±1°	±0° 42'	±0° 42'	
Stroke tolerance (mm)	+1 / 0				+1.4 / 0		

Note 1) This cylinder can be used in zones 1 and 21 and in zones 2 and 22. If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zones 2 and 22 and not in zones 1 and 21.

Symbol


Double Acting/Single Rod



Rubber Bumper

Air Cushion


Double Acting/Double Rod



Rubber Bumper

Air Cushion

Non-rotating rod: Double Acting/Single Rod




Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

ATEX Compliant

ISO Cylinder/Standard/Double Acting Series 55-C95

Ø32, Ø40, Ø50, Ø63, Ø80, Ø100, Ø125, Ø160, Ø200, Ø250

How to Order



Model Selection

Execution	Model	Bore size										Adjustable Stroke End Cushioning	Piston Rod Options			
		32	40	50	63	80	100	125	160	200	250		Standard Hard Chrome	W	XC6	
Standard Type	55-C95 SB	●	●	●	●	●	●	●	●	●	●	●	●	●	○	○
	55-C95 SDB	●	●	●	●	●	●	●	●	●	●	●	●	●	○	○
With Mounting Centre Trunnion	55-C95 ST	●	●	●	●	●	●	●	●	●	●	●	●	●	○	○
	55-C95 SDT	●	●	●	●	●	●	●	●	●	●	●	●	●	○	○
Non-rotating piston rod	55-C95 KB	●	●	●	●	●	●	—	—	—	—	●	Note 3	○	●	
	55-C95 KDB	●	●	●	●	●	●	—	—	—	—	●	Note 3	○	●	

W = Double Rod
○ Options
● Standard

Note1) 55-C95 can be used in zones 1 and 21 and in zones 2 and 22.

Note2) If the 55-C95 cylinder is used with SMC category 3 type auto switch, then the 55-C95 cylinder can only be used in zones 2 and 22 and not in zones 1 and 21.

Note3) Piston rod material is stainless steel.

For 55-C95

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-A54□, A67□, and F5P□, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.	Electrical entry	Indicator	Wiring (Output)	Load voltage		Lead wire* (m)			Applicable load		
					DC	AC	0.5 (—)	3 (L)	5 (Z)	IC circuit	Relay PLC	
Reed auto switch	D-A54□-588	Grommet	Yes	2-wiring	24V	12V	—	●	●	●	—	Relay PLC
	D-A67□-588		No		24V or less	—	●	●	—	IC circuit		
Solid state auto switch	D-F5P□-588	Grommet	Yes	3-wiring (PNP)	24V	5V,12V	—	●	●	○	IC circuit	Relay PLC

• Lead wire length 0.5m --- Nil (e.g.) D-A54-588
3 m --- L (e.g.) D-A54L-588
5 m --- Z (e.g.) D-A54Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

When ordering a tie rod mounting type auto switch, also order a mounting bracket from the following list at the same time.

Auto switch mounting bracket/ Part no. (Tie rod mounting)

Auto switch Model	Tube I.D. (mm)						
	32,40	50,63	80,100	125	160	200	250
D-A54□-588							
D-A67□-588	BT-03	BT-05	BT-06	BT-08	BT-16	BT-16	BT-20
D-F5P□-588							

Note 2) When mounting an auto switch on a 55- series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

ATEX Compliant ISO Cylinder/Standard Series 55-C95




Specifications


Bore size	ø32	ø40	ø50	ø63	ø80	ø100	ø125	ø160	ø200	ø250
ATEX category	II 2GDc 95°C (T5) Ta -10°C to 40°C 115°C (T4) Ta 40°C to 60°C									
Action	Double acting									
Fluid	Air									
Proof pressure	1.5MPa									
Max. operating pressure	1.0MPa									
Min. operating pressure	0.05MPa									
Ambient and fluid temperature	-10 to 60°C (No freezing)									
Lubrication	Not required (Non-lube)									
Operating piston speed	50 to 1000 mm/s							50 to 700 mm/s	50 to 500 mm/s	
Allowable stroke tolerance	to 250: $+1.0_0$, 251 to 1000: $+1.4_0$ 1001 to 1500: $+1.8_0$, 1501 to 2000: $+2.2_0$, 2001 to 2400: $+2.6_0$									
Cushion	Both ends (Air cushion)									
Port size	G1/8	G1/4	G1/4	G3/8	G3/8	G1/2	G1/2	G3/4	G3/4	G1
Mounting	Basic, axial foot, front flange, rear flange, single rear clevis, double rear clevis, centre trunnion									

Symbol

Double Acting/
Single Rod




Double Acting/
Double Rod




Non-rotating rod:

Double Acting/
Single Rod



Double Acting/
Double Rod



Standard Stroke

Bore size (mm)	Standard stroke (mm)
32	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500
40	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500
50	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600
63	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600
80	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600, 700, 800
100	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600, 700, 800
125	Each stroke will be made to order
160	Each stroke will be made to order
200	Each stroke will be made to order
250	Each stroke will be made to order

(*) Please consult SMC for longer stroke.

Maximum Stroke

Bore size (mm)	Standard		Non-rotating (K)		XC6		XC14
	Single rod	Double rod	Single rod	Double rod	Single rod	Double rod	Single rod
32	1000	1000	500	500	1000	1000	1000
40	1900	1000	500	500	1700	1000	1900
50	1900	1000	600	600	1700	1000	1900
63	1900	1000	600	600	1700	1000	1900
80	1900	1000	800	800	1700	1000	1900
100	1900	1000	800	800	1700	1000	1900
125	2000	1000	-	-	1600	1000	2000
160	2000	1200	-	-	1600	1200	2000
200	2000	1200	-	-	1600	1200	2000
250	2400	1200	-	-	1500	1200	2400

(*) Please consult SMC for longer stroke.

Mounting Bracket, Mounting Accessories

Description	Bore size	ø32	ø40	ø50	ø63	ø80	ø100	ø125	ø160	ø200	ø250
L	Foot	L5032	L5040	L5050	L5063	L5080	L5100	L5125	L5160	L5200	L5250
F, G	Flange	F5032	F5040	F5050	F5063	F5080	F5100	F5125	F5160	F5200	F5250
C	Single rear clevis	C5032	C5040	C5050	C5063	C5080	C5100	C5125	C5160	C5200	C5250
D	Double rear clevis	D5032	D5040	D5050	D5063	D5080	D5100	D5125	D5160	D5200	D5250
DS	Double rear clevis (for ES accessory)	DS5032	DS5040	DS5050	DS5063	DS5080	DS5100	Note 5)			
ES	Angled rear clevis with ball joint	ES5032	ES5040	ES5050	ES5063	ES5080	ES5100				
E	Angled rear clevis	E5032	E5040	E5050	E5063	E5080	E5100				
GKM	Rod clevis ⁽²⁾	GKM10-20	GKM12-24	GKM16-32	GKM16-32	GKM20-40	GKM20-40				
KJ	Piston rod ball joint ⁽³⁾	KJ10D	KJ12D	KJ16D	KJ16D	KJ20D	KJ20D				
JA	Floating joint	JA30-10-125	JA40-12-125	JA50-16-150	JA50-16-150	JAH50-20-150	JAH50-20-150				

Note 1) Accessories for each mounting bracket are as follows.

Foot, Flange, Single clevis: Mounting bolts

Double rear clevis: (D,DS): Clevis pin

Note 2) GKM according to ISO 8140

Note 3) KJ according to ISO 8139

Note 4) Piston rod nut is standard

Note 5) Please consult SMC


Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

ATEX Compliant

ISO Cylinder/Standard/Double Acting Series 55-CP95

Ø32, Ø40, Ø50, Ø63, Ø80, Ø100, Ø125

How to Order



Model Selection

Execution	Model	Bore Size							Adjustable Stroke End Cushioning	Piston Rod Options		
		32	40	50	63	80	100	125		Standard Hard Chrome	W	XC6
Standard Type	55-CP95 SB	●	●	●	●	●	●	●	●	●	○	○
	55-CP95 SDB	●	●	●	●	●	●	●	●	●	○	○
Non-rotatin piston rod	55-CP95 KB	●	●	●	●	●	●	-	●	Note 3)	○	●
	55-CP95KDB	●	●	●	●	●	●	-	●	Note 3)	○	●

W = Double Rod
○ Options
● Standard

Note1) 55-C95 can be used in zones 1 and 21 and in zones 2 and 22.

Note2) If the 55-C95 cylinder is used with SMC category 3 type auto switch, then the 55-C95 cylinder can only be used in zones 2 and 22 and not zones 1 and 21.

Note3) Piston rod material is stainless steel.

For 55-CP95

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-Z73, Z80, Y7P, and Y7PV, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.	Electrical entry	Indicator	Wiring (Output)	Load voltage			Lead wire* (m)			Applicable load
					DC	AC		0.5 (-)	3 (L)	5 (Z)	
Reed auto switch	D-Z73□-588	Grommet (in-line)	Yes	2-wiring	24V	12V	—	●	●	●	—
	D-Z80□-588		No		24V or less	48V	48V or less	●	●	—	
Solid state auto switch	D-Y7P□-588	Grommet (in-line)	Yes	3-wiring (PNP)	24V	5V, 12V	—	●	●	○	IC circuit
	D-Y7PV□-588							Grommet (Perpendicular)	●	●	

* Lead wire length
0.5m --- Nil (e.g.) D-Z73-588
3 m --- L (e.g.) D-Z73L-588
5 m --- Z (e.g.) D-Z73Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

When ordering a direct mounting type auto switch, also order a mounting bracket from the following list at the same time.

Auto switch mounting bracket/ Part no. (Direct mounting type)

Auto switch Model	Tube I.D. (mm)
D-Z73□-588 D-Z80□-588 D-Y7P□-588 D-Y7PV□-588	32,40,50,63,80,100,125 BMP1-032

Note 2) When mounting an auto switch on a 55- series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

ATEX Compliant ISO Cylinder/Standard **Series 55-CP95**





Specifications

Bore size	ø32	ø40	ø50	ø63	ø80	ø100	ø125
ATEX category 1)	II 2GDc 95°C (T5) Ta -10°C to 40°C 115°C (T4) Ta 40°C to 60°C						
Action	Double acting						
Fluid	Air (Non-lube)						
Proof pressure	1.5MPa						
Max. operating pressure	1.0MPa						
Min. operating pressure	0.05MPa						
Lubrication	Not required (Non-lube)						
Ambient and fluid temperature	-10 to 60°C						
Operating piston speed	50 to 1000mm/s						50 to 700 mm/s
Allowable stroke tolerance	to 250: $+1.0_0$, 251 to 1000: $+1.4_0$, 1001 to 1500: $+1.8_0$, 1501 to 2000: $+2.2_0$						
Cushion	Both ends (Air cushion)						
Port size	G1/8	G1/4	G1/4	G3/8	G3/8	G1/2	G1/2
Mounting	Basic, axial foot, front flange, rear flange, single rear clevis, double rear clevis						

Symbol

Double Acting/
Single Rod



Double Acting/
Double Rod



Non-rotating rod:

Double Acting/
Single Rod

Double Acting/
Double Rod



Note 1) This cylinder can be used in zones 1 and 21 and in zones 2 and 22.
If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zones 2 and 22 and not in zones 1 and 21.

Standard Stroke

Bore size (mm)	Standard stroke (mm)
32	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500
40	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500
50	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600
63	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600
80	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600, 700, 800
100	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600, 700, 800
125	Each stroke will be made to order

(*) Intermediate strokes are available

Maximum Stroke

Bore size (mm)	Standard		Non-rotating (K)		XC6	
	Single rod	Double rod	Single rod	Double rod	Single rod	Double rod
32	1900	1000	500	500	1700	1000
40	1900	1000	500	500	1700	1000
50	1900	1000	600	600	1700	1000
63	1900	1000	600	600	1700	1000
80	1900	1000	800	800	1700	1000
100	1900	1000	800	800	1700	1000
125	2000	1000	-	-	-	-

Mounting Bracket, Mounting Accessories

Description	Bore size	ø32	ø40	ø50	ø63	ø80	ø100	ø125
L	Foot	L5032	L5040	L5050	L5063	L5080	L5100	L5125
F, G	Flange	F5032	F5040	F5050	F5063	F5080	F5100	F5125
C	Single rear clevis	C5032	C5040	C5050	C5063	C5080	C5100	C5125
D	Double rear clevis	D5032	D5040	D5050	D5063	D5080	D5100	D5125
DS	Double rear clevis (for ES accessory)	DS5032	DS5040	DS5050	DS5063	DS5080	DS5100	Note 5)
ES	Angled rear clevis with ball joint	ES5032	ES5040	ES5050	ES5063	ES5080	ES5100	
E	Angled rear clevis	E5032	E5040	E5050	E5063	E5080	E5100	
GKM	Rod clevis	GKM10-20	GKM12-24	GKM16-32	GKM16-32	GKM20-40	GKM20-40	
KJ	Piston rod ball joint	KJ10D	KJ12D	KJ16D	KJ16D	KJ20D	KJ20D	
JA	Floating joint	JA30-10-125	JA40-12-125	JA50-16-150	JA50-16-150	JAH50-20-150	JAH50-20-150	

Note 1) Accessories for each mounting bracket are as follows.

Foot, Flange, Single clevis: Mounting bolts
Double rear clevis: (D,DS): Clevis pin

Note 2) GKM according to ISO 8140

Note 3) KJ according to ISO 8139

Note 4) Piston rod nut is standard

Note 5) Please consult SMC

Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

ATEX Compliant

Air Cylinder/Standard/Double Acting Series 55-CG1

Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100

How to Order

55 - C D G1 W B N 20 TN

ATEX category 2

Built in magnet

-	None
D	Built-in magnet

Rod

-	Single rod
W	Double rod

Mounting

B	Basic
L	Axial foot
F	Front flange
G	Rear flange
U*	Front trunnion
T*	Rear trunnion
D	Clevis

* Not available for bore sizes Ø80 and Ø100.

Cushion

N	Rubber bumper
A	Air cushion

Bore size

20	20mm	50	50mm
25	25mm	63	63mm
32	32mm	80	80mm
40	40mm	100	100mm

Cylinder stroke (mm)

Bore size (mm)	Standard stroke (1) (mm)	Long stroke (2) (mm)
20	25, 50, 75, 100, 125, 150, 200	201 to 350
25		301 to 400
32		301 to 450
40	25, 50, 75, 100, 125, 150, 200, 250, 300	301 to 800
50/63		301 to 1200
80		301 to 1400
100		301 to 1500

Note 1) Other intermediate strokes can be manufactured upon receipt of order. Spacers are not used for the intermediate strokes.

Note 2) Long stroke applies to the axial foot and the front flange style. If other mounting brackets are used or the length exceeds the stroke limit, the stroke should be determined based on the stroke selection table in the technical data.

Thread type of port

Rubber bumper

-	Rc	Ø20-Ø100
TN	NPT	Ø20-Ø100
TF	G	Ø32-Ø100

Air cushion

-	M5x0.8	Ø20-Ø25
-	Rc	Ø32-Ø100
TN	NPT	Ø32-Ø100
TF	M5 X 0.8	Ø20-Ø25
TF	G	Ø32-Ø100


ATEX Compliant ISO Cylinder/Standard *Series 55-CG1*



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Symbol


Double Acting/Single Rod



Rubber Bumper

Air Cushion

Double Acting/Double Rod



Rubber Bumper

Air Cushion

Specifications

Bore size (mm)	20	25	32	40	50	63	80	100
ATEX category ¹⁾	II 2GDc 95°C (T5) Ta -10°C to 40°C 115°C (T4) Ta 40°C to 60°C							
Action	Double acting/Single rod							
Lubrication	Non-lube							
Fluid	Air							
Proof pressure	1.5MPa							
Max. operating pressure	1.0MPa							
Min. operating pressure	0.05MPa							
Ambient and fluid temperature	-10 to +60°C (No freezing)							
Piston speed	50 to 1000mm/s							50 to 700mm/s
Stroke tolerance	Up to 1000 ^{+1.4} ₀ mm, Up to 1200 ^{+1.8} ₀ mm							Up to 1000 ^{+1.4} ₀ mm Up to 1500 ^{+1.8} ₀ mm
Cushion	Rubber bumper/Air cushion							
Mounting*	Basic, Axial foot, Front flange, Rear flange, Front trunnion, Rear trunnion, Clevis (Used for changing the port location by 90 degrees.)							

* Front/Rear trunnion styles are not available for bore sizes ø80 and ø100.

Note 1) This cylinder can be used in zones 1 and 21 and in zones 2 and 22.
If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zones 2 and 22 and not in zones 1 and 21.

Accessories

Mounting		Basic	Axial foot	Front flange	Rear flange	Front trunnion	Rear trunnion	Clevis
Standard	Rod end nut	●	●	●	●	●	●	●
	Clevis pin	—	—	—	—	—	—	●
Option	Single knuckle joint	●	●	●	●	●	●	●
	Double knuckle joint** (With pins)	●	●	●	●	●	●	●
	Pivot bracket	—	—	—	—	●*	●*	●
	Rod boot	●	●	●	●	●	●	●

* Pivot bracket is not available for bore sizes ø80 and ø100.

** Pins and snap rings for double knuckle joint are included, not mounted.

Mounting Bracket Part No.

Mounting bracket	Bore size (mm)							
	20	25	32	40	50	63	80	100
Axial foot*	CG-L020	CG-L025	CG-L032	CG-L040	CG-L050	CG-L063	CG-L080	CG-L100
Flange	CG-F020	CG-F025	CG-F032	CG-F040	CG-F050	CG-F063	CG-F080	CG-F100
Trunnion	CG-T020	CG-T025	CG-T032	CG-T040	CG-T050	CG-T063	—	—
Clevis**	CG-D020	CG-D025	CG-D032	CG-D040	CG-D050	CG-D063	CG-D080	CG-D100
Pivot bracket	CG-020-24A	CG-025-24A	CG-032-24A	CG-040-24A	CG-050-24A	CG-063-24A	CG-080-24A	CG-100-24A

* Order two foot brackets per cylinder.

** Clevis pins, snap rings and mounting bolts are attached for the clevis.

*** Mounting bolts are attached for the foot type and the flange type.

ATEX Compliant

Air Cylinder/Standard/Double Acting Series 55-CS1

Non-lube: $\varnothing 125$, $\varnothing 160$, $\varnothing 180$, $\varnothing 200$, $\varnothing 250$, $\varnothing 300$

How to Order

55-CDS1 [] [L] [] [N] 160 — 300 [R]

ATEX category 2

Build in magnet

-	$\varnothing 125$ ~ $\varnothing 300$	Without magnet
D	$\varnothing 125$ ~ $\varnothing 200$	Built in magnet*

*(Aluminium tube)

Rod type

-	Single rod
W	Double rod

Mounting

B	Basic
L	Foot
F	Front flange
G	Rear flange
C	Single clevis
D	Double clevis
T	Centre trunnion

Mounting options for W type: B, L, F, T

Non-lube

Tube material

Symbol	Bore size	Tube material
-	$\varnothing 125$ to $\varnothing 160$	Aluminum tube
-	$\varnothing 180$ to $\varnothing 300$	Steel tube
F	$\varnothing 125$ to $\varnothing 160$	Steel tube

Table above applies to without magnet type

Rod boot/Cushion

Cushion	N	No cushion
	R	With cushion on rod side
	H	With cushion on head side
	-	With both sides cushion

Cylinder stroke (mm)
(Refer to following page for max. stroke table.)

Bore size

Non-lube	
125	125mm
140	140mm
160	160mm
180	180mm
200	200mm
250	250mm
300	300mm

Mounting Bracket Part No.

Bore size (mm)	125	140	160	180	200	250	300
Foot*	CS1-L12	CS1-L14	CS1-L16	CS1-L18	CS1-L20	CS1-L25	CS1-L30
Flange	CS1-F12	CS1-F14	CS1-F16	CS1-F18	CS1-F20	CS1-F25	CS1-F30
Single clevis	CS1-C12	CS1-C14	CS1-C16	CS1-C18	CS1-C20	CS1-C25	CS1-C30
Double clevis**	CS1-D12	CS1-D14	CS1-D16	CS1-D18	CS1-D20	CS1-D25	CS1-D30



* Order 2 foot brackets for one cylinder.

** When ordering the double clevis, the clevis pin and the cotter pin (2 pcs.) are attached.

For 55-CS1

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-A54, A67, and F5P, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.	Electrical entry	Indicator	Wiring (Output)	Load voltage		Lead wire* (m) ^{Note1)}			Applicable load		
					DC	AC	0.5 (-)	3 (L)	5 (Z)	IC circuit	Relay PLC	
Reed auto switch	D-A54□-588	Grommet	Yes	2-wiring	24V	12V	—	●	●			●
	D-A67□-588				24V or less	—	●	●	—	IC circuit		
Solid state auto switch	D-F5P□-588	Grommet	Yes	3-wiring (PNP)	24V	5V,12V	—	●	●	○	IC circuit	

- Lead wire length 0.5m --- Nil (e.g.) D-A54-588
- 3 m --- L (e.g.) D-A54L-588
- 5 m --- Z (e.g.) D-A54Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

When ordering a tie rod mounting type auto switch, also order a mounting bracket from the following list at the same time.

Auto switch mounting bracket/ Part no. (Tie rod mounting)

Auto switch Model	Tube I.D. (mm)			
	125,140	160	180	200
D-A54□-588				
D-A67□-588	BT-12	BT-16	BT-18A	BT-20
D-F5P□-588				


ATEX Compliant Air Cylinder/Standard *Series 55-CS1*



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.


Symbol

Double Acting/Single Rod



Air Cushion

Double Acting/Double Rod



Air Cushion

Specifications

Style	Non-lube
ATEX category ¹⁾	CE Ex II 2GDc 95°C (T5) Ta 0°C to 40°C 115°C (T4) Ta 40°C to 60°C
Fluid	Air (Non-lube)
Proof pressure ²⁾	1.57MPa
Max. operating pressure ²⁾	0.97MPa
Min. operating pressure	0.05MPa
Piston speed	50 to 500 mm/s
Cushion	None, air cushion
Ambient and fluid temperature	0 to 60°C (No freezing)
Stroke length tolerance (mm)	250 or less: $+1.0_0$, 251 to 1,000: $+1.4_0$, 1,001 to 1,500: $+1.8_0$ 1501 to 2000: $+2.2_0$
Mounting	Basic, Foot, Front flange, Rear flange, Single clevis, Double clevis, Centre trunnion

Note 1) This cylinder can be used in zones 1 and 21 and in zones 2 and 22.
If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zones 2 and 22 and not in zones 1 and 21.

Note 2) For the CDS1 diameter 180 and 200 the Proof pressure is 1.2MPa and the Max. operating pressure is 0.7MPa.

Accessories

Mounting		Basic	Foot	Front flange	Rear flange	Single clevis	Double clevis	Centre trunnion
Standard	Clevis pin, Cotter pin	—	—	—	—	—	●	—
	Rod end nut	●	●	●	●	●	●	●
Accessory	Single knuckle joint	●	●	●	●	●	●	●
	Double knuckle joint (Knuckle pin, Cotter pin)	●	●	●	●	●	●	●

(mm)

Max. Stroke	Without autoswitch				With autoswitch	
	Aluminum alloy		Carbon steel tube		Aluminium alloy	
	Basic Rear flange Single clevis Double clevis Centre trunnion	Foot Front flange	Basic Rear flange Single clevis Double clevis	Foot Front flange	B, G, C, D, T	L, F
125	1000 or less	1000 or less	1000 or less	1400 or less	1000 or less	1400 or less
140	1000 or less	1000 or less	1000 or less	1400 or less	1000 or less	1400 or less
160	1200 or less	1000 or less	1200 or less	1400 or less	1200 or less	1400 or less
180	—	—	1200 or less	1800 or less	1200 or less	1500 or less
200	—	—	1200 or less	1800 or less	998 or less	998 or less
250	—	—	1200 or less	2000 or less	-	-
300	—	—	1200 or less	2000 or less	-	-

ATEX Compliant

Compact Cylinder/Standard: Double Acting Single Rod Series 55-CQ2

ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160, ø180, ø200

How to Order

55- ATEX category 2

CDQ2 Port size

B Built-in magnet

20 Mounting

30 Stroke (mm)

D Action

Body option

—	Standard (Rod end female thread)
C	With rubber bumper
M	Rod end male thread

* Combination of body option is possible. (CM)
Note2) All large bore cylinder ø125 to ø200 have C (rubber bumper) as standard.

Bore size (mm)	Standard stroke (mm)	Long Stroke (mm)
12~16	5, 10, 15, 20, 25, 30	—
20, 25	5, 10, 15, 20, 25, 30, 35, 40, 45, 50	—
32~40	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100	125, 150, 175, 200, 250, 300
50~100	10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100	—
125~200	10, 20, 30, 40, 50, 75, 100, 125, 150, 175, 200, 250, 300	—

* Long strokes are only available with rubber bumpers.

B	Through-hole (Standard)	F	Front flange
A	Both ends tapped	G	Rear flange
L	Foot	D	Double clevis

*Only B type (Through-hole and both ends tapped) is available for large bore cylinder ø125 to ø200.

Bore size	
12	12mm
16	16mm
20	20mm
25	25mm
32	32mm
40	40mm
50	50mm
63	63mm
80	80mm
100	100mm
125	125mm
140	140mm
160	160mm
180	180mm
200	200mm

Mounting Bracket Part No.

Bore size (mm)	Foot (4)	Flange	Double clevis
12	CQ-L012	CQ-F012	CQ-D012
16	CQ-L016	CQ-F016	CQ-D016
20	CQ-L020	CQ-F020	CQ-D020
25	CQ-L025	CQ-F025	CQ-D025
32	CQ-L032	CQ-F032	CQ-D032
40	CQ-L040	CQ-F040	CQ-D040
50	CQ-L050	CQ-F050	CQ-D050
63	CQ-L063	CQ-F063	CQ-D063
80	CQ-L080	CQ-F080	CQ-D080
100	CQ-L100	CQ-F100	CQ-D100

Note 4) 2 pcs. per cylinder should be ordered when foot brackets are required.

Note 5) Each package contains the following parts.

Foot, Flange: Body mounting bolt
Double clevis: Clevis pin, C shape snap ring for axis, body mounting bolt

For 55-CDQ2

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-A73(H), A80(H), F7P(V), A93(V), A90(V), Z73, Z80, M9□(V) and Y7P(V), please refer to the relevant pages in Best Pneumatics. (Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.			Electrical entry	Indicator	Wiring (Output)	Load voltage		Lead wire* (m)			Applicable load	
	Rail mounting ø12 to ø160	Direct mounting ø32 to ø100	ø125 to ø200				DC	AC	0.5 (—)	3 (L)	5 (Z)		
Reed auto switch	D-A73□-588	D-A93V□-588	—	Grommet (Perpendicular entry)	Yes	2-wiring	24V	12V	—	●	●	●	Relay PLC
	D-A80□-588	D-A90V□-588	—	Grommet (In-line entry)	No		24V or less	48V	48V or less	●	●	—	
	D-A73H□-588	D-A93□-588	D-Z73□-588	Grommet (Perpendicular entry)	Yes	2-wire or 3-wire	24V	12V	—	●	●	●	
	D-A80H□-588	D-A90□-588	D-Z80□-588	Grommet (In-line entry)	No		24V or less	48V	48V or less	●	●	—	
Solid state auto switch	D-F7PV□-588	D-M9□V-588	D-Y7PV□-588	Grommet (Perpendicular entry)	Yes	2-wire or 3-wire	24V	5V, 12V	—	●	●	○	IC circuit
	D-F7P□-588	D-M9□-588	D-Y7P□-588	Grommet (In-line entry)	No					●	●	○	

* Lead wire length
0.5m --- Nil (e.g.) D-A73-588
3 m --- L (e.g.) D-A73L-588
5 m --- Z (e.g.) D-A73Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

When ordering a rail mounting type auto switch, also order a mounting bracket from the following list at the same time.

Auto switch mounting bracket/ Part no. (Rail mounting type)

Auto switch Model	Part no.
D-A73□-588, D-A73H□-588	BQ-2 (32-160)
D-A80□-588, D-A80H□-588	BQ-1 (12-25)
D-F7P□-588, D-F7PV□-588	

ATEX Compliant Compact Cylinder/Standard *Series 55-CQ2*

Style


Bore size (mm)		12	16	20	25	32	40	50	63	80	100	125	140	160	180	200		
Pneumatic	Mounting	Through-hole (Standard)	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
		Both ends tapped	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	Built-in magnet		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	Piping	Screw-in style	M5	M5	M5	M5	M5 ⁽¹⁾ G1/8	G1/8	G1/4	G1/4	G3/8	G3/8	G3/8	G3/8	G3/8	G3/8	G1/2	G1/2
			Rod end male thread	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
With rubber bumper		●	●	●	●	●	●	●	●	●	●	● ⁽²⁾						

Note 1) Among those without an auto switch, only the 5mm stroke uses M5 piping.

Note 2) Rubber bumper is standard for bore sizes over ø125.

JIS Symbol

Double Acting: Single Rod



Specifications

Bore size (mm)	12	16	20	25	32	40	50	63	80	100	125	140	160	180	200
ATEX category ¹⁾	CE  II 2GDC 85°C (T6) Ta -10°C to 40°C 105°C (T4) Ta 40°C to 60°C														
Style	Pneumatic (Non-lube)														
Fluid	Air														
Proof pressure	1.5MPa												1.05MPa		
Max. operating pressure	1.0MPa												0.7MPa		
Min. operating pressure	0.07MPa		0.05MPa												
Ambient and fluid temperature	-10°C to 60°C (No freezing)														
Cushion	None, rubber bumper										Rubber bumper				
Rod end thread	Male thread, Female thread														
Tolerance of stroke length (mm)	+1.0 0										+1.4 0				
Mounting	Through-hole, Both end tapped, Foot, Front flange, Rear flange, Double clevis										Through-hole both end tapped				
Piston speed	50 to 500mm/s												20 to 400 mm/s		

Note 1) This cylinder can be used in zones 1 and 21 and in zones 2 and 22.
 If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zones 2 and 22 and not in zones 1 and 21.

Note 2) Stroke length tolerance does not include the amount of bumper compression.


Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

ATEX Compliant

ISO Standards/Compact Cylinder Series 55-C55

ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100

How to Order



When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable Auto Switches

Auto switch conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

(Note: Reed auto switches for 100 VAC and 100 VDC are not within the specification.)

For detailed specifications on the A93(V), A90(V) and M9□(V), please refer to pages 37 and 53.

Type	Model	Electrical entry direction	Indicator light	Wiring (Output)	Load voltage			Lead wire length (m) *			Applicable load
					DC	AC		0.5(Nil)	3(L)	5(Z)	
Reed switch	D-A93V□-588	Grommet (Perpendicular)	Yes	2-wire	24 V	12 V	—	●	●	●	—
	D-A90V□-588		No		24 V or less	48 V	48 V or less	●	●	—	IC circuit
	D-A93□-588	Grommet (In-line)	Yes		24 V	12 V	—	●	●	●	—
	D-A90□-588		No		24 V or less	48 V	48 V or less	●	●	—	IC circuit
Solid state switch	D-M9V□-588	Grommet (Perpendicular)	Yes	2-wire or 3-wire	24 V	5 V, 12 V	—	●	●	○	IC circuit
	D-M9□-588	Grommet (In-line)	Yes					●	●	○	IC circuit

* Lead wire length symbols: 0.5 m Nil (Example) D-A93-588
 3 m L (Example) D-A93L-588
 5 m Z (Example) D-A93Z-588

* ○ solid state auto switch is available after receiving an order.

(Note) When mounting an auto switch on a 55-series (Category 2) model, the ATEX class of the cylinder with auto switch changes to category 3, which is the same class as the auto switch

ATEX Compliant Compact Cylinder *Series 55-C55*



Symbol

Double Acting/Single Rod



Specifications

Bore size (mm)	20	25	32	40	50	63	80	100
ATEX category	CE Ex II 2GDc 85°C(T6) Ta -10°C to 40°C 105°C(T4) Ta 40°C to 60°C							
Type	Pneumatic (Non-lube)							
Action	Double acting, Single rod							
Fluid	Air							
Proof pressure	1.5 MPa							
Maximum operating pressure	1.0 MPa							
Minimum operating pressure	0.05 MPa						0.03 MPa	
Ambient and fluid temperature	-10 to 60C (No freezing)							
Cushion	Rubber bumper on both end							
Stroke length tolerance	+1.0 mm 0							
Mounting	Through-hole/Both ends tapped common							
Piston speed	50 to 500 mm/s						50 to 300 mm/s	

Standard Stroke

Bore size (mm)	Standard stroke (mm)
20 to 63	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 60, 80, 100, 125, 150
80 to 100	10, 15, 20, 25, 30, 35, 40, 45, 50, 60, 80, 100, 125

Mounting Bracket Part No.

Bore size (mm)	Foot	Flange	Single clevis
20	C55-L020	C55-F020	C55-C020
25	C55-L025	C55-F025	C55-C025
32	C55-L032	C55-F032	C55-C032
40	C55-L040	C55-F040	C55-C040
50	C55-L050	C55-F050	C55-C050
63	C55-L063	C55-F063	C55-C063
80	C55-L080	C55-F080	C55-C080
100	C55-L100	C55-F100	C55-C100

- Order two foot brackets per cylinder.
- Parts belonging to each bracket are as follows.
Foot, Flange, Single clevis/Body mounting bolt

Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.


ATEX Compliant

Dual Rod Cylinder

Series 55-CXS/W

ø6, ø10, ø15, ø20, ø25, ø32

How to Order



For 55-CXS

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-Z73, Z80, Y7P, and Y7PV, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.	Electrical entry	Indicator	Wiring (Output)	Load voltage			Lead wire* (m)			Applicable load	
					DC	AC		0.5 (-)	3 (L)	5 (Z)		
Reed auto switch	D-Z73□-588	Grommet (In-line)	Yes	2-wiring	24V	12V	—	●	●	●	—	Relay PLC
	D-Z80□-588		No		24V or less	48V	48V or less	●	●	—		
Solid state auto switch	D-Y7P□-588	Grommet (In-line)	Yes	3-wiring (PNP)	24V	5V, 12V	—	●	●	○	IC circuit	Relay PLC
	D-Y7PV□-588	Grommet (Perpendicular)						●	●	○		

- Lead wire length 0.5m --- Nil (e.g.) D-Z73-588
- 3 m --- L (e.g.) D-Z73L-588
- 5 m --- Z (e.g.) D-Z73Z-588


Note 1) ○ solid state auto switch is available after receiving an order.

Note 2) When mounting an auto switch on a 55-series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

ATEX Compliant Dual Rod Cylinder *Series 55-CXS*



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.



CXS Specifications

Bore size (mm)	6	10	15	20	25	32
ATEX category ¹⁾	CE Ex II 2GDc		65°C (T6) Ta -10°C to 40°C 85°C (T6) Ta 40°C to 60°C			
Fluid	Air (Non-lube)					
Min. operating pressure	0.15MPa	0.1MPa		0.05MPa		
Max. operating pressure	0.7MPa					
Proof pressure	1.05MPa					
Ambient and fluid temperature	-10 to 60°C (No freezing)					
Piston speed	30 to 300 mm/s	30 to 800 mm/s	30 to 700 mm/s		30 to 600 mm/s	
Piping port	M5 X 0.8				G1/8	
Stroke adjustable range	0 to -5 mm to the standard stroke					
Bearing	Slide bearing, Ball bushing bearing (Same dimensions)					
Cushion	Rubber bumper					

CXSW Specifications

Bore size (mm)	6	10	15	20	25	32
ATEX category ¹⁾	CE Ex II 2GDc		65°C (T6) Ta -10°C to 40°C 85°C (T6) Ta 40°C to 60°C			
Fluid	Air (Non-lube)					
Min. operating pressure	0.15MPa		0.1MPa			
Max. operating pressure	0.7MPa					
Proof pressure	1.05MPa					
Ambient and fluid temperature	-10 to 60°C (No freezing)					
Piston speed	50 to 500mm/s					
Piping port	M5 X 0.8				G1/8	
Stroke adjustable range	0 to -10mm (Extension side: 5mm, Retraction side: 5mm)					
Bearing	Slide bearing, Ball bearing (Same dimensions)					
Cushion	Rubber bumper					

Note 1) This cylinder can be used in zones 1 and 21 and in zones 2 and 22.
If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zones 2 and 22 and not in zones 1 and 21.

ATEX Compliant

Mechanically Jointed Rodless Cylinder Series 55-MY1B

Basic Type/ø10, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100

How to Order

Basic Type

55-MY1B 25 300 XB11

Bore size	
10	10mm
16	16mm
20	20mm
25	25mm
32	32mm
40	40mm
50	50mm
63	63mm
80	80mm
100	100mm

ATEX category 2

Basic type

Piping thread

Symbol	Type	Bore size
-	M thread	ø10-ø20
-	Rc	ø25-ø100
TN	NPT	
TF	G	

Stroke

Refer to the standard stroke table below.

Special

-	Standard type
XB11	Long Stroke type

Piping


-	Standard type
G	Centralized piping type

Standard strokes

Bore size (mm)	Standard stroke (mm)	Max. stroke (mm)
10, 16	100, 200, 300, 400, 500, 600, 700	3000
20, 25, 32, 40, 50, 63, 80, 100	800, 900, 1000, 1200, 1400, 1600, 1800, 2000	5000

(*) Strokes are manufacturable in 1mm increments, up to the maximum stroke. however, when exceeding a 2000 mm stroke, specify "-XB11" at the end of the model number.

Specifications



Bore size (mm)	10	16	20	25	32	40	50	63	80	100
ATEX category 1)	CE Ex II 2Gc 75°C (T6) Ta 5 to 40°C 95°C (T5) Ta 40 to 60°C									
Fluid	Air									
Action	Double acting									
Operating pressure range	0.2 to 0.8MPa		0.1 to 0.8MPa							
Proof pressure	1.2MPa									
Ambient and fluid temperature	5 to 60°C									
Cushion	Rubber bumper	Air cushion								
Lubrication	Non-lube									
Stroke length tolerance	1000 or less ^{+1.8} ₀ 1001 to 3000 ^{+2.8} ₀		2700 or less ^{+1.8} , 2701 to 5000 ^{+2.8} ₀							
Port size	Front/Side ports		M5 x 0.8		Rc, NPT, G 1/8		Rc, NPT, G 1/4		Rc, NPT, G 3/8	
Operating piston speed	100 to 500 mm/s		100 to 1000 mm/s							

Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

For 55-MY1B

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-A93(V), A90(V), Z73, Z80, M9 and Y7PV, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Note 1) This cylinder can be used in zone 1 and 2.

If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zone 2 and not in zone 1.

Type	Model No.		Electrical entry	Indicator	Wiring (Output)	Load voltage			Lead wire* (m)			Applicable load	
	ø10 to ø20	ø25 to ø100				DC	AC	0.5 (-)	3 (L)	5 (Z)			
Reed auto switch	D-A93V□-588	-	Grommet (Perpendicular entry)	Yes	2-wiring	24V	12V	-	●	●	●	Relay PLC	
	D-A90V□-588	-		No		24V or less	48V	48V or less	●	●	-		IC circuit
	D-A93□-588	D-Z73□-588	Grommet (In-line entry)	Yes		24V	12V	-	●	●	●		-
	D-A90□-588	D-Z80□-588		No		24V or less	48V	48V or less	●	●	-		IC circuit
Solid state auto switch	D-M9□V-588	D-Y7PV□-588	Grommet (Perpendicular entry)	Yes	2-wire or 3-wire	24V	5V, 12V	-	●	●	○	IC circuit	
	D-M9□-588	D-Y7P□-588							Grommet (In-line entry)	●	●		○

* Lead wire length
0.5m --- Nil (e.g.) D-A93-588
3 m --- L (e.g.) D-A93L-588
5 m --- Z (e.g.) D-A93Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

Note 2) When mounting an auto switch on a 55-series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

ATEX Compliant

Mechanically Jointed Rodless Cylinder Series 55-MY1M

Slide Bearing Type/ø16, ø20, ø25, ø32, ø40, ø50, ø63

How to Order

Slide Bearing Guide Type

55-MY1M 25 300 XB11

ATEX category 2

Slide bearing guide type

Stroke
Refer to the standard stroke table below.

Special

-	Standard type
XB11	Long Stroke type

Standard strokes

Bore size (mm)	Standard stroke (mm)	Max. stroke (mm)
16	100, 200, 300, 400, 500, 600, 700	3000
20, 25, 32, 40, 50, 63	800, 900, 1000, 1200, 1400, 1600, 1800, 2000	5000

Bore size

16	16mm
20	20mm
25	25mm
32	32mm
40	40mm
50	50mm
63	63mm


Piping

-	Standard type
G	Centralized piping type

Port thread types

Symbol	Type	Bore size
-	M thread	ø16-ø20
-	Rc	ø25-ø63
TN	NPT	
TF	G	

(*) Strokes are manufacturable in 1mm increments, up to the maximum stroke. however, when exceeding a 2000 mm stroke, specify "-XB11" at the end of the model number.



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications

Bore size (mm)	16	20	25	32	40	50	63
ATEX category 1)	CE Ex II 2Gc		75°C (T6) Ta 5°C to 40°C 95°C (T5) Ta 40°C to 60°C				
Fluid	Air						
Action	Double acting						
Operating pressure range	0.15 to 0.8MPa						
Proof pressure	1.2MPa						
Ambient and fluid temperature	5 to 60°C						
Cushion	Air cushion						
Lubrication	Non-lube						
Stroke length tolerance	1000 or less ^{+1.8} ₀ 1001 to 3000 ^{+2.8} ₀		2700 or less ^{+1.8} ₀ , 2701 to 5000 ^{+2.8} ₀				
Port size	Front/Side ports M5 x 0.8		Rc, NPT, G 1/8		Rc, NPT, G 1/4		Rc, NPT, G 3/8
Operating piston speed	100 to 1000 mm/s						

Note 1) This cylinder can be used in zones 1 and 2.
If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zone 2 and not in zone 1.

For 55-MY1M

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-A93(V), A90(V), Z73, Z80, M9□(V) and Y7PV, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.		Electrical entry	Indicator	Wiring (Output)	Load voltage		Lead wire* (m)			Applicable load		
	ø16 to ø20	ø25 to ø63				DC	AC	0.5 (-)	3 (L)	5 (Z)			
Reed auto switch	D-A93V□-588	-	Grommet (Perpendicular entry)	Yes	2-wiring	24V	12V	-	●	●	●	Relay PLC	
	D-A90V□-588					24V or less	48V	48V or less	●	●	-		IC circuit
	D-A93□-588	D-Z73□-588	Grommet (In-line entry)	No		24V	12V	-	●	●	●		-
	D-A90□-588	D-Z80□-588				24V or less	48V	48V or less	●	●	-		IC circuit
Solid state auto switch	D-M9□V-588	D-Y7PV□-588	Grommet (Perpendicular entry)	Yes	3-wire or 2 wire	24V	5V, 12V	-	●	●	○	IC circuit	
	D-M9□-588	D-Y7P□-588							Grommet (In-line entry)	●	●		○

• Lead wire length
0.5m --- Nil (e.g.) D-A93-588
3 m --- L (e.g.) D-A93L-588
5 m --- Z (e.g.) D-A93Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

Note 2) When mounting an auto switch on a 55- series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

ATEX Compliant

Mechanically Jointed Rodless Cylinder Series 55-MY1H

High Precision Guide Type/ø10, ø16, ø20, ø25, ø32, ø40

How to Order

High Precision Guide Type

55-MY1H 25 300 XB10

ATEX category 2

High precision guide type

Stroke
Refer to the standard stroke table below.

Special

Standard strokes

Bore size (mm)	Standard stroke (mm) (*)	Max. stroke (mm)
10	50, 100, 150, 200, 250, 300, 350, 400, 450, 500, 550, 600	—
16	50, 100, 150, 200, 250, 300, 350, 400, 450, 500, 550, 600	1000
20		
25		
32		
40	1500	

Bore size

10	10mm
16	16mm
20	20mm
25	25mm
32	32mm
40	40mm

Piping

—	Standard type
G	Centralized piping type

—	Standard type
XB10	Intermediate stroke (using exclusive body)
XB11	Long Stroke type

Note) Bore size 10 is only available as Standard. XB10 and XB11 is not available.

Port thread types

Symbol	Type	Bore size
—	M thread	ø10~ø20
	Rc	
TN	NPT	ø25~ø40
TF	G	

(*) Strokes are manufacturable in 1 mm increments, up to the maximum stroke. However, add "-XB10" to the end of the part number for nonstandard strokes from 51 to 599. Also when exceeding a 600 mm stroke specify "-XB11" at the end of the model number (except for ø10). Ø10 can only be manufactured up to 600mm stroke.


Specifications

Bore size (mm)	10	16	20	25	32	40
ATEX category 1)						
Fluid	Air					
Action	Double acting					
Operating pressure range	0.2 to 0.8MPa		0.1 to 0.8MPa			
Proof pressure	1.2MPa					
Ambient and fluid temperature	5 to 60°C					
Cushion	Rubber bumper	Air cushion				
Lubrication	Non-lube					
Stroke length tolerance	+1.8 (mm) 0					
Port size	Front/Side ports		M5 x 0.8		Rc, NPT, G 1/8	Rc, NPT, G 1/4
Operating piston speed	100 to 500 mm/s		100 to 1000 mm/s			

Note 1) This cylinder can be used in zone 1 and 2. If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zone 2 and not in zone 1.



Symbol



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

For 55-MY1H

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93°C X)

For detailed specifications on the D-A93(V), A90(V), Z73, Z80, M9□(V) and Y7PV, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.		Electrical entry	Indicator	Wiring (Output)	Load voltage			Lead wire* (m)			Applicable load	
	ø10 to ø20	ø25 to ø40				DC	AC	0.5 (—)	3 (L)	5 (Z)			
Reed auto switch	D-A93V□-588	—	Grommet (Perpendicular entry)	Yes	2-wiring	24V	12V	—	●	●	●	Relay PLC	
	D-A90V□-588					24V or less	48V	48V or less	●	●	—		IC circuit
	D-A93□-588	D-Z73□-588	Grommet (In-line entry)	No		24V	12V	—	●	●	●		—
	D-A90□-588	D-Z80□-588				24V or less	48V	48V or less	●	●	—		IC circuit
Solid state auto switch	D-M9□V-588	D-Y7PV□-588	Grommet (Perpendicular entry)	Yes	2-wire or 3-wire	24V	5V, 12V	—	●	●	○	IC circuit	
	D-M9□-588	D-Y7P□-588	Grommet (In-line entry)	No					●	●	○		

• Lead wire length
0.5m --- Nil (e.g.) D-A93-588
3 m --- L (e.g.) D-A93L-588
5 m --- Z (e.g.) D-A93Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

Note 2) When mounting an auto switch on a 55- series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

How to Order

High Precision Guide Type **55-MY1H** **25** **300** **X1985**

ATEX category 2

High precision guide type

Bore size

25	25mm
32	32mm
40	40mm

Stroke

Refer to the standard stroke table below.

Rust proof guide

Piping

-	Standard type
G	Centralized piping type

Port thread types

Symbol	Type	Bore size
-	Rc	ø25-ø40
TN	NPT	
TF	G	

Standard strokes

Bore size (mm)	Stroke (mm) (*)
25	50, 100, 150, 200, 250 300, 350, 400, 450, 500, 550, 600, 750
32	
40	

(*) X1985 type can only be manufactured with the strokes listed in table.

ATEX Compliant

Rotary Actuator: Vane Type

Series 55-CRB1

Sizes: 50, 63, 80, 100

How to Order

55-CRB1 **B** **W** **80** **90** **S** **□** **□**

ATEX category 2

Mounting

B	Basic type
L*	Foot type

Refer to Table 1 below if only foot assembly is required separately.

* Foot accessory is shipped together with the actuator but not mounted on it.

Table 1: Foot assembly part no.

Model	Unit part no.
CRB1LW 50	P411020-5
CRB1LW 63	P411030-5
CRB1LW 80	P411040-5
CRB1LW100	P411050-5

Size

50
63
80
100

Thread Port

—	Rc(PT)
XF	G(PF)
XN	NPT

Shaft type

W	Double shaft (long shaft key & four chamfers)
----------	---

Rotation


Classification	Symbol	Single vane	Double vane
Standard	90	90°	90°
	180	180°	—
	270	270°	—
Optional	100	100°	100°
	190	190°	—
	280	280°	—

Vane type

S	Single vane
D	Double vane


Connecting port position

-	Side ports
E	Axial ports




Rotary actuator Vane Type **Series 55-CRB1**

Specifications



JIS symbol



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Model (Size)	CRB1BW50	CRB1BW63	CRB1BW80	CRB1BW100	CRB1BW50	CRB1BW63	CRB1BW80	CRB1BW100	
Vane type	Single vane (S)				Double vane (D)				
ATEX category ¹⁾	CE $\text{\textcircled{Ex}}$ II 2Gc				90°C (T5) Ta 5°C to 40°C 110°C (T4) Ta 40°C to 60°C				
Rotation	Standard	90° ⁺⁴ , 180° ⁺⁴ , 270° ⁺⁴			90° ⁺⁴				
	Optional	100° ⁺⁴ , 190° ⁺⁴ , 280° ⁺⁴			100° ⁺⁴				
Fluid	Air (non-lube)								
Proof pressure (MPa)	1.5MPa								
Ambient and fluid temperature	5° to 60°C								
Max. operating pressure (MPa)	1.0MPa								
Min. operating pressure (MPa)	0.15MPa								
Speed regulation range (sec/90°)	0.1 to 1								
Allowable kinetic energy (J)	0.082	0.12	0.398	0.6	0.112	0.16	0.54	0.811	
Shaft load	Allowable radial load (N)	245	390	490	588	245	390	490	588
	Allowable thrust load (N)	196	340	490	539	196	340	490	539
Bearing type	Ball bearing								
Port position	Side ports or axial ports								
Size	Side ports	Rc, NPT, G 1/8		Rc, NPT, G 1/4		Rc, NPT, G 1/8		Rc, NPT, G 1/4	
	Axial ports	Rc, NPT, G 1/8		Rc, NPT, G 1/4		Rc, NPT, G 1/8		Rc, NPT, G 1/4	
Mounting	Basic, Foot								

Note 1) This actuator can be used in zones 1 and 2.

ATEX Compliant

Rotary Actuator: Vane Type

Series 55-CRB2

Sizes: 10, 15, 20, 30, 40

How to Order

55-CRB2 **B** **W** **180** **S** **E**

ATEX category 2

Mounting

B	Basic type
F¹⁾	Flange type

* When ordering "F" mounting type, flange is shipped together with the actuator, but not mounted.
* Flange can be mounted at 60 degrees intervals.
Note1) Not available for size 40.

Standard Shaft type

W	Double shaft with single flat (sizes 10 to 30)
	Long shaft key, Short shaft with single flat (size 40)

Size

10
15
20
30
40

Rotation

Vane type	Symbol	Rotation
Single vane	90	90°
	180	180°
	270	270°
Double vane	90	90°
	100	100°

Connecting port position

-	Side ports
E	Axial ports

Side ports



Axial ports



* Fittings are sold separately.


Vane type

S	Single vane
D	Double vane

Flange Assembly Part No.

Model	Assembly part no.
CRB2FW10	P211070-2
CRB2FW15	P211090-2
CRB2FW20	P211060-2
CRB2FW30	P211080-2

Rotary actuator Vane Type **Series 55-CRB2**



Single Vane Specifications

Model (Size)	CRB2BW10-□S	CRB2BW15-□S	CRB2BW20-□S	CRB2BW30-□S	CRB2BW40-□S	
Vane type	Single vane					
ATEX category ¹⁾	CE  II 2Gc		130°C (T4) Ta 5°C to 40°C 150°C (T3) Ta 40°C to 60°C			
Rotation	90°, 180°	270°	90°, 180°	270°	90°, 180°, 270°	
Fluid	Air (non-lube)					
Proof pressure (MPa)	1.05			1.5		
Ambient and fluid temperature	5° to 60°C					
Max. operating pressure (MPa)	0.7			1.0		
Min. operating pressure (MPa)	0.2	0.15				
Speed regulation range (sec/90°) ^{Note 2)}	0.03 to 0.3			0.04 to 0.3	0.07 to 0.5	
Allowable kinetic energy (J)	0.00015	0.001	0.003	0.02	0.04	
Shaft load	Allowable radial load (N)	15	15	25	30	60
	Allowable thrust load (N)	10	10	20	25	40
Bearing type	Ball bearing					
Port position	Side ports or axial ports					
Size	Side ports	M5	M3	M5	M3	M5
	Axial ports	M3			M5	
Shaft type	Double shaft (with single flat on both shafts)				Double shaft (Long shaft key & single flat)	
Mounting	Basic, Flange				Basic	


Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Note 1) This rotary actuator can be used in zones 1 and 2.

Double Vane Specifications

Model (Size)	CRB2BW10-□D	CRB2BW15-□D	CRB2BW20-□D	CRB2BW30-□D	CRB2BW40-□D	
Vane type	Double vane					
ATEX category ¹⁾	CE  II 2Gc		130°C (T4) Ta 5°C to 40°C 150°C (T3) Ta 40°C to 60°C			
Rotation	90°, 100°					
Fluid	Air (non-lube)					
Proof pressure (MPa)	1.05			1.5		
Ambient and fluid temperature	5° to 60°C					
Max. operating pressure (MPa)	0.7			1.0		
Min. operating pressure (MPa)	0.2	0.15				
Speed regulation range (sec/90°) ^{Note 2)}	0.03 to 0.3			0.04 to 0.3	0.07 to 0.5	
Allowable kinetic energy (J)	0.0003	0.0012	0.0033	0.02	0.04	
Shaft load	Allowable radial load (N)	15	15	25	30	60
	Allowable thrust load (N)	10	10	20	25	40
Bearing type	Ball bearing					
Port position	Side ports or axial ports					
Port size (Side ports, Axial ports)	M3			M5		
Shaft type	Double shaft (double shaft with single flat on both shafts)					
Mounting	Basic, Flange				Basic	

JIS symbol



* The following notes apply to both Single and Double Vane Specification tables above.
 Note 2) Make sure to operate within the speed regulation range.
 Exceeding the maximum speed (0.3 sec/90°) can cause the unit to stick or not operate.


ATEX Compliant

Rotary Actuator: Free-Mounting Type


Series 55-CRBU2

Sizes: 10, 15, 20, 30, 40

How to Order



Rotary Actuator Free-Mounting Type **Series 55-CRBU2**



Single Vane Specifications

Model (Size)	CRBU2W10-□S	CRBU2W15-□S	CRBU2W20-□S	CRBU2W30-□S	CRBU2W40-□S
ATEX category ¹⁾	CE  II 2Gc 130°C (T4) Ta 5°C to 40°C 150°C (T3) Ta 40°C to 60°C				
Rotation	90°, 180°, 270°				
Fluid	Air (non-lube)				
Proof pressure (MPa)	1.05			1.5	
Ambient and fluid temperature	5° to 60°C				
Max. operating pressure (MPa)	0.7			1.0	
Min. operating pressure (MPa)	0.2	0.15			
Speed regulation range (sec/90°) ^{Note 2)}	0.03 to 0.3			0.04 to 0.3	0.07 to 0.5
Allowable kinetic energy (J)	0.00015	0.001	0.003	0.02	0.04
Shaft load	Allowable radial load (N)	15	25	30	60
	Allowable thrust load (N)	10	20	25	40
Bearing type	Ball bearing				
Port position	Side ports or axial ports				
Port size	Side ports	M5			
	Axial ports	M3	M5		
Shaft type	Double shaft (Double shaft with single flat on both shafts)				Double shaft (Long shaft key & Single flat)


Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Note 1) This rotary actuator can be used in zones 1 and 2.

Double Vane Specifications

Model (Size)	CRBU2W10-□D	CRBU2W15-□D	CRBU2W20-□D	CRBU2W30-□D	CRBU2W40-□D
ATEX category ¹⁾	CE  II 2Gc 130°C (T4) Ta 5°C to 40°C 150°C (T3) Ta 40°C to 60°C				
Rotation	90°, 100°				
Fluid	Air (non-lube)				
Proof pressure (MPa)	1.05			1.5	
Ambient and fluid temperature	5° to 60°C				
Max. operating pressure (MPa)	0.7			1.0	
Min. operating pressure (MPa)	0.2	0.15			
Speed regulation range (sec/90°) ^{Note 2)}	0.03 to 0.3			0.04 to 0.3	0.07 to 0.5
Allowable kinetic energy (J)	0.0003	0.0012	0.0033	0.02	0.04
Shaft load	Allowable radial load (N)	15	25	30	60
	Allowable thrust load (N)	10	20	25	40
Bearing type	Ball bearing				
Port position	Side ports or axial ports				
Port size	Side ports	M5			
	Axial ports	M3	M5		
Shaft type	Double shaft (Double shaft with single flat on both shafts)				Double shaft (Long shaft key & Single flat)

JIS symbol



* The following notes apply to both Single and Double Vane Specification tables above.

Note 2) Make sure to operate within the speed regulation range. Exceeding the maximum speeds can cause the unit to stick or not operate.



ATEX Compliant

Compact Rotary Actuator: Rack-and-Pinion Type Series 55-CRQ2

How to Order

55-CDRQ2B S 20 90

ATEX category 2

Built-in magnet

-	None
D	Magnet

Shaft type

S	Single shaft with one chamfer	10, 15
S	Single shaft with key	20-40
W	Double shaft with one chamfer	10, 15
W	Double shaft with key	20-40

Size

10
15
20
30
40

Air cushion

Sizes	Air cushion	
10, 15	Without	-
20, 30, 40	Without	-
	With	C


Rotation

90	80° to 100°
180	170° to 190°

Port thread type

Size	Port thread	
10, 15	Nil	M5
	Nil	Rc1/8
20, 30, 40	TF	G1/8
	TN	NPT1/8
	TT	NPTF1/8

Specifications




Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Size	10	15	20	30	40
ATEX category ¹⁾	CE $\text{\textcircled{Ex}}$ II 2Gc 70°C (T6) Ta 0°C to 40°C 90°C (T5) Ta 40°C to 60°C				
Fluid	Air (non-lube)				
Maximum operating pressure	0.7MPa		1MPa		
Minimum operating pressure	0.15MPa		0.1MPa		
Ambient and fluid temperature	0 to 60°C (with no freezing)				
Cushion	Rubber bumper		Non attached, Air cushion		
Angle adjustment	Rotation end $\pm 5^\circ$				
Rotation	80° to 100°, 170° to 190°				
Port size	M5 x 0.8		Rc, G, NPT, NPTF 1/8		
Output Nm at 0.5 MPa	0.3	0.75	1.8	3.1	5.3

Note 1) This cylinder can be used in zones 1 and 2.

If the cylinder is used with SMC category 3 type auto switch, then the cylinder can only be used in zone 2 and not in zone 1.

JIS symbol



Allowable Kinetic Energy and Rotation Time Adjustment Range

Size	Allowable kinetic energy				Cushion angle	Stable operational rotation time adjustment range
	Allowable kinetic energy (J)			Rotation time (s/90°)		
	Without cushion	Rubber bumper	With air cushion *			
10	—	0.25×10^{-3}	—	—	0.2 to 0.7	
15	—	0.39×10^{-3}	—	—	0.2 to 0.7	
20	0.025	—	0.12	40°	0.2 to 1	
30	0.048	—	0.25	40°	0.2 to 1	
40	0.081	—	0.40	40°	0.2 to 1	

*) Allowable kinetic energy with cushion

Maximum energy absorption with optimal adjustment of cushion needle

Compact Rotary Actuator **Series 55-CRQ2**

For 55-CRQ2

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93° C X)

For detailed specifications on the D-A93A, A90, A93V, A90V, M9□(V), please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.	Electrical entry	Indicator	Wiring (Output)	Load voltage			Lead wire ² (m)			Applicable load
					DC	AC		0.5 (-)	3 (L)	5 (Z)	
Reed auto switch	D-A93□-588	Grommet (In-line)	Yes	2-wiring	24V	12V	—	●	●	●	—
	D-A90□-588		No		24V or less	48V	48V or less	●	●	—	IC circuit
	D-A93V□-588	Grommet (Perpendicular)	Yes		24V	12V	—	●	●	●	—
	D-A90V□-588		No		24V or less	48V	48V or less	●	●	—	IC circuit
Solid state auto switch	D-M9□-588	Grommet (In-line)	Yes	2-wire or 3-wire	24V	5V, 12V	—	●	●	○	IC circuit
	D-M9□V-588	Grommet (Perpendicular)						●	●	○	

- Lead wire length 0.5m --- Nil (e.g.) D-A93-588
 3 m --- L (e.g.) D-A93L-588
 5 m --- Z (e.g.) D-A93Z-588

Note 1) ○ solid state auto switch is available after receiving an order.

Note 2) When mounting an auto switch on a 55-series (Category 2) Model, the ATEX category of the auto switch cylinder changes to Category 3, which is the same category as the auto switch.

ATEX Compliant

Rotary Actuator: Vane Type

Series 56-CRB1

Sizes: 50, 63, 80, 100

How to Order

56-CDRB1 **B** **W** **80** **90** **S** **□** **□**

ATEX category 3

With auto switch unit

-	Without switch unit
D	With switch unit

Mounting

B	Basic type
L*	Foot type

Refer to Table 1 below if only foot assembly is required separately.
* Foot accessory is shipped together with the actuator but not mounted on it.

Size

50
63
80
100

Thread Port

-	Rc(PT)
XF	G(PF)
XN	NPT

Connecting port position

-	Side ports
E	Axial ports

Shaft type

W	Double shaft (long shaft key & four chamfers)
----------	---

Rotation

Classification	Symbol	Single vane	Double vane
Standard	90	90°	90°
	180	180°	—
	270	270°	—
Optional	100	100°	100°
	190	190°	—
	280	280°	—

Vane type

S	Single vane
D	Double vane

Table 1: Foot assembly part no.

Model	Unit part no.
CRB1LW 50	P411020-5
CRB1LW 63	P411030-5
CRB1LW 80	P411040-5
CRB1LW100	P411050-5

Side ports and **Axial ports** diagrams showing A port and B port locations.

For 56-CDRB1

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93° C X)

For detailed specifications on the D-R73, R80, and S7P, please refer to the relevant pages in Best Pneumatics.

(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Type	Model No.	Electrical entry	Indicator	Wiring (Output)	Load voltage		Lead wire* (m)			Applicable load	
					DC	AC	0.5 (-)	3 (L)	5 (Z)		
Reed auto switch	D-R73□-588	Grommet (In-line)	Yes	2-wiring	24V	—	—	●	●	●	IC circuit Relay PLC
	D-R80□-588		No			5V,12V	24V or less	●	●	○	
Solid state auto switch	D-S7P□-588	Grommet (In-line)	Yes	3-wiring (PNP)	24V	5V,12V	—	●	●	○	IC circuit

- Lead wire length 0.5m --- Nil (e.g.) D-R73-588
- 3 m --- L (e.g.) D-R73L-588
- 5 m --- Z (e.g.) D-R73Z-588


Note 1) ○ auto switch is available after receiving an order.

Note) Refer to the table below for the ATEX temperature class of a rotary actuator (56-CDRB1) with an autoswitch mounted to it.


	Rotary Actuator	Auto switch	Rotary actuator with auto switch
Normal temperature range (5°C to 40°C)	T6	T5	Equivalent to T5
Special temperature range (40°C to 60°C)	T4	T5	Equivalent to T4

Rotary Actuator Vane Type *Series 56-CRB1*

Specifications



JIS symbol



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Model (Size)	CRB1BW50	CRB1BW63	CRB1BW80	CRB1BW100	CRB1BW50	CRB1BW63	CRB1BW80	CRB1BW100	
Vane type	Single vane (S)				Double vane (D)				
ATEX category ¹⁾	II 3G				84°C (T6) Ta 5°C to 40°C 104°C (T4) Ta 40°C to 60°C				
Rotation	Standard	90° ⁺⁴ ₀ , 180° ⁺⁴ ₀ , 270° ⁺⁴ ₀			90° ⁺⁴ ₀				
	Optional	100° ⁺⁴ ₀ , 190° ⁺⁴ ₀ , 280° ⁺⁴ ₀			100° ⁺⁴ ₀				
Fluid	Air (non-lube)								
Proof pressure (MPa)	1.5MPa								
Ambient and fluid temperature	5° to 60°C								
Max. operating pressure (MPa)	1.0MPa								
Min. operating pressure (MPa)	0.15MPa								
Speed regulation range (sec/90°)	0.1 to 1								
Allowable kinetic energy (J)	0.082	0.12	0.398	0.6	0.112	0.16	0.54	0.811	
Shaft load	Allowable radial load (N)	245	390	490	588	245	390	490	588
	Allowable thrust load (N)	196	340	490	539	196	340	490	539
Bearing type	Ball bearing								
Port position	Side ports or axial ports								
Size	Side ports	Rc, NPT, G 1/8	Rc, NPT, G 1/4	Rc, NPT, G 1/8	Rc, NPT, G 1/8	Rc, NPT, G 1/4	Rc, NPT, G 1/4	Rc, NPT, G 1/4	
	Axial ports	Rc, NPT, G 1/8	Rc, NPT, G 1/4	Rc, NPT, G 1/8	Rc, NPT, G 1/8	Rc, NPT, G 1/4	Rc, NPT, G 1/4	Rc, NPT, G 1/4	
Mounting	Basic, Foot								

Note 1) This actuator can be used in zone 2 and not in zone 1.

ATEX Compliant

Rotary Actuator: Vane Type

Series 56-CRB2

Sizes: 10, 15, 20, 30, 40

How to Order

56-CDRB2 **B** **W** **180** **S**

ATEX category 3

With auto switch unit

-	Without switch unit
D	With switch unit

Mounting

B	Basic type
F¹⁾	Flange type

* When ordering "F" mounting type, flange is shipped together with the actuator, but not mounted.
* Flange can be mounted at 60 degrees intervals.
Note1) Not available for size 40.

Standard Shaft type

W	Double shaft with single flat (sizes 10 to 30)
	Long shaft key, Short shaft with single flat (size 40)

Size

10
15
20
30
40

Rotation

Vane type	Symbol	Rotation
Single vane	90	90°
	180	180°
	270	270°
Double vane	90	90°
	100	100°

Connecting port position

-	Body size
E	Axial position

* E not possible with switch unit

Vane type

S	Single vane
D	Double vane

Flange Assembly Part No.

Model	Assembly part no.
CRB2FW10	P211070-2
CRB2FW15	P211090-2
CRB2FW20	P211060-2
CRB2FW30	P211080-2

For 56-CDRB2

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93° C X)
For detailed specifications on the D-93A, 90A, S9P, S9PV, R73, R80, and S7P, please refer to the relevant pages in Best Pneumatics.
(Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Applicable Size	Type	Model No.	Electrical entry	Indicator	Wiring (Output)	Load voltage		Lead wire* (m)			Applicable load	
						DC	AC	0.5 (-)	3 (L)	5 (Z)		
10, 15	Reed auto switch	D-93A□-588	Grommet (In-line)	Yes	2-wiring	24V	-	—	●	●	●	—
		D-90A□-588		No			5V, 12V	24V or less	●	●	●	IC circuit
	Solid state auto switch	D-S9P□-588	Grommet (In-line)	Yes	3-wiring (PNP)	24V	5V, 12V	—	●	●	○	IC circuit
		D-S9PV□-588	Grommet (Perpendicular)				No	—	—	●	●	●
20, 30, 40	Reed auto switch	D-R73□-588	Grommet (In-line)	Yes	2-wiring	24V	—	—	●	●	●	IC circuit
		D-R80□-588		No			5V, 12V	24V or less	●	●	○	IC circuit
	Solid state auto switch	D-S7P□-588	Grommet (In-line)	Yes	3-wiring (PNP)	24V	5V, 12V	—	●	●	○	IC circuit


* Lead wire length 0.5m --- Nil (e.g.) D-R73-588
3 m --- L (e.g.) D-R73L-588
5 m --- Z (e.g.) D-R73Z-588

Note 1) ○ auto switch is available after receiving an order.

Note) Refer to the table below for the ATEX temperature class of a rotary actuator (56-CDRB1) with an autoswitch mounted to it.

	Rotary Actuator	Auto switch	Rotary actuator with auto switch
Normal temperature range (5°C to 40°C)	T5	T5	Equivalent to T5
Special temperature range (40°C to 60°C)	T4	T5	Equivalent to T4

Rotary Actuator Vane Type *Series 56-CRB2*



Single Vane Specifications

Model (Size)	CRB2BW10-□S	CRB2BW15-□S	CRB2BW20-□S	CRB2BW30-□S	CRB2BW40-□S	
Vane type	Single vane					
ATEX category ¹⁾	CE Ex II 3G		100°C (T5) Ta 5°C to 40°C 120°C (T4) Ta 40°C to 60°C			
Rotation	90°, 180°	270°	90°, 180°	270°	90°, 180°, 270°	
Fluid	Air (non-lube)					
Proof pressure (MPa)	1.05			1.5		
Ambient and fluid temperature	5° to 60°C					
Max. operating pressure (MPa)	0.7			1.0		
Min. operating pressure (MPa)	0.2	0.15				
Speed regulation range (sec/90°) ^{Note 2)}	0.03 to 0.3			0.04 to 0.3	0.07 to 0.5	
Allowable kinetic energy (J)	0.00015	0.001	0.003	0.02	0.04	
Shaft load	Allowable radial load (N)	15	15	25	30	60
	Allowable thrust load (N)	10	10	20	25	40
Bearing type	Ball bearing					
Port position	Side ports or axial ports					
Size	Side ports	M5	M3	M5	M3	M5
	Axial ports	M3			M5	
Shaft type	Double shaft (with single flat on both shafts)				Double shaft (Long shaft key & single flat)	
Mounting	Basic, Flange				Basic	
Auto switch	Mountable (Side ports only)					


Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Note 1) This rotary actuator can be used in zone 2 and not in zone 1.

Double Vane Specifications

Model (Size)	CRB2BW10-□D	CRB2BW15-□D	CRB2BW20-□D	CRB2BW30-□D	CRB2BW40-□D	
Vane type	Double vane					
ATEX category ¹⁾	CE Ex II 3G		100°C (T5) Ta 5°C to 40°C 120°C (T4) Ta 40°C to 60°C			
Rotation	90°, 100°					
Fluid	Air (non-lube)					
Proof pressure (MPa)	1.05			1.5		
Ambient and fluid temperature	5° to 60°C					
Max. operating pressure (MPa)	0.7			1.0		
Min. operating pressure (MPa)	0.2	0.15				
Speed regulation range (sec/90°) ^{Note 2)}	0.03 to 0.3			0.04 to 0.3	0.07 to 0.5	
Allowable kinetic energy (J)	0.0003	0.0012	0.0033	0.02	0.04	
Shaft load	Allowable radial load (N)	15	15	25	30	60
	Allowable thrust load (N)	10	10	20	25	40
Bearing type	Ball bearing					
Port position	Side ports or axial ports					
Port size (Side ports, Axial ports)	M3			M5		
Shaft type	Double shaft (double shaft with single flat on both shafts)					
Mounting	Basic, Flange				Basic	
Auto switch	Mountable (Side ports only)					

JIS symbol



* The following notes apply to both Single and Double Vane Specification tables above.
 Note 2) Make sure to operate within the speed regulation range.
 Exceeding the maximum speed (0.3 sec/90°) can cause the unit to stick or not operate.


ATEX Compliant

Rotary Actuator: Free-Mounting Type

Series 56-CRBU2

Sizes: 10, 15, 20, 30, 40

How to Order



For 56-CDRBU2

When using an Auto switch, select the appropriate switch from the following table and order it separately.

Applicable auto switch specifications

Auto switch only conforms to Category 3. (II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C), (II 3D tD A22 IP67 T93° C X)
 For detailed specifications on the D-93A, 90A, S9P, S9PV, R73, R80, and S7P, please refer to the relevant pages in Best Pneumatics.
 (Note: Reed auto switches for AC 100V and DC 100V are not within the specification.)

Applicable Size	Type	Model No.	Electrical entry	Indicator	Wiring (Output)	Load voltage		Lead wire* (m)			Applicable load	
						DC	AC	0.5 (-)	3 (L)	5 (Z)		
10, 15	Reed auto switch	D-93A□-588	Grommet (In-line)	Yes	2-wiring	24V	-	-	●	●	●	-
		D-90A□-588		No			5V, 12V	24V or less	●	●	●	IC circuit
	Solid state auto switch	D-S9P□-588	Grommet (In-line)	Yes	3-wiring (PNP)	24V	5V, 12V	-	●	●	○	IC circuit
		D-S9PV□-588		Grommet (Perpendicular)			No	●	●	○	IC circuit	
20, 30, 40	Reed auto switch	D-R73□-588	Grommet (In-line)	Yes	2-wiring	24V	-	-	●	●	●	-
		D-R80□-588		No			5V, 12V	24V or less	●	●	○	IC circuit
	Solid state auto switch	D-S7P□-588	Grommet (In-line)	Yes	3-wiring (PNP)	24V	5V, 12V	-	●	●	○	IC circuit

• Lead wire length 0.5m --- Nil (e.g.) D-R73-588
 3 m --- L (e.g.) D-R73L-588
 5 m --- Z (e.g.) D-R73Z-588

Note 1) ○ auto switch is available after receiving an order.

Note) Refer to the table below for the ATEX temperature class of a rotary actuator (56-CDRB1) with an autoswitch mounted to it.

	Rotary Actuator	Auto switch	Rotary actuator with auto switch
Normal temperature range (5°C to 40°C)	T5	T5	Equivalent to T5
Special temperature range (40°C to 60°C)	T4	T5	Equivalent to T4

Rotary Actuator Free-Mounting Type **Series 56-CRBU2**

Single Vane Specifications



Model (Size)	CRBU2W10-□S	CRBU2W15-□S	CRBU2W20-□S	CRBU2W30-□S	CRBU2W40-□S
ATEX category ¹⁾	II 3G 100°C (T5) Ta 5°C to 40°C 120°C (T4) Ta 40°C to 60°C				
Rotation	90°, 180°, 270°				
Fluid	Air (non-lube)				
Proof pressure (MPa)	1.05			1.5	
Ambient and fluid temperature	5° to 60°C				
Max. operating pressure (MPa)	0.7			1.0	
Min. operating pressure (MPa)	0.2	0.15			
Speed regulation range (sec/90°) ^{Note 2)}	0.03 to 0.3			0.04 to 0.3	0.07 to 0.5
Allowable kinetic energy (J)	0.00015	0.001	0.003	0.02	0.04
Shaft load	Allowable radial load (N)	15	25	30	60
	Allowable thrust load (N)	10	20	25	40
Bearing type	Ball bearing				
Port position	Side ports or axial ports				
Port size	Side ports	M5			
	Axial ports	M3	M5		
Shaft type	Double shaft (Double shaft with single flat on both shafts)				Double shaft (Long shaft key & Single flat)


Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Note 1) This rotary actuator can be used in zone 2 and not in zone 1.

Double Vane Specifications

Model (Size)	CRBU2W10-□D	CRBU2W15-□D	CRBU2W20-□D	CRBU2W30-□D	CRBU2W40-□D
ATEX category ¹⁾	II 3G 100°C (T5) Ta 5°C to 40°C 120°C (T4) Ta 40°C to 60°C				
Rotation	90°, 100°				
Fluid	Air (non-lube)				
Proof pressure (MPa)	1.05			1.5	
Ambient and fluid temperature	5° to 60°C				
Max. operating pressure (MPa)	0.7			1.0	
Min. operating pressure (MPa)	0.2	0.15			
Speed regulation range (sec/90°) ^{Note 2)}	0.03 to 0.3			0.04 to 0.3	0.07 to 0.5
Allowable kinetic energy (J)	0.0003	0.0012	0.0033	0.02	0.04
Shaft load	Allowable radial load (N)	15	25	30	60
	Allowable thrust load (N)	10	20	25	40
Bearing type	Ball bearing				
Port position	Side ports or axial ports				
Port size	Side ports	M5			
	Axial ports	M3	M5		
Shaft type	Double shaft (Double shaft with single flat on both shafts)				Double shaft (Long shaft key & Single flat)

JIS symbol



* The following notes apply to both Single and Double Vane Specification tables above.

Note 2) Make sure to operate within the speed regulation range.

Exceeding the maximum speeds can cause the unit to stick or not operate.

ATEX Compliant Solid-state Switch / Direct Mounting

D-M9N(V)-588•D-M9P(V)-588•D-M9B(V)-588

CE Ex II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X



Note All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Auto Switch Specifications

PLC: Programmable Logic Controller

D-M9□/ D-M9□V (With indicator light)						
Auto switch part no.	D-M9N	D-M9NV	D-M9P	D-M9PV	D-M9B	D-M9BV
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular
Wiring type	3-wire				2-wire	
Output type	NPN		PNP		—	
Applicable load	IC circuit, Relay, PLC				24 VDC relay, PLC	
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)				—	
Current consumption	10 mA or less				—	
Load voltage	28 VDC or less		—		24 VDC (10 to 28 VDC)	
Load current	40 mA or less				2.5 to 40 mA	
Internal voltage drop	0.8 V or less at 10 mA (2 V or less at 40 mA)				4 V or less	
Leakage current	100 μA or less at 24 VDC				0.8 mA or less	
Indicator light	Red LED illuminates when turned ON.					

- Lead wires: Oilproof flexible heavy-duty vinyl cord: ø2.7 x 3.2 ellipse, 0.15mm², 2 cores (D-M9B(V)), 3 cores (D-M9N(V)), (D-M9P(V))
- This category 3 type autoswitch can only be used in zones 2 and 22.

How to Order

Standard Model Number

D-M9 N V L -588


- Series Model Number**: D-M9
- Wiring and output**:

N	3-wire NPN
P	3-wire PNP
B	2-wire
- Electrical entry**:

—	In-line
V	Perpendicular
- Suffix for ATEX certified CAT.3**: -588
- Lead wire length**:

—	0.5 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Auto Switch Internal Circuit



Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			



ATEX Compliant 2-Colour Solid State Switch: Direct Mounting

Series D-M9NW(V)/D-M9PW(V)/D-M9BW(V)-588

II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
 CE Ex II 3D tD A22 IP67 T93°C X



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Auto Switch Specifications


PLC: Programmable Logic Controller

D-M9□W/D-M9□WV (With 2 colour indicator light)						
Auto switch part no.	D-M9NW	D-M9NWV	D-M9PW	D-M9PWV	D-M9BW	D-M9BWV
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular
Wiring type	3-wire			2-wire		
Output type	NPN		PNP		—	
Applicable load	IC circuit, Relay, PLC				24 VDC relay, PLC	
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V)					
Current consumption	10 mA or less					
Load voltage	28 VDC or less		—		24 VDC (10 to 28 VDC)	
Load current	40 mA or less				2.5 to 40 mA	
Internal voltage drop	0.8 V or less at 10 mA (2 V or less at 40 mA)				4 V or less	
Leakage current	100 μA or less at 24 VDC				0.8 mA or less	
Indicator light	Operating position Red LED illuminates. Optimum operating position Green LED illuminates.					


- Lead wires — Oilproof flexible heavy-duty vinyl cord: ø2.7 x 3.2 ellipse, 0.15 mm², 2 cores (D-M9BW(V)), 3 cores (D-M9NW(V), D-M9PW(V))
- This category 3 type autoswitch can only be used in zones 2 and 22.

Auto Switch Internal Circuit


D-M9NW, D-M9NWV




D-M9PW, D-M9PWV



D-M9BW, D-M9BWV



Indicator light / Display method



How to Order

D-M9 N W V L -588

Model no. 2 colour display Suffix for ATEX certified CAT.3

Wiring/Output type

N	3-wire NPN
P	3-wire PNP
B	2-wire

Electrical entry direction

—	In-line
V	Perpendicular

Lead wire length

—	0.5 m
M	1 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			

ATEX Compliant Solid State Switch/Band Mounting

D-H7A2-588

CE Ex II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
 II 3D tD A22 IP67 T93°C X

Grommet



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications

PLC: Programmable Logic Controller

D-H7 (With indicator light)	
Auto switch model number	D-H7A2
Wiring	3 wire
Output	PNP
Application	IC circuit/Relay/PLC
Power voltage	5/12/24V DC (4.5 to 28 VDC)
Current consumption	10mA or less
Load current	80mA or less
Internal voltage drop	0.8V or less
Current leakage	100μA or less at 24 VDC
Indicator light	Red LED illuminates when turned ON.

- Lead wire—Oilproof heavy-duty vinyl cord, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue)
- This category 3 type autoswitch can only be used in zones 2 and 22.


How to order

D-H7A2 **-588**

- Switch No.
- Lead wire length
- Suffix for ATEX certified CAT.3

—	0.5 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Internal Circuit



Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			

ATEX Compliant Solid State Switch/Rail Mounting

D-F7P(V)-588

CE Ex II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X

Grommet



Note All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications

PLC: Programmable Logic Controller

D-F7P, D-F7PV (With indicator light)

Auto switch model number	D-F7P	D-F7PV
Electrical entry	In-line	Perpendicular
Wiring	3 wire	
Output	PNP	
Application	IC circuit/Relay/PLC	
Power voltage	5/12/24V DC (4.5 to 28VDC)	
Current consumption	10mA or less	
Load current	80mA or less	
Internal voltage drop	0.8V or less	
Current leakage	100µA or less at 24VDC	
Indicator light	Red LED illuminates when turned ON	

- Lead wire — Oilproof heavy-duty vinyl cord, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue)
- This category 3 type autoswitch can only be used in zones 2 and 22.

How to order

D-F7P **-588**

Switch No. ●

● Suffix for ATEX certified CAT.3

Electrical entry ●


● Lead wire length

-	In Line
V	Perpendicular

-	0.5 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Internal Circuit

D-F7P, D-F7PV



Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			

ATEX Compliant Solid State Switch/Tie-rod Mounting

D-F5P-588

CE Ex II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
 II 3D tD A22 IP67 T93°C X

Grommet



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications


PLC: Programmable Logic Controller

D-F5P (With indicator light)	
Auto switch model number	D-F5P
Wiring	3 wire
Output	PNP
Application	IC circuit/Relay/PLC
Power voltage	5/12/24V DC (4.5 to 28VDC)
Current consumption	10mA or less
Load current	80mA or less
Internal voltage drop	0.8V or less
Current leakage	100μA or less at 24VDC
Indicator light	Red LED illuminates when turned ON


• Lead wire — Oilproof heavy-duty vinyl cord, ø4, 0.3mm², 3 cores (Brown, Black, Blue)

• This category 3 type autoswitch can only be used in zones 2 and 22.

Internal Circuit



How to order



-	0.5 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			

ATEX Compliant Solid State Switch/Direct Mounting

D-Y7P(V)-588

CE Ex II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
 II 3D tD A22 IP67 T93°C X

Grommet



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications

PLC: Programmable Logic Controller

D-Y7P/D-Y7PV (With indicator light)		
Auto switch model number	D-Y7P	D-Y7PV
Electrical entry	In-line	Perpendicular
Wiring	3 wire	
Output	PNP	
Application	IC circuit/Relay/PLC	
Power voltage	5/12/24V DC (4.5 to 28VDC)	
Current consumption	10mA or less	
Load current	80mA or less	
Internal voltage drop	0.8V or less	
Current leakage	100μA or less at 24VDC	
Indicator light	Red LED illuminates when turned ON	

● Lead wire — Oilproof heavy-duty vinyl cord, $\phi 3.4$, 0.15mm², 3 cores (Brown, Black, Blue)

● This category 3 type autoswitch can only be used in zones 2 and 22.

How to order

D-Y7P [] [] -588

Switch No. ●

● Suffix for ATEX certified CAT.3

Electrical entry ●


● Lead wire length

-	In-Line
V	Perpendicular

-	0.5 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Internal Circuit

D-Y7P, D-Y7PV




Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			



ATEX Compliant Solid State Switch / Direct Mounting

D-S7P-588

CE Ex II 3G Ex nA II T5 X $-10^{\circ}\text{C} \leq \text{Ta} \leq +60^{\circ}\text{C}$
 II 3D tD A22 IP67 T93°C X



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.



Specifications

PLC: Programmable Logic Controller

D-S7P1/D-S7P2 (With indicator light)		
Auto switch model number	D-S7P1	D-S7P2
Electrical entry	In-Line	Perpendicular
Wiring	3 wire	
Output	PNP	
Application	IC circuit/Relay/PLC	
Power voltage	5/12/24V DC (4.5 to 28VDC)	
Current consumption	10mA or less	
Load current	80mA or less	
Internal voltage drop	0.8V or less	
Current leakage	100 μ A or less at 24VDC	
Indicator light	Red LED illuminates when turned ON	

● Lead wire — Oilproof heavy-duty vinyl cord, $\phi 3.4$, 0.2mm², 3 cores (Brown, Black, Blue)

● This category 3 type autoswitch can only be used in zones 2 and 22.

How to order

D-S7P **-588**

Switch No. ● Mounting ● Lead wire length ● Suffix for ATEX certified CAT.3

1	Right hand mounting
2	Left hand mounting

-	0.5 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			


ATEX Compliant Solid State Switch/Direct Mounting

D-S9P-588


CE Ex II 3G Ex nA II T5 X $-10^{\circ}\text{C} \leq T_a \leq +60^{\circ}\text{C}$
 II 3D tD A22 IP67 T93°C X



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.



Internal Circuit



Specifications

PLC: Programmable Logic Controller

D-S9P/D-S9PV (With indicator light)		
Auto switch model number	D-S9P	D-S9PV
Electrical entry	In-Line	Perpendicular
Wiring	3 wire	
Output	PNP	
Application	IC circuit/Relay/PLC	
Power voltage	5/12/24V DC (4.5 to 28VDC)	
Current consumption	10mA or less	
Load current	80mA or less	
Internal voltage drop	0.8V or less	
Current leakage	100 μ A or less at 24VDC	
Indicator light	Red LED illuminates when turned ON	

- Lead wire — Oilproof heavy-duty vinyl cord, $\phi 3.4$, 0.2mm², 3 cores (Brown, Black, Blue)
- This category 3 type autoswitch can only be used in zones 2 and 22.

How to order

D-S9P **-588**

Switch No. • • **Suffix for ATEX certified CAT.3**

Electrical entry •

—	In-Line
V	Perpendicular

Mounting •

1	Right hand mounting
2	Left hand mounting

Lead wire length

—	0.5 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			

ATEX Compliant Solid-state Switch / Direct Mounting

D-F6P-588

CE  II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X



Specifications


PLC: Programmable Logic Controller

D-F6P (With indicator light)	
Auto switch part no.	D-F6P
Electrical entry direction	In-line
Wiring type	3-wire
Output type	PNP
Applicable load	IC circuit, relay, and PLC
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V)
Current consumption	10 mA or less
Load current	40 mA or less
Internal voltage drop	0.8 V or less
Leakage current	100 μA or less at 24 V DC
Indicator light	Red LED illuminates when turned ON.

- Lead wires — Oilproof heavy-duty vinyl cord: 2.7 x 3.2 ellipse, 0.15 mm², 3 cores (Brown, Black, Blue)
- This category 3 type autoswitch can only be used in zones 2 and 22.

Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Internal Circuit



How to order

D-F6P  **-588**




Switch No.

Suffix for ATEX certified CAT.3

Lead wire length

—	0.5 m
L	3 m
Z	5 m
SAPC	0.5 m + M8 - 3 pins pre-wired connector
MAPC	1 m + M8 - 3 pins pre-wired connector
SBPC	0.5 m + M8 - 4 pins pre-wired connector
MBPC	1 m + M8 - 4 pins pre-wired connector
SDPC	0.5 m + M12 - 4 pins pre-wired connector
MDPC	1 m + M12 - 4 pins pre-wired connector

Connector Specifications

Connector type	M8-3 pins	M8-4 pins	M12-4 pins
Pin arrangement			



ATEX Compliant Reed Switch/Band Mounting

D-C73/D-C80-588

CE Ex II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X

Grommet



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.


Specifications

PLC: Programmable Logic Controller

D-C7 (With indicator light)		
Auto switch model number	D-C73	
Application	Relay/PLC	
Load voltage	24V DC	
Max. load current and range	5 to 40mA	
Contact protection circuit	None	
Internal voltage drop	≤ 2.4V	
Indicator light	Red LED illuminates when turned ON	
D-C8 (Without indicator light)		
Auto switch model number	D-C80	
Application	Relay/PLC/IC circuit	
Load voltage	24V $\frac{AC}{DC}$ or less	48V $\frac{AC}{DC}$ or less
Max. load current	50mA	40mA
Contact protection circuit	None	
Internal resistance	1Ω or less (Including 3m lead wire)	

- Lead wire — Oilproof vinyl heavy insulation cable, $\phi 3.4$, 0.2mm², 2 cores (Brown, Blue), 0.5m
- This category 3 type autoswitch can only be used in zones 2 and 22.

Internal Circuit



Note) ① In the case operation load is an inductive load.
② In the case the wiring length to load is more than 5m.
Be sure to use the auto switch with the contact protection box in any case mentioned above.

How to order

D-C [] [] [] **-588**

• Suffix for ATEX certified CAT.3

Switch No. • Lead wire length

73	With indicator lamp
80	Without indicator lamp

-	0.5m
L	3m
Z	5m (Except D-C80)

ATEX Compliant Reed Switch/Rail Mounting

D-A73(H)/D-A80(H)-588

CE  II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X

Grommet



Specifications

PLC: Programmable Logic Controller


D-A73, D-A73H (With indicator light)		
Auto switch model number	D-A73, D-A73H	
Application	Relay/PLC	
Load voltage	24V DC	
Load current range	5 to 40mA	
Contact protection circuit	None	
Internal voltage drop	≤ 2.4V	
Indicator light	Red LED illuminates when turned ON	
D-A80, D-A80H (Without indicator light)		
Auto switch model number	D-A80, D-A80H	
Application	Relay/IC circuit/PLC	
Load voltage	24V ^{AC} / _{DC} or less	48V ^{AC} / _{DC} or less
Max. load current	50mA	40mA
Contact protection circuit	None	
Internal resistance	1Ω or less (Including 3m lead wire)	

- Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 2 cores (Brown, Blue), 0.5m
- This category 3 type autoswitch can only be used in zones 2 and 22.


Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Internal Circuit

D-A73, D-A73H




D-A80, D-A80H



- Note) ① In the case operation load is an inductive load.
② In the case the wiring length to load is ">" 5m.
Be sure to use the auto switch with the contact protection box in any case mentioned above.

How to order





ATEX Compliant Reed Switch/Tie-rod Mounting

D-A54/D-A67-588

CE II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X

Grommet



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications

PLC: Programmable Logic Controller

D-A5 (With indicator light)	
Auto switch model number	D-A54
Application	Relay/PLC
Load voltage	24V DC
Max. load current and range	5 to 50mA
Contact protection circuit	Built-in
Internal voltage drop	2.4V or less (~20mA) / 3.5 V or less (~50mA)
Indicator light	Red LED illuminates when turned ON

D-A6 (Without indicator light)	
Auto switch model number	D-A67
Application	PLC/IC circuit
Load voltage	MAX. 24V DC
Max. load current	30mA
Contact protection circuit	None
Internal resistance	1Ω or less

● Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 2 cores (Brown, Blue), 0.5m

● This category 3 type autoswitch can only be used in zones 2 and 22.

How to order

D-A -588

● Suffix for ATEX certified CAT.3


● Switch No.

54	With indicator lamp
67	Without indicator lamp

● Lead wire length

-	0.5m
L	3m
Z	5m (Except D-A67)

Internal Circuit



ATEX Compliant Reed Switch/Direct Mounting

D-A90(V)/D-A93(V)-588

II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
 II 3D tD A22 IP67 T93°C X

Grommet



Note All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.


Specifications

PLC: Programmable Logic Controller


D-A90, D-A90V (Without indicator light)	
Auto switch model number	D-A90, D-A90V
Application	IC circuit/Relay/PLC
Load voltage	24V $\frac{AC}{DC}$ or less
Max. load current	50mA
Contact protection circuit	None
Internal resistance	1Ω or less (Including 3m lead wire)
D-A93, D-A93V (With indicator light)	
Auto switch model number	D-A93, D-A93V
Application	Relay/PLC
Load voltage	24V DC
Max. load current and load current range	5 to 40mA
Contact protection circuit	None
Internal voltage drop	≤ 2.4V (up to 20mA) / ≤ 3V (up to 40mA)
Indicator light	Red LED illuminates when turned ON

- Lead wire
D-A90(V)/D-A93(V) — Oilproof vinyl heavy insulation cable, ø2.7, 0.18mm² X 2cores (Brown, Blue)
- This category 3 type autoswitch can only be used in zones 2 and 22.

Dimensions



Internal Circuit




Note) ① In the case operation load is an inductive load.
 ② In the case the wiring length to load is "≥" 5m.
 Be sure to use the auto switch with the contact protection box in any case mentioned above.

ATEX Compliant Reed Switch/Direct Mounting

D-90A/D-93A-588

CE $\text{\textcircled{Ex}}$ II 3G Ex nA II T5 X $-10^{\circ}\text{C} \leq \text{Ta} \leq +60^{\circ}\text{C}$
 II 3D tD A22 IP67 T93°C X

Grommet
Lead wire: Heavy insulation cable



Note All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications


PLC: Programmable Logic Controller

D-90A (Without indicator light)	
Auto switch model number	D-90A
ATEX Category	$\text{CE } \text{\textcircled{Ex}}$ II 3GD EEx nA II T5 X $-10^{\circ}\text{C} \leq \text{Ta} \leq +60^{\circ}\text{C}$ IP67
Application	Relay/IC circuit/PLC
Load voltage	24V $\frac{\text{AC}}{\text{DC}}$ or less
Max. load current	50mA
Internal resistance	1Ω or less
D-93A (With indicator light)	
Auto switch model number	D-93A
ATEX Category	$\text{CE } \text{\textcircled{Ex}}$ II 3GD EEx nA II T5 X $-10^{\circ}\text{C} \leq \text{Ta} \leq +60^{\circ}\text{C}$ IP67
Application	Relay/PLC
Load voltage	24V DC
Load current range	5 to 40mA
Internal voltage drop	$\leq 2.4\text{V}$
Indicator light	Red LED illuminates when turned ON


- Lead wire — Oilproof vinyl heavy insulation cable, 0.2mm², 2 cores (Brown, Blue), 0.5m
- This category 3 type autoswitch can only be used in zones 2 and 22.

Internal Circuit

D-90A



D-93A



Note) ① In the case operation load is an inductive load.

② In the case the wiring length to load is ">" 5m.

Be sure to use the auto switch with the contact protection box in any case mentioned above.

How to order

D- [] [] A [] -588

• Suffix for ATEX certified CAT.3

• Switch No.

93	With indicator lamp
90	Without indicator lamp

• Lead wire length

-	0.5m
L	3m
Z	5m

ATEX Compliant Reed Switch/Direct Mounting

D-Z73/D-Z80-588

CE  II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X

Grommet



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications

PLC: Programmable Logic Controller


D-Z7 (With indicator light)	
Auto switch model number	D-Z73
Application	Relay/PLC
Load voltage	24V DC
Max. load current and load current range	5 to 40mA
Contact protection circuit	None
Internal voltage drop	2.4V or less (20mA) / 3V or less (~40mA)
Indicator light	Red LED illuminates when turned ON

D-Z8 (Without indicator light)		
Auto switch model number	D-Z80	
Application	Relay/PLC/IC circuit	
Load voltage	24V ^{AC} / _{DC} or less	48V ^{AC} / _{DC} or less
Max. load current		40mA
Contact protection circuit	50mA	None
Internal resistance	1Ω or less	

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores, 2 cores (Brown, Blue), 0.5m (for only D-Z73 ø2.7, 0.18mm², 2 cores)

• This category 3 type autoswitch can only be used in zones 2 and 22.

Internal Circuit



Note) ① In the case operation load is an inductive load.

② In the case the wiring length to ">" 5m.

Be sure to use the auto switch with the contact protection box in any case mentioned above.

How to order

D-Z **-588**
 • Suffix for ATEX certified CAT.3

Switch No. ●

73	With indicator lamp
80	Without indicator lamp

• Lead wire length

-	0.5m
L	3m
Z	5m (Except D-Z80)

ATEX Compliant Reed Switch/Direct Mounting

D-E73A/D-E80A-588

CE  II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X

Grommet



Note) All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

Specifications

PLC: Programmable Logic Controller

D-E73A (With indicator light)	
Auto switch model number	D-E73A
Application	Relay/PLC
Load voltage	24V DC
Max. load current and load current range	5 to 40mA
Contact protection circuit	None
Internal voltage drop	2.4V or less
Indicator light	Red LED illuminates when turned ON

D-E80A (Without indicator light)		
Auto switch model number	D-E80A	
Application	Relay/PLC/IC circuit	
Load voltage	24V ^{AC} / _{DC} or less	48V ^{AC} / _{DC} or less
Max. load current	50mA	40mA
Contact protection circuit	None	
Internal resistance	1Ω or less	

- Lead wire— Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², Black, Blue), 2 cores (Brown, Blue), 0.5m
- This category 3 type autoswitch can only be used in zones 2 and 22.

How to order

D-E **A** **-588**

• **Suffix for ATEX certified CAT.3**

• **Switch No.**


73	With indicator lamp
80	Without indicator lamp

• **Lead wire length**

-	0.5m
L	3m

Note) Z (5 metres) is not available on D-E73A and D-E80A

Internal Circuit



Note) ① In the case operation load is an inductive load.

② In the case the wiring length to load is ">" 5m.

Be sure to use the auto switch with the contact protection box in any case mentioned above.

ATEX Compliant Reed Switch/Direct Mounting


D-R73/D-R80-588

CE Ex II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +60°C
II 3D tD A22 IP67 T93°C X

Grommet




Note All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.




Internal circuit

D-R731/R732



D-R801/R802



Note) ① In the case operation load is an inductive load.
② In the case the wiring length to load is ">" 5m.
Be sure to use the auto switch with the contact protection box in any case mentioned above.

Specifications

PLC: Programmable Logic Controller

D-R73□ (With indicator light)	
Auto switch model no.	D-R731/D-R732
Applicable load	Relay, PLC
Load voltage	24V DC
Load current range	5 to 40mA
Internal voltage drop	2.4V or less
Indicator light	Red LED illuminates when turned ON
D-R80□ (Without indicator light)	
Auto switch model no.	D-R801/D-R802
Applicable load	Relay, IC circuit, PLC
Load voltage	24V _{DC} ^{AC} or less
Max. load current	50mA
Internal resistance	1Ω or less



- Lead wire — Oil proof heavy - duty vinyl cord, ø3.4, 0.2mm², 2 cores (Brown, blue)
- This category 3 type autoswitch can only be used in zones 2 and 22.

How to order

D-R □ □ □ □ -588

● Suffix for ATEX certified CAT.3

● Switch No.

73	With indicator light
80	Without indicator light

● Lead wire length

-	0.5m
L	3m
Z	5m

● Mounting

1	Right hand mounting
2	Left hand mounting

Pneumatic Cylinder Positioner

Series 56-IP200

Series 56-IP210

CE  II 3GD c T4...T6 (See table below)

How to Order



56 - **IP2** **0** **0**

Conform to ATEX
directive category 3

Stroke 25
to 300mm

Model

0	Standard
1	Movability type of outer cylinder function inner cylinder

Temperature and Material

-	Standard	-5° to 60°C
T	High	-5° to 100°C
L	Low	-30° to 60°C
S	Feedback spring and zero adjuster screw made of stainless steel	

Specifications

Classification	Ambient temperature range		
	Low temp. model 56-IP20□-□ L□-□	Standard model 56-IP20□-□□-□-□	High temp. model 56-IP20□-□-□-□-□
II 3GD c T4	—	—	-5°C to 100°C
II 3GD c T5	—	—	-5°C to 80°C
II 3GD c T6	-30°C to 60°C	-5°C to 60°C	-5°C to 60°C


Supply pressure	0.3~0.7MPa
Signal pressure	0.02~0.1MPa
Port size	Rc 1/4 (standard)
Pressure gauge port type	Rc1/8
Linearity	Less than +/- 2% F.S.
Hysteresis	Less than 1% F.S.
Repeatability	Less than 1% F.S.
Sensitivity	Less than ±0.5% F.S.
Air consumption	18l/min (ANR) or less (at 0.5 MPa supply)
Max. air flow	200l/min (ANR) or less (at 0.5 MPa supply)
Applicable cylinder (mm)	50 ~ 300 bore sizes / 25 ~ 300 mm stroke
Operating temperature	-5°C ~ 60°C (Standard)
	-30°C ~ 60°C (Low Temperature)
	-5°C~100°C (High Temperature)

Note) Standard air temperature: 20°, Absolute pressure: 101.3KPa.
Relative humidity: 65%

Pneumatic-Pneumatic Positioner


Series 55/56-IP5000 (Lever type)

Series 55/56-IP5100 (Rotary type)



For more details, other specifications, dimensions, see the specific catalogue.

How to Order



Specifications

Classification	Ambient temperature range		
	Low temp. model 55-IP5□00-□□□□L-□	Standard model 55-IP5□00-□□□□-□	High temp. model 55-IP5□00-□□□□T□-□
II 2GD c T4	-	-	-5°C ≤ Ta ≤ 100°C
II 2GD c T5	-	-20°C ≤ Ta ≤ 80°C	-5°C ≤ Ta ≤ 80°C
II 2GD c T6	-30°C ≤ Ta ≤ 60°C	-20°C ≤ Ta ≤ 60°C	-5°C ≤ Ta ≤ 60°C

Classification	Ambient temperature range		
	Low temp. model 56-IP5□00-□□□□L-□	Standard model 56-IP5□00-□□□□-□	High temp. model 56-IP5□00-□□□□T□-□
II 3GD c T4	-	-	-5°C ≤ Ta ≤ 100°C
II 3GD c T5	-	-20°C ≤ Ta ≤ 80°C	-5°C ≤ Ta ≤ 80°C
II 3GD c T6	-30°C ≤ Ta ≤ 60°C	-20°C ≤ Ta ≤ 60°C	-5°C ≤ Ta ≤ 60°C

Item	55/56-IP5000		55/56-IP5100	
	Lever type lever feedback		Rotary type cam feedback	
	Single action	Double action	Single action	Double action
Supply pressure	0.14~0.7MPa			
Input pressure	0.02~0.1MPa			
Standard stroke	10~85mm		60°~100°	
Sensitivity	Within 0.1%F.S.		Within 0.5%F.S.	
Linearity	Within ±1%F.S.		Within ±2%F.S.	
Hysteresis	Within 0.75%F.S.		Within 1%F.S.	
Repeatability	Within ±0.5%F.S.			
Output flow rate	80l/min (ANR) or more (SUP.=0.14MPa) 200l/min (ANR) or more (SUP.=0.4MPa)			
Air consumption	Within 5l/min (ANR) (SUP.=0.14MPa) Within 11l/min (ANR) (SUP.=0.4MPa)			
Ambient and using fluid Temperature	-20°C~80°C (Standard model) -30°C~60°C (Low Temp.) -5°C~100°C (High Temp.)			
Thermal coefficient	Within 0.1%F.S./°C			
Air connection port	Rc1/4 (Standard)			
Material	Aluminium diecast, Stainless steel, Brass, Nitrile rubber			
Mass	Approx. 1.4kg		Approx. 1.2kg	
Size	118 x 102 x 86 (Body)		118 x 92 x 77.5 (Body)	

Note) Standard air temperature: 20°, Absolute pressure: 101.3kPa.
Relative humidity: 65%



Electro-Pneumatic Positioner

Series IP6000 (Lever type)

Series IP6100 (Rotary type)

CE II 2G Ex ib IIC T5/T6

For more details, other specifications, dimensions, see the specific catalogue.

How to Order

IP6 000 – 0 1 0 – [] – X14

Positioner type

000	Lever type
100	Rotary type

Pressure gauge (SUP, OUT1)

1	0.2MPa (R1/8)
2	0.3MPa (R1/8)
3	1.0MPa (R1/8)

Accessories Note 1)

–	Without accessory (standard)	With standard lever (10 to 85 mm stroke) for IP6000
A	With ø0.7 output restrictor integrated pilot valve	Common to IP6000 and IP6100 small capacity actuators
B	With ø1.0 output restrictor integrated pilot valve	
C	With fork lever type fitting MX	Only for IP6100
D	With fork lever type fitting SX	
E	With lever unit for a 35 to 100 mm stroke	Only for IP6000
F	With lever unit for a 50 to 140 mm stroke	
G	With compensation spring (A)	Common to IP6000 and IP6100

Note 1) If multiple accessories are required, they should be indicated in alphabetical order.

Specifications

Item	Type	IP6000		IP6100	
		Lever type lever		Rotary type cam	
		Single action	Double action	Single action	Double action
Input current		4~20mADC (Standard) <small>Note1</small>			
Input resistance		235 ± 15Ω (4~20mADC)			
Supply air pressure		0.14~0.7Mpa			
Standard stroke		10~85mm (External lever allowable runout angle 10°~30°)		60°~100° <small>Note2</small>	
Sensitivity		Within 0.1%F.S.		Within 0.5%F.S.	
Linearity		Within ±1%F.S.		Within ±2%F.S.	
Hysteresis		Within 0.75%F.S.		Within 1%F.S.	
Repeatability		Within ±0.5%F.S.			
Thermal coefficient		Within 0.1%F.S./°C			
Output flow rate		80l/min (ANR) or more (SUP.=0.14MPa) <small>Note3</small>			
Air consumption		Within 5l/min (ANR) (SUP.=0.4MPa)			
Ambient and using fluid Temperature		-20°C~80°C (T5)			
		-20°C~60°C (T6)			
Explosion protected Construction		Intrinsic safety type of explosion protection (0344 II 2G Ex ib IIC T5/T6) Approval No. KEMA No.03 ATEX1119			
Air connection port		1/4NPT female screw			
Electric wiring connection port		M20 x 1.5			
Material		Aluminium diecast for the body			
Mass		Approx. 2.4kg			
Classification of degree of protection		JISF8007 IP55 (Conform to IEC 60529)			
Parameters (Current circuit)		Ui ≤ 28V, Ii ≤ 125mA, Pi ≤ 1.2W, Ci ≤ OnF, Li ≤ OmH			

Note 1) 1/2 split range is possible with the standard type (by adjusting the span).


Note 2) The stroke is adjustable in 0~60 and 0~100.

Note 3) Standard air (JIS B0120): temp. 20°C, absolute press. 760mmHg, ratio humidity 65%.

Series IP6000/6100

Dimensions / IP6000








IP6000-0□0-□-X14 (lever type)



Electro-Pneumatic Positioner Series IP6000/6100

Dimensions / IP6100

IP6100-0□0-□-X14 (rotary type)



Electro-Pneumatic Positioner

Series IP8000 (Lever type)

Series IP8100 (Rotary type)

CE Ex II 2G Ex ib IIC T5/T6

 For more details, other specifications, dimensions, see the specific catalogue.

How to Order

IP8 **000** - 0 **0** 0 - **X14** - **L**

Positioner type

000	Lever type
100	Rotary type

ATEX category 2

Option Note 2)

Symbol	Option
—	Standard: -20°C to 80°C
L	Low temperature (-40 to 60°C)
W	With top window (IP8100 Only)

Note 2) Combination of L and W is not available.

Accessories Note 1)

	Without accessory (standard)	With standard lever (10 to 85 mm stroke) for IP8000
A	With $\phi 0.7$ output restrictor integrated pilot valve	Common to IP8000 and IP8100 small capacity actuators
B	With $\phi 1.0$ output restrictor integrated pilot valve	
C	With fork lever type fitting MX	Only for IP8100
D	With fork lever type fitting SX	
E	With lever unit for a 35 to 100 mm stroke	Only for IP8000
F	With lever unit for a 50 to 140 mm stroke	
G	With compensation spring (A)	Common to IP8000 and IP8100
H	With external scale plate	Only for IP8100

Note 1) If multiple accessories are required, they should be indicated in alphabetical order.

Pressure gauge (SUP, OUT1)

0	Not provided
1	0.2MPa (R1/8)
2	0.3MPa (R1/8)
3	1.0MPa (R1/8)



Lever type
IP8000



Rotary type
IP8100

Specifications

Item	Type	IP8000		IP8100	
		Lever type lever feedback		Rotary type cam feedback	
		Single action	Double action	Single action	Double action
Input current		4 to 20mA DC (standard) <small>Note 1)</small>			
Input resistance		235 \pm 15 Ω (4 to 20mA DC)			
Supply air pressure		0.14 to 0.7MPa			
Standard stroke		10 to 85mm (Deflection angle 10 to 30°)		60 to 100° <small>Note 2)</small>	
Sensitivity		Within 0.1%F.S.		Within 0.5%F.S.	
Linearity		Within $\pm 1\%$ F.S.		Within $\pm 2\%$ F.S.	
Hysteresis		Within 0.75%F.S.		Within 1%F.S.	
Repeatability		Within 0.5%F.S.			
Coefficient of temperature		Within 0.1%F.S. / °C			
Output flow rate		80 ℓ /min (ANR) or more (SUP = 0.14MPa) <small>Note 3)</small>			
Air consumption		Within 5 ℓ /min (ANR) or less (SUP = 0.14MPa)			
Ambient and using fluid temperature		Standard type: -20 to 80°C (T5) / -20 to 60°C (T6) Low temperature type: -40 to 60°C (T6)			
Explosion protected construction		Intrinsic safety type of explosion protection (CE 0344 Ex II 2G Ex ib IIC T5/T6) Approval no. KEMA 03 ATEX1119			
Air connection port		1/4 NPT female screw			
Electrical wiring connection		M20x1.5			
Material		Aluminum diecast body			
Weight		Approx. 2.4kg			
Classification of degree of protection		JISF8007, IP65 (conforms to IEC 60529)			
Parameters		Ui \leq 28 V, Ii \leq 125 mA, Pi \leq 1.2W, Ci \leq 0nF, Li \leq 0mH			

Note 1) 1/2 Split range is possible with the standard type (by adjusting the span).

Note 2) The stroke is adjustable in 0 to 60°C and 0 to 100°

Note 3) Standard air (JIS B0120): temp. 20°C, absolute press. 760mmHg, ratio humidity 65%.

Electro-Pneumatic Positioner Series IP8000/8100

Accessory / Option

Pilot valve with output restriction (IP8000, 8100 type)

In general, mounting on a small-size actuator may cause hunting. For prevention, a pilot valve with a built-in output restriction is available. The restriction is removable.


(Ambient temperature: Standard)

Actuator Capacity	Orifice size	Part number	Pilot unit part number
90cm ³	ø0.7	P36801080	P565010-18
180cm ³	ø1	P36801081	P565010-19


Fork lever joints (IP8100 type)

Two types of the fork lever joints are available dependent upon different mounting dimensions. This is recommended because it can absorb off-centering, compared with direct mounting type.

Part name	Part number
Fork lever assembly MX	P368010-36
Fork lever assembly SX	P368010-37



Side mounting with the fork lever assembly MX




Side mounting with the fork lever assembly SX

External feedback lever (IP8000 type)

Different feedback levers are available dependent upon valve strokes. Consult with SMC in case of 10mm or less stroke.


Stroke	Unit number	Size M	Size N
10 to 85mm (standard)	P368010-20	125	150
35 to 100mm (Accessory "E")	P368010-21	110	195
50 to 140mm (Accessory "F")	P368010-22	110	275




Cable gland (for -X14)

Cable gland

Description	Part number	Suited cable outer diameter
Cable gland	07-9534-1M2B	ø6 to ø12



Exploded View




Replacement Parts (Ambient temperature: Standard)

No.	Description	Part no.	Note
1	Pilot valve unit	P565010-7	IP8000/8100
2	Base seal	P56501012-3	
3	Cover seal	P56501013	

Electro-Pneumatic Positioner *Series IP8000 / 8100*

Dimensions / IP8100

IP8100-0□0-□-X14 (rotary type)





Smart Positioner (Lever type / Rotary type) Series 52-IP8001/8101

CE Ex II 1G Ex ia IIC T4/T5/T6

How to Order

ATEX Directive Intrinsically Safe Explosion proof

ATEX directive compliance
52 ATEX directive category 1 Intrinsically safe explosion-proof

ATEX temperature

Symbol	ATEX temperature	Applicable model	
		IP8001	IP8101
—	T4	●	●
T6	T5/T6	●	●

Specifications
4 Intrinsically safe explosion proof (ATEX) + output function + HART communication

Type

Lever type IP8001

Rotary type IP8101

001	Lever type
101	Rotary type

Pressure gauge

Symbol	Pressure gauge	Applicable model	
		IP8001	IP8101
1	0.2 MPa	●	—
2	0.3 MPa	●	—
3	1.0 MPa	●	●

Connection

Symbol	Air		Electric	
	IP8001	IP8101	IP8001	IP8101
—	Rc1/4	G1/2	G1/2	G1/2
M ^{Note)}	Rc1/4	M20 x 1.5	M20 x 1.5	M20 x 1.5
N	Rc1/4	1/2NPT	1/2NPT	1/2NPT
1	1/4NPT	G1/2	G1/2	G1/2
2 ^{Note)}	1/4NPT	M20 x 1.5	M20 x 1.5	M20 x 1.5
3	1/4NPT	1/2NPT	1/2NPT	1/2NPT
4	G1/4	G1/2	G1/2	G1/2
5 ^{Note)}	G1/4	M20 x 1.5	M20 x 1.5	M20 x 1.5
6	G1/4	1/2NPT	1/2NPT	1/2NPT

Accessories ^{Note 1)}

Symbol	Accessories	Applicable model	
		IP8001	IP8101
—	None (Standard)	●	●
C	Fork lever-type fitting M	—	●
D	Fork lever-type fitting S	—	●
E	For stroke 35 to 100 mm with lever unit ^{Note 2)}	●	—
F	For stroke 50 to 140 mm with lever unit ^{Note 2)}	●	—
H	With external scale plate	—	●
W	Body with LCD window	●	●

Note 1) If two or more accessories are required, the part numbers should be given in alphabetical order. (ex. IP8101-010-CH)
Note 2) Standard lever is not attached.

Electro-Pneumatic Positioner Smart Positioner **Series 52-IP8001/8101**

Specifications Note 1)

Item	Type	IP8001		IP8101	
		Smart Positioner			
		Lever type		Rotary type	
		Single action / Double action			
Input current	4 to 20 mA DC (Standard) <small>Note 2)</small>				
Min. operating current	3.85 mA DC or more				
Intra-terminal voltage	12 V DC (equivalent to 600 Ω input resistance, at 20 mA DC)				
Max. supplied power	1 W (Imax: 100 mA DC, Vmax: 28 V DC)				
Supply air pressure	0.14 to 0.7 MPa		0.3 to 0.7 MPa		
Standard stroke	10 to 85 mm (Allowable deflection angle 10 to 30°)		60 to 100°		
Sensitivity <small>Note 3)</small>	Within 0.2% F.S.				
Linearity <small>Note 3)</small>	Within ±1% F.S.				
Hysteresis <small>Note 3)</small>	Within 0.5% F.S.				
Repeatability <small>Note 3)</small>	Within ±0.5% F.S.				
Coefficient of temperature	Within 0.05% F.S./°C				
Supply pressure fluctuation	— <small>Note 4)</small>				
Output flow <small>Note 5)</small>	80 ℓ/min (ANR) or more (SUP = 0.14 MPa)		200 ℓ/min (ANR) or more (SUP = 0.4 MPa)		
Air consumption <small>Note 5)</small>	2 ℓ/min (ANR) or less (SUP = 0.14 MPa) 4 ℓ/min (ANR) or less (SUP = 0.4 MPa)		11 ℓ/min (ANR) or less (SUP = 0.4 MPa)		
Ambient and fluid temperature	-20°C to 80°C (T4/T5) -20°C to 60°C (T6)				
Explosion proof construction <small>Note 6)</small>	ATEX intrinsically safe explosion-proof construction (II 1G Ex ia IIC T4/T5/T6)				
ATEX intrinsically safe explosion-proof parameter (current circuit)	Ui ≤ 28 V, Ii ≤ 100 mA, Pi ≤ 0.7 W, Ci ≤ 12.5 nF, Li ≤ 1.5 mH				
Exterior covering enclosure	JISF8007, IP65 (conforms to IEC Pub.60529)				
Transmission method <small>Note 6)</small>	HART transmission				
Air connection port <small>Note 7)</small>	Rc 1/4 female thread, NPT 1/4 female thread, G 1/4 female thread				
Electrical connection port <small>Note 7)</small>	G 1/2 female thread, M20 x 1.5 female thread, NPT 1/2 female thread				
Material/coating	Aluminum diecast body/baking finish with denatured epoxy resin				
Weight	2.6 kg				

Note 1) Specification values are given at normal temperature (20°C).

Note 2) 1/2 Split range (Standard)

Note 3) Characteristics relating to accuracy differ depending on combination with other constituent loop equipment, such as positioners and actuators.

Note 4) While there is no output changes due to pressure fluctuations, when the pressure supply setting is changed following calibration, once again adjust balance current and perform calibration.

Note 5) (ANR) indicates JIS B0120 standard air.

Note 6) Model selection required for explosion proof construction and HART transmission.

Note 7) Thread type can be specified by model selection.

Optional Specifications

Item	Type	52-IP8□01-0□4	
		Smart Positioner	
Analogue output	Wiring	2-wire	
	Output signal	4 to 20 mA DC	
	Power supply voltage	10 to 28 V DC	
	Load resistance	0 to 750 Ω	
	Accuracy	±0.5% F.S. or less <small>Note 1)</small>	
Alarm output 1, 2	Wiring	2-wire	
	Applicable standards	DIN19234/NAMUR Standard	
	Power supply voltage	5 to 28 V DC	
	Load resistance	(Constant current output)	
	Alarm ON	≥ 2.1 mA DC	
	Alarm OFF (Leakage current)	≤ 1.2 mA DC	
	Response time	50 msec or less	

Note 1) Indicates analogue output accuracy with respect to LCD display position value (P value).


Series 52-IP8001/8101

Accessory / Option


Fork lever-type fittings (8101)

2 types of rotary type IP8101 fork lever-type fittings, that differ by installation dimensions dependent on bracket installation method, and 2 types of installation portion thread sizes, are available. When installing on the side surface, using fork lever assembly M provides interchangeability with the installation dimensions of SMC IP610 positioner. When installing on the rear surface, using fork lever assembly S also provides interchangeability with the installation dimensions of SMC IP610 positioner.

Part name	Unit number	Installation portion thread size	Model selection accessory
Fork lever assembly M	P368010-24	M8 x 1.25	C
Fork lever assembly S	P368010-25		D



Side mounting with the fork lever assembly M




Rear mounting with the fork lever assembly S

External feedback lever (IP8001)

Different feedback levers are available dependent upon valve strokes. Order according to the valve stroke.


Feedback lever types

Stroke	Unit number	Size M	Size N	Model selection accessory
	IP8001			
10 to 85 mm	P565010-323	125	150	Standard accessory
35 to 100 mm	P565010-324	110	195	E
50 to 140 mm	P565010-325	110	275	F
6 to 12 mm	P565010-329	75	75	Available as special order



Exploded View

IP8101




Replacement Parts (Common for IP8001/8101)

No.	Description	Part no.	
		IP8001	IP8101
1	Pilot valve unit	P565010-322	P565010-303
2	Base seal	P56501012-3	
3	Cover seal	P56501013	

Electro-Pneumatic Positioner Smart Positioner **Series 52-IP8001/8101**


Dimensions / IP8001 (Lever type)

□-IP8001-W



Dimensions / IP8101 (Rotary type)

□-IP8101- \square 4



Process Pump. Automatically operated type Air operated type

Series 56-PA3000/5000

Automatically operated type (internal switching type)

Air operated type (external switching type)

CE Ex II 3 GD c T6 Ta 0°C to 60°C



For more details, other specifications, dimensions, see the specific catalogue.

How to Order

Automatically operated type (internal switching type)


PA3000



PA5000



Symbol



Automatically operated type

56 — PA 3 1 1 0 — [] 03 — []

ATEX category 3

Body size

3	3/8 standard
5	1/2 standard

Liquid contact body material

1	ADC12 (Aluminum)
2	SCS14 (Stainless steel)

Diaphragm material

1	PTFE
2	NBR

Option

—	Body only
N	With silencer*

* For AIR EXH: AN200-02 (NPT: AN200-N02)

Fluid connection port size

03	3/8 (10A): PA3
04	1/2 (15A): PA5
06	3/4 (20A): PA5

Thread type

—	Rc
T*	NPTF
F*	G
N*	NPT

* T, F, N are order made specifications.

Automatically operated type

Air operated type (external switching type)


PA3000



PA5000



Symbol



Air operated type

56 — PA 3 1 1 3 — [] 03

ATEX category 3

Body size

3	3/8 standard
5	1/2 standard

Liquid contact body material

1	ADC12 (Aluminum)
2	SCS14 (Stainless steel)

Diaphragm material

1	PTFE
---	------

Fluid connection port size

03	3/8 (10A): PA3
04	1/2 (15A): PA5
06	3/4 (20A): PA5

Thread type

—	Rc
T*	NPTF
F*	G
N*	NPT

* T, F, N are order made specifications.

Air operated type

Process Pump. Automatically operated type Air operated type

Series 55-PA3000/5000

Automatically operated type (internal switching type)
Air operated type (external switching type)



For 55-PA3□□0: II 2 GD c T6 Ta 0°C to 60°C
For 55-PA3□□3: II 2 GD c T5 Ta 0°C to 60°C
For 55-PA5□□□: II 2 GD c T6 Ta 0°C to 60°C



For more details, other specifications, dimensions, see the specific catalogue.

How to Order

Automatically operated type (internal switching type)

PA3000



PA5000



ATEX
Group II category 2

55 — PA 3 1 1 0 — □ □ 03 — □ □

Body size

3	3/8 standard
5	1/2 standard

Liquid contact body material

1	ADC12 (Aluminum)
2	SCS14 (Stainless steel)

Diaphragm material

1	PTFE
2	NBR

Option

—	Body only
N	With silencer*

* For AIR EXH: 2504-002 (NPT: 2504-N002)

Fluid connection port size


03	3/8 (10A): PA3
04	1/2 (15A): PA5
06	3/4 (20A): PA5

Thread type

—	Rc
T*	NPTF
F*	G
N*	NPT

* T, F, N are order made specifications.

Symbol



Automatically operated type

Automatically operated type

Air operated type (external switching type)

PA3000



PA5000



ATEX
Group II category 2

55 — PA 3 1 1 3 — □ □ 03

Body size

3	3/8 standard
5	1/2 standard

Liquid contact body material

1	ADC12 (Aluminum)
2	SCS14 (Stainless steel)

Diaphragm material

1	PTFE
---	------

Fluid connection port size


03	3/8 (10A): PA3
04	1/2 (15A): PA5
06	3/4 (20A): PA5

Thread type

—	Rc
T*	NPTF
F*	G
N*	NPT

* T, F, N are order made specifications.

Symbol



Air operated type

Air operated type



Booster Regulator

Series 56-VBA1100 and 20A to 43A


CE II 3 GD c T6 Ta 2°C to 50°C

For more details, other specifications, dimensions, see the specific catalogue.

How to Order

Series VBA 10A
2□A
4□A

56-VBA 40A - 04 GN -



• ATEX category 3

• Body size

Body size	Specifications
10A	1/4, Handle-operated type
20A	3/8, Handle-operated type
40A	1/2, Handle-operated type
22A	3/8, Air-operated type
42A	1/2, Air-operated type
43A	1/2, Max. operating pressure 1.6 MPa

* Pressure increase ratio: Twice

• Thread type ^{Note)}

Symbol	Thread type
—	Rc
F	G
N	NPT
T	NPTF

Note) Thread types apply to the IN, OUT, and EXH ports of the VBA10A and to the IN, OUT, EXH, and gauge ports of the VBA2□A and VBA4□A. The gauge ports of the VBA10A are Rc thread type regardless of the thread type indication.

• Semi-standard

Symbol	Specifications
—	Pressure unit on the product name label and pressure gauge: MPa
Z ^{Note)}	Pressure unit on the product name label and pressure gauge: psi

Note) Thread type: NPT, NPTF
Under the new measurement Law, the pressure unit of "psi" on the pressure gauges cannot be used in Japan.

• Option

Symbol	Option
—	None
G	Pressure gauge
N	Silencer
S	High-noise reduction silencer ^{Note)}
GN	Pressure gauge, Silencer
GS	Pressure gauge, High-noise reduction silencer ^{Note)}

Note) The high-noise reduction silencer is not available on the 56-VBA10A-N02 and 56-VBA10A-T02.

• Port size

Symbol	Port size	Applicable series
02	1/4	VBA10A
03	3/8	VBA2□A
04	1/2	VBA4□A



Series VBA1111

56-VBA 1111 - 02 GN

• ATEX category 3

• Body size

111	1/4
-----	-----

* Pressure: 2 MPa

• Pressure increase ratio

1	4 times
---	---------

• Thread type ^{Note)}

Symbol	Thread type
—	Rc
F	G
N	NPT
T	NPTF


Note) Thread types apply to the IN, OUT, and EXH ports. The gauge ports are Rc thread type.
For the G thread type, add an E at the beginning of the model number (56-EVBA1111-F02□).
For the NPTF thread type, add an N at the beginning of the model number (56-NVBA1111-T02□).

• Option

Symbol	Option
—	None
G	Pressure gauge
N	Silencer
GN	Pressure gauge, Silencer

• Port size

Symbol	Port size
02	1/4



VBA1111-02

Updated Product
Coming Soon

Standard Specifications

Model	VBA10A-02	VBA20A-03	VBA40A-04	VBA22A-03	VBA42A-04	VBA43A-04	VBA1111-02
Fluid	Compressed air						
Pressure increase ratio	Twice					Twice	Twice to 4 times
Pressure adjustment mechanism	Handle-operated with relief mechanism ^{Note 1)}			Air-operated		Handle-operated with relief mechanism ^{Note 1)}	
Max. flow rate ^{Note 2)} (l/min (ANR))	230	1000	1900	1000	1900	1600	60
Set pressure range (MPa)	0.2 to 2.0	0.2 to 1.0		0.2 to 1.0		0.2 to 1.6	0.2 to 2.0
Supply pressure range (MPa)	0.1 to 1.0						
Proof pressure (MPa)	3	1.5		1.5		2.4	3
Port size (IN/OUT/EXH: 3 locations) (Rc)	1/4	3/8	1/2	3/8	1/2	1/2	1/4
Pressure gauge port size (IN/OUT: 2 locations) (Rc)	1/8	1/8	1/8	1/8	1/8	1/8	1/16
Ambient and fluid temperature (°C)	2 to 50 (No freezing)						
Installation	Horizontal						
Lubrication	Grease (Non-lube)						
Weight (kg)	0.84	3.9	8.6	3.9	8.6	8.6	0.98

Note 1) If the OUT pressure is higher than the set pressure by the handle, excessive pressure is exhausted from the back of the handle.

Note 2) Flow rate at IN= OUT= 0.5 MPa. The pressure varies depending on the operating conditions.

Options/Part No.

Pressure Gauge, Silencer (When thread type is Rc or G.)

Description	Model	VBA10A-02	VBA20A-03	VBA40A-04	VBA22A-03	VBA42A-04	VBA43A-04	VBA1111-02
		VBA10A-F02	VBA20A-F03	VBA40A-F04	VBA22A-F03	VBA42A-F04	VBA43A-F04	EVBA1111-F02
Pressure gauge	G	G27-20-01	G36-10-01		KT-VBA22A-7	G36-10-01	G27-20-01	G27-20-R1
Silencer	N	AN200-02	AN300-03	AN400-04	AN300-03	AN400-04	AN400-04	AN200-02
High-noise reduction silencer	S	ANA1-02	ANA1-03	ANA1-04	ANA1-03	ANA1-04	ANA1-04	—

Note 1) In the case of option GN, two pressure gauges and one silencer are included as accessories.

Note 2) KT-VBA22A-7 is a pressure gauge with fittings. (Please order two units when using with IN and OUT.)

Note 3) Pressure unit of pressure gauge: MPa.

Pressure Gauge, Silencer (When thread type is NPT or NPTF.)

Description	Model	VBA10A-N02 *	VBA20A-N03 *	VBA40A-N04 *	VBA22A-N03 *	VBA42A-N04 *	VBA43A-N04 *	VBA1111-N02
		VBA10A-T02 *	VBA20A-T03 *	VBA40A-T04 *	VBA22A-T03 *	VBA42A-T04 *	VBA43A-T04 *	NVBA1111-T02
		*: when "-Z"		*: when "-Z"		*: when "-Z"		
Pressure gauge *: no symbol ^{Note 6)}	G	G27-20-01	G36-10-N01		KT-VBA22A-7N	G36-10-N01	G27-20-N01	G27-20-R1-X214 ^{Note 5)}
Pressure gauge *: when "-Z" ^{Note 4)}		G27-P20-01	G36-P10-N01		KT-VBA22A-8N	G36-P10-N01	G27-P20-N01	—
Silencer	N	AN200-N02	AN300-N03	AN400-N04	AN300-N03	AN400-N04	AN400-N04	AN200-N02
High-noise reduction silencer	S	—	ANA1-N03	ANA1-N04	ANA1-N03	ANA1-N04	ANA1-N04	—

Note 1) In the case of option GN, two pressure gauges and one silencer are included as accessories.

Note 2) KT-VBA22A-7N, KT-VBA22A-8N are pressure gauges with fittings. (Please order two units when using with IN and OUT.)

Note 3) Under the new measurement law, the pressure unit of "psi" on the pressure gauges cannot be used in Japan.

Note 4) Pressure unit of pressure gauge: psi

Note 5) Pressure unit of pressure gauge: psi and MPa

Note 6) Pressure unit of pressure gauge: MPa.

Updated Product
Coming Soon

Pressure Switch: Reed Switch Type

Series 56-IS1000



CE $\text{\textcircled{Ex}}$ II 3 GD EEx Na II T5 Ta-5°C to 60°C T90°C
IP67 / IP40



For details about certified products conforming to international standards, visit us at www.smcworld.com.

Long service life:
5 million cycles




IS1000-01

Specifications

Model	IS1000-01
Fluid	Air/Inert gas
Proof pressure	1.0 MPa
Max. operating pressure	0.7 MPa
Regulating pressure range (at OFF point)	0.1 to 0.4 MPa
Hysteresis	0.08 MPa or less
Error of scale	±0.05 MPa
Repeatability	±0.05 MPa
Contacts	1a
Wiring specifications	Grommet, Lead wire length 0.5 m (Standard)
Enclosure	Equivalent to IP40
Ambient and fluid temperature	-5 to 60°C (No freezing)
Port size	R 1/8
Weight	74 g

Electrical Circuit

Up to 48 VAC/DC



Switch Characteristics

Max. contact capacity	AC 2 VA, 2 W DC	
Voltage	24 VAC/DC or less	48 VAC/DC
Max. operating current	50 mA	40 mA
Impact resistance	30G	

How to Order

56-IS1000-01 S - - -

- Atex Category 3
- Port size

01	R 1/8
N01	NPT 1/8
- Seal


-	None
S	With seal
- Pressure display with scale plate

-	MPa
P	Both MPa and psi (Note)

Note) For overseas use only.
Not for the Japanese market.
According to new measurement law.
- Option

-	Lead wire length 0.5 m
X201	Lead wire length 3 m
X202	Regulating pressure range 0.1 to 0.6 MPa
X215	Lead wire length 3 m Regulating pressure range 0.1 to 0.6 MPa

Operating Pressure Range



Pressure Switch: (S) for integration into modular Air Preparation Units

A compact integrated pressure switch can be easily installed and facilitates the pressure detection of the line.



JIS Symbol



	Symbol	Description			①				
		Lead wire length	Set pressure range	Pressure display	Body size				
					20	30	40	50	60
② Option	—	0.5 m	0.1 to 0.4 MPa	MPa	●	●	●	●	●
	P (Note)	0.5 m	0.1 to 0.4 MPa	MPa/psi dual scale	●	●	●	●	●
	X202	0.5 m	0.1 to 0.6 MPa	MPa	●	●	●	●	●
	X202-P (Note)	0.5 m	0.1 to 0.6 MPa	MPa/psi dual scale	●	●	●	●	●
	X201	3 m	0.1 to 0.4 MPa	MPa	●	●	●	●	●
	X201-P (Note)	3 m	0.1 to 0.4 MPa	MPa/psi dual scale	●	●	●	●	●
	X215	3 m	0.1 to 0.6 MPa	MPa	●	●	●	●	●
X215-P (Note)	3 m	0.1 to 0.6 MPa	MPa/psi dual scale	●	●	●	●	●	

Note) This product is for overseas use only according to the new Measurement Law. (The SI unit type is provided for use in Japan.)

Specifications


Fluid	Air
Ambient and fluid temperature	-5°C to 60°C (with no freezing)
Proof pressure	1.0 MPa
Maximum operating pressure	0.7 MPa
Set pressure range (when OFF)	0.1 to 0.4 MPa
Hysteresis	0.08 MPa or less

Switch Characteristics

Contact point configuration	1a
Maximum contact point capacity	2 VA (AC), 2 W (DC)
Operating voltage: AC, DC	48 V or less
Maximum operating current	12 V to 24 VAC, DC: 50 mA 48 VAC, DC: 40 mA

Note) For detailed specifications, please refer to Best Pneumatics, IS1000 Series.

Pressure switch



Model	A	B	C	D	Applicable model
56-IS1000M-20	11	76	66	28	AC20□
56-IS1000M-30	13	86	72	30	AC25□, AC30□
56-IS1000M-40	15	95	77	36	AC40□
56-IS1000M-50	17	99	79	44	AC40□-06
56-IS1000M-60	22	92.5	68.5	53	AC50□, AC55□, AC60□

Note) Separate spacers are required for modular unit.

Series 56-IS1000

Pressure Switch with Piping Adapter

56-IS1000E - **30** **03** - **□**

Atex Category 3

1 2 3 4



		Symbol	Description	1		
				Body size		
				20	30	40
2	Thread type	—	Rc	●	●	●
		N <small>Note</small>	NPT	●	●	●
		F <small>Note</small>	G	●	●	●

		Symbol	Description	+		
				Port size		
				●	●	●
3	Port size	01	1/8	●	—	—
		02	1/4	●	●	●
		03	3/8	●	●	●
		04	1/2	—	●	●
		06	3/4	—	—	●

		Symbol	Lead wire length	Regulating pressure range	Pressure display	Mounting position	+		
							Accessory		
							●	●	●
4		—	0.5 m	0.1 to 0.4 MPa	MPa	Right	●	●	●
		X250	0.5 m	0.1 to 0.4 MPa	MPa	Left	●	●	●
		P <small>Note</small>	0.5 m	0.1 to 0.4 MPa	MPa/psi dual scale	Right	●	●	●
		X250-P <small>Note</small>	0.5 m	0.1 to 0.4 MPa	MPa/psi dual scale	Left	●	●	●
		X202	0.5 m	0.1 to 0.6 MPa	MPa	Right	●	●	●
		X252	0.5 m	0.1 to 0.6 MPa	MPa	Left	●	●	●
		X202-P <small>Note</small>	0.5 m	0.1 to 0.6 MPa	MPa/psi dual scale	Right	●	●	●
		X252-P <small>Note</small>	0.5 m	0.1 to 0.6 MPa	MPa/psi dual scale	Left	●	●	●
		X201	3 m	0.1 to 0.4 MPa	MPa	Right	●	●	●
		X251	3 m	0.1 to 0.4 MPa	MPa	Left	●	●	●
		X201-P <small>Note</small>	3 m	0.1 to 0.4 MPa	MPa/psi dual scale	Right	●	●	●
		X251-P <small>Note</small>	3 m	0.1 to 0.4 MPa	MPa/psi dual scale	Left	●	●	●
		X215	3 m	0.1 to 0.6 MPa	MPa	Right	●	●	●
		X253	3 m	0.1 to 0.6 MPa	MPa	Left	●	●	●
		X215-P <small>Note</small>	3 m	0.1 to 0.6 MPa	MPa/psi dual scale	Right	●	●	●
		X253-P <small>Note</small>	3 m	0.1 to 0.6 MPa	MPa/psi dual scale	Left	●	●	●

Note) For thread type: NPT only. This product is for overseas use only according to the new Measurement Law.
(The SI unit type is provided for use in Japan.)

JIS Symbol



Specifications

Fluid	Air
Ambient and fluid temperature	-5°C to 60°C (with no freezing)
Proof pressure	1.0 MPa
Maximum operating pressure	0.7 MPa
Set pressure range (when OFF)	0.1 to 0.4 MPa
Hysteresis	0.08 MPa or less

Switch Characteristics

Contact point configuration	1a
Maximum contact point capacity	2VA(AC), 2W(DC)
Operating voltage: AC, DC	48V or less
Maximum operating current	12V to 24V AC, DC: 50 mA 48V AC, DC: 40 mA

Model <small>Note 1</small>	Port size	A	B	C	D	E	Applicable model
56-IS1000E-20□01	1/8	30	68	57	28	16	AC20□
56-IS1000E-20□02	1/4						AR20□, AW20□
56-IS1000E-20□03	3/8						AWM20, AWD20
56-IS1000E-30□02	1/4	32	74.5	60.5	30	13	AC25□, AC30□
56-IS1000E-30□03	3/8						AR25□, AR30□, AW30□
56-IS1000E-30□04	1/2						AWM30, AWD30
56-IS1000E-40□02	1/4	32	80.5	62.5	37	12.5	<small>Note 2</small>
56-IS1000E-40□03	3/8						AC40□
56-IS1000E-40□04	1/2						AR40□, AW40□
56-IS1000E-40□06	3/4						AWM40, AWD40

Note 1) □ in the model numbers indicates a thread type. No indication is necessary for Rc; however, indicate N for NPT, and F for G.

Note 2) Cannot be mounted on the AC40□-06 and AW40□-06.

Note 3) Separate interfaces are required for modular unit.

* The pressure switch on the AC40□-06 and above and the AW40□-06 can be mounted by screwing IS1000-01 into the piping adapter E500-□06-X501 or E600-□06-X501 to E600-□10-X501 (with top-face thread Rc 1/8). Products with a premounted switch are available as a special order. Please contact SMC regarding their availability.



5 Port Solenoid Valve Series 52-SY

CE II 2G Ex ia IIB T4...T6



For more details, other specifications, dimensions, see the specific catalogue

How to Order

52 - SY 5 1 2 0 L 3 01 F

ATEX category 2

Series

5	52-SY5000
7	52-SY7000
9	52-SY9000

Type of actuation

1	2-position single
2	2-position double
3	3-position closed centre
4	3-position exhaust centre
5	3-position pressure centre

Piping style

2	Body ported type
4	Base mounted type

Pilot

-	Internal pilot
R	External pilot*

*Only the base mounted type.

Barrier

-	Without barrier
A	Z728.H
B	MTL728P+
D	MTL5021

One per solenoid supplied.

Electrical entry

L	Plug connector type
LL	Plug connector with cover type
TT	Terminal type

Lead wire length

3	300 mm
6	600 mm
10	1000 mm
15	1500 mm
20	2000 mm
30	3000 mm
100	10000 mm (semi-standard)

L type has 300mm and 600mm only.

Bracket

-	No bracket
F1	With foot bracket*
F2	With side bracket**

*Foot bracket only available for 2 position single solenoid valve 52-SY5000 and 52-SY7000.
**Side bracket only for 52-SY5000 and 52-SY7000.
***No bracket for only body ported type's 52-SY9000.

Thread style

-	Rc
F	G
N	NPT
T	NPTF

Type of actuation

Sign	Port size	Compatible series
01	1/8	52-SY5000
C4	ø4 One-touch fitting	
C6	ø6 One-touch fitting	
C8	ø8 One-touch fitting	
N3	ø5/32" One-touch fitting	
N7	ø1/4" One-touch fitting	
N9	ø5/16" One-touch fitting	
02	1/4	52-SY7000
C8	ø8 One-touch fitting	
C10	ø10 One-touch fitting	
N9	ø5/16" One-touch fitting	
N11	ø3/8" One-touch fitting	52-SY9000
02	1/4	
03	3/8	
C8	ø8 One-touch fitting	
C10	ø10 One-touch fitting	
C12	ø12 One-touch fitting	
N9	ø5/16" One-touch fitting	
N11	ø3/8" One-touch fitting	

Port size (Base mounted type)

Sign	Port size	Compatible series
-	No sub-plate	
02	1/4	52-SY5000
02	1/4	52-SY7000
03	3/8	
03	3/8	52-SY9000
04	1/2	

Manual override

-	Non locking push style
D	Push-turn locking slotted style
E	Push-turn locking lever style



For more details, other specifications, dimensions, see the specific catalogue

Specifications

Series		52-SY5000	52-SY7000	52-SY9000
Ambient and fluid temperature	Temperature class T6	45°C		
	Temperature class T4, T5	50°C		
Coil temperature rise		40°C or less (at rated)		
Barrier input voltage (non hazardous area)		24VDC (system rated voltage) at 1.1W		
Solenoid valve input voltage (hazardous area)		12VDC at 0.52W		
Intrinsically safe		ia		
Gas group		IIB		
Electrical entry	L type plug connector	IP30 (LL type : IP40)		
	T type terminal box	IP65		

Note1) Impact resistance: No malfunction resulted from the impact test using a drop impact tester. The test were performed one time each in the axial and right angle directions of the main valve and armature, in both energised and de-energised states (Valve in the initial stage).

Vibration resistance: No malfunction occurred in a one-sweep test between 8.3 and 2000Hz. The test was performed for both energised and de-energised states in the axial and right angle directions of the main valve and armature (valve in the initial stage).

Standard SY manifolds Types 20, 41, 42 are used for 52-SY valves

Manifold specifications for 20 type

Model	SS5Y5-20	SS5Y7-20
Applicable valve	52-SY5*20	52-SY7*20
Manifold style	Single base/ B mounting	
1 (SUP)/ 3/5 (EXH)	Common SUP/ Common EXH	
Valve stations	2 to 20 (1)	
4/2 (A/B) Location	Valve	
Port size	1,3,5 (P,EA,EB) Port	1/4
	4,2 (A,B) Port	1/8 C4 (One-touch fittings for ø4mm) C6 (One-touch fittings for ø6mm) C8 (One-touch fittings for ø8mm)
Manifold base weight W (g) n: Station	W=36n+64	W=43n+64

Note1) For more than 10 stations (more than 5 stations in case of SS5Y7), supply pressure to P port on both sides and exhaust from EA/EB port on both side.

Note2) 52-SY9*20 valve are not available with manifold as standard. Please contact SMC if you require it.

Note3) 52-SY series are not available with resin type manifold (23 type, 20P type and 45 type).

Manifold specifications for 41 and 42 type

Model	SS5Y5-41	SS5Y5-42	SS5Y7-42
Applicable valve	52-SY5*40		52-SY7*40
Manifold style	Single base/ B mounting		
1 (SUP)/ 3/5 (EXH)	Common SUP/ Common EXH		
Valve stations	2 to 20 (1)		
4/2 (A/B)	Location		
	Base		
Porting spec.	Direction		
	Side		
Port size	1,3,5 (P,EA,EB) Port	1/4	
	4,2 (A,B) Port	1/8 C6 (One-touch fittings for ø6mm) C8 (One-touch fittings for ø8mm)	1/4 C6 (One-touch fittings for ø6mm) C8 (One-touch fittings for ø8mm)
Manifold base weight W (g) n: Station	W=61n+101	W=79n+127	W=100n+151

Note1) For more than 10 stations (more than 5 stations in case of SS5Y7), supply pressure to P port on both sides and exhaust from EA/EB port on both side.

Note2) 52-SY9*40 valve are not available with manifold as standard. Please contact SMC if you require it.

Note3) 52-SY series are not available with resin type manifold (23 type, 20P type and 45 type).

Safety Instructions

- 1) This product is not suitable for Zone 0. The suitable zones are Zones 1 and 2.
- 2) SMC-TAS and TAU Series, antistatic tubing, is available if required.
- 3) the solenoid valve has polarity (+ -). Confirm the correct polarity by referring to the colour of the lead wires. If the polarity is reversed, the barrier maybe damaged.
- 4) Confirm that the solenoid input voltage at the lead wires is DC 10.8V (min).
- 5) The product must be connected to a certified barrier or certified intrinsically safe circuit with the follow maximum Values:

U_i= 28V
I_i= 225mA (resistively limited)
P_i= 1W
C_i= 0 nF
L_i= 0 mH

Note) The valve is not connected to barrier when supplied.

Response time

Configuration	Response time (ms) (0.5MPa)		
	52-SY5000	52-SY7000	52-SY9000
2-position single	26 or less	38 or less	50 or less
2-position double	22 or less	30 or less	50 or less
3-position	38 or less	56 or less	70 or less

Note1) According to dynamic performance test JIS B8375-1981.

Note2) Response time when barriers were combined with a valve.

System A: Valve + Z728.H (Pepperl + Fuchs)

B: Valve + MTL728P+

Note3) When system D is used, the ON time is delayed 17ms more than response time in table.

System D: Valve + MTL5021

Manifold specifications for 20 type

Model	Port size		Flow characteristics					
	1,5,3 (P,EA,EB)	4,2 (A,B)	1 > 4/2 (P>A/B)			4/2 > 5/3 (A/B > EA/EB)		
			c[dm ³ /(s.bar)]	b	Cv	c[dm ³ /(s.bar)]	b	Cv
SS5Y5-20	1/4	C8	1.90	0.28	0.48	2.20	0.20	0.53
SS5Y7-20	1/4	C10	3.60	0.93	3.60	0.93	0.27	0.88

Note) Values for 5 stations manifold with a 2 position single type valve.

Manifold specifications for 41 and 42 type


Model	Port size		Flow characteristics					
	1,5,3 (P,EA,EB)	4,2 (A,B)	1 > 4/2 (P>A/B)			4/2 > 5/3 (A/B > EA/EB)		
			c[dm ³ /(s.bar)]	b	Cv	c[dm ³ /(s.bar)]	b	Cv
SS5Y5-41	1/4	C8	1.80	0.23	0.44	1.90	0.16	0.45
SS5Y5-42	1/4	C8	1.90	0.20	0.46	1.90	0.12	0.43
SS5Y7-42	1/4	C10	3.00	0.25	0.75	3.00	0.12	0.66

Note) Values for 5 stations manifold with a 2 position single type valve.


Dimensions

Body ported type
Dimensions/ Series 52-SY5000
2-position single
Plug connector type (L)
52-SY5120-L□□-01□(-F2)


In case with foot bracket
52-SY5120-L□□-01□-F1



Plug connector with cover type (LL)
52-SY5120-LL□□-01□(-F2)




Terminal type (TT)
52-SY5120-TT□□-01□(-F2)




Series 52-SY

Dimensions


Body ported type
 Dimensions/Series 52-SY5000
 2-position double
 Plug connector type (L)
 52-SY5220-L□□-01□(-F2)



Plug connector with cover type (LL)
 52-SY5220-LL□□-01□(-F2)



Terminal type (TT)
 52-SY5220-TT□□-01□(-F2)



Dimensions

Body ported type

Dimensions/Series 52-SY5000


3-position closed centre-exhaust centre-pressure centre

Plug connector type (L)

3

52-SY5420-L□□-01□(-F2)

5




Plug connector with cover type (LL)

3

52-SY5420-LL□□-01□(-F2)

5




Terminal type (TT)

3

52-SY5420-TT□□-01□(-F2)

5





Series 52-SY


Dimensions

Body ported type
Dimensions/Series 52-SY7000
2-position single
Plug connector type (L)
52-SY7120-L□□-02□(-F2)


In case with foot bracket
52-SY7120-L□□-02□(-F1)



Plug connector with cover type (LL)
52-SY7120-LL□□-02□(-F2)




Terminal type (TT)
52-SY7120-TT□□-02□(-F2)




Dimensions


Body ported type
 Dimensions/Series 52-SY7000
 2-position double
 Plug connector type (L)
 52-SY7220-L□□-02□(-F2)



Plug connector with cover type (LL)
 52-SY7220-LL□□-02□(-F2)



Terminal type (TT)
 52-SY7220-TT□□-02□(-F2)



Series 52-SY

Dimensions

Body ported type

Dimensions/Series 52-SY7000


3-position closed centre-exhaust centre-pressure centre

Plug connector type (L)

3

52-SY7420-L□□-02□(-F2)

5




Plug connector with cover type (LL)

3

52-SY7420-LL□□-02□(-F2)

5




Terminal type (TT)

3


52-SY7420-TT□□-02□(-F2)

5




Dimensions


Body ported type
Dimensions/Series 52-SY9000
2-position single
Plug connector type (L)
52-SY9120-L □ □ -02 □
 -03 □



Plug connector with cover type (LL)
52-SY9120-LL □ □ -02 □
 -03 □




Terminal type (TT)
52-SY9120-TT □ □ -02 □
 -03 □




Series 52-SY

Dimensions


Body ported type
 Dimensions/Series 52-SY9000
 2-position double
 Plug connector type (L)
 52-SY9220-L□□-02□
 03□



Plug connector with cover type (LL)
 52-SY9220-LL□□-02□
 03□




Terminal type (TT)
 52-SY9220-TT□□-02□
 03□



Dimensions


Body ported type
 Dimensions/Series 52-SY9000
 2-position closed centre - exhaust centre -
 pressure centre
 Plug connector type (L)

3
 52-SY9420-L□□-02□
 5




Plug connector with cover type (LL)

3
 52-SY9420-LL□□-02□
 5



Terminal type (TT)


3
 52-SY9420-TT□□-02□
 5




Series 52-SY

Dimensions


Base mounted type
 Dimensions/Series 52-SY5000
 2-position single
 Plug connector type (L)
 52-SY5140(R)-L□□-02□



Plug connector with cover type (LL)
 52-SY5140(R)-LL□□-02□




Terminal type (TT)
 52-SY5140(R)-TT□□-02□




Dimensions


Base mounted type
Dimensions/Series 52-SY5000
2-position double
Plug connector type (L)
52-SY5240(R)-L□□-02□



Plug connector with cover type (LL)
52-SY5240(R)-LL□□-02□



Terminal type (TT)
52-SY5240(R)-TT□□-02□



Series 52-SY

Dimensions

Base mounted type

Dimensions/Series 52-SY5000




3-position closed centre - exhaust centre - pressure centre

Plug connector type (L)

3

52-SY5440(R)-L□□-02□

5




Plug connector with cover type (LL)

3

52-SY5440(R)-LL□□-02□

5




Terminal type (TT)

3


52-SY5440(R)-TT□□-02□

5




Dimensions


Base mounted type
Dimensions/Series 52-SY7000
2-position single
Plug connector type (L)
52-SY7140(R)-L□□-02□



Plug connector with cover type (LL)
52-SY7140(R)-LL□□-02□




Terminal type (TT)
52-SY7140(R)-TT□□-02□




Series 52-SY

Dimensions


Base mounted type
 Dimensions/Series 52-SY7000
 2-position double
 Plug connector type (L)
 52-SY7240(R)-L□□-02□



Plug connector with cover type (LL)
 52-SY7240(R)-LL□□-02□



Terminal type (TT)
 52-SY7240(R)-TT□□-02□



Dimensions

Base mounted type

Dimensions/Series 52-SY7000



3-position closed centre - exhaust centre - pressure centre

Plug connector type (L)

3

52-SY7440(R)-L□□-02□

5




Plug connector with cover type (LL)

3

52-SY7440(R)-LL□□-02□

5




Terminal type (TT)

3

52-SY7440(R)-TT□□-02□

5




Series 52-SY

Dimensions


Base mounted type
Dimensions/Series 52-SY9000
3-position closed centre -
exhaust centre - Pressure centre
Plug connector type (L)

3
52-SY9440(R)-L □ □ -02 □
 5 03




Plug connector with cover type (LL)

3
52-SY9440(R)-LL □ □ -02 □
 5 03



Terminal type (TT)

3
52-SY9440(R)-TT □ □ -02 □
 5 03







5-Port Solenoid Valve Series 56-VQC1000

Manifold with M- or T- kit
 II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +50°C
 II 3D Ex tD A22 IP67 T85°C X
 Manifold with 56-EX500
 II 3G Ex nA II T5 X +5°C ≤ Ta ≤ +45°C
 II 3D Ex tD A22 IP67 T80°C X
 Special condition X "Protect from Impact"



For more details, other specifications, dimensions, see the specific catalogue.

How to Order Manifolds



Contact SMC for 56-EX250 with Profibus DP

How to Order Valves

56 - VQC 1 1 0 0 **5**

ATEX category 3

Series
1 56-VQC1000

Type of actuation

1	2-position single (A)(B) 4 2 5 1 3 (R1)(P)(R2)	A Note)	4-position dual 3-port valve (A) (A) (B) 4 2 5 1 3 (R1) (P) (R2) N.C (P) N.C
	2-position double (metal) (A)(B) 4 2 5 1 3 (R1)(P)(R2)		B Note)
2	2-position double (rubber) (A)(B) 4 2 5 1 3 (R1)(P)(R2)	C Note)	4-position dual 3-port valve (C) (A) (B) 4 2 5 1 3 (R1) (P) (R2) N.C (P) N.O
	3-position closed centre (A)(B) 4 2 5 1 3 (R1)(P)(R2)		Note) For rubber seal type only.
3	3-position exhaust centre (A)(B) 4 2 5 1 3 (R1)(P)(R2)		
4	3-position pressure centre (A)(B) 4 2 5 1 3 (R1)(P)(R2)		
5			

Coil voltage
5 24VDC

Function

-	Standard type
R	External pilot

Manual override

- Nil: Non-locking push type
- B: Locking type (Slotted)
- C: Locking type (Manual)
- D: Slide locking type (Manual)

Seal type

0	Metal seal
1	Rubber seal

Note) "56-" solenoid valve should be installed in "56-VV5QC11" manifold.
Power consumption when starting is 1W, when maintaining 0.35W.
"56-VQC" solenoid valve has no polarity

Specifications for 56-VQC 1000/2000 and 4000

Valve Configuration		Metal seal	Rubber seal	
Fluid		Air/Inert gas		
Valve specifications	56-VQC1000/2000	Max. operating pressure	0.7MPa	
		Min. operating pressure	Single	0.1MPa
	Double		0.1MPa	
	3-position		0.1MPa	0.2MPa
	4-position	—	0.15MPa	
56-VQC4000	Max. operating pressure	1.0MPa		
	Min. operating pressure	Single	0.15MPa	0.2MPa
		Double	0.15MPa	
		3-position	0.15MPa	0.2MPa
Proof pressure		1.5MPa		
Fluid temperature		-10 to 50°C Note 1)		
Lubrication		Not required		
Manual override		Push type/Locking type (tool required)/Locking type Note 2)/Slide locking type Note 2)		
Impact resistance/Vibration resistance		150/30 m/s ² Note 3)		
Enclosure		Dust proof (conforms to IP67)		
Electrical specifications	Rated coil voltage		24VDC	
	Allowable voltage fluctuation		±10% of rated voltage	
	Coil insulation type		Equivalent to B type	
	Power consumption (Current) Note 4)	24VDC	1W (42mA) for inrush / 0.35W (15mA) for holding	

Note 1) Use dry air to prevent condensation at low temperatures.
 Note 2) Only for 56-VQC1000/2000.
 Note 3) **Impact resistance:** No malfunction resulted from the impact test using a drop impact tester. The test was performed one time each in the axial and right angle directions of the main valve and armature, for both energized and de-energized states.
Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000Hz. Test was performed in the axial and right angle directions of the main valve and armature for both energized and de-energized states.
 Note 4) The power-saving unit is included in the manifold.




5-Port Solenoid Valve Series 56-VQC2000



Manifold with M- or T- kit
 II 3G Ex nA II T5 X -10°C ≤ Ta ≤ +50°C
 II 3D Ex tD A22 IP67 T85°C X
 Manifold with 56-EX500
 II 3G Ex nA II T5 X +5°C ≤ Ta ≤ +45°C
 II 3D Ex tD A22 IP67 T80°C X
 Special condition X "Protect from Impact"

For more details, other specifications, dimensions, see the specific catalogue.

How to Order Manifolds



M	Kit (Multiple connector kit)	T	Kit (Terminal block box kit)	S	Kit (Serial output kit)
upto 24 solenoid coils		upto 20 solenoid coils		upto 16 solenoid coils SI unit: 56-EX500	
MD0	Multiple connector kit (26P) without cable	TD0	Terminal block box kit	SDA2	Serial kit for PROFIBUS DP / DEVICENET™
MD1	Multiple connector kit (26P) with 1.5m cable		1 to 10 stations (20 stations)		1 to 8 stations (16 stations)
MD2	Multiple connector kit (26P) with 3.0m cable				
MD3	Multiple connector kit (26P) with 5.0m cable				

Contact SMC for 56-EX250 with Profibus DP

How to Order Valves

56 - VQC 2 1 0 0 [] - 5 []

ATEX category 3

Series
2 56-VQC2000

Coil voltage
5 24VDC

Type of actuation

1	2-position single (A)(B) 4 2 5 1 3 (R1)(P)(R2)	A Note)	4-position dual 3-port valve (A) (A) (B) 4 2 5 1 3 (R1) 1 (R2) N.C (P) N.C
	2-position double (metal) (A)(B) 4 2 5 1 3 (R1)(P)(R2)		4-position dual 3-port valve (B) (A) (B) 4 2 5 1 3 (R1) 1 (R2) N.O (P) N.O
2	2-position double (rubber) (A)(B) 4 2 5 1 3 (R1)(P)(R2)	C Note)	4-position dual 3-port valve (C) (A) (B) 4 2 5 1 3 (R1) 1 (R2) N.C (P) N.O
	3-position closed centre (A)(B) 4 2 5 1 3 (R1)(P)(R2)		Note) For rubber seal type only.
3-position exhaust centre (A)(B) 4 2 5 1 3 (R1)(P)(R2)			
3-position pressure centre (A)(B) 4 2 5 1 3 (R1)(P)(R2)			

Function


-	Standard type
R	External pilot

Seal type


0	Metal seal
1	Rubber seal

Manual override


Nil: Non-locking push type




B: Locking type (Slotted)



C: Locking type (Manual)



D: Slide locking type (Manual)



Note) "56-" solenoid valve should be installed in "56-VV5QC21" manifold. Power consumption when starting is 1W, when maintaining 0.35W. "56-VQC" solenoid valve has no polarity

5-Port Solenoid Valve


Series 56-VQC4000

Manifold with M- or T- kit
 II 3G Ex nA II T5 X $-10^{\circ}\text{C} \leq T_a \leq +50^{\circ}\text{C}$
 II 3D Ex tD A22 IP67 T85°C X
 Manifold with 56-EX500
 II 3G Ex nA II T5 X $+5^{\circ}\text{C} \leq T_a \leq +45^{\circ}\text{C}$
 II 3D Ex tD A22 IP67 T80°C X
 Special condition X "Protect from Impact"



For more details, other specifications, dimensions, see the specific catalogue.

How to Order Manifolds



M Kit (Multiple connector kit)		T Kit (Terminal block box kit)		S Kit (Serial output kit)	
upto 16 solenoid coils		upto 16 solenoid coils		upto 16 solenoid coils SI unit: 56-EX500	
MD0	Multiple connector kit (26P) without cable	TD0	Terminal block box kit	SDA2	Serial kit for PROFIBUS-DP/DEVICENET™
MD1	Multiple connector kit (26P) with 1.5m cable				
MD2	Multiple connector kit (26P) with 3.0m cable		1 to 10 stations (16 stations)		1 to 8 stations (16 stations)
MD3	Multiple connector kit (26P) with 5.0m cable				

Contact SMC for 56-EX250 with Profibus DP








How to Order Valves

56 - VQC 4 1 0 0 [] - 5 []


ATEX category 3 (points to '56')


Series
4 | 56-VQC4000

Type of actuation

1	2-position single  (A)(B) 4 2 5 1 3 (R1)(P)(R2)	4	3-position exhaust center  (A)(B) 4 2 5 1 3 (R1)(P)(R2)
	2		2-position double (metal)  (A)(B) 4 2 5 1 3 (R1)(P)(R2)
2	2-position double (rubber)  (A)(B) 4 2 5 1 3 (R1)(P)(R2)	5	3-position pressure center  (A)(B) 4 2 5 1 3 (R1)(P)(R2)
	3		3-position perfect  (A)(B) 4 2 5 1 3 (R1)(P)(R2)
3	3-position closed centre  (A)(B) 4 2 5 1 3 (R1)(P)(R2)		

Manual override

Nil: Non-locking push type


B: Locking type (Slotted)


Coil voltage
5 | 24VDC

Function

-	Standard type
R	External pilot

Seal type

0	Metal seal
1	Rubber seal

Note) "56-" solenoid valve should be installed in "56-VV5QC41" manifold.
Power consumption when starting is 1W, when maintaining 0.35W.
"56-VQC" solenoid valve has no polarity.

Options for 56-VQC

Name	56-VQC1000	56-VQC2000	56-VQC4000
Blanking plate assembly	VVQ1000-10A-1	VVQ2000-10A-1	VVQ4000-10A-1
Individual SUP spacer	VVQ1000-P-1-C6	VVQ2000-P-1-C8	VVQ4000-P-1-□□
Individual EXH spacer	VVQ1000-R-1-C6	VVQ2000-R-1-C8	VVQ4000-R-1-□□
SUP stop valve spacer	-	VVQ2000-24A-1	VVQ4000-37A-1
SUP block plate	VVQ1000-16A	VVQ2000-16A	VVQ4000-16A
EXH block plate	-	VVQ2000-19A	VVQ4000-16A
EXH block base assembly	VVQC1000-19A-□-□□	-	-
Back pressure check valve	VVQ1000-18A	VVQ2000-18A	-
Port plug	VVQ0000-58A	VVQ1000-58A	-
Dual flow fitting assembly	VVQ1000-52A-C8	VVQ2000-52A-C10	-
Elbow fitting assembly	VVQ1000-F-L-□	VVQ2000-F-L-□	-
Port plug	VVQ0000-58A	VVQ1000-58A	-
Blanking plug	KQ2P-□□	KQ2P-□□	KQ2P-□□
DIN rail mounting bracket	VVQ1000-57A(-S)	VVQ2000-57A(-S)	-
Name plate	VVQ1000-N-□	VVQ2000-N-□	-

Notes) □: Please refer to standard catalogues for details.


Do not use options other than specified in this table.

Only these standard parts without "56-" prefix can be used.


M 56-VQC1000

Kit (Multiple Connector Kit)

56-VV5QC11



Multi-connector cable assembly
 AXT100-MC26-015:1.5m
 AXT100-MC26-030:3m
 AXT100-MC26-050:5m



Formulas

$L1 = 10.5n + 45$

$L2 = 10.5n + 123$ (1 power saving unit for 1 to 12 solenoids)


$L2 = 10.5n + 144$ (2 power saving units for 13 to 24 solenoids) n: Stations (Max. 24 single wire stations)

L \ n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
L1	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213	223.5	234	244.5	255	265.5	276	286.5	297
L2	133.5	144	154.5	165	175.5	186	196.5	207	217.5	228	238.5	249	280.5	291	301.5	312	322.5	333	343.5	354	364.5	375	385.5	396
L3	162.5	175	175	187.5	200	212.5	225	237.5	237.5	250	262.5	275	300	312.5	325	337.5	350	362.5	375	375	387.5	400	412.5	425
L4	173	185.5	185.5	198	210.5	223	235.5	248	248	260.5	273	285.5	310.5	323	335.5	348	360.5	373	385.5	385.5	398	410.5	423	435.5

S 56-VQC1000

Kit (Serial Transmission Kit) Decentralised Serial wiring

56-VV5QC11
SDA2 Kit (Serial Transmission Kit: 56-EX500)




Formulas
 L1 = 10.5n + 45
 L2 = 10.5n + 114.5 (1 power saving unit for 1 to 12 solenoids)
 L2 = 10.5n + 135.5 (2 power saving units for 13 to 16 solenoids) n: Stations (Max. 16 single wire stations)

L \ n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213
L2	125	135.5	146	156.5	167	177.5	188	198.5	230	240.5	251	261.5	272	282.5	293	303.5
L3	150	162.5	175	187.5	187.5	200	212.5	225	250	262.5	275	287.5	300	312.5	312.5	325
L4	160.5	173	185.5	198	198	210.5	223	235.5	260.5	273	285.5	298	310.5	323	323	335.5

T 56-VQC1000

Kit (Terminal Block Box Kit)

56-VV5QC11



Formulas

$$L1 = 10.5n + 45$$

$$L2 = 10.5n + 175.5 \quad (1 \text{ power saving unit for } 1 \text{ to } 12 \text{ solenoids})$$

$$L2 = 10.5n + 196.5 \quad (2 \text{ power saving units for } 13 \text{ to } 20 \text{ solenoids})$$


n: Stations (Max. 20 single wire stations)

L \ n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213	223.5	234	244.5	255
L2	186	196.5	207	217.5	228	238.5	249	259.5	270	280.5	291	301.5	333	343.5	354	364.5	375	385.5	396	406.5
L3	212.5	225	237.5	237.5	250	262.5	275	287.5	300	300	312.5	325	362.5	375	375	387.5	400	412.5	425	437.5
L4	223	235.5	248	248	260.5	273	285.5	298	310.5	310.5	323	335.5	373	385.5	385.5	398	410.5	423	435.5	448

M 56-VQC2000

Kit (Multiple Connector Kit)

56-VV5QC21



Formulas

$$L1 = 16n + 57$$

$$L2 = 16n + 131.5 \quad (1 \text{ power saving unit for } 1 \text{ to } 12 \text{ solenoids})$$



$$L2 = 16n + 152.5 \quad (2 \text{ power saving units for } 13 \text{ to } 24 \text{ solenoids}) \quad n: \text{Stations (Max. 24 single wire stations)}$$

L \ n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313	329	345	361	377	393	409	425	441
L2	147.5	163.5	179.5	195.5	211.5	227.5	243.5	259.5	275.5	291.5	307.5	323.5	360.5	376.5	392.5	408.5	424.5	440.5	456.5	472.5	488.5	504.5	520.5	536.5
L3	175	187.5	200	225	237.5	250	275	287.5	300	312.5	337.5	350	387.5	400	412.5	437.5	450	462.5	487.5	500	512.5	525	550	562.5
L4	185.5	198	210.5	235.5	248	260.5	285.5	298	310.5	323	348	360.5	398	410.5	423	448	460.5	473	498	510.5	523	535.5	560.5	573

T 56-VQC2000

Kit (Terminal Block Box Kit)

56-VV5QC21



Formulas

$$L1 = 16n + 45$$

$$L2 = 16n + 184 \quad (1 \text{ power saving unit for } 1 \text{ to } 12 \text{ solenoids})$$


$$L2 = 16n + 205 \quad (2 \text{ power saving units for } 13 \text{ to } 20 \text{ solenoids}) \quad n: \text{Stations (Max. 20 single wire stations)}$$

L \ n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313	329	345	361	377
L2	200	216	232	248	264	280	296	312	328	344	360	376	413	429	445	461	477	493	509	525
L3	225	237.5	262.5	275	287.5	300	325	337.5	350	375	387.5	400	437.5	450	475	487.5	500	512.5	537.5	550
L4	235.5	248	273	285.5	298	310.5	335.5	348	360.5	385.5	398	410.5	448	460.5	485.5	498	510.5	523	548	560.5


M 56-VQC4000

Kit (Multiple Connector Kit)

56-VV5QC41



Multi-connector cable assembly
 AXT100-MC26-015:1.5m
 AXT100-MC26-030:3m
 AXT100-MC26-050:5m



- 2n-Rc1/4,3/8,C8,C10,C12<4(A),2(B)Port>
- Rc1/4:Rc1/4 Thread
- Rc3/8:Rc3/8 Thread
- C8 :One-touch fitting for ø8
- C10:One-touch fitting for ø10
- C12:One-touch fitting for ø12


Formulas
 $L1 = 25n + 106$
 $L2 = 25n + 181.5$ (1 power saving unit for 1 to 12 solenoids)
 $L2 = 25n + 202.5$ (2 power saving units for 13 to 16 solenoids) n: Stations (Max. 16 single wire stations)

L \ n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	131	156	181	206	231	256	281	306	331	356	381	406	431	456	481	506
L2	206.5	231.5	256.5	281.5	306.5	331.5	356.5	381.5	406.5	431.5	456.5	481.5	527.5	552.5	577.5	602.5

S 56-VQC4000

Kit (Serial Transmission Kit) Decentralised Serial wiring

56-VV5QC41
SDA2 Kit (Serial Transmission Kit: 56-EX500)



Formulas

$L1 = 25n + 106$

$L2 = 25n + 173$ (1 power saving unit for 1 to 12 solenoids)

$L2 = 25n + 194$ (2 power saving units for 13 to 16 solenoids)




n: Stations (Max. 16 single wire stations)

L \ n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	131	156	181	206	231	256	281	306	331	356	381	406	431	456	481	506
L2	198	223	248	273	298	323	348	373	398	423	448	473	519	544	569	594

T 56-VQC4000

Kit (Terminal Block Box Kit)

56-VV5QC41



Formulas

$L1 = 25n + 106$

$L2 = 25n + 213$ (1 power saving unit for 1 to 12 solenoids)

$L2 = 25n + 234$ (2 power saving units for 13 to 16 solenoids) n: Stations (Max. 16 single wire stations)


L \ n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	131	156	181	206	231	256	281	306	331	356	381	406	431	456	481	506
L2	238	263	288	313	338	363	388	413	438	463	488	513	538	563	588	613



Decentralised Serial Wiring Series 56-EX250

For more details, other specifications, dimensions, see the specific catalogue.

How to Order



56 - EX250 - S **PR1** - X42

ATEX category 3

Protocol
PR1 PROFIBUS DP

SI Unit Specifications

Model	56-EX250-SPR1-X42	
Protocol	PROFIBUS DP-V0	
Transmission speed	(9.6/19.2/45.45/93.75/187.5/500 kbps), (1.5/3/6/12 Mbps)	
Output specifications	Number of outputs	Max. 32 points
	Output type	P-ch MOS-FET open drain type
	Connected load	Solenoid valve with protection circuit for 24 VDC and 1.5 W or less surge voltage (made by SMC)
	Power supply	22.8 to 22.4 VDC
	Solenoid valve residual voltage	0.3 VDC or less
Input specifications	Number of inputs	Max. 32 points
	Input type	TTL
	Connected block	56-EX250-IE2-X43
	Power supply for block	19.2 to 28.8 VDC
	Current supply for block	Max. 1 A
Current consumption	0.1A or less (inside of SI unit)	
Enclosure	IP67	
Weight	250 g	

II 3G Ex nA II T4 X 5°C ≤ Ta ≤ 45°C
II 3D tD A22 IP67 T66°C X

How to Order

Input block

56 - EX250 - IE **2** - X43

Block type

2 M12 connector, 4 inputs

ATEX category 3

Input Block Specifications

Model	56-EX250-IE2-X43	
Applicable sensor	Current source type (PNP output) Current sink type (NPN output) / converted by a switch	
Rated voltage	24 VDC (Max. 1V of voltage effect against SI unit supply voltage)	
Rated input current	8 mA typ.	
Input delay time	3 msec. Typ.	
Sensor supply current	Max. 30 mA/Sensor	
Enclosure	IP67	
Weight	90 g	

II 3G Ex nA II T4 X 5°C ≤ Ta ≤ 45°C
II 3D tD A22 IP67 T77°C X



Decentralised Serial Wiring Series 56-EX500

- CE

 II 3G Ex nA II T4 X 5°C ≤ Ta ≤ 45°C
 II 3D tD A22 IP65 T57°C X

(Gateway 56-EX500-GPR1A)
- CE

 II 3G Ex nA II T4 X 5°C ≤ Ta ≤ 45°C
 II 3D tD A22 IP65 T53°C X

(Gateway 56-EX500-GDN1-X8)
- CE

 II 3G Ex nA II T5 X 5°C ≤ Ta ≤ 45°C
 II 3D tD A22 IP67 T54°C X

(SI units 56-EX500-Q□01)
- CE

 II 3G Ex nA II T5 X 5°C ≤ Ta ≤ 45°C
 II 3D tD A22 IP67 T52°C X

(SI units 56-EX500-S□01)
- CE

 II 3G Ex nA II T5 X 5°C ≤ Ta ≤ 45°C
 II 3D tD A22 IP65 T60°C X

(Input unit 56-EX500-IB1, Input blocks 56-IE1 to 4)
- CE

 II 3G Ex nA II T5 X 5°C ≤ Ta ≤ 45°C
 II 3D tD A22 IP65 T66°C X

(Input blocks 56-EX500-IE5 to 6)

For more details, other specifications, dimensions, see the specific catalogue.

How to Order

Gateway (GW) Unit



56 - EX500 - G PR1A

ATEX category 3

Communication Protocol

PR1A	PROFIBUS DP
DN1-X8	Device Net (TM)

Input Unit Manifold




Gateway (GW) Unit Specifications

Model	56-EX500-GDN1-X8	EX500-GPR1A
Applicable PLC/Communication protocol	DeviceNet™	PROFIBUS DP-V0
Communication speed	125/250/500 Kbps	(9,6/19,2/45,45/93,75/187,5/500 Kbps),(1,5/3/6/12 Mbps)
Rated voltage	24 V DC	
Power supply voltage range	Input and control unit power supply: 24 VDC ± 10% Solenoid valve power supply: 24 VDC + 10%/−5% (Warning of voltage drop at approx. 20 V or less)	
Current consumption	200 mA or less (single GW unit)	
Inputs/outputs points	Maximum 64 inputs/64 outputs	Maximum 32 inputs/64 outputs
Input/output branches	4 branches (16 inputs/16 outputs per branch)	4 branches (8 inputs/16 outputs per branch)
Branch cable	8 core PVC coated cable	
Branch cable length	5 m or less (Max. total length: 10 m or less)	
Communication connector	M12 connector (8 pins, socket)	
Power connector	M12 connector (5 pins, plug)	
Ambient operating temperature/humidity	+5 to +45°C at 35% to 85% RH (without condensation)	
Enclosure	IP65	
Weight	470 g	

Series 56-EX500

How to Order


Input manifold




When ordering an input block manifold, enter the [Input manifold part no.] + [Input block part no.] together.

The [input block], [end block] and [DIN rail] are included in the input manifold. Refer to How to Order.

Example M8 and M12 on a single manifold



Input block



Input Unit Specifications

Model	56-EX500-IB1
Connected block	Current source type input block (PNP input block) or Current sink type input block (NPN input block)
Communication connector	M12 connector (8-pins, plug)
Number of connection blocks	max. 4 blocks (for 56-EX500-GPR1A) max. 8 blocks (for 56-EX500-GDN1-X8)
Block supply voltage	24 VDC
Block supply current	max. 0.3 A (for 56-EX500-GPR1A) max. 0.65 A (for 56-EX500-GDN1-X8)
Current consumption	100 mA or less (at rated voltage)
Short circuit protection	1A Typ. for each unit (shut off power supply) To restart, remove power to the GW unit once, then reapply it.
Enclosure	IP65
Weight ^{Note)}	100g (Input unit + end block)

Note) Not including the DIN rail weight.

Input Block Specifications

Model	56-EX500-IE1,3,5	56-EX500-IE2,4,6
Applicable sensor	Current source type (PNP output)	Current sink type (NPN output)
Sensor connector	M8 connector (3 pins) or, M12 connector (4 pins)	
Number of inputs	2 inputs/8 inputs (M8 only)	
Rated voltage	24 VDC	
Input delay	1 msec. or less	
Sensor supply current	Max. 30 mA/Sensor	
Enclosure	IP65	
Weight	[For M8: 20g] [For M12: 40g] [8 point integrated type, for M8: 55g]	



Valve for Water and Chemical-base Fluids (2/3 Port Air Operated Valve) Series VCC

CE II 2GD c 75°C (T6X)

How to Order

Valve

VCC1 **2** - **00**

Passage number

2	2 port valve
3	3 port valve
2D	2 port/Diaphragm type (Applicable for 2 liquid paint)

Port size

00	For manifold mounting
02	Rc1/4 (for single unit) <small>Note)</small>
02F	G1/4 (for single unit) <small>Note)</small>

Note) Part number for sub-base
For 2 port: VCC12-S-⁰²_{02F} [^{Rc1/4}_{G1/4}]
For 3 port: VCC13-S-⁰²_{02F} [^{Rc1/4}_{G1/4}]



VCC12(D)-00



VCC13-00



VCC12(D)-02(F)



VCC13-02(F)

Manifold

Standard

VV **M** CC1- **06** **06** **C4**

Type (Passage number)

2	2 port valve, Cleaning valve
3	3 port valve
M	2/3 port valves mixed mounting

Pilot port fitting size

C4	ø4 one-touch fitting (Antistatic)
C6	ø6 one-touch fitting (Antistatic)

2 port valve mountable number



00	No 2 port valves used
02	2 pcs. (colours)
04	4 pcs. (colours)
⋮	⋮

3 port valve mountable number

00	No 3 port valves used
02	2 pcs. (colours)
04	4 pcs. (colours)
⋮	⋮

Note) Maximum mountable valve number: 40 pcs.
(total of 2 port and 3 port valves)

Circuit example



Series VCC

How to Order

Manifold

With gate valve **VV** **M** **CC1-06** **06** **C4-G** **04**

Passage number

2	2 port valve, Cleaning valve
M	2/3 port valves mixed mounting

2 port valve mountable number

00	No 2 port valves used
02	2 pcs. (colours)
04	4 pcs. (colours)
⋮	⋮

3 port valve mountable number

00	No 3 port valves used
02	2 pcs. (colours)
04	4 pcs. (colours)
⋮	⋮

Note) Maximum mountable valve number: 40 pcs. (total of 2 port, 3 port and gate valves)

Gate valve and cleaning valve mountable number



02	Cleaning valve (2 port valve): 1 pc. + Gate valve: 1 pc.
04	Cleaning valve (2 port valve): 3 pcs. + Gate valve: 1 pc.
06	Cleaning valve (2 port valve): 5 pcs. + Gate valve: 1 pc.

Pilot port fitting size

C4	ø4 one-touch fitting (Antistatic)
C6	ø6 one-touch fitting (Antistatic)

* The gate valve and cleaning valve (2 port valve) are not included. They are ordered separately. (Gate valve is equivalent to 2 port valve.)
* When cleaning valve number is an even number, use the blanking plug for 2 port valve.

Circuit example



SUS316L Stainless steel fitting

VCK **K** **0604-02F**

Shape

H	Male connector
K	40° swivel elbow
L	90° swivel elbow

Port size

02F G1/4

* G1/4 bottom seal has a special shape.

Applicable tubing (O.D. x I.D.)

0604	6 x 4
0806	8 x 6
1075	10 x 7.5
1008	10 x 8
1209	12 x 9



VCKH
Male connector



VCKK
40° swivel elbow



VCKL
90° swivel elbow

Option

Blanking Plug Assembly

Type	Model	Description	Qty.
For a 2 port valve	VVCC12-10A-1	Blanking plug (with O-ring)	1
		Hexagon socket head plug (R1/4)	1
For a 3 port valve	VVCC13-10A-1	Blanking plug (with O-ring)	1
		Hexagon socket head plug (R1/4)	2



Specifications

Model	VCC12	VCC13	VCC12D
Passage number	2 port	3 port	2 port (Diaphragm type)
Construction (Fluid contact material)	Poppet seal (PEEK resin + Stainless steel) + Special fluororesin sliding part		Poppet seal (PEEK resin + Stainless steel) + Special fluororesin diaphragm
Fluid	Water/Chemical-based paint, Ink, Cleaning solvent (Water, Butyl acetate), Air		
Operating pressure range (MPa)	0 to 1.0 (Instantaneous pulsation pressure: 1.2)		0 to 0.7 (Instantaneous pulsation pressure: 0.9)
Withstand pressure (MPa)	2		1.5
Pilot pressure (MPa)	0.4 to 0.7		
Orifice size (mm)	ø3.8		
Effective area (mm ²)	6		
Fluid temperature (°C)	5 to 50		
Ambient temperature (°C)	5 to 50		
Explosion proof construction	Explosion protection $\text{C} \text{E} \text{Ex} \text{II} \text{2GD} \text{c} \text{75}^\circ\text{C} \text{(T6X)}$		
Lubrication	Not possible (Default lubricant: White vaseline)		
Mounting orientation	Unrestricted		
Valve leakage (cm ³ /min)	1 or less (3 port valve IN → RETURN: 20 or less) ^{Note 1)}		1 or less ^{Note 2)}

Note 1) Supply pressure: Valve leakage at 1.2 MPa (for air)

Note 2) Supply pressure: Valve leakage at 0.9 MPa (for air)


SUS316L Stainless Steel Fitting Specifications

Applicable tubing	Nylon/Fluoro tubing
Fluid	Water/Chemical-based paint, Ink, Cleaning solvent (Water, Butyl acetate), Air
Max. operating pressure (at 20°C) (MPa)	1.0
Ambient and fluid temperature (°C)	0 to 60°C

Weight

Valve	VCC12 (2 port)	37 g	
	VCC13 (3 port)	48 g	
Blanking plug assembly	For 2 port	29 g	
	For 3 port	45 g	
Manifold block * Valves are not attached.	For 2 port (2 stations, one-piece style)	150 g	
	For 3 port (2 stations, one-piece style)	254 g	
	For gate valve	300 g	
End plate	For 2 port	409 g	
	For 3 port	495 g	
	For 2/3 port mixed mounting	452 g	
Fitting	VCKH	ø6	24 g
		ø8	25 g
		ø10	33 g
		ø12	36 g
	VCKK	ø6	25 g
		ø8	26 g
		ø10	32 g
		ø12	37 g
	VCKL	ø6	29 g
		ø8	30 g
		ø10	37 g
		ø12	41 g

- 2 valves per station (30 mm pitch)
- 2/3 port valves mixed mounting
- Resin manifold block




Series VCC

Manifold Specifications

Series VCC

1. How to Order a Manifold



* This "How to Order" is that of the example below.

① Type (Passage number)

2	2 port valve
3	3 port valve
M	2/3 port valves mixed mounting

② 2 port valve mountable number Note 1)

00	Without 2 port valve
02	2 pcs. (colours)
04	4 pcs. (colours)
⋮	⋮
40	40 pcs. (colors) <small>Note 2)</small>

④ Pilot port fitting size

C4	ø4 one-touch fitting
C6	ø6 one-touch fitting

③ 3 port valve mountable number Note 1)

00	Without 3 port valve
02	2 pcs. (colours)
04	4 pcs. (colours)
⋮	⋮
40	40 pcs. (colors) <small>Note 2)</small>

⑤ Gate valve and cleaning valve mountable number Note 1)


-	Without gate valve <small>Note 3)</small>
G02	Cleaning valve: 1 pc. + Gate valve: 1 pc.
G04	Cleaning valve: 3 pcs. + Gate valve: 1 pc.
G06	Cleaning valve: 5 pcs. + Gate valve: 1 pc.

Note 1) Two valves can be installed per manifold block. Total valve number must be an even number.

Note 2) Maximum valve number is forty (40) valves (colours) by a total of ② + ③ + ⑤.

Note 3) When "Without gate valve" is selected, use 2 port valve of ② as a cleaning valve.


2. How to Order a Valve



① Type (Passage number)

2	2 port valve
3	3 port valve
2D	2 port/Diaphragm type

3. How to Order the Blanking Plug




① Type (Passage number)

2	For 2 port valves
3	For 3 port valves

Used when the number of valves used on the manifold base is an odd number.

4. How to Order the SUS316L Stainless Steel Fitting




① Type (Shape)

K	40° swivel elbow
L	90° swivel elbow
H	Male connector

② Piping port

1209	Piping port for ø12 x ø9
1008	Piping port for ø10 x ø8
1075	Piping port for ø10 x ø7.5
0806	Piping port for ø8 x ø6
0604	Piping port for ø6 x ø4



Fill in this format.

Date: Year ____ / Month ____ / Date ____

Company name		Department		Person in charge	
Phone		Fax		Repeat	<input type="checkbox"/> Repeat <input type="checkbox"/> Not Repeat
Device description		Drawing number		Production number	

Ordered part number (Please order with this part number.)

Manifold valve part no. _____ SMC use _____

Manifold

V V □ C C 1 - □ □ □ □ - □ □ □ □

Valve

V C C 1 □ □ - 0 0

To fill in the blanks □ in the manifold number, please refer to the symbols in the catalogue. Select the valve referring to the specification table.

Specification Sheet

* Fill in the symbol for stainless steel fitting. For others, mark necessary items with a circle.

Unit		Cleaning unit (with gate valve) ^{Note 2)}	Standard unit															
Part number (Mountable valve number)		G06	G04	G02	02	04	06	08	10	12	14	16	18	20				40
2 port valve	Stations ^{Note 1)}	4	2	1	1	3	5	7	9	11	13	15	17	19				39
	Description/Model	5	3	Gate	2	4	6	8	10	12	14	16	18	20				40
	Valve options	2 port valve (Sliding type) VCC12-00																
		2 port valve (Diaphragm type) VCC12D-00																
		Blanking plug for 2 port valve VVCC12-10A-1																
Fitting ^{Note 3)}	Piping port IN port																	

Unit		D side	Standard unit															
Part number (Mountable valve number)			02	04	06	08	10	12	14	16	18	20						40
3 port valve	Stations ^{Note 1)}		1	3	5	7	9	11	13	15	17	19						39
	Description/Model		2	4	6	8	10	12	14	16	18	20						40
	Valve options	3 port valve (Sliding type) VCC13-00																
		Blanking plug for 3 port valve VVCC13-10A-1																
	Fitting ^{Note 3)}	Piping port IN port																
	Piping port RETURN port																	

Select stainless steel fitting for IN, RETURN port from the table below, and enter the symbol into the specification table.

Symbol	Description	Part no.
A	For piping ø12 x ø9 40° swivel elbow	VCKK1209-02F
B	For piping ø10 x ø8 40° swivel elbow	VCKK1008-02F
C	For piping ø10 x ø7.5 40° swivel elbow	VCKK1075-02F
D	For piping ø8 x ø6 40° swivel elbow	VCKK0806-02F
E	For piping ø6 x ø4 40° swivel elbow	VCKK0604-02F

Symbol	Description	Part no.
F	For piping ø12 x ø9 Male connector	VCKH1209-02F
G	For piping ø10 x ø8 Male connector	VCKH1008-02F
H	For piping ø10 x ø7.5 Male connector	VCKH1075-02F
J	For piping ø8 x ø6 Male connector	VCKH0806-02F
K	For piping ø6 x ø4 Male connector	VCKH0604-02F

Fill in the model number in the table below for connecting the fitting to the OUT port. (See SUS316L stainless steel fitting type.) For connecting the elbow union, the piping direction is on top (IN, RETURN port side).

OUT port Stainless steel fitting V C K □ □ □ □ - 0 2 F

Note 1) Two valves can be installed per manifold block. Assign two valves in one square.

Note 2) Please order a cleaning unit when the gate valve is necessary.

Note 3) When the fitting is necessary for IN, RETURN port, please order by selecting the necessary stainless steel fitting symbol in the port of each station. For 40° swivel elbow, the piping direction is on D side.

Serial No. _____

Customer code		U/C			Department code		Code for person in charge		Registered image no.	
Fill in for faxed order	Customer's order no.				Date of delivery				SMC order no.	

----- Component list -----

	Part no.	Qty.	Part no.	Qty.	Part no.	Qty.
1		6		11		
2		7		12		
3		8		13		
4		9		14		
5		10		15		

Manifold Specifications — Example of how to fill in

Condition	Valve type		Valve arrangement	Fitting arrangement	
	2 port valve		7 pcs.	IN port	ø10 x ø8 (40° swivel elbow)
	3 port valve		24 pcs.	IN port	ø12 x ø9 (40° swivel elbow)
				RETURN port	ø6 x ø5 (Male connector)
	Cleaning unit	Gate valve	1 pc.		
Cleaning valve		4 pcs.	IN port	ø8 x ø6 (40° swivel elbow)	
			OUT port	ø10 x ø8 (90° swivel elbow)	
			Pilot port	One-touch fitting for ø4	

Put "M", because 2 port valves (including a cleaning unit) and 3 port valves are installed together.

Seven (7) 2 port valves are installed. Since two valves are installed per manifold base, it must be an even number, so the number of the valve that can be installed is "08". * Specify four (4) stations for manifold.

When twenty-four (24) 3 port valves are used, specify "24". * Specify twelve (12) stations for manifold.

Specify when the gate valve is necessary for cleaning the valve. This example requires one gate valve and four cleaning valves, but specify "06" as the number of valves that can be installed, as this must be an even number.

Manifold Valve

The upper table is for 2 port valves. The lower is for 3 port valves.

Sheet

* Fill in the symbol for stainless steel fittings. For others, mark necessary items with a circle.

To fill in the blanks in the manifold number, please refer to the symbols in the catalogue. Select the valve referring to the specification table.

Pilot port piping size

Part number (Mountable valve number)	Stations (Note 1)	Description/Model	Fitting (Note 3)	Standard unit																			
				G06	G04	G02	02	04	06	08	10	12	14	16	18	20	24	28	32	36	40		
2 port valve - Valve options - Fitting	4 5	2 port valve (Sliding type) VCC12-00	IN port	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○			
		2 port valve (Diaphragm type) VCC12D-00	IN port	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○			
		Blanking plug for 2 port valve VVCC12-10A-1	IN port	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○			
3 port valve - Valve options - Fitting	1 2	3 port valve (Sliding type) VCC13-00	IN port	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○			
		Blanking plug for 3 port valve VVCC13-10A-1	IN port	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○			
		RETURN port	IN port	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○			

Select stainless steel fitting for IN, RETURN port from the table below, and enter the symbol into the specification table.

Symbol	Description	Part no.
A	For piping ø12 x ø9 40° swivel elbow	VCKK1209-02F
B	For piping ø10 x ø8 40° swivel elbow	VCKK1008-02F
C	For piping ø10 x ø7.5 40° swivel elbow	VCKK1075-02F
D	For piping ø8 x ø6 40° swivel elbow	VCKK0806-02F
E	For piping ø6 x ø4 40° swivel elbow	VCKK0604-02F

Symbol	Description	Part no.
F	For piping ø12 x ø9 Male connector	VCKH1209-02F
G	For piping ø10 x ø8 Male connector	VCKH1008-02F
H	For piping ø10 x ø7.5 Male connector	VCKH1075-02F
J	For piping ø8 x ø6 Male connector	VCKH0806-02F
K	For piping ø6 x ø4 Male connector	VCKH0604-02F

Fill in the model number in the table below for connecting the fitting to the OUT port. (See SUS316L stainless steel fitting type.) For connecting the elbow union, the piping direction is on top (IN, RETURN port side).

OUT port Stainless steel fitting **V C K L 7008 - 0 2 F**

Note 1) Two valves can be installed per manifold block. Assign two valves in one square.
 Note 2) Please order a cleaning unit when the gate valve is necessary.
 Note 3) When the fitting is necessary for the IN, RETURN port, please order by selecting the necessary stainless steel fitting symbol in the port of each. For 40° swivel elbow, piping direction is on D side.

Customer/SMC use						Serial No.	
Customer code	U/C	Department code	Code for person in charge	Registered image no.			
Fill in for faxed order	Customer's order no.	Date of delivery	SMC order no.				
Part no.	Qty.	Part no.	Qty.	Part no.	Qty.		
1 VVMCC1-0824C4-G06	1	6 VCKK1008-02F	7	11			
2 VCC12-00	12	7 VCKK0806-02F	4	12			
3 VCC13-00	24	8 VCKH0604-02F	24	13			
4 VVCC12-10A-1	2	9 VCKL1008-02F	1	14			
5 VCKK1209-02F	24	10		15			

2 port valve is specified for the gate valve and the cleaning valve. 7 valves + 1 valve + 4 valves = 12 valves



ATEX Compliant 2 Port Steam Valve

Series 56-VND

CE II 3G 195°C (T3)
-5°C ≤ Ta ≤ 60°C

How to Order

Air operated **56-VND** **2** **0** **D** **S** - **15A** -

ATEX category 3

Body option

-	Standard (Copper alloy)
S*	Stainless steel body

* Threaded type only

Thread type

-	Rc
F	G
N	NPT
T	NPTF

Valve size

Symbol	Orifice dia. (mm)	Symbol			Symbol	Port size Rc
		0 N.C.	2 N.O.	4 N.C.		
1	ø7	—	●	●	6A	1/8
		—	●	●	8A	1/4
		—	●	●	10A	3/8
2	ø15	●	●	—	10A	3/8
		●	●	—	15A	1/2
3	ø20	●	●	—	20A	3/4
4	ø25	●	●	—	25A	1
5	ø32	●	●	—	32A	1 1/4
		●	●	—	32F	1 1/4 B Flange
6	ø40	●	●	—	40A	1 1/2
		●	●	—	40F	1 1/2 B Flange
7	ø50	●	●	—	50A	2
		●	●	—	50F	2B Flange


Option

-	None
B*	With bracket
L	With indicator light (visual verification of operation)
BL*	With bracket and indicator light (visual verification of operation)

* Brackets (for valve size 1/2/3/4 only) will be assembled at the time of shipment.
Bracket part no.
Valve size 1: VN1-A16 (with thread)
Valve size 2 to 4: VN□-16

Note: All other specifications (dimensions, drawings, etc.) are the same as the non ATEX type.

JIS Symbol




Model

Model	Port size		Orifice dia. ø (mm)	Flow characteristics Av x 10 ⁻⁶ m ²	Mass (kg)
	Rc	Flange ^{Note)}			
56-VND10□D-6A	1/8	—	7	26	0.3
56-VND10□D-8A	1/4	—		28	
56-VND10□D-10A	3/8	—		31	
56-VND20□D-10A	—	—	15	120	0.6
56-VND20□D-15A	1/2	—		130	
56-VND30□D-20A	3/4	—	20	240	0.9
56-VND40□D-25A	1	—		25	
56-VND50□D-32A	1 1/4	—	32	440	2.3
56-VND50□D-32F	—	32		40	
56-VND60□D-40A	1 1/2	—	40	920	7.2
56-VND60□D-40F	—	40		50	
56-VND70□D-50A	2	—	50	1500	10.8
56-VND70□D-50F	—	50			

Note) The companion flange is JIS B 2210 10K (standard) or its equivalent.

Table ① Operating pressure - Pilot pressure (N.O.)



Valve Specifications

Fluid (Main piping)		Steam
Fluid temperature		-5 to 180°C ^{Note 1)}
Ambient temperature		-5 to 60°C ^{Note 1)}
Proof pressure		1.5 MPa
Operating pressure range		0 to 0.97 MPa
External pilot air	Pressure	N.C. 0.3 to 0.7 MPa
		N.O. 0.1 + 0.25 x (Operating pressure) to 0.25 + 0.25 x (Operating pressure) MPa Refer to below "Graph (1)".
	Lubrication	Not required
Temperature		-5°C to 60°C
ATEX Category		CE II 3G 195°C (T3) -5°C ≤ Ta ≤ 60°C
Seal material		PTFE

Note 1) No freezing





High Purity Chemical Valve Series 55-LVA

55-LVA10 and 55-LVA12 II 2G c IIB T6 X 0°C ≤ Ta ≤ +50°C II 2G c IIB T4 X 0°C ≤ Ta ≤ +60°C Special condition X "Protect for impact"
55-LVA2□, 55-LVA3□, 55-LVA4□, 55-LVA5□, 55-LVA6□ and 55-LVA200 II 2GD c IIB 80°C T6 X 0°C ≤ Ta ≤ +50°C II 2GD c IIB 130°C T4 X 0°C ≤ Ta ≤ +60°C Special condition X "Protect for impact"

Note) The manifold type is not available with ATEX certification

How to Order Valves (Single Type)

55-LVA 2 0 - 02 - A

Body class

Symbol	Body class	Orifice dia
1	1	ø2
2	2	ø4
3	3	ø8
4	4	ø12
5	5	ø20
6	6	ø22

Valve type

0	N.C.
1	N.O.
2	Double acting

Note) Refer to "Variations" in the table below for valve type combinations.

Port size

Symbol	Port size	Body class
01	1/8	1
02	1/4	2
01	1/8	3
02	1/4	3
03	3/8	3
03	3/8	4
04	1/2	4
04	1/2	5
06	3/4	5
10	1	6

Thread type

Symbol	Thread type
-	Rc
N	NPT
F	G

Option

-	None
1	With flow rate adjustment
2	With by-pass
3	With flow rate adjustment & by-pass
4	With indicator

Note) Refer to "Variations" in the table below for option combinations. Options can not be combined each other.

Material

Symbol	Body	Actuator section End plate	Dia- phragm	Applicable option				Note
				1	2	3	4	
A	Stainless steel	PPS —	PTFE	●			●	—
B	PPS	PPS	PTFE	●			●	Except 55-LVA50/60
C	PFA	PPS	PTFE	●	●	●	●	Except 55-LVA10/50/60
D	Stainless steel	PPS —	NBR	●			●	Except 55-LVA60
E	Stainless steel	PPS —	EPR	●			●	Except 55-LVA60
F	PFA	PVDF	PTFE					Hydrofluoric acid compatible (Only 55-LVA40)
G	PPS	PPS	NBR	●			●	Except 55-LVA50/60
H	PPS	PPS	EPR	●			●	Except 55-LVA50/60
N	PFA	PPS	PTFE	●	●	●	●	Ammonium hydroxide compatible Except 55-LVA10/50/60

Variations

Type	Symbol	Valve type	Model									
			Orifice diameter									
			55-LVA10	55-LVA20	55-LVA30	55-LVA40	55-LVA50	55-LVA60				
			Body material (Note 1)									
			Port size									
			1/8	1/4	1/8	1/4	1/4	3/8	1/2	1/2	3/4	1
			Stainless steel (SUS316)									
			○	○	○	○	○	○	○	○	○	○
			PPS									
			○	○	—	○	—	○	—	—	—	—
			PFA									
			—	—	—	○	—	○	—	—	—	—
Basic type	 .PA .PB .PA B H A B H A B H A N.C. N.O. Double acting	N.C.	○	○	○	○	○	○	○	○	○	○
		N.O.	—	—	○	○	○	○	○	○	○	○
		Double acting	○	○	○	○	○	○	○	○	○	○
With flow rate adjustment	 .PA .PA B H A B H A N.C. Double acting	N.C.	—	—	○	○	○	○	○	○	○	○
		Double acting	—	—	○	○	○	○	○	○	○	○
With by-pass	 .PA .PA B H A B H A N.C. Double acting	N.C.	—	—	—	—	○	—	○	—	—	—
		Double acting	—	—	—	—	○	—	○	—	○	—
With flow rate adjustment & by-pass	 .PA .PA B H A B H A N.C. Double acting	N.C.	—	—	—	—	○	—	○	—	—	—
		Double acting	—	—	—	—	○	—	○	—	—	—
With indicator	 .PA B H A N.C.	N.C.	—	—	○	○	○	○	○	○	○	○

Note) Refer to the "Material" table for the applicable optional body materials.

High Purity Chemical Valve **Series 55-LVA**

Standard Specifications



Basic type



With flow rate adjustment

Model		55-LVA10	55-LVA20	55-LVA30	55-LVA40	55-LVA50	55-LVA60
Orifice diameter		ø2	ø4	ø8	ø12	ø20	ø22
Port size		1/8, 1/4	1/8, 1/4	1/4, 3/8	3/8, 1/2	1/2, 3/4	1
Flow characteristics	$Av \times 10^{-6}m^2$	1.7	8.4	40.8	79.2	144	192
	Cv	0.07	0.35	1.7	3.3	6	8
Withstand pressure (MPa)		1					
Operating pressure (MPa)		0 to 0.5				0 to 0.4	
Back pressure (MPa)	N.C./N.O. ^{Note 2)}	0.15 or less	0.3 or less			0.2 or less	
	Double acting	0.3 or less	0.4 or less			0.3 or less	
Valve leakage (cm ³ /min)		0 (with water pressure)					
Pilot air pressure (MPa)		0.3 to 0.5					
Pilot port size		M5		1/8			
Fluid temperature (°C)	Temperature class T6	0 to 50					
	Temperature class T4	0 to 100 ^{Note 1)}					
Ambient temperature (°C)	Temperature class T6	0 to 50					
	Temperature class T4	0 to 60					
Weight (kg)	Stainless steel (SUS)	0.12	0.18	0.44	0.86	1.67	1.96
	PPS	0.05	0.08	0.18	0.32	—	—
	PFA	—	0.09	0.20	0.35	—	—



Note 1) 0 to 60°C when the diaphragm is NBR or EPR.

Note 2) The N.O. type is not available for 55-LVA10.

Note 3) Contact SMC if the valve will be used with vacuum and B → A flow.

Piping

⚠ Caution

1. Avoid using metal fittings with a resin body (taper threads).


This can cause damage to the valve body.

Series 55-LVA


Dimensions

Body material: Stainless steel

Basic type




With flow rate adjustment



Dimensions (mm)

Model	S
55-LVA2□	12.5
55-LVA3□	24
55-LVA4□	29
55-LVA5□	34.5
55-LVA6□	36

With indicator



Dimensions (mm)

Model	W
55-LVA20	66.5
55-LVA30	89.5
55-LVA40	110
55-LVA50	140.5
55-LVA60	148

Dimensions

(mm)


Model	A	B	C	E	F	G	H	K	L	N	P	Q	R
55-LVA1□	20	33	49.5	10	M5	27.5	11	—	13	27.5	Rc 1/8, 1/4 NPT 1/8, 1/4 G 1/8, 1/4	M5	4.2
55-LVA2□	30	33	57	10	M5	31	13	22	22	26			M3
55-LVA3□	36	47	78.5	13	M6	42.5	17.5	37	26	38.5	Rc 1/4, 3/8 NPT 1/4, 3/8 G 1/4, 3/8		
55-LVA4□	46	60	95.5	16	M8	54.5	18	47.5	33.5	47.5	Rc 3/8, 1/2 NPT 3/8, 1/2 G 3/8, 1/2	Rc 1/8 NPT 1/8 G 1/8	Rc 1/8 NPT 1/8 G 1/8
55-LVA5□	58	75	122.5	19	M8	61.5	27.5	60	43	55.5	Rc 1/2, 3/4 NPT 1/2, 3/4 G 1/2, 3/4		
55-LVA6□	58	85	130	24	M8	69	27.5	60	43	63	Rc 1 NPT 1 G1		

High Purity Chemical Valve *Series 55-LVA*

Dimensions

Body material: PPS



Basic type



55-LVA10


With flow rate adjustment

With indicator



Dimensions (mm)

Model	S
55-LVA2□	12.5
55-LVA3□	24
55-LVA4□	29
55-LVA5□	34.5



Dimensions (mm)

Model	W
55-LVA20	67
55-LVA30	88.5
55-LVA40	110.5
55-LVA50	147

Dimensions

(mm)





Model	A	B	C	D	E	G	H	J	K	L	M	N	P	Q	R
55-LVA1□	20	33	49.5	—	10	27.5	11	—	4	11	—	27.5	Rc 1/8, 1/4 NPT 1/8, 1/4 G1/8, 1/4	M5	4.2
55-LVA2□	30	36	57.5	44	11	31.5	13	4	20	37	3.5	26.5	Rc 1/4 NPT 1/4 G1/4		M3
55-LVA3□	36	47	77.5	56	15	41.5	17.5	7.5	34	46	5.5	37.5	Rc 3/8 NPT 3/8 G3/8	Rc 1/8 NPT 1/8 G1/8	Rc 1/8 NPT 1/8 G1/8
55-LVA4□	46	60	96.5	68	22	55	18	8	42	57	5.5	48	Rc 1/2 NPT 1/2 G1/2		

Series 55-LVA


Dimensions

Body material: PFA


Basic type



With flow rate adjustment



With indicator



Dimensions (mm)

Model	S
55-LVA2□	12.5
55-LVA3□	24
55-LVA4□	29

Dimensions (mm)

Model	W
55-LVA20	70.5
55-LVA30	92.5
55-LVA40	110.5

Dimensions

Model	A	B	C	D	E	G	H	J	K	L	M	N	P	Q	R	U
55-LVA2□	30	36	61	44	14.5	35	13	4	20	37	3.5	30	Rc 1/4 NPT 1/4 G 1/4	—	M5	M3
55-LVA3□	36	47	81.5	56	19	45.5	17.5	7.5	34	46	5.5	41.5	Rc 3/8 NPT 3/8 G 3/8	—	Rc 1/8 NPT 1/8 G 1/8	Rc 1/8 NPT 1/8 G 1/8
55-LVA4□	46	60	96	68	22	55	18	8	42	57	5.5	48	Rc 1/2 NPT 1/2 G 1/2	—	Rc 1/8 NPT 1/8 G 1/8	Rc 1/8 NPT 1/8 G 1/8

3 Port Series 55-LVA



Standard Specifications

Model		55-LVA200
Orifice diameter		ø4
Port size		1/4
Flow characteristics	Av x 10 ⁻⁶ m ²	7.2
	Cv	0.3
Withstand pressure (MPa)		1
Operating pressure (MPa)		0 to 0.5
Valve leakage (cm ³ /min)		0 (with water pressure)
Pilot air pressure (MPa)		0.4 to 0.5
Pilot port size		M5
Max. operating frequency		1.0
Fluid temperature (°C)	Temperature class T6	0 to 50
	Temperature class T4	0 to 100
Ambient temperature (°C)	Temperature class T6	0 to 50
	Temperature class T4	0 to 60
Weight (kg)		0.162

How to Order Valve

55-LVA 2 0 0 – 02 □ – C

Body class

Symbol	Body class	Orifice dia.
2	2	ø4

Valve type

0	N.C.
---	------

Thread type

Symbol	Thread type
-	Rc
N	NPT

Port size


Symbol	Port size
02	1/4

Material

Symbol	Body	Actuator section	Diaphragm
C	PFA	PPS	PTFE

Series 55-LVA

Dimensions





Safety Instructions

The following safety instructions are intended to prevent hazardous situations and/or equipment damage. The instructions indicate the level of potential hazard by labeling "**Caution**", "**Warning**", or "**Danger**". To ensure safety, please observe all safety practices, including ISO 4414 ^{Note 1)}, JIS B8370 ^{Note 2)}.

 **Caution** : Operator error could result in injury or equipment damage.

 **Warning** : Operator error could result in serious injury or loss of life.

 **Danger** : In extreme conditions, there is a possibility of serious injury or loss of life.

Note 1) ISO 4414: Pneumatic fluid power – Recommendations for the application of equipment to transmission and control systems.

Note 2) JIS B 8370: Pneumatic system axion

Warning

1. The compatibility of pneumatic equipment is the responsibility of the person who designs the pneumatic system or decides its specifications.

Since the products specified here are used in various operating conditions, their compatibility with a specific pneumatic system must be based on specifications or post analysis and/or tests to meet a specific requirement.

2. Only trained personnel should operate pneumatically machinery and equipment.

Compressed air can be dangerous if an operator is unfamiliar with it. Assembly, handling or repair of pneumatic systems should be performed by trained and experienced operators.

3. Do not service machinery/equipment or attempt to remove components until the safety of the worker is confirmed.

1. Inspection and maintenance of machinery/equipment should only be performed after confirming that all safety locked-out control positions are engaged.
2. When equipment is to be removed, confirm that all safety precautions have been followed. Cut the pressure supply for the equipment and exhaust all residual compressed air in the system.
3. Before restarting any machinery/equipment exercise caution to prevent quick extension of a cylinder piston rod, etc. (Bleed air into the system gradually to create back pressure.)

4. Contact SMC if the product will be used in any of the following conditions.

1. Conditions and environments beyond the given specifications or if product is used outdoors.
2. Installation on equipment in conjunction with atomic energy, railway, air navigation, vehicles, medical equipment, food and beverage, recreation equipment, emergency stop circuits, press applications or safety equipment.
3. An application which has the possibility of having a negative affect on people, property, or applications with special safety requirements.



Common Precautions

Be sure to read before handling.

Selection

⚠ Warning

1. Confirm specifications.

Products represented in this catalogue are designed for use in compressed air applications only (including vacuum), unless otherwise indicated. Do not use the products outside of their designed parameters. Contact SMC when using the product with fluids other than compressed air (including vacuum).

Installation

⚠ Warning

1. Do not install unless the safety instructions have been read and understood.

Keep this catalogue on file for future reference.

2. Maintenance

When installing the product, allow for maintenance access.

3. Tightening torque

When installing the product, follow the torque specification.

Piping

⚠ Caution

1. Before piping

Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil and other debris from inside the pipe.

2. Sealant tape

When installing piping or a fitting into a port, make sure that the sealant material does not clog the pressure port. Leave the first 1.5 to 2 thread turns exposed at the end of the pipe/fitting when using sealant tape.

Air Supply

⚠ Warning

1. Operation fluid

Consult with SMC when using the product in applications which use fluids other than compressed air (including vacuum).

Regarding products for general fluids, consult with SMC regarding applicable fluids.

2. Large amount of drainage.

Compressed air containing larger amount of drainage can cause malfunction of pneumatic equipment.

Please installation of an air dryer and mist separator (Drain Catch) before air filter.

3. Drain

If condensation in the air filter is not emptied on a regular basis, condensation that flows to the outlet side can cause a malfunction. If it is difficult to check and remove, installation of a filter with an auto-drain function is recommended. Refer to Best Pneumatics for details on compressed air quality.

4. Use clean air

Do not use compressed air which includes chemicals, synthetic oils containing organic solvents, salt, or corrosive gases, etc., as this can cause damage or malfunction.

Environment

⚠ Warning

1. Do not use in an environment where the product is directly exposed to corrosive gases, chemicals, sea water, water or steam.

2. In locations which receive direct sunlight, provide a protective cover, etc.

3. Do not operate in locations where vibration or impact occurs.

4. Do not use in locations where radiated heat will be received from nearby heat sources.

5. Avoid striking the product with a metallic object.

6. Avoid using this product in a non-explosive environment which can become explosive due to air leakage.

Maintenance

⚠ Warning

1. Maintenance procedures are outlined in the operation manual.

Failure to follow proper procedures can result in product malfunction and or lead to damage to the equipment or machine.

2. Maintenance

If handled improperly, compressed air can be dangerous. Assembly, handling and repair of pneumatic systems should only be performed by qualified personnel.

3. Drain

Remove condensation from the filter bowl on a regular basis.

4. Shut down before maintenance

Before attempting any kind of maintenance confirm that the supply pressure is shut off and all residual air pressure is released from the system to be worked on.

5. Start-up after maintenance

Apply operating pressure and power to the equipment, then check for proper operation and possible air leaks. If operation is abnormal, verify product set-up parameters.

6. Do not make any modification to the product.

SMC products “out of scope” of the ATEX Directive

Products that are out of scope of the ATEX Directive do not need a declaration of conformity to ATEX for use in potentially explosive atmospheres. These products can be used in ATEX zones as specified.

SMC products which are out of scope of the ATEX Directive match part of the definitions of components or equipment (see ATEX Directive Article 1(3)).

See below for definitions of components and equipment.

For “equipment out of scope” and also equipment within the scope, the user has the responsibility for hazards arising from the assembly of several products. For “components out of scope”, the user has the responsibility to assess the suitability of using these products in an explosive atmosphere and in his application.

Equipment out of scope

Equipment is defined by the ATEX Directive as “*machines, apparatus, fixed or mobile devices, control components and instrumentation thereof and detection or prevention systems which, separately or jointly, are intended for the generation, transfer, storage, measurement, control and conversion of energy and/or the processing of material and which are capable of causing an explosion through their own potential sources of ignition.*” (Article 1(3))

Out of scope

Equipment in scope of the ATEX directive has an autonomous function in a process and an ignition source of its own.

Products that fit the definition of equipment but do not have an ignition source of their own are “out of scope”.

Therefore products such as hand valves, pressure gauges, pressure regulators etc are “out of scope” if an Ignition Hazard Assessment shows that they do not have any ignition sources of their own. This does not include ignition hazards that arise from the assembly of these products in a circuit. An example for this is heat due to adiabatic compression, which can occur in a dead ended pipe when the pressure cycles but also at a closed valve or in a pressure gauge.

SMC can supply a declaration confirming that “equipment out of scope” does not have any ignition sources of their own for use in given zones. Please contact SMC if you require a declaration.

Table 1: SMC products (equipment), which are out of scope because they do not have any potential ignition source of their own.

Product description	Series	Out of scope for zone:	Note
Heavy duty Auto Drain	ADH4000	1, 2	1
Air filters	AF10/20/30/40/50/60	1, 2, 21, 22	1
Main line filters	AFF2B~AFF75B	1, 2, 21, 22	1
Mist separators	AM150~850	1, 2, 21, 22	1
Micro mist separators	AMD150~850, AMD801	1, 2, 21, 22	1
Super mist separators	AME150~850	1, 2, 21, 22	1
Odour removal filters	AMF150~850, AMF801	1, 2, 21, 22	1
Water separators	AMG150~850	1, 2, 21, 22	1
Micro mist separator with pre-filter	AMH150~850	1, 2, 21, 22	1
Clean gas filter	SFA, SFB, SFC	1, 2, 21, 22	1
Micro mist separator	AFD20/30/40	1, 2, 21, 22	1
Mist separator	AFM20/30/40	1, 2, 21, 22	1
Lubricator	AL10/20/30/40/50/60	1, 2, 21, 22	1, 2
Large flow lubricator	AL800/900	1, 2, 21, 22	1, 2
MR Unit	AMR3000~6000	1, 2	1
Regulator	AR10/20/25/20/30/40/50/60	1, 2, 21, 22	1, 2
Pilot operated regulator	AR425 bis 935	1, 2, 21, 22	1
Miniature regulator	ARJ	1, 2, 21, 22	1
Manifold regulator	ARM5, ARM10/11, ARM1000/2000/2500/3000	1, 2, 21, 22	1, 2, 3
Precision regulator	ARP20~40	1, 2, 21, 22	1, 2
Regulator for 2 MPa	ARX	1, 2, 21, 22	1
Filter regulator	AW10/20/30/40/60	1, 2, 21, 22	1, 2
Clean regulator	SRH, SRP11#1	1, 2, 21, 22	1
Air hydro Converter	CCT	1, 2	1
Pressure Gauges	G(A)14/15/27/33/36/46/46E, GZ46, GC3, GD40	1, 2, 21, 22	1
Booster relay	IL100	1, 2	1
Lock up valve	IL201/211/220	1, 2	1
Precision regulator	IR1000/2000/3000	1, 2	1
Vacuum regulator	IRV1000/2000/3000, IRV10/20	1, 2	1
Filter regulator	IW212~217	1, 2	1
Hand valve	VH200/201/400/401	1, 2, 21, 22	1
Finger valve	VHK2	1, 2	1

Product description	Series	Out of scope for zone:	Note
2 Port Micro Mechanical Valve	VM11□□-4N(U)-□□□	1, 2, 21, 22	1, 4, 5, 6
2/3 Port Mechanical Valve	VM12□-□□□-□□□, VM131-□□□-35□ VM220-□02-□□□, VM230-□02-35□	1, 2, 21, 22	1, 4, 5, 6
3 port mechanical valve	VM430-□01-□□□, VM830-□01-□□	1, 2, 21, 22	1, 5, 6
5 port mechanical valves	VZM45□-□01-□□□-(F), VZM55□-□01-□□□-(F) VFM35□-□02-□□□-(F), VFM25□-□02-□□□-(F)	1,2, 21, 22	1, 5, 6
3 port residual pressure release valve	VHS20/30/40/50	1, 2, 21, 22	1
Multistage ejector	ZL	1, 2	1, 2

Note 1:

- Limited to explosive atmospheres types IIA, IIB
- It is the circuit designer's responsibility to ensure significant heat generation due to compression of operating gas does not occur.
- The explosive atmosphere is not allowed to enter the pneumatic circuit, even in case of expected malfunction.
- The product is not intended for use in an environment where stray electric currents can be induced or where cathodic corrosion protection is used.
- Exhaust air or leakage should not be allowed to whirl up gathered dust and create a potentially explosive dust atmosphere.

Note 2:

Excluding options with electrical pressure/vacuum/level switch or electrical valve

Note 3:

For ARM10/11, ARM5: Excluding options with 3-way valve.

Note 4:

2 port only, 3 port excluded: for 3-position twist selector (VM100, 200): 3 port only, 5 port excluded.

Note 5:

For types with roller, the friction between roller and its axle must be assessed with the assembly the valve is used for.

Note 6:

The valves must not be actuated beyond the total travel given in the documentation, even in the case of expected malfunction.

Note 7:

Excluding option Z: with miniature indicator.

Components

"Components" are defined by the ATEX Directive as "any item essential to the safe functioning of equipment and protective systems but with no autonomous function." (Article 1(3))
It is the users' responsibility to assess components when he assembles them into equipment or protective systems covered by the ATEX Directive.

Out of scope

Products that do not have an autonomous function and are not essential to the safe functioning of ATEX equipment and protective systems are out of scope of the ATEX Directive.

SMC products which are out of scope as they do not have an autonomous function and which SMC does not explicitly intend for the safe functioning of ATEX equipment and protective systems are listed in Table 2. These have to be assessed by the user, when he carries out the Ignition Hazard Assessment of his assembly.

Table 2: SMC products without autonomous function (components), which are out of scope because they are not (intended to be) essential to the safe functioning of ATEX equipment and protective systems

Product description	Series	Product description	Series
Check valve	AK, AKB, AKH	Multi holder	TM, TMA
Silencers	AN□, 25□□	Holder	TMH
Quick exhaust valve	AQ	Shuttle valve	VR12□□, VR12□□F
Speed controller	AS, ASP, ASD	Cross interface	Y24~Y54
Multi-connector	DM, KDM	Vacuum pads	ZP
Self align fittings	H, DL, L, LL	Valve for Water and Chemical-base Fluids, for manifold mounting	VCC12(D)-00
Floating joint	JA, JB, JS	Brackets	Mounting brackets for cylinders, FRL, valves and so on when sold on their own.
Insert fittings	KF, KFG	Manifold base	SS5Y5-20-□□-(□□□) SS5Y5-41-□□-□□(□) SS5Y5-42-□□-□□(□) SS5Y7-20-□□-(□□□) SS5Y7-42-□□-□□(□)
S Couplers	KK, KKA, KK130		
Fittings	KQ, KQ2, KP, KA, KG, KJ, KM, KR, KW		
Miniature fittings	M, MS		
Tubing	T, TS, TU, TUS, TUH, TRB, TRS, TRBU, TA, TPH, TPS		

Note) Out of scope for / can be used in all zones subject to assessment by user.



www.smc.eu



DKI-50185-C-UK