

G-CUT SC PU B GLOVES

Update: 18/05/2021

Item #	EAN	Product
887680	3660338410710	Size 6
887681	3660338410727	Size 7
887682	3660338410734	Size 8
887683	3660338410741	Size 9
887684	3660338410758	Size 10
887685	3660338410765	Size 11



Description

White HPPE fiber/Spandex knitted glove
 Grey polyurethane coating on palm and tips of fingers
 Elastic wrist

Applications

Handling sharp objects in a dry or slightly greasy environment.

Characteristics

The glove offers maximum comfort and added sturdiness.
 The tight knit (gauge 13) gives the glove perfect support, limits the penetration of dirt and offers a good touch.
 The HPPE/Spandex thread provides outstanding properties against cuts.
 The polyurethane coating at the palm and fingertips provides outstanding abrasion resistance.

Standards and certifications

**UK
CA**

This glove has been tested as per:
 - EN 388: 2016. Protective gloves against mechanical risks. Category II.
 It complies with European Regulation (EU) 2016/425 on Personal Protective Equipment (PPE).
 EU type examination certificate issued by CTC organisme notifié n°0075.

EN388:2016	Level 1	Level 2	Level 3	Level 4	Level 5	Levels G-CUT SC PU B
Abrasion resistance (number of cycles)	100	500	2000	8000	-	4
Blade cut resistance (index)	1,2	2,5	5,0	10,0	20,0	X
Tear resistance (in Newtons)	10	25	50	75	-	4
Perforation resistance (in Newtons)	20	60	100	150	-	2

EN 388:2016



4x42B

Cut (as per EN ISO13997) (N)	Level A	Level B	Level C	Level D	Level E	Level F	Level G-CUT SC PU B
	2	5	10	15	22	30	B (6 N)

Packaging

- Minimum packaging 10 pairs - Cartons of 100 pairs.