

Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- · 1.1 Product identifier 600077
- · Trade name: Zinc-aluminium spray E-COLL
- · Article number: 4317784349161
- · 1.2 Relevant identified uses of the substance or mixture and uses advised against
- · Sector of Use
- SU21 Consumer uses: Private households / general public / consumers
- SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- · Application of the substance / the mixture Anticorrosion additive
- · 1.3 Details of the supplier of the safety data sheet

· Manufacturer/Supplier:

E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH EDE Platz 1 D-42389 Wuppertal Germany

Tel. +49 202 6096-0 e-mail: sdb@ede.de

- · Further information obtainable from: Product safety department
- 1.4 Emergency telephone number: Giftinformationszentrum Mainz Tel.: +49 (6131) 19240

SECTION 2: Hazards identification

· 2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Aerosol 1	H222-H229	Extremely flammable aerosol. Pressurised container: May burst if heated.
Eye Irrit. 2	H319	Causes serious eye irritation.
STOT SE 3	H336	May cause drowsiness or dizziness.
Aquatic Chronic 3	H412	Harmful to aquatic life with long lasting effects.

· 2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 The product is close find and labelled according to the CLP regu

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms



· Signal word Danger

Hazard-determining components of labelling: acetone

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

(Contd. of page 1)

ethyl acetate Hydrocarbons, C9-C11, n-alcanes, isoalcanes, aromatics (<2%) Solvent naphtha (petroleum), light arom.

· Hazard statements

- H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.
- Causes serious eye irritation. H319
- H336 May cause drowsiness or dizziness.
- Harmful to aquatic life with long lasting effects. H412

· Precautionary statements

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P261	Avoid breathing spray.
P271	Use only outdoors or in a well-ventilated area.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if
	present and easy to do. Continue rinsing.
P337+P313	If eye irritation persists: Get medical advice/attention.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P501	Dispose of contents/container in accordance with local/regional/national/international
	regulations.

· Additional information:

EUH066 Repeated exposure may cause skin dryness or cracking.

· 2.3 Other hazards

· Results of PBT and vPvB assessment

- · PBT: Not applicable.
- · vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Chemical characterisation: Mixtures

 Dangerous components: 		
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32-xxxx	butane, pure Flam. Gas 1A, H220 Press. Gas (Comp.), H280	25-<50%
CAS: 67-64-1 EINECS: 200-662-2 Index number: 606-001-00-8 Reg.nr.: 01-2119471330-49	acetone Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	10-<25%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21-xxxx	propane Flam. Gas 1A, H220 Press. Gas (Comp.), H280	10-<25%



Printing date 19.11.2020



Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

	(Cor	ntd. of page 2)
CAS: 141-78-6 EINECS: 205-500-4 Index number: 607-022-00-5 Reg.nr.: 01-2119475103-46-xxxx	ethyl acetate Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	10-<25%
CAS: 1330-20-7 EINECS: 215-535-7 Index number: 601-022-00-9 Reg.nr.: 01-2119488216-32	xylene Flam. Liq. 3, H226 Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315	1-<5%
CAS: 7429-90-5 EINECS: 231-072-3 Index number: 013-002-00-1 Reg.nr.: 01-2119529243-45	aluminium powder (stabilised)	1-<5%
EC number: 919-857-5 Index number: 649-327-00-6 Reg.nr.: 01-2119463258-33-xxxx	Hydrocarbons, C9-C11, n-alcanes, isoalcanes, aromatics (<2%) Flam. Liq. 3, H226 Asp. Tox. 1, H304 STOT SE 3, H336	1-<5%
CAS: 7440-66-6 EINECS: 231-175-3 Index number: 030-001-01-9 Reg.nr.: 01-2119467174-37	zinc powder -zinc dust (stabilized)	1-<5%
CAS: 64742-95-6 EINECS: 265-199-0 Index number: 649-356-00-4 Reg.nr.: 01-2119455851-35-xxxx	Solvent naphtha (petroleum), light arom. Flam. Liq. 3, H226 Asp. Tox. 1, H304 Aquatic Chronic 2, H411 STOT SE 3, H335-H336	1-<5%

· Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· 4.1 Description of first aid measures

- After inhalation: Supply fresh air.
- After skin contact: Immediately wash with water and soap and rinse thoroughly.
- · After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

- · After swallowing: Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- 4.3 Indication of any immediate medical attention and special treatment needed No further relevant information available.

(Contd. on page 4)

EU



Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

(Contd. of page 3)

SECTION 5: Firefighting measures

- · 5.1 Extinguishing media
- · Suitable extinguishing agents:

CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

- · For safety reasons unsuitable extinguishing agents: Water with full jet
- 5.2 Special hazards arising from the substance or mixture Can form explosive gas-air mixtures.
- · 5.3 Advice for firefighters
- · Protective equipment:

Do not inhale explosion gases or combustion gases. Wear self-contained respiratory protective device.

· Additional information Cool endangered receptacles with water spray.

SECTION 6: Accidental release measures

- 6.1 Personal precautions, protective equipment and emergency procedures Wear protective equipment. Keep unprotected persons away. Ensure adequate ventilation
- · 6.2 Environmental precautions:

Inform respective authorities in case of seepage into water course or sewage system. Do not allow to enter sewers/ surface or ground water.

· 6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust). Do not flush with water or aqueous cleansing agents

· 6.4 Reference to other sections

See Section 7 for information on safe handling. See Section 8 for information on personal protection equipment. See Section 13 for disposal information.

SECTION 7: Handling and storage

• **7.1 Precautions for safe handling** Open and handle receptacle with care. Use only in well ventilated areas.

· Information about fire - and explosion protection:



Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

Do not spray onto a naked flame or any incandescent material.



Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

(Contd. of page 4) Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.

· 7.2 Conditions for safe storage, including any incompatibilities

- · Storage:
- Requirements to be met by storerooms and receptacles:
 Store in a cool location.
 Observe official regulations on storing packagings with pressurised containers.
- · Information about storage in one common storage facility: Store away from oxidising agents.
- Further information about storage conditions: Keep container tightly sealed. Protect from heat and direct sunlight.

• 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

· 8.1 Control parameters

• Additional information about design of technical facilities: No further data; see item 7.

 Ingredients with limit values that require monitoring at the workplace: 		
CAS: 6	7-64-1 acetone	
IOELV	Long-term value: 1210 mg/m ³ , 500 ppm	
CAS: 141-78-6 ethyl acetate		
IOELV	Short-term value: 1468 mg/m ³ , 400 ppm Long-term value: 734 mg/m ³ , 200 ppm	

- Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls
- · Personal protective equipment:
- \cdot General protective and hygienic measures:

Wash hands before breaks and at the end of work. Do not inhale gases / fumes / aerosols. Avoid contact with the eyes.

· Respiratory protection:

Not necessary if room is well-ventilated. Use suitable respiratory protective device in case of insufficient ventilation. Self-contained respiratory protective device.

(Contd. on page 6)



Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

(Contd. of page 5)

· Protection of hands:



Protective gloves

Material of gloves

Butyl rubber, BR Recommended thickness of the material: ≥ 0.4 mm

· Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye protection:



Tightly sealed goggles

· Body protection: Solvent resistant protective clothing

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

 Appearance: Form: Colour: Odour: Odour threshold: 	Aerosol Grey Characteristic Not determined.
· pH-value:	Not determined.
 Change in condition Melting point/freezing point: Initial boiling point and boiling range 	-187 °C Not applicable, as aerosol.
· Flash point:	Not applicable, as aerosol.
· Flammability (solid, gas):	Extremely flammable aerosol.
· Ignition temperature:	>200 °C
· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Not determined.



Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

(Contd. of page 6)

 Explosion limits: Lower: Upper: Oxidising properties 	1.1 Vol % 15 Vol % Not determined.
· Vapour pressure at 20 °C:	7,400 hPa
· Density at 20 °C:	0.68 g/cm ³
· Relative density	Not determined.
 Vapour density Evaporation rate 	Not determined. Not applicable.
 Solubility in / Miscibility with water: 	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
 Viscosity: Dynamic: Kinematic: 	Not determined. Not determined.
 Solvent separation test: VOC (EC) % VOC (EC) g/I 	95.50 % 655.2 g/l
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

· 10.1 Reactivity No further relevant information available.

- · 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.
- 10.3 Possibility of hazardous reactions No dangerous reactions known.
- · 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- · 10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

· 11.1 Information on toxicological effects

· Acute toxicity Based on available data, the classification criteria are not met.



Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

			(Contd. of page 7)
· LD/LC50 values relevant for classification:			
	CAS: 106-97-8 butane, pure		
Inhalative	LC50/4h	658 ppm (rat)	
CAS: 67-6	4-1 aceto	one	
Oral	LD50	5,800 mg/kg (rat)	
Dermal	LD50	20,000 mg/kg (rabbit)	
Inhalative	LC50/4h	76 mg/m³ (rat)	
CAS: 74-9	8-6 propa	ane	
Inhalative	LC50/4h	>20 mg/m ³ (rat)	
CAS: 141-	78-6 ethy	/l acetate	
Oral	LD50	5,620 mg/kg (rabbit)	
Inhalative	LC50/4h	1,600 ppm (rat)	
CAS: 1330)-20-7 xyl	lene	
Oral	LD50	4,300 mg/kg (rat)	
Dermal	LD50	2,000 mg/kg (rabbit)	
Hydrocark	oons, C9-	C11, n-alcanes, isoalcanes, aromatics (<2%)	
Oral	LD50	>15,000 mg/kg (rat) (OECD 401)	
Dermal	LD50	3,400 mg/kg (rat) (OECD 402)	
Inhalative	LC50/4h	13,100 ppm (rat) (OECD 403)	
CAS: 6474	12-95-6 S	olvent naphtha (petroleum), light arom.	
Oral	LD50	>6,800 mg/kg (rat)	
Dermal	LD50	>3,400 mg/kg (rab)	
Inhalative	LC50/4h	>10.2 ppm (rat)	

· Primary irritant effect:

· Skin corrosion/irritation Based on available data, the classification criteria are not met.

· Serious eye damage/irritation

Causes serious eye irritation.

• Respiratory or skin sensitisation Based on available data, the classification criteria are not met.

· Additional toxicological information:

\cdot CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)

- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- Carcinogenicity Based on available data, the classification criteria are not met.
- Reproductive toxicity Based on available data, the classification criteria are not met.

· STOT-single exposure

May cause drowsiness or dizziness.

- · STOT-repeated exposure Based on available data, the classification criteria are not met.
- \cdot Aspiration hazard Based on available data, the classification criteria are not met.

EU -



Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

(Contd. of page 8)

SECTION 12: Ecological information

· 12.1 Toxicity

•	· Aquatic toxicity:		
	CAS: 67-64-1 acetone		
	LC50/48h	8,800 mg/l (Daphnia magna)	
	NOEC	430 mg/l (algae)	
	NOEC/16h	1,700 mg/l (Pseudomonas putida)	
	NOEC/48h	1,700 mg/l (Pseudomonas putida) 4,740 mg/l (Pseudokirchneriella subcapitata)	
	96h LC50	5,540 mg/l (Oncorhynchus mykiss)	

- · 12.2 Persistence and degradability No further relevant information available.
- · 12.3 Bioaccumulative potential No further relevant information available.
- · 12.4 Mobility in soil No further relevant information available.
- · Ecotoxical effects:
- · Remark: Harmful to fish
- · Additional ecological information:
- General notes: Harmful to aquatic organisms Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water Do not allow product to reach ground water, water course or sewage system.
- · 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.
- · vPvB: Not applicable.
- · 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods:
- · European waste catalogue

16 05 04* gases in pressure containers (including halons) containing hazardous substances

SECTION 14: Transport information		
· 14.1 UN-Number · ADR, IMDG, IATA	UN1950	
 • 14.2 UN proper shipping name • ADR 	UN1950 AEROSOLS	(Contd. on page 10)

- EU ----



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 19.11.2020	Version number 308	Revision: 19.11.2020
Trade name: Zinc-aluminium spray	/ E-COLL	
· IMDG, IATA	AEROSOLS	(Contd. of page 9)
 • 14.3 Transport hazard class(es) 		
· ADR		
· Class · Label	2 5F Gases. 2.1	
· IMDG, IATA		
· Class · Label	2 Gases. 2.1	
· 14.4 Packing group	2.1	
· ADR	Void	
 · 14.5 Environmental hazards: · Marine pollutant: 	No	
 14.6 Special precautions for use EMS Number: Stowage Code 	F-D,S-U SW1 Protected from sou SW22 For AEROSOLS v litre: Category A. For AE 1 litre: Category B. For V C, Clear of living quarter	with a maximum capacity of 1 ROSOLS with a capacity above VASTE AEROSOLS: Category s.
 Segregation Code 	litre: Segregation as for class 1 except for division 1.4. For AEROSOLS with a c Segregation as for the a For WASTE AEROSOLS	capacity above 1 litre: ppropriate subdivision of class 2.
 14.7 Transport in bulk according Marpol and the IBC Code 	g to Annex II of Not applicable.	
· Transport/Additional informatio	n:	
 ADR Limited quantities (LQ) Excepted quantities (EQ) Transport category 	1L Code: E0 Not permitted as Excepte	
Tunnel restriction code	2 D	(Contd. on page 11)



Printing date 19.11.2020

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

(Contd. of page 10)

- ·IMDG
- · Limited quantities (LQ)
- · Excepted quantities (EQ)
- · UN "Model Regulation":

1L Code: E0 Not permitted as Excepted Quantity UN1950, AEROSOLS, 2.1

SECTION 15: Regulatory information

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

- · Directive 2012/18/EU
- Named dangerous substances ANNEX I Methanol
- · Qualifying quantity (tonnes) for the application of lower-tier requirements 150 t
- · Qualifying quantity (tonnes) for the application of upper-tier requirements 500 t
- · REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3

DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II

None of the ingredients is listed.

· Exposure scenario(s)

Exposure scenario(s) of ingredients (if present) are available on request at: sdb@ede.de

SECTION 16: Other information

Reasons for alterations

· Relevant phrases

H220 Extremely flammable gas.

- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H228 Flammable solid.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.
- H312 Harmful in contact with skin.
- H315 Causes skin irritation.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- H335 May cause respiratory irritation.
- H336 May cause drowsiness or dizziness.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H411 Toxic to aquatic life with long lasting effects.

· Department issuing SDS: Product safety department

· Contact: sdb@ede.de

Version number 308

Revision: 19.11.2020

Trade name: Zinc-aluminium spray E-COLL

(Contd. of page 11)

EU -

· Abbreviations and acronyms: ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road) IMDG: International Maritime Code for Dangerous Goods IATA: International Air Transport Association GHS: Globally Harmonised System of Classification and Labelling of Chemicals EINECS: European Inventory of Existing Commercial Chemical Substances ELINCS: European List of Notified Chemical Substances CAS: Chemical Abstracts Service (division of the American Chemical Society) VOC: Volatile Organic Compounds (USA, EU) LC50: Lethal concentration, 50 percent LD50: Lethal dose, 50 percent PBT: Persistent, Bioaccumulative and Toxic vPvB: very Persistent and very Bioaccumulative Flam. Gas 1A: Flammable gases - Category 1A Aerosol 1: Aerosols – Category 1 Press. Gas (Comp.): Gases under pressure - Compressed gas Flam. Liq. 2: Flammable liquids - Category 2 Flam. Liq. 3: Flammable liquids - Category 3 Flam. Sol. 1: Flammable solids - Category 1 Acute Tox. 4: Acute toxicity - dermal - Category 4 Skin Irrit. 2: Skin corrosion/irritation - Category 2 Eye Irrit. 2: Serious eye damage/eye irritation - Category 2 STOT SE 3: Specific target organ toxicity (single exposure) – Category 3 Asp. Tox. 1: Aspiration hazard – Category 1 Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard - Category 1 Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard - Category 1 Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard - Category 2 Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard - Category 3

·* Data compared to the previous version altered.



Printing date 19.11.2020