

**Synchro-Power® Polyurethane Belts****Product No. Series 7762 (continued)****T10 Pitch — 16mm Wide (continued)**

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-1610-16	7762-2213	161	1610	.26
T10-1700-16	7762-0596	170	1700	.15
T10-1750-16	7762-2214	175	1750	.28
T10-1780-16	7762-2215	178	1780	.29

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-1880-16	7762-2216	188	1880	.30
T10-1960-16	7762-2217	196	1960	.31
T10-2250-16	7762-2218	225	2250	.36

T10 Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-20	7762-2220	26	260	.05
T10-370-20	7762-2221	37	370	.07
T10-400-20	7762-2222	40	400	.08
T10-410-20	7762-2223	41	410	.08
T10-440-20	7762-2224	44	440	.09
T10-450-20	7762-2225	45	450	.09
T10-500-20	7762-2226	50	500	.10
T10-530-20	7762-2227	53	530	.11
T10-560-20	7762-2228	56	560	.11
T10-600-20	7762-2229	60	600	.12
T10-610-20	7762-2230	61	610	.12
T10-630-20	7762-2231	63	630	.13
T10-660-20	7762-2232	66	660	.13
T10-690-20	7762-2233	69	690	.14
T10-700-20	7762-2234	70	700	.14
T10-720-20	7762-2235	72	720	.14
T10-730-20	7762-2236	73	730	.15
T10-750-20	7762-2237	75	750	.15
T10-780-20	7762-2238	78	780	.16
T10-800-20	7762-0230	80	800	.20
T10-810-20	7762-2239	81	810	.16
T10-840-20	7762-2240	84	840	.17
T10-880-20	7762-2241	88	880	.18
T10-890-20	7762-2242	89	890	.18
T10-900-20	7762-2243	90	900	.18
T10-910-20	7762-2244	91	910	.18
T10-920-20	7762-2245	92	920	.18
T10-950-20	7762-0343	95	950	.25
T10-960-20	7762-2246	96	960	.19
T10-970-20	7762-2247	97	970	.19

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-980-20	7762-2248	98	980	.20
T10-1000-20	7762-0356	100	1000	.25
T10-1010-20	7762-2249	101	1010	.20
T10-1080-20	7762-2250	108	1080	.22
T10-1100-20	7762-2251	110	1100	.22
T10-1110-20	7762-2252	111	1110	.22
T10-1140-20	7762-2253	114	1140	.23
T10-1150-20	7762-2254	115	1150	.23
T10-1210-20	7762-2255	121	1210	.24
T10-1240-20	7762-2256	124	1240	.25
T10-1250-20	7762-2257	125	1250	.25
T10-1300-20	7762-2258	130	1300	.26
T10-1320-20	7762-2259	132	1320	.27
T10-1350-20	7762-2260	135	1350	.27
T10-1390-20	7762-2261	139	1390	.28
T10-1400-20	7762-2262	140	1400	.28
T10-1420-20	7762-2263	142	1420	.29
T10-1450-20	7762-2264	145	1450	.29
T10-1460-20	7762-2265	146	1460	.29
T10-1500-20	7762-2266	150	1500	.30
T10-1560-20	7762-2267	156	1560	.31
T10-1600-20	7762-0620	160	1600	.32
T10-1610-20	7762-2268	161	1610	.32
T10-1700-20	7762-0597	170	1700	.19
T10-1750-20	7762-2269	175	1750	.35
T10-1780-20	7762-2270	178	1780	.36
T10-1880-20	7762-2271	188	1880	.38
T10-1960-20	7762-2272	196	1960	.39
T10-2250-20	7762-2273	225	2250	.45

T10 Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-25	7762-2275	26	260	.07
T10-370-25	7762-2276	37	370	.09
T10-400-25	7762-2277	40	400	.10
T10-410-25	7762-2278	41	410	.10
T10-440-25	7762-2279	44	440	.11
T10-450-25	7762-2280	45	450	.11
T10-500-25	7762-2281	50	500	.13
T10-530-25	7762-2282	53	530	.13
T10-560-25	7762-2283	56	560	.14
T10-600-25	7762-2284	60	600	.15
T10-610-25	7762-2285	61	610	.15
T10-630-25	7762-2286	63	630	.16
T10-660-25	7762-2287	66	660	.17
T10-690-25	7762-2288	69	690	.17
T10-700-25	7762-2289	70	700	.18
T10-720-25	7762-2290	72	720	.18
T10-730-25	7762-2291	73	730	.18

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-750-25	7762-2292	75	750	.19
T10-780-25	7762-2293	78	780	.20
T10-800-25	7762-0331	80	800	.25
T10-810-25	7762-2294	81	810	.20
T10-840-25	7762-2295	84	840	.21
T10-880-25	7762-2296	88	880	.22
T10-890-25	7762-2297	89	890	.22
T10-900-25	7762-2298	90	900	.23
T10-910-25	7762-2299	91	910	.23
T10-920-25	7762-2300	92	920	.23
T10-950-25	7762-0344	95	950	.25
T10-960-25	7762-2301	96	960	.24
T10-970-25	7762-2302	97	970	.24
T10-980-25	7762-2303	98	980	.25
T10-1000-25	7762-0357	100	1000	.25
T10-1010-25	7762-2304	101	1010	.25
T10-1080-25	7762-2305	108	1080	.27

