

Cable Ties with Ball-Lock

MBT-Series, Stainless Steel 304


Metal ties are ideal for all applications that require high strength, reliability and fire resistance. The MBT range of stainless steel cable ties can be used in chemical industries and on oil platforms as well as in mass transit, shipbuilding and mining industries. MBT ties are also suitable for machine building, apparatus construction and in the outside area of radio technology. Additionally, MBT ties are ideal for securing lighting in theatres and exhibition halls.

Features and Benefits

- Cable ties MBT, made from stainless steel 304
- Patented non-releasable locking feature
- Corrosion resistant
- Weather resistant
- Outstanding chemical resistance
- High temperature resistant
- Non-burning



Patented



Stainless Steel Cable Ties, uncoated, MBT_SS, MBT_HS.




Stainless Steel Cable Ties, uncoated, MBT_XHS.




Supports quality processes around the production of food stuffs, such as e.g. HACCP.*



The MBT-Series (up to 7.9 mm) can be used in combination with the stainless steel P-Mount. The mount is simple to install with a screw or bolt and ensures a durable fixing solution. Please see page 149.



MBT-Series 4.6 mm and 7.9 mm width



MBT-Series 12.3 mm width

TYPE	Width (W)	Length (L)	Bundle Ø min.	Bundle Ø max.		Material	Pack Cont.	Tools	E-number	Article-No.
MBT5SS	4.6	127.0	12.0	25.0	900	SS304	100 pcs.	15-18	00 000 00	111-93058
MBT8SS	4.6	201.0	17.0	50.0	900	SS304	100 pcs.	15-18	00 000 00	111-93088
MBT14SS	4.6	362.0	17.0	102.0	900	SS304	100 pcs.	15-18	00 000 00	111-93148
MBT20SS	4.6	521.0	17.0	152.0	900	SS304	100 pcs.	15-18	00 000 00	111-93208
MBT27SS	4.6	685.0	17.0	203.0	900	SS304	100 pcs.	15-18	00 000 00	111-93278
MBT33SS	4.6	838.0	17.0	254.0	900	SS304	100 pcs.	15-18	00 000 00	111-93338
MBT8HS	7.9	201.0	17.0	50.0	2,000	SS304	50 pcs.	15-18	00 000 00	111-94088
MBT14HS	7.9	362.0	17.0	102.0	2,000	SS304	50 pcs.	15-18	00 000 00	111-94148
MBT20HS	7.9	521.0	17.0	152.0	2,000	SS304	50 pcs.	15-18	00 000 00	111-94208
MBT27HS	7.9	685.0	17.0	203.0	2,000	SS304	50 pcs.	15-18	00 000 00	111-94278
MBT33HS	7.9	838.0	17.0	254.0	2,000	SS304	50 pcs.	15-18	00 000 00	111-94338
MBT14XHS	12.3	362.0	17.0	102.0	2,700	SS304	50 pcs.	15-18	00 000 00	111-95148
MBT20XHS	12.3	521.0	17.0	152.0	2,700	SS304	50 pcs.	15-18	00 000 00	111-95208
MBT27XHS	12.3	681.0	17.0	203.0	2,700	SS304	50 pcs.	15-18	00 000 00	111-95278
MBT33XHS	12.3	838.0	17.0	254.0	2,700	SS304	50 pcs.	15-18	00 000 00	111-95338


All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Recommended Tools				
	15	16	17	18
	MK9SST	MK9PSST	HDT16	KST-STG200
	559	559	560	560

For more information on toolings please refer to the Application Tooling chapter.

*HACCP stands for Hazard Analysis Critical Control Points. It is a method of identifying and eliminating potential hazards in food production. Those hazards that cannot be eliminated are controlled in such a way that the consumer is protected. These controls are known as Critical Control Points (CCPs). They are CRITICAL because if they fail or are not carried out, the risk of the product harming the customer increases.



Cable Ties with Ball-Lock

MBT-Series, Stainless Steel 316

Metal ties are predestinated for all areas with requirements for high holding force, reliability and fire resistance. The MBT range of stainless steel cable ties can be used in chemical industry and on oil platform as well as in mass transit, shipbuilding and mining industry. MBT ties are also suitable for machine building, apparatus construction and in the outside area of radio technology. Additionally MBT ties are a good solution to fix lighting in theatres and exhibition halls.

Features and Benefits

- MBT cable ties made from stainless steel 316
- Patented non-releasable locking feature
- Corrosion resistant
- Weather resistant
- Outstanding chemical resistance
- Antimagnetic
- High temperature resistant
- Non-burning




Stainless Steel Cable Ties, uncoated, MBT_S, MBT_H.



Supports quality processes around the production of food stuffs, such as e.g. HACCP.*




Patented



Material specification please see page 26.



The MBT-Series (up to 7.9 mm) can be used in combination with the stainless steel P-Mount. The mount is simple to install with a screw or bolt and ensures a durable fixing solution. Please see page 149.



MBT-Series 4.6 mm and 7.9 mm width

TYPE	Width (W)	Length (L)	Bundle Ø min.	Bundle Ø max.		Material	Pack Cont.	Tools	E-number	Article-No.
MBT5S	4.6	127.0	12.0	25.0	900	SS316	100 pcs.	15-18	00 000 00	111-93059
MBT8S	4.6	201.0	12.0	50.0	900	SS316	100 pcs.	15-18	00 000 00	111-93089
MBT14S	4.6	362.0	12.0	102.0	900	SS316	100 pcs.	15-18	00 000 00	111-93149
MBT20S	4.6	521.0	12.0	152.0	900	SS316	100 pcs.	15-18	00 000 00	111-93209
MBT27S	4.6	685.0	12.0	203.0	900	SS316	100 pcs.	15-18	00 000 00	111-93279
MBT33S	4.6	838.0	12.0	254.0	900	SS316	100 pcs.	15-18	00 000 00	111-93339
MBT8H	7.9	201.0	12.0	50.0	2,000	SS316	50 pcs.	15-18	00 000 00	111-94089
MBT14H	7.9	362.0	12.0	102.0	2,000	SS316	50 pcs.	15-18	00 000 00	111-94149
MBT20H	7.9	521.0	12.0	152.0	2,000	SS316	50 pcs.	15-18	00 000 00	111-94209
MBT27H	7.9	685.0	12.0	203.0	2,000	SS316	50 pcs.	15-18	00 000 00	111-94279
MBT33H	7.9	838.0	12.0	254.0	2,000	SS316	50 pcs.	15-18	00 000 00	111-94339

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.


Recommended Tools				
	15	16	17	18
	MK9SST	MK9PSST	HDT16	KST-STG200
	559	559	560	560

For more information on toolings please refer to the Application Tooling chapter.

*HACCP stands for Hazard Analysis Critical Control Points. It is a method of identifying and eliminating potential hazards in food production. Those hazards that cannot be eliminated are controlled in such a way that the consumer is protected. These controls are known as Critical Control Points (CCPs). They are CRITICAL because if they fail or are not carried out, the risk of the product harming the customer increases.




For product specific approvals and specifications please refer to the Appendix.




Cable Ties with Ball-Lock

MBT-Series, Stainless Steel 316



MBT-Series 12.3 mm width



MBT-Series 16.0 mm width

TYPE	Width (W)	Length (L)	Bundle Ø min.	Bundle Ø max.		Material	Pack Cont.	Tools	E-number	Article-No.
MBT14XH	12.3	362.0	12.0	102.0	2,700	SS316	50 pcs.	15-18	00 000 00	111-95149
MBT20XH	12.3	521.0	12.0	152.0	2,700	SS316	50 pcs.	15-18	00 000 00	111-95209
MBT27XH	12.3	681.0	12.0	203.0	2,700	SS316	50 pcs.	15-18	00 000 00	111-95279
MBT33XH	12.3	838.0	12.0	254.0	2,700	SS316	50 pcs.	15-18	00 000 00	111-95339
MBT14UH	16.0	362.0	12.0	102.0	4,100	SS316	50 pcs.	15;17	00 000 00	111-01301
MBT20UH	16.0	521.0	12.0	152.0	4,100	SS316	50 pcs.	15;17	00 000 00	111-01302
MBT27UH	16.0	681.0	12.0	203.0	4,100	SS316	50 pcs.	15;17	00 000 00	111-01303
MBT33UH	16.0	838.0	12.0	254.0	4,100	SS316	50 pcs.	15;17	00 000 00	111-01304
MBT43UH	16.0	1,092.0	12.0	330.0	4,100	SS316	25 pcs.	15;17	00 000 00	111-01305
MBT49UH	16.0	1,245.0	12.0	380.0	4,100	SS316	25 pcs.	15;17	00 000 00	111-01306

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Recommended Tools				
	15	16	17	18
	MK9SST	MK9PSST	HDT16	KST-STG200
	559	559	560	560

For more information on toolings please refer to the Application Tooling chapter.



For product specific approvals and specifications please refer to the Appendix.



Double Wrap Cable Ties with Ball-Lock

MBTXHD- / MBTUHD-Series, Stainless Steel 316

The double wrap ties of the MBT-series are used in applications where a fixing requires an extraordinary high tensile strength.

Features and Benefits

- Stainless steel MBT ties with double wrap operation
- Wraps around the bundle and passes through the head twice
- Very high tensile strength to carry enormous applied loads
- Head with two locking balls
- Resistant to arduous conditions and environments



Double wrap Stainless Steel Cable Ties, uncoated, MBT_UHD.




Supports quality processes around the production of food stuffs, such as e.g. HACCP.*




Patented



Material specification please see page 26.



MBT-Series 12.3 mm width



MBT-Series 16.0 mm width

TYPE	Width (W)	Length (L)	Bundle Ø min.	Bundle Ø max.	N	Material	Pack Cont.	Tools	E-number	Article-No.
MBT27XHD	12.3	681.0	17.0	100.0	5,000	SS316	50 pcs.	15-18	00 000 00	111-01307
MBT33XHD	12.3	838.0	17.0	120.0	5,000	SS316	50 pcs.	15-18	00 000 00	111-01308
MBT43XHD	12.3	1,092.0	17.0	160.0	5,000	SS316	25 pcs.	15-18	00 000 00	111-01309
MBT49XHD	12.3	1,245.0	17.0	180.0	5,000	SS316	25 pcs.	15-18	00 000 00	111-01310
MBT60XHD	12.3	1,524.0	17.0	230.0	5,000	SS316	25 pcs.	15-18	00 000 00	111-01311
MBT27UHD	16.0	681.0	25.0	100.0	7,000	SS316	50 pcs.	15;17	00 000 00	111-01312
MBT33UHD	16.0	838.0	25.0	120.0	7,000	SS316	50 pcs.	15;17	00 000 00	111-01313
MBT43UHD	16.0	1,092.0	25.0	160.0	7,000	SS316	25 pcs.	15;17	00 000 00	111-01314
MBT49UHD	16.0	1,245.0	25.0	180.0	7,000	SS316	25 pcs.	15;17	00 000 00	111-01315
MBT60UHD	16.0	1,524.0	25.0	230.0	7,000	SS316	25 pcs.	15;17	00 000 00	111-01316

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Recommended Tools				
	15	16	17	18
	MK9SST	MK9PSST	HDT16	KST-STG200
	559	559	560	560

For more information on toolings please refer to the Application Tooling chapter.

*HACCP stands for Hazard Analysis Critical Control Points. It is a method of identifying and eliminating potential hazards in food production. Those hazards that cannot be eliminated are controlled in such a way that the consumer is protected. These controls are known as Critical Control Points (CCPs). They are CRITICAL because if they fail or are not carried out, the risk of the product harming the customer increases.



Cable Ties with Ball-Lock and Coating

MBT-FC-Series, Stainless Steel 316

The MBT range of stainless steel cable ties can be used in the most arduous of conditions or where the additional security, strength and fire resistance of a metal fixing is required. Used in all industries from mass transit, ship building, oil rigs, mining and chemical industry, theatres and exhibition halls. In the event of a fire, cables will remain securely held in place and will not fall to block emergency exits.

Features and Benefits

- Fully coated MBT, made from type 316 stainless steel with polyester coating
- Patented non-releasable locking feature
- Coated cable tie with smooth edges
- Comfortable handling and installation
- Eliminates contact corrosion between dissimilar materials during application



Patented



Material specification please see page 26.




The MBT-Series (up to 7.9 mm) can be used in combination with the stainless steel P-Mount. The mount is simple to install with a screw or bolt and ensures a durable fixing solution. Please see page 149.



Stainless Steel Cable Ties, coated, MBT_SFC, MBT_HFC.



Stainless Steel Cable Ties, coated, MBT_XHFC.



MBT-Series 4.6 mm and 7.9 mm width

TYPE	Width (W)	Length (L)	Bundle Ø min.	Bundle Ø max.		Material	Pack Cont.	Tools	E-number	Article-No.
MBT5SFC	4.6	127.0	15.0	25.0	540	SS316, SP	100 pcs.	15-18	00 000 00	111-00288
MBT8SFC	4.6	201.0	17.0	50.0	540	SS316, SP	100 pcs.	15-18	00 000 00	111-00289
MBT14SFC	4.6	362.0	17.0	102.0	540	SS316, SP	100 pcs.	15-18	00 000 00	111-00290
MBT20SFC	4.6	521.0	17.0	152.0	540	SS316, SP	100 pcs.	15-18	00 000 00	111-00291
MBT27SFC	4.6	681.0	17.0	203.0	540	SS316, SP	100 pcs.	15-18	00 000 00	111-00292
MBT33SFC	4.6	838.0	17.0	254.0	540	SS316, SP	100 pcs.	15-18	00 000 00	111-00293
MBT8HFC	7.9	201.0	17.0	50.0	1,020	SS316, SP	50 pcs.	15-18	00 000 00	111-00294
MBT14HFC	7.9	362.0	17.0	102.0	1,020	SS316, SP	50 pcs.	15-18	00 000 00	111-00295
MBT20HFC	7.9	521.0	17.0	152.0	1,020	SS316, SP	50 pcs.	15-18	00 000 00	111-00296
MBT27HFC	7.9	681.0	17.0	203.0	1,020	SS316, SP	50 pcs.	15-18	00 000 00	111-00297
MBT33HFC	7.9	838.0	17.0	254.0	1,020	SS316, SP	50 pcs.	15-18	00 000 00	111-00298

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.


Recommended Tools				
	15	16	17	18
	MK9SST	MK9PSST	HDT16	KST-STG200
	559	559	560	560

For more information on toolings please refer to the Application Tooling chapter.




Cable Ties with Ball-Lock and Coating

MBT-FC-Series, Stainless Steel 316



MBT-Series 12.3 mm width



MBT-Series 16.0 mm width


TYPE	Width (W)	Length (L)	Bundle Ø min.	Bundle Ø max.		Material	Pack Cont.	Tools	E-number	Article-No.
MBT14XHFC	12.3	362.0	17.0	102.0	1,620	SS316, SP	50 pcs.	15-18	00 000 00	111-00299
MBT17XHFC	12.3	434.0	17.0	125.0	1,620	SS316, SP	50 pcs.	15-18	00 000 00	111-01500
MBT20XHFC	12.3	521.0	17.0	152.0	1,620	SS316, SP	50 pcs.	15-18	00 000 00	111-00300
MBT23XHFC	12.3	575.0	17.0	168.0	1,620	SS316, SP	50 pcs.	15-18	00 000 00	111-01501
MBT27XHFC	12.3	681.0	17.0	203.0	1,620	SS316, SP	50 pcs.	15-18	00 000 00	111-00301
MBT30XHFC	12.3	754.0	17.0	225.0	1,620	SS316, SP	50 pcs.	15-18	00 000 00	111-01502
MBT33XHFC	12.3	838.0	17.0	254.0	1,620	SS316, SP	50 pcs.	15-18	00 000 00	111-00302
MBT43XHFC	12.3	1,092.0	17.0	330.0	1,620	SS316, SP	25 pcs.	15-18	00 000 00	111-01503
MBT49XHFC	12.3	1,245.0	17.0	380.0	1,620	SS316, SP	25 pcs.	15-18	00 000 00	111-01504
MBT14UHFC	16.0	362.0	25.0	102.0	2,500	SS316, SP	50 pcs.	15;17	00 000 00	111-01512
MBT17UHFC	16.0	434.0	25.0	125.0	2,500	SS316, SP	50 pcs.	15;17	00 000 00	111-01513
MBT20UHFC	16.0	521.0	25.0	152.0	2,500	SS316, SP	50 pcs.	15;17	00 000 00	111-01514
MBT23UHFC	16.0	575.0	25.0	168.0	2,500	SS316, SP	50 pcs.	15;17	00 000 00	111-01515
MBT27UHFC	16.0	681.0	25.0	203.0	2,500	SS316, SP	50 pcs.	15;17	00 000 00	111-01516
MBT30UHFC	16.0	754.0	25.0	225.0	2,500	SS316, SP	50 pcs.	15;17	00 000 00	111-01517
MBT33UHFC	16.0	838.0	25.0	254.0	2,500	SS316, SP	50 pcs.	15;17	00 000 00	111-01518
MBT43UHFC	16.0	1,092.0	25.0	330.0	2,500	SS316, SP	25 pcs.	15;17	00 000 00	111-01519
MBT49UHFC	16.0	1,245.0	25.0	380.0	2,500	SS316, SP	25 pcs.	15;17	00 000 00	111-01520

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Recommended Tools				
	15	16	17	18
	MK9SST	MK9PSST	HDT16	KST-STG200
	559	559	560	560

For more information on toolings please refer to the Application Tooling chapter.



Double Wrap Cable Ties with Ball-Lock and Coating

MBTXHDFC- / MBTUHDFC-Series, Stainless Steel 316

The MBT range of stainless steel cable ties can be used in the most arduous of conditions or where the additional security, strength and fire resistance of a metal fixing is required. Used in all industries from mass transit, ship building, oil rigs, mining and chemical industry, theatres and exhibition halls. In the event of a fire, cables will remain securely held in place and will not fall to block emergency exits.

Features and Benefits

- MBT cable ties, made from stainless steel SS316 with a polyester coating
- Patented non-releasable locking feature
- Double wrap operation
- Corrosion resistant
- Weather resistant
- Outstanding chemical resistance
- Antimagnetic
- High temperature resistant
- Non-burning




Stainless Steel Cable Ties, coated, MBT_UHDFC.




Patented



Material specification please see page 26.



MBT-Series 12.3 mm width



MBT-Series 16.0 mm width

TYPE	Width (W)	Length (L)	Bundle Ø min.	Bundle Ø max.	N	Material	Pack Cont.	Tools	E-number	Article-No.
MBT27XHDFC	12.3	681.0	17.0	100.0	2,500	SS316, SP	50 pcs.	15-18	00 000 00	111-01505
MBT33XHDFC	12.3	838.0	17.0	120.0	2,500	SS316, SP	50 pcs.	15-18	00 000 00	111-01506
MBT43XHDFC	12.3	1,092.0	17.0	160.0	2,500	SS316, SP	25 pcs.	15-18	00 000 00	111-01507
MBT49XHDFC	12.3	1,245.0	17.0	180.0	2,500	SS316, SP	25 pcs.	15-18	00 000 00	111-01508
MBT60XHDFC	12.3	1,524.0	17.0	230.0	2,500	SS316, SP	25 pcs.	15-18	00 000 00	111-01509
MBT27UHDFC	16.0	681.0	25.0	100.0	5,000	SS316, SP	50 pcs.	15;17	00 000 00	111-01521
MBT33UHDFC	16.0	838.0	25.0	120.0	5,000	SS316, SP	50 pcs.	15;17	00 000 00	111-01522
MBT43UHDFC	16.0	1,092.0	25.0	160.0	5,000	SS316, SP	25 pcs.	15;17	00 000 00	111-01523
MBT49UHDFC	16.0	1,245.0	25.0	180.0	5,000	SS316, SP	25 pcs.	15;17	00 000 00	111-01524
MBT60UHDFC	16.0	1,524.0	25.0	230.0	5,000	SS316, SP	25 pcs.	15;17	00 000 00	111-01525

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Recommended Tools				
	15	16	17	18
	MK9SST	MK9PSST	HDT16	KST-STG200
	559	559	560	560

For more information on toolings please refer to the Application Tooling chapter.