

Micrometer set

0-100 mm

Application

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

Version

- Scale with anti-glare, brushed chromium plated finish
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force
- With 25, 50 and 75 mm setting gauges

Delivery

In case



Art. No.	31342 400
Calibration Group	D, E
Min./max. length measuring range	0-100 mm
Measuring spindle increments	0.5 mm
Measuring surface diameter	6.5 mm
Spindle clamping	Yes
Number of bracket measuring screws	4
Number of setting dimensions	3
DIN	863

EAN-Code

4050293155211