



# Lithium Coin Cell - CR2430

- Reliable energy for your application
- Standard cells and customized packs
- ESD protection
- UL recognized
- Battery Certification Experts



RoHS compliant



Pb free



REACH compliant



Conflict mineral free


## Technical Data Sheet · CR 2430

### SPECIFICATIONS


Nominal Voltage	3V
Jauch part number	245786
Nominal Capacity	320 mAh
Standard Load	15 kΩ
Standard Current	0.2 mA
Max. Continuous Current	4 mA
Max. Pulse Current	18 mA
Operating Temperature	-30°C to +70°C*
Weight	Approx. 4 gr.
Chemistry	Li/MnO <sub>2</sub>

\* In applications where the battery is exposed to temperatures >60°C, please contact Jauch.


### DIMENSIONS




### DISCHARGE CHARACTERISTICS




### TEMPERATURE CHARACTERISTICS



### PULSE DISCHARGE CHARACTERISTICS



### LOAD VS: CAPACITY



**Available Terminals and Wire Connectors:**  
 please contact Jauch for diagram of batteries with terminals  
[batterytechnology@jauch.com](mailto:batterytechnology@jauch.com)